

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008287

Luminaire Tested: S122DIP-B865D925UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008287
REPORT IS A COMBINATION OF REPORTS P984975 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7098.0 lumens
Efficiency: N/A
Efficacy: 94.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008287

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008287

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	95	90	86	82	86	82	79	75	68	65	63	54	52	51	42	41	40
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	18	15
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14326	14326	14326
5°	14390	13714	13636
10°	14294	13239	13046
15°	14091	12747	12439
20°	13837	12231	11864
25°	13585	11737	11343
30°	13234	11236	10827
35°	12878	10751	10447
40°	12502	10333	10070
45°	12145	9953	9742
50°	11761	9603	9417
55°	11357	9232	9087
60°	10863	8845	8741
65°	10352	8400	8341
70°	9770	7922	7911
75°	9023	7444	7505
80°	7856	6946	7087
85°	6667	6480	6723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12145 cd/sqm

TEST NUMBER: P1008287

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.8	1.2
10°-20°	246.0	3.5
20°-30°	372.8	5.3
30°-40°	454.0	6.4
40°-50°	488.4	6.9
50°-60°	474.4	6.7
60°-70°	414.3	5.8
70°-80°	318.8	4.5
80°-90°	215.7	3.0
90°-100°	188.3	2.7
100°-110°	260.3	3.7
110°-120°	476.1	6.7
120°-130°	711.4	10.0
130°-140°	730.3	10.3
140°-150°	666.1	9.4
150°-160°	533.3	7.5
160°-170°	343.6	4.8
170°-180°	118.3	1.7
0°-30°	704.6	9.9
0°-40°	1158.6	16.3
0°-60°	2121.4	29.9
0°-90°	3070.2	43.3
90°-120°	924.7	13.0
90°-150°	3032.6	42.7
90°-180°	4028.0	56.7
0°-180°	7098.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	905	905	905	905	905	
5°	908	904	896	904	902	86
15°	866	868	868	880	879	244
25°	787	796	808	824	828	362
35°	678	700	725	754	763	424
45°	556	592	637	678	691	429
55°	426	474	542	589	606	381
65°	291	355	433	487	504	289
75°	161	235	319	375	392	171
85°	47	128	212	268	286	50
90°	14	100	191	248	266	12
95°	69	101	186	240	255	77
105°	280	345	168	223	241	300
115°	522	552	634	256	206	514
125°	734	745	804	846	860	655
135°	906	920	941	978	987	700
145°	1049	1048	1064	1078	1080	657
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1008287

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	905.0	905.0	905.0	905.0	905.0
2.5°	911.5	907.6	898.4	905.0	902.3
5°	907.6	903.6	895.8	903.6	902.3
7.5°	901.0	898.4	891.8	901.0	899.7
10°	893.2	890.5	886.6	897.1	895.8
12.5°	880.0	881.3	878.7	889.2	887.9
15°	865.6	868.2	868.2	880.0	878.7
17.5°	847.2	852.5	856.4	868.2	868.2
20°	828.9	835.4	840.7	855.1	855.1
22.5°	809.2	817.1	825.0	839.4	842.0
25°	786.9	796.1	807.9	823.6	827.6
27.5°	760.7	775.1	788.2	807.9	810.5
30°	734.5	751.5	768.6	789.5	793.5
32.5°	705.6	725.3	746.3	771.2	779.1
35°	678.1	700.4	725.3	754.1	763.3
37.5°	647.9	672.8	704.3	735.8	745.0
40°	617.7	646.6	682.0	716.1	727.9
42.5°	588.9	617.7	659.7	697.7	709.5
45°	556.1	591.5	637.4	678.1	691.2
47.5°	524.6	562.6	615.1	657.1	671.5
50°	491.8	532.5	591.5	636.1	650.5
52.5°	460.3	503.6	566.6	612.5	628.2
55°	426.2	473.5	541.7	588.9	605.9
57.5°	393.5	445.9	514.1	565.3	582.3
60°	358.0	414.4	489.2	539.0	557.4
62.5°	326.6	385.6	460.3	514.1	531.2
65°	291.2	355.4	432.8	486.6	503.6
67.5°	259.7	326.6	405.3	459.0	477.4
70°	225.6	293.8	375.1	431.5	447.2
72.5°	194.1	264.9	347.6	402.6	422.3
75°	161.3	234.8	318.7	375.1	392.1
77.5°	129.8	205.9	291.2	347.6	365.9
80°	98.4	178.4	263.6	318.7	337.1
82.5°	72.1	150.8	237.4	292.5	309.5
85°	47.2	128.5	212.5	267.6	285.9
87.5°	28.9	107.5	191.5	245.3	262.3
90°	14.0	100.0	191.1	248.1	265.6
92.5°	34.3	100.2	182.9	235.9	252.5
95°	68.9	100.9	185.9	240.3	255.1
97.5°	114.4	97.1	187.5	238.8	255.4
100°	168.3	93.7	182.4	238.1	254.3
102.5°	226.4	267.8	175.0	232.1	249.2
105°	279.9	344.9	167.6	223.4	241.4
107.5°	343.8	397.6	160.2	214.7	232.7
110°	403.5	448.7	253.0	205.1	223.1

TEST NUMBER: P1008287

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	461.1	498.2	543.4	197.7	214.9
115°	522.2	552.0	633.5	256.5	206.2
117.5°	573.9	602.4	672.8	583.6	361.2
120°	633.3	652.1	720.7	768.2	661.3
122.5°	683.6	699.3	765.9	806.7	819.4
125°	733.6	745.3	804.4	846.0	860.5
127.5°	780.3	791.6	840.5	882.3	895.0
130°	824.4	837.5	875.0	916.3	925.9
132.5°	869.4	879.7	909.3	947.5	957.1
135°	905.8	920.2	941.4	978.0	986.7
137.5°	945.4	956.2	971.8	1005.6	1012.1
140°	984.0	989.9	1002.4	1031.5	1034.9
142.5°	1016.4	1021.4	1033.1	1056.0	1058.1
145°	1049.3	1048.4	1063.7	1077.9	1079.9
147.5°	1078.9	1076.2	1091.5	1097.3	1097.6
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)