

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008289

Luminaire Tested: S122DIP-B865D925UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008289
REPORT IS A COMBINATION OF REPORTS P984977 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B865D925UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7094.0 lumens
Efficiency: N/A
Efficacy: 94.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008289

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008289

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	93	89	86	90	86	83	80	72	70	68	60	58	57	49	48	46
2	89	81	75	70	82	75	70	65	64	60	56	53	50	47	43	41	39
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33
4	74	63	55	49	68	59	52	46	50	44	40	42	38	34	34	31	29
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	27	25
6	63	51	42	37	58	47	40	35	40	34	30	34	29	26	28	25	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	21528	21528	21528
5°	21563	20520	20374
10°	21386	19585	19195
15°	21074	18642	17956
20°	20651	17617	16783
25°	20229	16547	15611
30°	19697	15541	14381
35°	19197	14479	13172
40°	18579	13433	12031
45°	17963	12395	10911
50°	17292	11337	9750
55°	16587	10207	8649
60°	15794	8984	7505
65°	14924	7740	6302
70°	13819	6380	5090
75°	12290	4917	3930
80°	10443	3341	2529
85°	7571	1555	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17963 cd/sqm

TEST NUMBER: P1008289

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.0	1.8
10°-20°	360.1	5.1
20°-30°	529.2	7.5
30°-40°	614.7	8.7
40°-50°	613.9	8.7
50°-60°	535.3	7.5
60°-70°	395.7	5.6
70°-80°	223.9	3.2
80°-90°	61.3	0.9
90°-100°	40.9	0.6
100°-110°	152.3	2.1
110°-120°	403.9	5.7
120°-130°	669.8	9.4
130°-140°	711.5	10.0
140°-150°	661.3	9.3
150°-160°	531.6	7.5
160°-170°	342.6	4.8
170°-180°	117.9	1.7
0°-30°	1017.4	14.3
0°-40°	1632.1	23.0
0°-60°	2781.3	39.2
0°-90°	3462.2	48.8
90°-120°	597.0	8.4
90°-150°	2639.6	37.2
90°-180°	3632.0	51.2
0°-180°	7094.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1360	1360	1360	1360	1360	
5°	1360	1355	1340	1351	1348	129
15°	1295	1287	1270	1275	1268	365
25°	1172	1161	1139	1142	1139	539
35°	1011	998	977	969	962	631
45°	822	813	794	779	774	635
55°	622	615	599	583	577	557
65°	420	412	399	387	380	415
75°	220	217	210	203	205	234
85°	54	52	51	47	46	60
90°	1	11	18	22	24	7
95°	58	29	35	39	38	69
105°	272	299	55	64	68	291
115°	515	531	553	138	74	507
125°	729	740	758	764	766	650
135°	902	916	924	933	931	697
145°	1046	1045	1060	1067	1062	654
155°	1152	1144	1155	1160	1153	531
165°	1214	1208	1211	1217	1211	343
175°	1242	1235	1237	1243	1234	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P1008289

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1360.0	1360.0	1360.0	1360.0	1360.0
2.5°	1367.8	1361.3	1346.9	1360.0	1357.4
5°	1360.0	1354.7	1340.4	1350.8	1348.2
7.5°	1350.8	1343.0	1328.6	1339.1	1336.4
10°	1336.4	1327.3	1311.6	1322.1	1318.1
12.5°	1316.8	1309.0	1293.3	1299.8	1297.2
15°	1294.6	1286.7	1269.7	1275.0	1268.4
17.5°	1267.1	1259.3	1242.3	1248.8	1242.3
20°	1237.1	1229.2	1210.9	1214.8	1209.6
22.5°	1207.0	1195.2	1178.2	1178.2	1175.6
25°	1171.7	1161.2	1139.0	1141.6	1139.0
27.5°	1132.4	1123.3	1106.3	1102.4	1095.8
30°	1093.2	1082.8	1063.1	1059.2	1054.0
32.5°	1051.4	1043.5	1022.6	1014.8	1009.5
35°	1010.8	997.8	976.8	969.0	962.4
37.5°	965.1	953.3	932.4	923.2	916.7
40°	918.0	907.5	886.6	874.8	869.6
42.5°	872.2	861.8	840.8	827.8	819.9
45°	822.5	813.4	793.8	779.4	774.1
47.5°	774.1	765.0	744.1	729.7	721.8
50°	723.1	716.6	698.3	680.0	673.5
52.5°	673.5	664.3	647.3	632.9	623.8
55°	622.5	614.6	598.9	583.2	576.7
57.5°	571.5	564.9	547.9	532.2	527.0
60°	520.5	515.2	496.9	482.5	478.6
62.5°	470.8	461.6	448.5	435.5	430.2
65°	419.8	411.9	398.8	387.1	380.5
67.5°	367.5	360.9	349.1	340.0	334.8
70°	319.1	313.8	302.1	292.9	287.7
72.5°	269.4	264.1	257.6	248.5	244.5
75°	219.7	217.1	210.5	202.7	205.3
77.5°	175.2	170.0	167.4	163.5	159.5
80°	130.8	129.5	126.8	122.9	120.3
82.5°	88.9	88.9	87.6	82.4	82.4
85°	53.6	52.3	51.0	47.1	45.8
87.5°	23.5	20.9	18.3	14.4	13.1
90°	0.9	10.8	17.9	22.4	24.2
92.5°	22.4	18.8	21.5	23.3	24.2
95°	58.3	28.7	35.0	39.4	38.5
97.5°	104.9	31.4	45.7	48.4	49.3
100°	158.7	35.9	51.1	58.3	60.1
102.5°	217.8	216.0	52.9	62.7	65.4
105°	272.5	299.4	54.7	64.5	68.1
107.5°	336.2	358.6	56.5	66.3	69.9
110°	397.1	415.9	156.9	67.2	70.8

TEST NUMBER: P1008289

CATALOG NUMBER: S122DIP-B865D925UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	454.5	470.6	455.4	69.0	71.7
115°	515.4	530.7	553.1	138.0	73.5
117.5°	568.3	586.2	601.5	473.3	238.4
120°	627.5	640.9	657.1	667.8	546.8
122.5°	677.7	692.0	710.0	715.3	716.2
125°	728.8	740.4	757.5	763.7	766.4
127.5°	775.4	787.9	801.4	810.4	811.2
130°	819.3	833.7	843.5	853.4	852.5
132.5°	864.1	875.8	885.6	893.7	892.8
135°	901.8	916.1	924.2	933.2	931.4
137.5°	941.2	952.0	960.9	969.9	967.2
140°	979.8	986.9	996.8	1004.9	1000.4
142.5°	1012.0	1018.3	1030.0	1037.1	1032.7
145°	1046.1	1045.2	1060.4	1066.7	1062.2
147.5°	1075.7	1073.0	1088.2	1092.7	1089.1
150°	1104.4	1098.1	1112.4	1117.8	1113.3
152.5°	1128.6	1121.4	1134.8	1140.2	1134.0
155°	1151.9	1143.8	1154.6	1159.9	1152.8
157.5°	1170.7	1163.5	1171.6	1177.9	1170.7
160°	1186.8	1181.5	1186.8	1192.2	1185.9
162.5°	1201.2	1195.8	1200.3	1206.6	1198.5
165°	1213.7	1208.4	1211.0	1217.3	1211.0
167.5°	1223.6	1218.2	1220.9	1227.2	1219.1
170°	1231.7	1226.3	1228.1	1234.3	1226.3
172.5°	1237.0	1231.7	1233.5	1239.7	1231.7
175°	1241.5	1235.2	1237.0	1243.3	1234.3
177.5°	1243.3	1237.0	1237.9	1244.2	1236.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)