

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001900

Luminaire Tested: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001900
REPORT IS A COMBINATION OF REPORTS P996525 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5681.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68	68	68	63
1	101	97	93	89	94	91	87	84	80	77	75	70	68	66	60	59	58	58	58	53
2	92	85	79	73	86	80	74	70	70	66	63	62	58	56	53	51	49	49	49	45
3	84	75	67	62	79	70	64	59	62	57	53	55	51	47	48	45	42	42	42	39
4	77	66	58	52	72	63	56	50	56	50	45	49	45	41	43	39	37	37	37	33
5	71	59	51	45	66	56	49	43	50	44	39	44	39	36	39	35	32	32	32	29
6	66	53	45	39	61	51	43	38	45	39	35	40	35	31	35	31	28	28	28	26
7	61	48	40	35	57	46	39	33	41	35	31	36	32	28	32	28	25	25	25	23
8	56	44	36	31	53	42	35	30	37	32	27	33	29	25	30	26	23	23	23	21
9	53	40	33	28	49	38	31	27	34	29	25	31	26	23	27	23	21	21	21	19
10	49	37	30	25	46	35	29	24	32	26	22	29	24	20	25	22	19	19	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10523	10523	10523	10523
5°	10496	12072	10558	9071
10°	10419	14085	10498	7959
15°	10293	16237	10365	7121
20°	10160	17607	10233	6384
25°	9965	17405	10061	5841
30°	9775	14386	9895	5561
35°	9509	10721	9613	5391
40°	9197	8076	9286	5309
45°	8721	6482	8830	5195
50°	8153	5461	8271	5142
55°	7485	4753	7602	5081
60°	6836	4185	7036	4997
65°	6227	3601	6285	4789
70°	5511	2962	5629	4409
75°	4807	2277	4775	3747
80°	3780	1496	3739	2845
85°	2489	673	2336	1658

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 13607 cd/sqm

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.6	2.2
10°-20°	387.7	6.8
20°-30°	615.8	10.8
30°-40°	684.3	12.0
40°-50°	622.3	11.0
50°-60°	508.5	9.0
60°-70°	363.0	6.4
70°-80°	199.8	3.5
80°-90°	55.1	1.0
90°-100°	210.8	3.7
100°-110°	440.2	7.7
110°-120°	391.3	6.9
120°-130°	329.4	5.8
130°-140°	274.8	4.8
140°-150°	209.8	3.7
150°-160°	147.5	2.6
160°-170°	86.8	1.5
170°-180°	28.2	0.5
0°-30°	1129.1	19.9
0°-40°	1813.4	31.9
0°-60°	2944.3	51.8
0°-90°	3562.1	62.7
90°-120°	1042.3	18.3
90°-150°	1856.4	32.7
90°-180°	2119.0	37.3
0°-180°	5681.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1290	1290	1290	1290	1290	
5°	1285	1514	1293	1138	1285	122
15°	1227	2080	1236	912	1227	346
25°	1120	2208	1131	741	1120	516
35°	972	1306	983	656	972	607
45°	775	732	785	587	775	598
55°	545	479	554	512	545	490
65°	340	308	343	410	340	336
75°	167	154	166	253	167	175
85°	34	32	32	79	34	40
90°	1	12	1	12	1	3
95°	19	140	19	140	19	21
105°	67	804	67	804	67	71
115°	118	772	118	772	118	117
125°	164	616	164	616	164	146
135°	195	551	195	551	195	151
145°	225	450	225	450	225	141
155°	256	377	256	377	256	118
165°	278	329	278	329	278	79
175°	290	296	290	296	290	28
180°	291	291	291	291	291	

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1290.5	1303.3	1308.7	1312.9	1326.8	1331.1	1332.2	1338.6	1343.9	1345.0	1345.0
5°	1285.1	1305.5	1321.5	1336.5	1358.9	1368.5	1380.3	1393.1	1410.2	1420.9	1426.3
7.5°	1276.6	1306.5	1331.1	1356.8	1387.8	1407.0	1417.7	1451.9	1475.5	1494.7	1518.2
10°	1263.8	1302.2	1337.5	1374.9	1418.8	1442.3	1465.8	1507.5	1540.7	1578.1	1608.0
12.5°	1244.5	1294.8	1337.5	1389.9	1444.4	1472.2	1500.0	1572.7	1611.2	1644.4	1697.8
15°	1227.4	1277.7	1338.6	1392.1	1459.4	1501.1	1541.7	1588.8	1649.7	1721.4	1772.7
17.5°	1208.2	1271.2	1327.9	1402.7	1477.6	1517.1	1550.3	1623.0	1708.5	1779.1	1826.1
20°	1181.4	1245.6	1320.4	1399.5	1488.3	1519.3	1563.1	1660.4	1737.4	1806.9	1883.9
22.5°	1150.4	1225.3	1304.4	1380.3	1472.2	1537.5	1585.6	1671.1	1764.1	1844.3	1930.9
25°	1120.5	1201.7	1271.2	1374.9	1472.2	1516.1	1570.6	1672.2	1773.7	1871.0	1959.8
27.5°	1088.4	1164.3	1258.4	1340.7	1450.9	1499.0	1557.8	1669.0	1777.0	1874.3	1969.4
30°	1053.1	1134.4	1212.4	1309.7	1416.6	1478.7	1533.2	1654.0	1764.1	1865.7	1954.4
32.5°	1013.6	1090.6	1173.9	1265.9	1378.2	1441.2	1509.7	1633.7	1751.3	1839.0	1907.4
35°	971.9	1049.9	1122.6	1216.7	1332.2	1395.3	1461.6	1598.4	1714.9	1786.6	1826.1
37.5°	925.9	999.7	1071.3	1164.3	1279.8	1347.2	1414.5	1547.1	1657.2	1717.1	1706.4
40°	882.1	948.4	1014.6	1102.3	1223.1	1294.8	1353.6	1487.2	1583.4	1609.1	1573.8
42.5°	831.8	888.5	952.6	1042.4	1160.0	1227.4	1301.2	1423.1	1494.7	1484.0	1424.1
45°	775.1	825.4	889.5	974.0	1093.8	1163.3	1225.3	1340.7	1393.1	1366.4	1257.3
47.5°	720.6	769.8	822.2	906.7	1023.2	1082.0	1145.1	1248.8	1278.7	1222.1	1113.0
50°	661.8	702.4	757.0	837.2	946.2	1008.2	1060.6	1144.0	1154.7	1085.2	971.9
52.5°	605.1	639.4	691.8	770.9	872.4	921.6	972.9	1046.7	1038.2	966.5	857.5
55°	545.3	577.4	625.5	698.2	788.0	835.0	878.9	944.1	925.9	852.1	757.0
57.5°	495.0	517.5	564.5	631.9	705.7	757.0	794.4	845.7	817.9	744.1	655.4
60°	437.3	465.1	504.6	559.2	631.9	666.1	699.2	733.4	714.2	643.6	564.5
62.5°	384.9	406.3	440.5	492.9	549.6	580.6	615.8	637.2	618.0	552.8	486.5
65°	340.0	357.1	383.8	426.6	481.1	506.8	527.1	547.4	531.4	470.4	422.3
67.5°	290.8	305.8	328.2	362.4	408.4	426.6	445.8	459.7	441.6	400.9	353.9
70°	247.0	257.7	279.1	304.7	336.8	353.9	369.9	383.8	367.8	333.6	298.3
72.5°	202.1	210.6	229.9	248.0	276.9	288.7	300.4	311.1	305.8	273.7	244.8
75°	166.8	170.0	182.8	197.8	216.0	228.8	237.4	243.8	239.5	213.8	195.7
77.5°	126.2	130.4	140.1	151.8	167.9	175.3	180.7	187.1	181.8	161.4	148.6
80°	91.9	93.0	98.4	109.1	119.7	120.8	126.2	134.7	131.5	117.6	108.0
82.5°	58.8	62.0	64.2	70.6	78.0	80.2	83.4	85.5	84.5	75.9	72.7
85°	34.2	34.2	36.4	40.6	42.8	46.0	47.0	48.1	50.3	44.9	41.7
87.5°	15.0	16.0	16.0	17.1	19.2	19.2	20.3	21.4	22.5	21.4	18.2
90°	0.6	1.7	3.4	4.0	4.6	4.6	4.6	8.0	8.0	9.1	10.3
92.5°	8.0	11.4	17.7	26.3	36.6	44.0	51.4	86.9	142.3	196.0	224.0
95°	18.9	20.6	26.3	33.7	47.4	59.4	71.4	121.2	214.9	351.5	465.8
97.5°	31.4	31.4	36.6	43.4	55.4	65.7	76.0	115.5	196.0	336.6	498.4
100°	43.4	43.4	47.4	54.3	65.2	74.3	83.4	117.2	181.8	298.4	459.5
102.5°	54.9	56.0	59.4	65.7	76.0	84.6	93.2	122.9	177.8	272.6	410.9
105°	66.9	68.6	71.4	78.3	88.6	96.9	105.2	132.6	180.0	260.1	374.9
107.5°	80.0	81.2	84.0	91.4	101.2	109.4	117.7	142.9	186.9	256.6	351.5
110°	93.2	94.3	97.2	104.0	114.3	122.0	129.7	154.9	194.9	257.8	340.6

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.7	106.9	110.3	116.6	126.9	134.6	142.3	166.3	203.5	261.2	335.5
115°	117.7	119.5	123.5	129.2	140.0	147.8	155.5	178.3	212.6	265.8	334.4
117.5°	130.3	132.0	135.5	141.7	152.0	160.0	168.0	189.8	221.8	270.3	333.8
120°	142.9	144.0	148.0	154.3	164.0	172.0	180.0	201.8	231.5	275.5	333.8
122.5°	154.3	155.5	159.5	165.2	176.0	183.8	191.5	213.2	240.6	280.6	333.2
125°	164.0	166.3	169.8	176.0	186.9	194.9	202.9	223.5	249.8	285.8	332.6
127.5°	173.2	174.9	178.9	185.8	197.2	205.2	213.2	233.2	257.8	289.8	331.5
130°	180.6	182.9	187.5	196.0	206.9	215.2	223.5	242.9	265.2	294.4	330.9
132.5°	188.0	189.8	196.0	204.0	216.0	223.8	231.5	250.9	272.6	298.4	330.4
135°	194.9	197.2	202.9	212.6	224.6	232.0	239.5	258.3	278.9	302.4	329.8
137.5°	201.8	204.0	210.3	219.5	232.1	239.2	246.3	264.1	283.5	304.6	329.8
140°	209.2	210.9	217.2	226.9	238.9	245.8	252.6	269.8	288.1	307.5	329.2
142.5°	217.2	218.9	224.6	233.8	245.2	251.8	258.3	274.9	291.5	309.8	329.2
145°	224.6	226.3	232.1	240.1	250.9	257.2	263.5	278.3	293.8	310.4	328.1
147.5°	233.2	233.8	238.9	247.5	256.6	262.4	268.1	282.3	296.1	310.9	326.4
150°	241.2	241.8	246.3	253.2	261.8	267.2	272.6	285.2	297.8	310.9	324.6
152.5°	248.6	248.6	253.2	259.5	266.9	271.8	276.6	287.5	298.9	309.8	321.8
155°	255.5	256.1	259.5	265.2	271.5	275.8	280.1	289.8	299.5	308.6	318.9
157.5°	262.3	262.3	265.8	270.3	276.1	279.5	282.9	291.5	299.5	307.5	316.1
160°	268.6	268.6	270.9	274.9	279.5	282.6	285.8	292.6	299.5	305.8	312.6
162.5°	274.3	273.8	275.5	278.9	282.9	285.2	287.5	293.8	299.5	304.1	309.2
165°	278.3	278.3	279.5	282.3	285.2	286.9	288.6	293.8	298.4	301.8	305.8
167.5°	282.9	282.3	282.9	285.2	286.9	288.4	289.8	293.8	297.2	299.5	302.4
170°	285.8	285.2	285.8	287.5	288.6	289.5	290.4	293.2	296.1	297.2	298.9
172.5°	288.6	288.1	288.1	289.2	289.8	290.4	290.9	292.6	294.9	294.9	295.5
175°	290.4	289.8	289.8	290.4	290.9	290.9	290.9	292.1	293.8	293.2	293.2
177.5°	291.5	290.9	290.4	290.9	290.9	290.9	290.9	291.5	292.6	291.5	291.5
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1348.2	1367.5	1376.0	1378.2	1389.9	1382.4	1385.6	1384.6	1393.1	1394.2	1394.2
5°	1446.6	1469.0	1476.5	1487.2	1503.2	1507.5	1504.3	1510.7	1522.5	1513.9	1526.8
7.5°	1550.3	1574.9	1592.0	1615.5	1620.9	1634.8	1643.3	1650.8	1652.9	1654.0	1656.1
10°	1646.5	1677.5	1701.0	1740.6	1749.2	1756.6	1794.1	1779.1	1798.3	1791.9	1794.1
12.5°	1724.6	1785.5	1804.8	1871.0	1877.5	1903.1	1901.0	1924.5	1928.8	1937.3	1928.8
15°	1827.2	1897.8	1928.8	1966.2	1987.6	2017.5	2022.9	2054.9	2067.8	2079.5	2067.8
17.5°	1921.3	1958.7	2037.8	2067.8	2081.7	2097.7	2138.3	2150.1	2169.3	2161.9	2183.2
20°	1968.3	2021.8	2105.2	2156.5	2177.9	2192.9	2227.1	2245.3	2252.7	2252.7	2254.9
22.5°	2010.0	2087.0	2149.0	2207.8	2227.1	2237.8	2258.1	2272.0	2275.2	2277.3	2279.5
25°	2047.5	2117.0	2167.2	2200.3	2207.8	2207.8	2219.6	2211.0	2197.1	2207.8	2214.2
27.5°	2047.5	2096.6	2119.1	2130.9	2130.9	2102.0	2084.9	2049.6	2019.7	2011.1	2030.3
30°	2013.2	2035.7	2004.7	1975.8	1953.4	1934.1	1866.8	1813.3	1802.6	1795.1	1824.0
32.5°	1934.1	1905.3	1844.3	1760.9	1727.8	1683.9	1631.5	1590.9	1566.3	1557.8	1551.4
35°	1794.1	1719.2	1640.1	1527.8	1504.3	1448.7	1377.1	1347.2	1306.5	1305.5	1319.4
37.5°	1641.2	1525.7	1440.2	1333.3	1300.1	1241.3	1173.9	1142.9	1115.1	1093.8	1119.4
40°	1462.6	1362.1	1231.7	1144.0	1097.0	1066.0	1009.3	975.1	962.3	951.6	967.6
42.5°	1295.8	1185.7	1084.1	994.3	955.8	920.6	883.1	850.0	840.4	839.3	851.1
45°	1130.1	1022.1	928.0	851.1	826.5	805.1	768.7	759.1	743.1	732.4	737.7
47.5°	997.5	886.3	808.3	749.5	728.1	709.9	686.4	670.4	656.5	652.2	658.6
50°	867.1	792.3	712.1	662.9	646.8	629.7	611.6	596.6	590.2	585.9	590.2
52.5°	762.3	682.1	627.6	588.0	572.0	559.2	546.3	539.9	531.4	533.5	537.8
55°	668.2	597.7	551.7	522.8	513.2	507.9	491.8	484.3	481.1	479.0	481.1
57.5°	579.5	528.2	494.0	469.4	456.5	453.3	440.5	440.5	437.3	434.1	435.2
60°	508.9	465.1	431.9	412.7	410.6	405.2	396.7	395.6	388.1	391.3	392.4
62.5°	437.3	402.0	379.6	367.8	360.3	358.2	352.8	351.8	348.5	349.6	347.5
65°	380.6	351.8	329.3	319.7	316.5	315.4	311.1	307.9	305.8	307.9	305.8
67.5°	324.0	304.7	287.6	278.0	273.7	272.6	269.4	267.3	268.4	265.2	267.3
70°	270.5	251.3	240.6	235.2	233.1	229.9	229.9	229.9	229.9	227.7	226.7
72.5°	227.7	208.5	201.0	197.8	195.7	194.6	191.4	192.5	191.4	190.3	194.6
75°	180.7	168.9	161.4	158.2	160.4	157.2	154.0	156.1	152.9	154.0	158.2
77.5°	136.9	131.5	127.2	125.1	123.0	120.8	120.8	118.7	118.7	118.7	118.7
80°	99.4	98.4	90.9	89.8	89.8	87.7	87.7	87.7	87.7	86.6	87.7
82.5°	66.3	65.2	63.1	62.0	59.9	60.9	60.9	58.8	58.8	57.7	58.8
85°	38.5	38.5	36.4	35.3	34.2	35.3	33.1	32.1	33.1	32.1	33.1
87.5°	18.2	16.0	17.1	16.0	13.9	15.0	12.8	13.9	12.8	11.8	13.9
90°	9.7	10.3	10.9	11.4	11.4	11.4	12.0	12.6	12.0	12.0	12.0
92.5°	186.3	137.7	102.9	81.2	74.1	66.9	58.3	54.3	52.0	52.0	52.0
95°	479.0	423.5	334.9	258.3	230.6	202.9	174.9	157.2	146.9	139.5	146.9
97.5°	600.7	609.8	565.8	503.0	471.0	439.0	400.1	365.8	348.6	334.9	348.6
100°	605.8	689.3	700.7	672.7	651.6	630.4	580.7	545.8	528.7	524.1	528.7
102.5°	563.0	685.3	753.3	770.5	764.8	759.0	733.3	710.4	692.2	688.7	692.2
105°	509.3	640.1	739.0	795.6	807.3	819.0	820.2	815.6	807.6	804.2	807.6
107.5°	465.2	584.7	691.6	770.5	794.5	818.5	843.6	853.9	858.5	859.0	858.5
110°	433.8	535.5	634.4	717.3	748.8	780.2	820.8	844.8	855.0	860.2	855.0

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	416.1	499.5	584.1	661.3	692.8	724.2	771.6	801.9	817.3	826.5	817.3
115°	406.4	477.8	548.1	615.0	642.4	669.9	715.0	749.3	767.6	772.2	767.6
117.5°	401.2	465.2	524.7	579.0	603.0	627.0	667.0	696.7	716.2	719.0	716.2
120°	397.2	457.2	510.4	556.1	576.4	596.7	629.3	654.4	669.3	675.6	669.3
122.5°	392.7	450.4	501.3	541.8	559.0	576.1	602.4	623.0	635.0	641.3	635.0
125°	387.5	442.4	491.5	531.0	546.7	562.4	585.3	601.8	612.7	616.1	612.7
127.5°	380.7	433.2	480.7	520.1	535.0	549.8	572.7	587.6	596.7	600.1	596.7
130°	374.4	421.8	467.0	505.8	521.0	536.1	559.6	573.8	583.0	586.4	583.0
132.5°	368.7	409.8	451.5	489.3	504.4	519.5	542.4	559.0	567.6	571.0	567.6
135°	362.9	398.9	436.1	471.0	485.2	499.5	522.4	538.4	547.5	551.0	547.5
137.5°	357.8	388.7	421.2	451.5	464.6	477.8	499.5	516.1	523.5	527.5	523.5
140°	353.8	380.1	406.9	432.7	444.7	456.7	476.7	489.3	497.3	501.8	497.3
142.5°	350.4	372.1	394.9	416.1	426.1	436.1	453.2	464.7	471.5	474.4	471.5
145°	346.4	364.7	384.1	401.2	409.2	417.2	431.5	441.2	447.0	449.8	447.0
147.5°	342.9	358.4	374.4	388.7	395.2	401.8	412.7	421.2	425.8	427.0	425.8
150°	338.9	352.6	365.8	377.2	382.4	387.5	396.7	404.1	407.5	408.1	407.5
152.5°	334.4	346.4	357.2	367.5	371.5	375.5	382.9	388.7	390.4	390.9	390.4
155°	329.8	340.1	349.2	357.8	361.2	364.7	370.4	374.9	376.7	376.7	376.7
157.5°	325.2	333.2	341.2	348.6	351.5	354.4	358.9	362.4	363.5	363.5	363.5
160°	320.1	326.9	333.2	339.5	341.8	344.1	347.5	350.9	351.5	351.5	351.5
162.5°	315.5	320.6	325.8	330.4	332.4	334.4	336.6	340.1	340.6	340.1	340.6
165°	310.4	314.9	318.4	322.4	323.8	325.2	327.5	329.8	329.2	328.6	329.2
167.5°	305.8	309.2	312.1	315.5	316.4	317.2	318.4	320.1	320.1	319.5	320.1
170°	301.2	304.1	305.8	308.1	309.0	309.8	310.9	311.5	310.9	310.9	310.9
172.5°	297.2	299.5	300.6	301.8	302.4	302.9	303.5	304.1	303.5	302.4	303.5
175°	294.4	295.5	296.1	297.2	297.2	297.2	297.2	298.4	297.2	296.1	297.2
177.5°	292.1	292.6	293.2	293.2	293.5	293.8	293.2	293.8	292.6	291.5	292.6
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1392.1	1388.8	1384.6	1384.6	1379.2	1379.2	1370.7	1355.7	1342.9	1338.6	1340.7
5°	1510.7	1511.8	1505.4	1500.0	1490.4	1482.9	1469.0	1442.3	1433.8	1416.6	1404.9
7.5°	1646.5	1642.2	1630.5	1621.9	1619.8	1602.7	1572.7	1540.7	1515.0	1497.9	1473.3
10°	1799.4	1782.3	1765.2	1759.8	1747.0	1718.2	1683.9	1648.7	1613.4	1576.0	1534.3
12.5°	1927.7	1894.6	1893.5	1880.7	1856.1	1840.0	1799.4	1749.2	1688.2	1646.5	1599.5
15°	2065.6	2034.6	2009.0	1985.4	1973.7	1926.6	1892.4	1829.3	1756.6	1711.7	1679.7
17.5°	2164.0	2150.1	2106.3	2095.6	2079.5	2025.0	1970.5	1908.5	1845.4	1782.3	1695.7
20°	2243.1	2234.6	2205.7	2190.7	2165.1	2122.3	2056.0	1984.4	1911.7	1821.9	1740.6
22.5°	2277.3	2266.6	2243.1	2230.3	2214.2	2177.9	2121.2	2040.0	1944.8	1864.6	1778.0
25°	2210.0	2229.2	2222.8	2217.5	2211.0	2189.7	2146.9	2075.3	1982.2	1891.4	1783.4
27.5°	2058.1	2091.3	2123.4	2127.6	2138.3	2146.9	2129.8	2078.5	2000.4	1904.2	1785.5
30°	1853.9	1868.9	1934.1	1953.4	1968.3	2022.9	2054.9	2042.1	1982.2	1895.6	1786.6
32.5°	1592.0	1631.5	1697.8	1743.8	1784.4	1845.4	1928.8	1961.9	1940.5	1870.0	1762.0
35°	1343.9	1391.0	1468.0	1526.8	1567.4	1654.0	1752.4	1824.0	1850.7	1815.4	1719.2
37.5°	1140.8	1197.5	1265.9	1288.3	1335.4	1442.3	1578.1	1677.5	1742.7	1746.0	1671.1
40°	987.9	1016.8	1071.3	1105.5	1151.5	1241.3	1373.9	1505.4	1603.8	1636.9	1597.3
42.5°	858.5	881.0	921.6	963.3	1005.0	1073.4	1195.3	1318.3	1450.9	1517.1	1516.1
45°	755.9	779.4	807.2	841.4	870.3	944.1	1040.3	1166.5	1280.9	1383.5	1409.2
47.5°	666.1	686.4	720.6	735.6	754.8	824.3	907.7	1025.3	1144.0	1261.6	1291.6
50°	599.8	616.9	640.4	650.1	671.4	722.8	791.2	886.3	1017.8	1125.8	1181.4
52.5°	539.9	552.8	570.9	578.4	593.4	631.9	693.9	768.7	877.8	989.0	1067.0
55°	488.6	497.2	510.0	518.5	529.2	563.5	609.4	676.8	770.9	867.1	943.0
57.5°	440.5	446.9	459.7	464.0	472.6	499.3	531.4	588.0	674.6	760.2	834.0
60°	395.6	399.9	407.4	417.0	423.4	441.6	471.5	518.5	588.0	666.1	726.0
62.5°	352.8	359.2	361.4	365.7	371.0	388.1	411.6	445.8	506.8	570.9	634.0
65°	309.0	314.3	318.6	319.7	325.0	337.9	359.2	389.2	428.7	484.3	543.1
67.5°	268.4	271.6	273.7	278.0	283.3	289.7	306.9	329.3	365.7	410.6	457.6
70°	230.9	230.9	234.1	235.2	241.6	249.1	256.6	278.0	310.1	346.4	378.5
72.5°	190.3	195.7	194.6	199.9	198.9	204.2	213.8	227.7	251.3	280.1	311.1
75°	155.0	158.2	158.2	158.2	160.4	164.7	170.0	182.8	201.0	224.5	242.7
77.5°	120.8	123.0	123.0	123.0	124.0	128.3	133.6	142.2	155.0	168.9	179.6
80°	86.6	88.7	88.7	90.9	90.9	91.9	97.3	101.6	108.0	118.7	129.4
82.5°	58.8	59.9	62.0	62.0	60.9	63.1	64.2	68.4	74.8	77.0	84.5
85°	32.1	33.1	34.2	34.2	35.3	37.4	36.4	40.6	40.6	44.9	47.0
87.5°	12.8	15.0	15.0	13.9	15.0	15.0	15.0	17.1	18.2	19.2	18.2
90°	12.6	12.0	11.4	11.4	11.4	10.9	10.3	9.7	10.3	9.1	8.0
92.5°	54.3	58.3	66.9	74.1	81.2	102.9	137.7	186.3	224.0	196.0	142.3
95°	157.2	174.9	202.9	230.6	258.3	334.9	423.5	479.0	465.8	351.5	214.9
97.5°	365.8	400.1	439.0	471.0	503.0	565.8	609.8	600.7	498.4	336.6	196.0
100°	545.8	580.7	630.4	651.6	672.7	700.7	689.3	605.8	459.5	298.4	181.8
102.5°	710.4	733.3	759.0	764.8	770.5	753.3	685.3	563.0	410.9	272.6	177.8
105°	815.6	820.2	819.0	807.3	795.6	739.0	640.1	509.3	374.9	260.1	180.0
107.5°	853.9	843.6	818.5	794.5	770.5	691.6	584.7	465.2	351.5	256.6	186.9
110°	844.8	820.8	780.2	748.8	717.3	634.4	535.5	433.8	340.6	257.8	194.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	801.9	771.6	724.2	692.8	661.3	584.1	499.5	416.1	335.5	261.2	203.5
115°	749.3	715.0	669.9	642.4	615.0	548.1	477.8	406.4	334.4	265.8	212.6
117.5°	696.7	667.0	627.0	603.0	579.0	524.7	465.2	401.2	333.8	270.3	221.8
120°	654.4	629.3	596.7	576.4	556.1	510.4	457.2	397.2	333.8	275.5	231.5
122.5°	623.0	602.4	576.1	559.0	541.8	501.3	450.4	392.7	333.2	280.6	240.6
125°	601.8	585.3	562.4	546.7	531.0	491.5	442.4	387.5	332.6	285.8	249.8
127.5°	587.6	572.7	549.8	535.0	520.1	480.7	433.2	380.7	331.5	289.8	257.8
130°	573.8	559.6	536.1	521.0	505.8	467.0	421.8	374.4	330.9	294.4	265.2
132.5°	559.0	542.4	519.5	504.4	489.3	451.5	409.8	368.7	330.4	298.4	272.6
135°	538.4	522.4	499.5	485.2	471.0	436.1	398.9	362.9	329.8	302.4	278.9
137.5°	516.1	499.5	477.8	464.6	451.5	421.2	388.7	357.8	329.8	304.6	283.5
140°	489.3	476.7	456.7	444.7	432.7	406.9	380.1	353.8	329.2	307.5	288.1
142.5°	464.7	453.2	436.1	426.1	416.1	394.9	372.1	350.4	329.2	309.8	291.5
145°	441.2	431.5	417.2	409.2	401.2	384.1	364.7	346.4	328.1	310.4	293.8
147.5°	421.2	412.7	401.8	395.2	388.7	374.4	358.4	342.9	326.4	310.9	296.1
150°	404.1	396.7	387.5	382.4	377.2	365.8	352.6	338.9	324.6	310.9	297.8
152.5°	388.7	382.9	375.5	371.5	367.5	357.2	346.4	334.4	321.8	309.8	298.9
155°	374.9	370.4	364.7	361.2	357.8	349.2	340.1	329.8	318.9	308.6	299.5
157.5°	362.4	358.9	354.4	351.5	348.6	341.2	333.2	325.2	316.1	307.5	299.5
160°	350.9	347.5	344.1	341.8	339.5	333.2	326.9	320.1	312.6	305.8	299.5
162.5°	340.1	336.6	334.4	332.4	330.4	325.8	320.6	315.5	309.2	304.1	299.5
165°	329.8	327.5	325.2	323.8	322.4	318.4	314.9	310.4	305.8	301.8	298.4
167.5°	320.1	318.4	317.2	316.4	315.5	312.1	309.2	305.8	302.4	299.5	297.2
170°	311.5	310.9	309.8	309.0	308.1	305.8	304.1	301.2	298.9	297.2	296.1
172.5°	304.1	303.5	302.9	302.4	301.8	300.6	299.5	297.2	295.5	294.9	294.9
175°	298.4	297.2	297.2	297.2	297.2	296.1	295.5	294.4	293.2	293.2	293.8
177.5°	293.8	293.2	293.8	293.5	293.2	293.2	292.6	292.1	291.5	291.5	292.6
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1331.1	1326.8	1323.6	1323.6	1314.0	1304.4	1299.0	1296.9	1294.8	1286.2	1274.4
5°	1385.6	1371.7	1362.1	1352.5	1336.5	1319.4	1302.2	1292.6	1278.7	1259.5	1245.6
7.5°	1446.6	1413.4	1402.7	1391.0	1358.9	1330.0	1306.5	1286.2	1263.8	1239.2	1214.6
10°	1497.9	1462.6	1439.1	1418.8	1377.1	1338.6	1303.3	1273.4	1244.5	1212.4	1182.5
12.5°	1547.1	1496.8	1472.2	1442.3	1398.5	1342.9	1296.9	1259.5	1216.7	1183.6	1147.2
15°	1615.5	1531.0	1490.4	1471.2	1412.4	1347.2	1291.6	1236.0	1200.7	1150.4	1118.3
17.5°	1626.2	1557.8	1531.0	1481.9	1411.3	1337.5	1273.4	1217.8	1164.3	1119.4	1077.7
20°	1663.6	1573.8	1531.0	1500.0	1407.0	1332.2	1261.6	1190.0	1138.7	1090.6	1043.5
22.5°	1687.1	1585.6	1540.7	1491.5	1402.7	1312.9	1229.5	1167.5	1104.4	1055.3	1017.8
25°	1680.7	1579.2	1528.9	1482.9	1374.9	1285.1	1210.3	1131.2	1072.4	1018.9	969.7
27.5°	1677.5	1563.1	1509.7	1458.3	1356.8	1262.7	1168.6	1104.4	1039.2	977.2	940.9
30°	1669.0	1542.8	1480.8	1425.2	1319.4	1221.0	1140.8	1066.0	1000.7	944.1	896.0
32.5°	1640.1	1508.6	1448.7	1388.8	1278.7	1180.4	1099.1	1029.6	964.4	905.6	859.6
35°	1601.6	1468.0	1402.7	1339.7	1229.5	1130.1	1055.3	982.6	921.6	865.0	821.1
37.5°	1563.1	1420.9	1360.0	1287.3	1185.7	1082.0	1005.0	939.8	883.1	824.3	776.2
40°	1507.5	1365.3	1298.0	1236.0	1117.3	1020.0	949.4	890.6	835.0	779.4	738.8
42.5°	1431.6	1304.4	1234.9	1166.5	1055.3	959.0	890.6	838.2	785.8	739.9	695.0
45°	1354.6	1230.6	1168.6	1107.7	986.8	896.0	832.9	784.8	740.9	690.7	654.3
47.5°	1261.6	1156.8	1094.8	1035.0	920.6	829.7	771.9	727.0	686.4	644.7	610.5
50°	1166.5	1075.6	1018.9	956.9	847.8	765.5	708.9	671.4	638.3	598.7	570.9
52.5°	1063.8	984.7	936.6	876.7	780.5	704.6	646.8	609.4	581.6	552.8	528.2
55°	954.8	897.0	845.7	797.6	706.7	638.3	587.0	553.8	534.6	507.9	486.5
57.5°	856.4	800.8	769.8	715.3	636.2	568.8	528.2	500.4	477.9	461.9	444.8
60°	753.8	708.9	674.6	635.1	565.6	508.9	466.2	450.1	426.6	414.8	407.4
62.5°	655.4	623.3	591.2	561.3	499.3	445.8	413.8	393.5	379.6	367.8	361.4
65°	562.4	532.4	510.0	483.3	431.9	389.2	359.2	343.2	329.3	326.1	318.6
67.5°	471.5	458.7	434.1	412.7	368.9	335.7	313.3	293.0	285.5	282.3	275.8
70°	394.5	379.6	360.3	342.1	309.0	280.1	259.8	252.3	241.6	240.6	233.1
72.5°	325.0	306.9	293.0	279.1	254.5	228.8	218.1	207.4	202.1	197.8	194.6
75°	257.7	244.8	235.2	223.5	202.1	185.0	170.0	165.7	162.5	161.4	159.3
77.5°	192.5	183.9	179.6	167.9	152.9	137.9	131.5	125.1	125.1	123.0	124.0
80°	136.9	131.5	126.2	119.7	106.9	100.5	95.2	90.9	88.7	87.7	88.7
82.5°	86.6	83.4	82.3	78.0	69.5	66.3	62.0	58.8	58.8	58.8	58.8
85°	48.1	48.1	48.1	41.7	38.5	35.3	33.1	32.1	32.1	32.1	33.1
87.5°	20.3	20.3	17.1	17.1	16.0	13.9	12.8	12.8	13.9	13.9	15.0
90°	8.0	4.6	4.6	4.6	4.0	3.4	1.7	0.6	1.7	3.4	4.0
92.5°	86.9	51.4	44.0	36.6	26.3	17.7	11.4	8.0	11.4	17.7	26.3
95°	121.2	71.4	59.4	47.4	33.7	26.3	20.6	18.9	20.6	26.3	33.7
97.5°	115.5	76.0	65.7	55.4	43.4	36.6	31.4	31.4	31.4	36.6	43.4
100°	117.2	83.4	74.3	65.2	54.3	47.4	43.4	43.4	43.4	47.4	54.3
102.5°	122.9	93.2	84.6	76.0	65.7	59.4	56.0	54.9	56.0	59.4	65.7
105°	132.6	105.2	96.9	88.6	78.3	71.4	68.6	66.9	68.6	71.4	78.3
107.5°	142.9	117.7	109.4	101.2	91.4	84.0	81.2	80.0	81.2	84.0	91.4
110°	154.9	129.7	122.0	114.3	104.0	97.2	94.3	93.2	94.3	97.2	104.0

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	166.3	142.3	134.6	126.9	116.6	110.3	106.9	105.7	106.9	110.3	116.6
115°	178.3	155.5	147.8	140.0	129.2	123.5	119.5	117.7	119.5	123.5	129.2
117.5°	189.8	168.0	160.0	152.0	141.7	135.5	132.0	130.3	132.0	135.5	141.7
120°	201.8	180.0	172.0	164.0	154.3	148.0	144.0	142.9	144.0	148.0	154.3
122.5°	213.2	191.5	183.8	176.0	165.2	159.5	155.5	154.3	155.5	159.5	165.2
125°	223.5	202.9	194.9	186.9	176.0	169.8	166.3	164.0	166.3	169.8	176.0
127.5°	233.2	213.2	205.2	197.2	185.8	178.9	174.9	173.2	174.9	178.9	185.8
130°	242.9	223.5	215.2	206.9	196.0	187.5	182.9	180.6	182.9	187.5	196.0
132.5°	250.9	231.5	223.8	216.0	204.0	196.0	189.8	188.0	189.8	196.0	204.0
135°	258.3	239.5	232.0	224.6	212.6	202.9	197.2	194.9	197.2	202.9	212.6
137.5°	264.1	246.3	239.2	232.1	219.5	210.3	204.0	201.8	204.0	210.3	219.5
140°	269.8	252.6	245.8	238.9	226.9	217.2	210.9	209.2	210.9	217.2	226.9
142.5°	274.9	258.3	251.8	245.2	233.8	224.6	218.9	217.2	218.9	224.6	233.8
145°	278.3	263.5	257.2	250.9	240.1	232.1	226.3	224.6	226.3	232.1	240.1
147.5°	282.3	268.1	262.4	256.6	247.5	238.9	233.8	233.2	233.8	238.9	247.5
150°	285.2	272.6	267.2	261.8	253.2	246.3	241.8	241.2	241.8	246.3	253.2
152.5°	287.5	276.6	271.8	266.9	259.5	253.2	248.6	248.6	248.6	253.2	259.5
155°	289.8	280.1	275.8	271.5	265.2	259.5	256.1	255.5	256.1	259.5	265.2
157.5°	291.5	282.9	279.5	276.1	270.3	265.8	262.3	262.3	262.3	265.8	270.3
160°	292.6	285.8	282.6	279.5	274.9	270.9	268.6	268.6	268.6	270.9	274.9
162.5°	293.8	287.5	285.2	282.9	278.9	275.5	273.8	274.3	273.8	275.5	278.9
165°	293.8	288.6	286.9	285.2	282.3	279.5	278.3	278.3	278.3	279.5	282.3
167.5°	293.8	289.8	288.4	286.9	285.2	282.9	282.3	282.9	282.3	282.9	285.2
170°	293.2	290.4	289.5	288.6	287.5	285.8	285.2	285.8	285.2	285.8	287.5
172.5°	292.6	290.9	290.4	289.8	289.2	288.1	288.1	288.6	288.1	288.1	289.2
175°	292.1	290.9	290.9	290.9	290.4	289.8	289.8	290.4	289.8	289.8	290.4
177.5°	291.5	290.9	290.9	290.9	290.9	290.4	290.9	291.5	290.9	290.4	290.9
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1271.2	1267.0	1269.1	1258.4	1248.8	1234.9	1223.1	1221.0	1218.9	1225.3	1221.0
5°	1234.9	1229.5	1224.2	1211.4	1192.1	1180.4	1163.3	1162.2	1155.8	1146.1	1148.3
7.5°	1195.3	1192.1	1184.6	1164.3	1147.2	1126.9	1113.0	1101.2	1095.9	1087.3	1084.1
10°	1163.3	1151.5	1145.1	1122.6	1102.3	1080.9	1062.8	1054.2	1044.6	1037.1	1031.7
12.5°	1119.4	1116.2	1098.0	1079.9	1062.8	1038.2	1024.3	999.7	986.8	993.3	991.1
15°	1090.6	1075.6	1071.3	1045.6	1016.8	1000.7	975.1	959.0	953.7	944.1	932.3
17.5°	1052.1	1042.4	1027.5	1003.9	970.8	948.4	930.2	915.2	908.8	896.0	886.3
20°	1015.7	999.7	987.9	966.5	934.5	905.6	883.1	873.5	857.5	846.8	841.4
22.5°	982.6	970.8	953.7	921.6	893.8	866.0	839.3	825.4	810.4	804.0	795.5
25°	941.9	922.7	910.9	875.6	845.7	823.3	798.7	780.5	771.9	761.2	759.1
27.5°	902.4	884.2	870.3	839.3	802.9	774.1	759.1	746.3	731.3	731.3	726.0
30°	862.8	850.0	828.6	798.7	764.5	736.7	719.5	707.8	702.4	698.2	697.1
32.5°	823.3	806.2	793.3	752.7	727.0	701.4	688.5	678.9	672.5	671.4	672.5
35°	782.6	763.4	750.6	714.2	688.5	665.0	659.7	651.1	647.9	646.8	652.2
37.5°	739.9	724.9	708.9	678.9	650.1	636.2	625.5	622.3	621.2	627.6	629.7
40°	700.3	687.5	672.5	640.4	619.0	604.1	598.7	595.5	599.8	606.2	609.4
42.5°	662.9	644.7	632.9	604.1	584.8	576.3	569.9	569.9	574.1	581.6	587.0
45°	623.3	609.4	597.7	572.0	554.9	545.3	544.2	545.3	550.6	556.0	562.4
47.5°	584.8	570.9	558.1	536.7	521.8	516.4	515.3	516.4	525.0	532.4	539.9
50°	549.6	534.6	522.8	502.5	490.7	484.3	485.4	490.7	497.2	507.9	517.5
52.5°	507.9	497.2	486.5	468.3	457.6	453.3	456.5	460.8	472.6	480.1	491.8
55°	467.2	457.6	449.1	435.2	426.6	423.4	425.5	431.9	441.6	454.4	468.3
57.5°	429.8	419.1	410.6	400.9	391.3	392.4	393.5	402.0	413.8	425.5	441.6
60°	388.1	381.7	374.2	362.4	358.2	358.2	361.4	371.0	381.7	400.9	414.8
62.5°	350.7	342.1	336.8	329.3	322.9	324.0	331.4	340.0	352.8	368.9	387.0
65°	312.2	302.6	298.3	291.9	289.7	290.8	296.2	309.0	322.9	336.8	353.9
67.5°	269.4	266.2	261.9	255.5	257.7	258.7	264.1	274.8	289.7	303.6	322.9
70°	233.1	226.7	225.6	220.2	220.2	223.5	234.1	241.6	255.5	270.5	290.8
72.5°	194.6	189.2	189.2	185.0	188.2	191.4	196.7	207.4	220.2	235.2	252.3
75°	155.0	152.9	155.0	152.9	152.9	158.2	164.7	173.2	187.1	203.1	217.0
77.5°	119.7	119.7	118.7	121.9	121.9	125.1	133.6	142.2	152.9	165.7	180.7
80°	87.7	87.7	87.7	90.9	94.1	94.1	99.4	110.1	119.7	128.3	142.2
82.5°	59.9	59.9	59.9	62.0	66.3	66.3	72.7	79.1	89.8	97.3	103.7
85°	36.4	36.4	35.3	37.4	38.5	41.7	47.0	51.3	56.7	63.1	69.5
87.5°	16.0	16.0	17.1	18.2	19.2	21.4	23.5	25.7	31.0	33.1	36.4
90°	4.6	4.6	4.6	8.0	8.0	9.1	10.3	9.7	10.3	10.9	11.4
92.5°	36.6	44.0	51.4	86.9	142.3	196.0	224.0	186.3	137.7	102.9	81.2
95°	47.4	59.4	71.4	121.2	214.9	351.5	465.8	479.0	423.5	334.9	258.3
97.5°	55.4	65.7	76.0	115.5	196.0	336.6	498.4	600.7	609.8	565.8	503.0
100°	65.2	74.3	83.4	117.2	181.8	298.4	459.5	605.8	689.3	700.7	672.7
102.5°	76.0	84.6	93.2	122.9	177.8	272.6	410.9	563.0	685.3	753.3	770.5
105°	88.6	96.9	105.2	132.6	180.0	260.1	374.9	509.3	640.1	739.0	795.6
107.5°	101.2	109.4	117.7	142.9	186.9	256.6	351.5	465.2	584.7	691.6	770.5
110°	114.3	122.0	129.7	154.9	194.9	257.8	340.6	433.8	535.5	634.4	717.3

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	126.9	134.6	142.3	166.3	203.5	261.2	335.5	416.1	499.5	584.1	661.3
115°	140.0	147.8	155.5	178.3	212.6	265.8	334.4	406.4	477.8	548.1	615.0
117.5°	152.0	160.0	168.0	189.8	221.8	270.3	333.8	401.2	465.2	524.7	579.0
120°	164.0	172.0	180.0	201.8	231.5	275.5	333.8	397.2	457.2	510.4	556.1
122.5°	176.0	183.8	191.5	213.2	240.6	280.6	333.2	392.7	450.4	501.3	541.8
125°	186.9	194.9	202.9	223.5	249.8	285.8	332.6	387.5	442.4	491.5	531.0
127.5°	197.2	205.2	213.2	233.2	257.8	289.8	331.5	380.7	433.2	480.7	520.1
130°	206.9	215.2	223.5	242.9	265.2	294.4	330.9	374.4	421.8	467.0	505.8
132.5°	216.0	223.8	231.5	250.9	272.6	298.4	330.4	368.7	409.8	451.5	489.3
135°	224.6	232.0	239.5	258.3	278.9	302.4	329.8	362.9	398.9	436.1	471.0
137.5°	232.1	239.2	246.3	264.1	283.5	304.6	329.8	357.8	388.7	421.2	451.5
140°	238.9	245.8	252.6	269.8	288.1	307.5	329.2	353.8	380.1	406.9	432.7
142.5°	245.2	251.8	258.3	274.9	291.5	309.8	329.2	350.4	372.1	394.9	416.1
145°	250.9	257.2	263.5	278.3	293.8	310.4	328.1	346.4	364.7	384.1	401.2
147.5°	256.6	262.4	268.1	282.3	296.1	310.9	326.4	342.9	358.4	374.4	388.7
150°	261.8	267.2	272.6	285.2	297.8	310.9	324.6	338.9	352.6	365.8	377.2
152.5°	266.9	271.8	276.6	287.5	298.9	309.8	321.8	334.4	346.4	357.2	367.5
155°	271.5	275.8	280.1	289.8	299.5	308.6	318.9	329.8	340.1	349.2	357.8
157.5°	276.1	279.5	282.9	291.5	299.5	307.5	316.1	325.2	333.2	341.2	348.6
160°	279.5	282.6	285.8	292.6	299.5	305.8	312.6	320.1	326.9	333.2	339.5
162.5°	282.9	285.2	287.5	293.8	299.5	304.1	309.2	315.5	320.6	325.8	330.4
165°	285.2	286.9	288.6	293.8	298.4	301.8	305.8	310.4	314.9	318.4	322.4
167.5°	286.9	288.4	289.8	293.8	297.2	299.5	302.4	305.8	309.2	312.1	315.5
170°	288.6	289.5	290.4	293.2	296.1	297.2	298.9	301.2	304.1	305.8	308.1
172.5°	289.8	290.4	290.9	292.6	294.9	294.9	295.5	297.2	299.5	300.6	301.8
175°	290.9	290.9	290.9	292.1	293.8	293.2	293.2	294.4	295.5	296.1	297.2
177.5°	290.9	290.9	290.9	291.5	292.6	291.5	291.5	292.1	292.6	293.2	293.2
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1217.8	1216.7	1211.4	1213.5	1207.1	1209.2	1212.4	1213.5	1217.8	1214.6	1213.5
5°	1142.9	1140.8	1137.6	1134.4	1133.3	1137.6	1130.1	1132.2	1134.4	1137.6	1141.9
7.5°	1082.0	1080.9	1077.7	1072.4	1070.2	1068.1	1069.2	1076.7	1075.6	1074.5	1082.0
10°	1026.4	1027.5	1021.1	1020.0	1013.6	1012.5	1013.6	1015.7	1018.9	1023.2	1024.3
12.5°	968.7	982.6	970.8	966.5	956.9	962.3	964.4	954.8	960.1	963.3	979.4
15°	932.3	925.9	918.4	918.4	914.1	912.0	906.7	914.1	918.4	924.8	922.7
17.5°	882.1	871.4	867.1	862.8	863.9	868.2	856.4	873.5	873.5	876.7	871.4
20°	838.2	829.7	824.3	822.2	819.0	816.8	815.8	820.1	826.5	828.6	834.0
22.5°	792.3	792.3	783.7	780.5	778.4	775.1	780.5	777.3	781.6	785.8	794.4
25°	753.8	753.8	750.6	746.3	743.1	740.9	744.1	743.1	746.3	751.6	753.8
27.5°	722.8	719.5	718.5	717.4	716.3	717.4	716.3	719.5	722.8	723.8	721.7
30°	696.0	692.8	693.9	693.9	695.0	693.9	692.8	696.0	697.1	695.0	696.0
32.5°	671.4	671.4	673.6	674.6	674.6	675.7	676.8	674.6	675.7	672.5	673.6
35°	651.1	653.3	655.4	656.5	657.5	656.5	658.6	657.5	655.4	653.3	652.2
37.5°	630.8	632.9	637.2	638.3	641.5	642.6	640.4	640.4	639.4	635.1	632.9
40°	609.4	611.6	616.9	620.1	622.3	625.5	623.3	623.3	619.0	614.8	611.6
42.5°	589.1	593.4	598.7	601.9	606.2	606.2	606.2	604.1	598.7	594.5	591.2
45°	568.8	569.9	577.4	582.7	587.0	587.0	587.0	583.8	580.6	572.0	567.7
47.5°	546.3	549.6	558.1	563.5	567.7	568.8	568.8	565.6	559.2	551.7	546.3
50°	521.8	527.1	536.7	544.2	549.6	551.7	548.5	546.3	538.9	530.3	523.9
52.5°	498.2	504.6	516.4	522.8	530.3	531.4	530.3	527.1	518.5	506.8	501.4
55°	474.7	480.1	492.9	503.6	510.0	512.1	510.0	504.6	494.0	482.2	476.8
57.5°	449.1	456.5	470.4	481.1	488.6	489.7	487.5	482.2	473.6	458.7	451.2
60°	422.3	431.9	445.8	456.5	466.2	467.2	465.1	457.6	446.9	431.9	425.5
62.5°	395.6	403.1	419.1	430.9	438.4	443.7	439.4	431.9	421.3	406.3	396.7
65°	364.6	375.3	389.2	399.9	408.4	409.5	407.4	400.9	389.2	373.1	365.7
67.5°	334.6	342.1	356.0	369.9	373.1	376.3	373.1	366.7	357.1	343.2	332.5
70°	298.3	304.7	321.8	331.4	335.7	338.9	336.8	330.4	321.8	309.0	300.4
72.5°	261.9	267.3	283.3	290.8	299.4	298.3	297.2	293.0	281.2	272.6	267.3
75°	223.5	229.9	240.6	250.2	253.4	253.4	253.4	250.2	242.7	228.8	223.5
77.5°	188.2	191.4	199.9	205.3	208.5	209.6	208.5	203.1	198.9	189.2	186.0
80°	144.3	152.9	159.3	160.4	164.7	164.7	164.7	162.5	158.2	148.6	147.5
82.5°	109.1	111.2	117.6	120.8	123.0	121.9	121.9	117.6	116.5	111.2	109.1
85°	73.8	77.0	75.9	80.2	81.3	79.1	79.1	81.3	75.9	77.0	73.8
87.5°	40.6	40.6	42.8	41.7	46.0	46.0	43.8	44.9	42.8	41.7	40.6
90°	11.4	11.4	12.0	12.6	12.0	12.0	12.0	12.6	12.0	11.4	11.4
92.5°	74.1	66.9	58.3	54.3	52.0	52.0	52.0	54.3	58.3	66.9	74.1
95°	230.6	202.9	174.9	157.2	146.9	139.5	146.9	157.2	174.9	202.9	230.6
97.5°	471.0	439.0	400.1	365.8	348.6	334.9	348.6	365.8	400.1	439.0	471.0
100°	651.6	630.4	580.7	545.8	528.7	524.1	528.7	545.8	580.7	630.4	651.6
102.5°	764.8	759.0	733.3	710.4	692.2	688.7	692.2	710.4	733.3	759.0	764.8
105°	807.3	819.0	820.2	815.6	807.6	804.2	807.6	815.6	820.2	819.0	807.3
107.5°	794.5	818.5	843.6	853.9	858.5	859.0	858.5	853.9	843.6	818.5	794.5
110°	748.8	780.2	820.8	844.8	855.0	860.2	855.0	844.8	820.8	780.2	748.8

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	692.8	724.2	771.6	801.9	817.3	826.5	817.3	801.9	771.6	724.2	692.8
115°	642.4	669.9	715.0	749.3	767.6	772.2	767.6	749.3	715.0	669.9	642.4
117.5°	603.0	627.0	667.0	696.7	716.2	719.0	716.2	696.7	667.0	627.0	603.0
120°	576.4	596.7	629.3	654.4	669.3	675.6	669.3	654.4	629.3	596.7	576.4
122.5°	559.0	576.1	602.4	623.0	635.0	641.3	635.0	623.0	602.4	576.1	559.0
125°	546.7	562.4	585.3	601.8	612.7	616.1	612.7	601.8	585.3	562.4	546.7
127.5°	535.0	549.8	572.7	587.6	596.7	600.1	596.7	587.6	572.7	549.8	535.0
130°	521.0	536.1	559.6	573.8	583.0	586.4	583.0	573.8	559.6	536.1	521.0
132.5°	504.4	519.5	542.4	559.0	567.6	571.0	567.6	559.0	542.4	519.5	504.4
135°	485.2	499.5	522.4	538.4	547.5	551.0	547.5	538.4	522.4	499.5	485.2
137.5°	464.6	477.8	499.5	516.1	523.5	527.5	523.5	516.1	499.5	477.8	464.6
140°	444.7	456.7	476.7	489.3	497.3	501.8	497.3	489.3	476.7	456.7	444.7
142.5°	426.1	436.1	453.2	464.7	471.5	474.4	471.5	464.7	453.2	436.1	426.1
145°	409.2	417.2	431.5	441.2	447.0	449.8	447.0	441.2	431.5	417.2	409.2
147.5°	395.2	401.8	412.7	421.2	425.8	427.0	425.8	421.2	412.7	401.8	395.2
150°	382.4	387.5	396.7	404.1	407.5	408.1	407.5	404.1	396.7	387.5	382.4
152.5°	371.5	375.5	382.9	388.7	390.4	390.9	390.4	388.7	382.9	375.5	371.5
155°	361.2	364.7	370.4	374.9	376.7	376.7	376.7	374.9	370.4	364.7	361.2
157.5°	351.5	354.4	358.9	362.4	363.5	363.5	363.5	362.4	358.9	354.4	351.5
160°	341.8	344.1	347.5	350.9	351.5	351.5	351.5	350.9	347.5	344.1	341.8
162.5°	332.4	334.4	336.6	340.1	340.6	340.1	340.6	340.1	336.6	334.4	332.4
165°	323.8	325.2	327.5	329.8	329.2	328.6	329.2	329.8	327.5	325.2	323.8
167.5°	316.4	317.2	318.4	320.1	320.1	319.5	320.1	320.1	318.4	317.2	316.4
170°	309.0	309.8	310.9	311.5	310.9	310.9	310.9	311.5	310.9	309.8	309.0
172.5°	302.4	302.9	303.5	304.1	303.5	302.4	303.5	304.1	303.5	302.9	302.4
175°	297.2	297.2	297.2	298.4	297.2	296.1	297.2	298.4	297.2	297.2	297.2
177.5°	293.5	293.8	293.2	293.8	292.6	291.5	292.6	293.8	293.2	293.8	293.5
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5	1290.5
2.5°	1213.5	1219.9	1213.5	1217.8	1219.9	1225.3	1227.4	1237.0	1240.2	1247.7	1247.7
5°	1140.8	1144.0	1145.1	1149.4	1153.6	1164.3	1171.8	1185.7	1201.7	1203.9	1213.5
7.5°	1082.0	1087.3	1095.9	1092.7	1100.2	1116.2	1125.8	1142.9	1159.0	1167.5	1179.3
10°	1029.6	1036.0	1039.2	1042.4	1056.3	1070.2	1085.2	1097.0	1118.3	1131.2	1140.8
12.5°	986.8	981.5	987.9	999.7	1015.7	1024.3	1044.6	1062.8	1078.8	1092.7	1101.2
15°	931.2	935.5	941.9	962.3	966.5	987.9	995.4	1015.7	1045.6	1058.5	1069.2
17.5°	877.8	891.7	904.5	912.0	924.8	941.9	963.3	985.8	1005.0	1020.0	1032.8
20°	835.0	848.9	856.4	861.7	874.6	898.1	918.4	946.2	970.8	982.6	999.7
22.5°	800.8	800.8	811.5	827.5	835.0	857.5	874.6	904.5	931.2	946.2	962.3
25°	758.0	764.5	773.0	786.9	797.6	815.8	840.4	866.0	894.9	907.7	928.0
27.5°	722.8	730.2	742.0	745.2	755.9	771.9	797.6	825.4	855.3	869.2	886.3
30°	696.0	700.3	704.6	711.0	720.6	734.5	755.9	780.5	816.8	827.5	848.9
32.5°	672.5	674.6	676.8	682.1	687.5	701.4	718.5	745.2	775.1	791.2	810.4
35°	651.1	649.0	650.1	653.3	658.6	664.0	682.1	704.6	732.4	751.6	766.6
37.5°	630.8	626.5	625.5	625.5	627.6	634.0	647.9	667.2	697.1	713.1	728.1
40°	608.4	604.1	601.9	600.9	599.8	604.1	614.8	634.0	657.5	672.5	689.6
42.5°	587.0	582.7	577.4	576.3	574.1	576.3	583.8	601.9	622.3	637.2	651.1
45°	565.6	558.1	551.7	547.4	548.5	545.3	550.6	564.5	588.0	597.7	611.6
47.5°	542.1	533.5	525.0	520.7	516.4	518.5	520.7	532.4	552.8	562.4	576.3
50°	519.6	507.9	498.2	492.9	489.7	487.5	489.7	501.4	516.4	525.0	536.7
52.5°	494.0	482.2	472.6	464.0	459.7	456.5	457.6	468.3	482.2	490.7	502.5
55°	470.4	455.5	442.6	431.9	428.7	427.7	426.6	434.1	445.8	454.4	464.0
57.5°	443.7	428.7	414.8	402.0	395.6	394.5	394.5	396.7	411.6	418.0	423.4
60°	417.0	400.9	386.0	374.2	364.6	361.4	360.3	364.6	372.1	378.5	386.0
62.5°	387.0	371.0	352.8	342.1	332.5	324.0	327.2	328.2	338.9	342.1	348.5
65°	358.2	340.0	325.0	307.9	297.2	291.9	289.7	291.9	300.4	301.5	305.8
67.5°	325.0	307.9	289.7	278.0	268.4	258.7	256.6	256.6	260.9	264.1	269.4
70°	293.0	275.8	255.5	242.7	233.1	224.5	221.3	220.2	223.5	225.6	230.9
72.5°	255.5	238.4	223.5	209.6	197.8	191.4	188.2	186.0	189.2	191.4	192.5
75°	216.0	202.1	187.1	173.2	165.7	159.3	155.0	151.8	154.0	154.0	154.0
77.5°	178.6	164.7	152.9	143.3	133.6	126.2	123.0	119.7	120.8	120.8	123.0
80°	139.0	129.4	119.7	111.2	102.6	96.2	94.1	90.9	88.7	87.7	87.7
82.5°	102.6	95.2	86.6	79.1	74.8	68.4	66.3	62.0	62.0	60.9	60.9
85°	68.4	64.2	55.6	50.3	47.0	43.8	41.7	39.6	36.4	36.4	35.3
87.5°	36.4	34.2	32.1	25.7	25.7	22.5	21.4	20.3	17.1	18.2	18.2
90°	11.4	10.9	10.3	9.7	10.3	9.1	8.0	8.0	4.6	4.6	4.6
92.5°	81.2	102.9	137.7	186.3	224.0	196.0	142.3	86.9	51.4	44.0	36.6
95°	258.3	334.9	423.5	479.0	465.8	351.5	214.9	121.2	71.4	59.4	47.4
97.5°	503.0	565.8	609.8	600.7	498.4	336.6	196.0	115.5	76.0	65.7	55.4
100°	672.7	700.7	689.3	605.8	459.5	298.4	181.8	117.2	83.4	74.3	65.2
102.5°	770.5	753.3	685.3	563.0	410.9	272.6	177.8	122.9	93.2	84.6	76.0
105°	795.6	739.0	640.1	509.3	374.9	260.1	180.0	132.6	105.2	96.9	88.6
107.5°	770.5	691.6	584.7	465.2	351.5	256.6	186.9	142.9	117.7	109.4	101.2
110°	717.3	634.4	535.5	433.8	340.6	257.8	194.9	154.9	129.7	122.0	114.3

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	661.3	584.1	499.5	416.1	335.5	261.2	203.5	166.3	142.3	134.6	126.9
115°	615.0	548.1	477.8	406.4	334.4	265.8	212.6	178.3	155.5	147.8	140.0
117.5°	579.0	524.7	465.2	401.2	333.8	270.3	221.8	189.8	168.0	160.0	152.0
120°	556.1	510.4	457.2	397.2	333.8	275.5	231.5	201.8	180.0	172.0	164.0
122.5°	541.8	501.3	450.4	392.7	333.2	280.6	240.6	213.2	191.5	183.8	176.0
125°	531.0	491.5	442.4	387.5	332.6	285.8	249.8	223.5	202.9	194.9	186.9
127.5°	520.1	480.7	433.2	380.7	331.5	289.8	257.8	233.2	213.2	205.2	197.2
130°	505.8	467.0	421.8	374.4	330.9	294.4	265.2	242.9	223.5	215.2	206.9
132.5°	489.3	451.5	409.8	368.7	330.4	298.4	272.6	250.9	231.5	223.8	216.0
135°	471.0	436.1	398.9	362.9	329.8	302.4	278.9	258.3	239.5	232.0	224.6
137.5°	451.5	421.2	388.7	357.8	329.8	304.6	283.5	264.1	246.3	239.2	232.1
140°	432.7	406.9	380.1	353.8	329.2	307.5	288.1	269.8	252.6	245.8	238.9
142.5°	416.1	394.9	372.1	350.4	329.2	309.8	291.5	274.9	258.3	251.8	245.2
145°	401.2	384.1	364.7	346.4	328.1	310.4	293.8	278.3	263.5	257.2	250.9
147.5°	388.7	374.4	358.4	342.9	326.4	310.9	296.1	282.3	268.1	262.4	256.6
150°	377.2	365.8	352.6	338.9	324.6	310.9	297.8	285.2	272.6	267.2	261.8
152.5°	367.5	357.2	346.4	334.4	321.8	309.8	298.9	287.5	276.6	271.8	266.9
155°	357.8	349.2	340.1	329.8	318.9	308.6	299.5	289.8	280.1	275.8	271.5
157.5°	348.6	341.2	333.2	325.2	316.1	307.5	299.5	291.5	282.9	279.5	276.1
160°	339.5	333.2	326.9	320.1	312.6	305.8	299.5	292.6	285.8	282.6	279.5
162.5°	330.4	325.8	320.6	315.5	309.2	304.1	299.5	293.8	287.5	285.2	282.9
165°	322.4	318.4	314.9	310.4	305.8	301.8	298.4	293.8	288.6	286.9	285.2
167.5°	315.5	312.1	309.2	305.8	302.4	299.5	297.2	293.8	289.8	288.4	286.9
170°	308.1	305.8	304.1	301.2	298.9	297.2	296.1	293.2	290.4	289.5	288.6
172.5°	301.8	300.6	299.5	297.2	295.5	294.9	294.9	292.6	290.9	290.4	289.8
175°	297.2	296.1	295.5	294.4	293.2	293.2	293.8	292.1	290.9	290.9	290.9
177.5°	293.2	293.2	292.6	292.1	291.5	291.5	292.6	291.5	290.9	290.9	290.9
180°	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9	290.9

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1290.5	1290.5	1290.5	1290.5
2.5°	1255.2	1265.9	1275.5	1290.5
5°	1227.4	1242.4	1262.7	1285.1
7.5°	1195.3	1218.9	1245.6	1276.6
10°	1165.4	1192.1	1226.3	1263.8
12.5°	1134.4	1166.5	1203.9	1244.5
15°	1099.1	1131.2	1172.9	1227.4
17.5°	1067.0	1105.5	1150.4	1208.2
20°	1029.6	1066.0	1115.1	1181.4
22.5°	996.5	1038.2	1092.7	1150.4
25°	960.1	996.5	1051.0	1120.5
27.5°	923.8	968.7	1021.1	1088.4
30°	888.5	925.9	982.6	1053.1
32.5°	850.0	894.9	947.3	1013.6
35°	808.3	851.1	900.2	971.9
37.5°	770.9	812.6	862.8	925.9
40°	729.2	773.0	819.0	882.1
42.5°	688.5	728.1	774.1	831.8
45°	649.0	683.2	724.9	775.1
47.5°	608.4	637.2	675.7	720.6
50°	564.5	595.5	624.4	661.8
52.5°	523.9	550.6	574.1	605.1
55°	484.3	502.5	521.8	545.3
57.5°	442.6	456.5	470.4	495.0
60°	400.9	413.8	421.3	437.3
62.5°	360.3	365.7	375.3	384.9
65°	315.4	322.9	328.2	340.0
67.5°	274.8	278.0	283.3	290.8
70°	232.0	239.5	241.6	247.0
72.5°	195.7	198.9	201.0	202.1
75°	155.0	158.2	160.4	166.8
77.5°	121.9	120.8	125.1	126.2
80°	89.8	86.6	87.7	91.9
82.5°	58.8	59.9	58.8	58.8
85°	36.4	35.3	33.1	34.2
87.5°	16.0	16.0	15.0	15.0
90°	4.0	3.4	1.7	0.6
92.5°	26.3	17.7	11.4	8.0
95°	33.7	26.3	20.6	18.9
97.5°	43.4	36.6	31.4	31.4
100°	54.3	47.4	43.4	43.4
102.5°	65.7	59.4	56.0	54.9
105°	78.3	71.4	68.6	66.9
107.5°	91.4	84.0	81.2	80.0
110°	104.0	97.2	94.3	93.2

TEST NUMBER: P1001900

CATALOG NUMBER: SA4XXDIP-B795D590UB30-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	116.6	110.3	106.9	105.7
115°	129.2	123.5	119.5	117.7
117.5°	141.7	135.5	132.0	130.3
120°	154.3	148.0	144.0	142.9
122.5°	165.2	159.5	155.5	154.3
125°	176.0	169.8	166.3	164.0
127.5°	185.8	178.9	174.9	173.2
130°	196.0	187.5	182.9	180.6
132.5°	204.0	196.0	189.8	188.0
135°	212.6	202.9	197.2	194.9
137.5°	219.5	210.3	204.0	201.8
140°	226.9	217.2	210.9	209.2
142.5°	233.8	224.6	218.9	217.2
145°	240.1	232.1	226.3	224.6
147.5°	247.5	238.9	233.8	233.2
150°	253.2	246.3	241.8	241.2
152.5°	259.5	253.2	248.6	248.6
155°	265.2	259.5	256.1	255.5
157.5°	270.3	265.8	262.3	262.3
160°	274.9	270.9	268.6	268.6
162.5°	278.9	275.5	273.8	274.3
165°	282.3	279.5	278.3	278.3
167.5°	285.2	282.9	282.3	282.9
170°	287.5	285.8	285.2	285.8
172.5°	289.2	288.1	288.1	288.6
175°	290.4	289.8	289.8	290.4
177.5°	290.9	290.4	290.9	291.5
180°	290.9	290.9	290.9	290.9

(END OF REPORT)