

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001915

Luminaire Tested: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001915
REPORT IS A COMBINATION OF REPORTS P996540 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5573.3 lumens
Efficiency: N/A
Efficacy: 108.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001915

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001915

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	33	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21
9	52	39	32	27	49	37	30	25	33	28	23	30	25	21	26	22	19
10	48	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10929	10929	10929
5°	10938	10615	10627
10°	10845	10320	10247
15°	10690	9969	9820
20°	10491	9591	9376
25°	10268	9190	8898
30°	9998	8757	8374
35°	9719	8314	7867
40°	9427	7837	7328
45°	9122	7359	6824
50°	8785	6895	6266
55°	8417	6353	5711
60°	8041	5760	5134
65°	7611	5148	4484
70°	7117	4409	3786
75°	6374	3555	3032
80°	5433	2570	2133
85°	4221	1430	1149

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9122 cd/sqm

TEST NUMBER: P1001915

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	2.3
10°-20°	355.9	6.4
20°-30°	523.8	9.4
30°-40°	608.9	10.9
40°-50°	608.8	10.9
50°-60°	532.5	9.6
60°-70°	395.3	7.1
70°-80°	224.3	4.0
80°-90°	65.4	1.2
90°-100°	217.0	3.9
100°-110°	441.4	7.9
110°-120°	393.4	7.1
120°-130°	330.5	5.9
130°-140°	275.8	4.9
140°-150°	210.6	3.8
150°-160°	148.0	2.7
160°-170°	87.1	1.6
170°-180°	28.3	0.5
0°-30°	1006.0	18.1
0°-40°	1614.9	29.0
0°-60°	2756.1	49.5
0°-90°	3441.1	61.7
90°-120°	1051.9	18.9
90°-150°	1868.7	33.5
90°-180°	2132.0	38.3
0°-180°	5573.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1340	1340	1340	1340	1340	
5°	1339	1335	1323	1335	1333	127
15°	1275	1270	1254	1261	1258	359
25°	1154	1147	1132	1133	1129	531
35°	993	986	971	963	958	621
45°	811	803	786	774	771	625
55°	613	610	595	582	576	549
65°	416	410	400	389	383	411
75°	221	216	210	206	205	235
85°	58	58	56	56	55	62
90°	1	5	10	12	12	5
95°	19	60	468	232	140	21
105°	67	97	376	811	808	72
115°	118	148	336	645	775	117
125°	165	196	334	549	619	147
135°	196	233	331	487	553	151
145°	226	258	330	411	452	142
155°	257	277	320	363	378	118
165°	280	288	307	325	330	79
175°	292	292	294	298	297	28
180°	292	292	292	292	292	

TEST NUMBER: P1001915

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1340.2	1340.2	1340.2	1340.2	1340.2
2.5°	1344.5	1341.3	1329.5	1340.2	1339.2
5°	1339.2	1334.9	1323.1	1334.9	1332.7
7.5°	1329.5	1325.2	1312.3	1322.0	1320.9
10°	1315.5	1311.2	1297.3	1305.9	1303.7
12.5°	1297.3	1293.0	1278.0	1287.6	1284.4
15°	1274.7	1270.4	1254.3	1260.8	1257.6
17.5°	1249.0	1243.6	1228.6	1232.9	1230.7
20°	1220.0	1214.6	1198.5	1201.7	1199.6
22.5°	1188.8	1181.3	1165.2	1171.6	1167.3
25°	1154.5	1146.9	1131.9	1133.0	1128.7
27.5°	1115.8	1108.3	1094.3	1092.2	1086.8
30°	1077.1	1068.5	1054.6	1050.3	1044.9
32.5°	1036.3	1028.8	1013.8	1008.4	1003.0
35°	993.4	985.9	970.8	963.3	957.9
37.5°	948.3	941.8	925.7	918.2	910.7
40°	904.2	895.6	879.5	868.8	863.4
42.5°	857.0	852.7	834.4	821.5	818.3
45°	810.8	803.3	786.1	774.3	771.1
47.5°	762.5	757.1	741.0	728.1	719.5
50°	713.1	708.8	693.7	678.7	672.3
52.5°	664.8	659.4	643.3	630.4	621.8
55°	613.2	610.0	594.9	582.1	575.6
57.5°	564.9	561.7	546.6	533.7	527.3
60°	514.4	509.0	495.1	485.4	480.0
62.5°	465.0	460.7	445.7	437.1	431.7
65°	415.6	410.2	399.5	388.8	383.4
67.5°	365.1	360.8	350.1	339.4	338.3
70°	319.0	311.4	302.8	294.3	291.0
72.5°	269.6	262.0	255.6	249.1	245.9
75°	221.2	215.9	210.5	206.2	205.1
77.5°	174.0	171.8	166.5	165.4	162.2
80°	132.1	128.9	126.7	124.6	123.5
82.5°	91.3	90.2	90.2	89.1	88.1
85°	58.0	58.0	55.8	55.8	54.8
87.5°	27.9	26.8	25.8	25.8	25.8
90°	0.6	4.6	10.3	11.5	12.1
92.5°	8.0	44.2	225.0	74.4	52.2
95°	18.9	59.6	467.8	231.6	140.1
97.5°	31.6	66.0	500.5	473.0	336.4
100°	43.6	74.6	461.5	654.4	526.3
102.5°	55.1	84.9	412.7	768.0	691.6
105°	67.2	97.3	376.5	810.8	807.6
107.5°	80.4	109.9	353.0	797.8	862.7
110°	93.6	122.6	342.1	751.9	863.8

TEST NUMBER: P1001915

CATALOG NUMBER: SA4XXDIP-B795D590UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	106.2	135.2	336.9	695.7	830.0
115°	118.2	148.4	335.8	645.2	775.4
117.5°	130.9	160.8	335.2	605.6	722.1
120°	143.5	172.8	335.2	578.8	678.4
122.5°	155.0	184.6	334.6	561.4	644.0
125°	164.7	195.8	334.1	549.0	618.8
127.5°	173.9	206.0	332.9	537.2	602.7
130°	181.4	216.1	332.3	523.2	588.9
132.5°	188.8	224.8	331.8	506.5	573.4
135°	195.7	233.0	331.2	487.4	553.3
137.5°	202.6	240.2	331.2	466.6	529.8
140°	210.1	246.8	330.6	446.6	504.0
142.5°	218.1	252.8	330.6	427.9	476.4
145°	225.6	258.3	329.5	411.0	451.7
147.5°	234.2	263.4	327.7	396.9	428.8
150°	242.2	268.4	326.0	384.0	409.8
152.5°	249.7	272.9	323.2	373.1	392.6
155°	256.6	277.0	320.3	362.8	378.3
157.5°	263.5	280.6	317.4	353.0	365.1
160°	269.8	283.8	314.0	343.2	353.0
162.5°	275.5	286.4	310.5	333.8	341.5
165°	279.5	288.2	307.1	325.2	330.0
167.5°	284.1	289.6	303.6	317.7	320.9
170°	287.0	290.8	300.2	310.2	312.2
172.5°	289.9	291.6	296.7	303.6	303.6
175°	291.6	292.2	294.5	298.5	297.3
177.5°	292.7	292.2	292.7	294.8	292.7
180°	292.2	292.2	292.2	292.2	292.2

(END OF REPORT)