

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008301

Luminaire Tested: S122RDIP-B1005D1080UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008301
REPORT IS A COMBINATION OF REPORTS P987831 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D1080UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7831.0 lumens
Efficiency: N/A
Efficacy: 81.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008301

CATALOG NUMBER: S122RDIP-B1005D1080UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008301

CATALOG NUMBER: S122RDIP-B1005D1080UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44			39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	39	38			33
3	81	72	65	60	74	66	60	55	56	51	48	46	43	40	37	35	33			28
4	74	64	56	51	68	59	53	47	50	45	41	41	38	35	33	31	29			25
5	68	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25			22
6	63	52	44	38	58	48	41	36	40	35	31	34	30	27	27	25	22			19
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20			17
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18			16
9	51	39	31	27	46	36	30	25	31	26	22	26	22	19	21	19	16			14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15			13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26984	26984	26984
5°	27028	25673	25482
10°	26762	24349	23545
15°	26394	22786	21338
20°	25908	21009	19029
25°	25410	19186	16916
30°	24739	17410	14609
35°	24083	15619	12627
40°	23419	13860	10586
45°	22642	12045	8806
50°	21840	10295	7169
55°	21005	8545	5692
60°	20037	6834	4306
65°	18919	5209	3501
70°	17570	3780	2785
75°	15881	2882	2126
80°	13429	1953	1427
85°	9365	893	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22642 cd/sqm

TEST NUMBER: P1008301

CATALOG NUMBER: S122RDIP-B1005D1080UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.8	2.0
10°-20°	438.6	5.6
20°-30°	615.8	7.9
30°-40°	671.2	8.6
40°-50°	616.9	7.9
50°-60°	484.5	6.2
60°-70°	315.4	4.0
70°-80°	162.4	2.1
80°-90°	44.0	0.6
90°-100°	48.6	0.6
100°-110°	181.2	2.3
110°-120°	480.7	6.1
120°-130°	797.2	10.2
130°-140°	846.8	10.8
140°-150°	787.0	10.1
150°-160°	632.7	8.1
160°-170°	407.7	5.2
170°-180°	140.3	1.8
0°-30°	1214.2	15.5
0°-40°	1885.4	24.1
0°-60°	2986.8	38.1
0°-90°	3508.6	44.8
90°-120°	710.5	9.1
90°-150°	3141.6	40.1
90°-180°	4322.0	55.2
0°-180°	7831.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1705	1697	1677	1691	1686	162
15°	1621	1604	1552	1523	1507	457
25°	1472	1422	1321	1257	1234	677
35°	1268	1190	1054	956	923	794
45°	1037	933	771	662	625	801
55°	788	668	501	409	380	704
65°	532	407	268	216	211	528
75°	284	176	123	113	111	300
85°	66	34	29	29	29	76
90°	1	13	21	27	29	7
95°	69	34	42	47	46	82
105°	324	356	65	77	81	347
115°	613	632	658	164	88	604
125°	867	881	902	909	912	774
135°	1073	1090	1100	1111	1108	829
145°	1245	1244	1262	1270	1264	779
155°	1371	1361	1374	1380	1372	632
165°	1444	1438	1441	1449	1441	408
175°	1478	1470	1472	1480	1469	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1008301

CATALOG NUMBER: S122RDIP-B1005D1080UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1704.7	1704.7	1704.7	1704.7	1704.7
2.5°	1712.4	1704.7	1687.8	1703.2	1700.1
5°	1704.7	1697.0	1677.0	1690.8	1686.2
7.5°	1690.8	1681.6	1660.0	1666.2	1658.4
10°	1672.3	1661.5	1630.7	1626.1	1616.8
12.5°	1649.2	1635.3	1593.7	1584.4	1567.4
15°	1621.4	1604.5	1552.0	1522.7	1507.3
17.5°	1589.0	1564.3	1499.5	1465.6	1440.9
20°	1552.0	1521.1	1444.0	1405.4	1371.5
22.5°	1511.9	1476.4	1386.9	1334.5	1311.3
25°	1471.8	1422.4	1320.6	1257.3	1234.2
27.5°	1424.0	1371.5	1258.9	1186.4	1150.9
30°	1373.0	1314.4	1191.0	1112.3	1070.7
32.5°	1323.7	1252.7	1126.2	1033.6	995.1
35°	1268.1	1189.5	1053.7	956.5	922.6
37.5°	1214.1	1129.3	985.8	879.4	840.8
40°	1157.1	1064.5	914.8	805.3	765.2
42.5°	1098.4	999.7	843.9	729.7	691.1
45°	1036.7	933.4	771.4	661.8	624.8
47.5°	978.1	868.6	701.9	592.4	558.5
50°	913.3	803.8	634.1	527.6	495.2
52.5°	850.1	734.3	569.3	467.5	438.1
55°	788.3	668.0	501.4	408.8	379.5
57.5°	725.1	601.7	441.2	354.8	330.1
60°	660.3	536.9	378.0	299.3	274.6
62.5°	597.0	473.6	324.0	249.9	237.6
65°	532.2	407.3	268.4	216.0	211.4
67.5°	470.5	345.6	216.0	189.8	185.1
70°	405.7	285.4	179.0	163.5	157.4
72.5°	344.0	229.9	149.6	137.3	134.2
75°	283.9	175.9	123.4	112.6	111.1
77.5°	223.7	125.0	97.2	91.0	87.9
80°	168.2	89.5	74.1	67.9	67.9
82.5°	117.2	60.2	50.9	47.8	47.8
85°	66.3	33.9	29.3	29.3	29.3
87.5°	24.7	12.3	12.3	10.8	10.8
90°	1.1	12.8	21.3	26.7	28.8
92.5°	26.7	22.4	25.6	27.7	28.8
95°	69.3	34.1	41.6	46.9	45.9
97.5°	124.8	37.3	54.4	57.6	58.7
100°	188.8	42.7	60.8	69.3	71.5
102.5°	259.2	257.1	62.9	74.7	77.9
105°	324.3	356.3	65.1	76.8	81.1
107.5°	400.1	426.7	67.2	78.9	83.2
110°	472.6	495.0	186.7	80.0	84.3

TEST NUMBER: P1008301

CATALOG NUMBER: S122RDIP-B1005D1080UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	540.9	560.1	542.0	82.1	85.3
115°	613.4	631.6	658.2	164.3	87.5
117.5°	676.4	697.7	715.9	563.3	283.8
120°	746.8	762.8	782.0	794.8	650.8
122.5°	806.5	823.6	844.9	851.4	852.4
125°	867.4	881.2	901.5	909.0	912.2
127.5°	922.8	937.8	953.8	964.4	965.5
130°	975.1	992.2	1003.9	1015.6	1014.6
132.5°	1028.4	1042.3	1054.1	1063.7	1062.6
135°	1073.3	1090.3	1099.9	1110.6	1108.5
137.5°	1120.2	1133.0	1143.7	1154.3	1151.1
140°	1166.1	1174.6	1186.3	1195.9	1190.6
142.5°	1204.5	1211.9	1225.8	1234.4	1229.0
145°	1245.0	1244.0	1262.1	1269.6	1264.2
147.5°	1280.2	1277.0	1295.2	1300.5	1296.2
150°	1314.4	1306.9	1324.0	1330.4	1325.0
152.5°	1343.2	1334.6	1350.6	1357.0	1349.6
155°	1370.9	1361.3	1374.1	1380.5	1372.0
157.5°	1393.3	1384.8	1394.4	1401.8	1393.3
160°	1412.5	1406.1	1412.5	1418.9	1411.4
162.5°	1429.6	1423.2	1428.5	1436.0	1426.4
165°	1444.5	1438.1	1441.3	1448.8	1441.3
167.5°	1456.3	1449.9	1453.1	1460.5	1450.9
170°	1465.9	1459.5	1461.6	1469.1	1459.5
172.5°	1472.3	1465.9	1468.0	1475.5	1465.9
175°	1477.6	1470.1	1472.3	1479.7	1469.1
177.5°	1479.7	1472.3	1473.3	1480.8	1471.2
180°	1474.4	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)