

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001923

Luminaire Tested: SA4XXDIP-B795D590UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001923
REPORT IS A COMBINATION OF REPORTS P996548 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D590UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5446.0 lumens
Efficiency: N/A
Efficacy: 106.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 51.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001923

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001923

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	79	79	79	68	68	68
1	101	96	92	89	94	90	87	84	79	77	74	69	67	65	60	58	57
2	92	84	78	72	86	79	73	69	69	65	61	61	57	55	53	50	48
3	84	74	66	60	78	69	63	57	61	56	52	54	50	46	47	44	41
4	76	65	57	51	71	62	54	49	54	49	44	48	43	40	42	38	35
5	70	58	50	44	66	55	48	42	49	43	38	43	38	34	38	34	31
6	65	52	44	38	61	50	42	37	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	37	31	26	32	28	24	29	25	22
9	52	39	32	27	49	37	30	26	34	28	24	30	25	22	26	22	20
10	49	36	29	24	46	34	28	23	31	25	21	28	23	20	25	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001923

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.3
10°-20°	352.4	6.5
20°-30°	518.6	9.5
30°-40°	602.8	11.1
40°-50°	602.8	11.1
50°-60°	527.2	9.7
60°-70°	391.4	7.2
70°-80°	222.1	4.1
80°-90°	65.2	1.2
90°-100°	47.9	0.9
100°-110°	143.4	2.6
110°-120°	243.7	4.5
120°-130°	321.4	5.9
130°-140°	360.9	6.6
140°-150°	354.8	6.5
150°-160°	298.4	5.5
160°-170°	198.5	3.6
170°-180°	69.5	1.3
0°-30°	996.1	18.3
0°-40°	1598.9	29.4
0°-60°	2728.9	50.1
0°-90°	3407.6	62.6
90°-120°	435.0	8.0
90°-150°	1472.0	27.0
90°-180°	2038.0	37.4
0°-180°	5446.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	2	8	12	16	17	6
95°	34	39	43	45	45	37
105°	132	133	135	137	139	140
115°	248	248	247	246	246	244
125°	361	361	360	359	358	322
135°	465	469	469	468	466	360
145°	565	568	568	568	566	354
155°	648	648	647	649	647	298
165°	705	703	702	706	703	199
175°	734	731	730	734	730	70
180°	735	735	735	735	735	

TEST NUMBER: P1001923

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	1.7	8.0	12.5	15.9	17.0
92.5°	14.8	22.2	25.0	26.7	27.3
95°	34.1	39.2	43.2	44.9	44.9
97.5°	54.5	59.1	63.6	65.9	65.9
100°	79.5	81.8	86.9	88.1	88.1
102.5°	105.7	106.3	110.8	112.5	113.1
105°	132.4	133.0	135.2	136.9	138.6
107.5°	160.2	160.8	161.4	163.6	163.1
110°	188.6	189.8	189.2	188.1	189.8



TEST NUMBER: P1001923

CATALOG NUMBER: SA4XXDIP-B795D590UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	218.2	218.2	217.0	217.0	217.0
115°	247.7	247.7	246.6	246.0	245.5
117.5°	275.6	275.6	275.0	273.3	271.6
120°	303.4	305.7	304.0	301.1	302.3
122.5°	332.4	333.0	332.4	330.7	327.8
125°	360.8	360.8	360.2	359.1	358.0
127.5°	386.4	388.1	386.9	385.8	385.2
130°	413.6	415.3	415.3	414.2	411.9
132.5°	441.5	442.6	442.0	440.9	440.3
135°	465.3	468.8	468.8	467.6	465.9
137.5°	492.1	493.8	494.9	493.2	493.8
140°	518.8	519.9	519.9	519.3	518.8
142.5°	543.2	544.3	543.8	543.8	543.8
145°	565.3	567.6	568.2	567.6	565.9
147.5°	588.1	590.9	590.3	589.8	589.2
150°	608.5	610.8	610.8	610.8	610.2
152.5°	627.8	629.0	629.6	631.3	629.6
155°	647.7	647.7	647.2	649.4	647.2
157.5°	664.8	663.6	663.6	665.3	663.6
160°	679.6	679.0	678.4	680.1	677.3
162.5°	693.2	691.5	690.9	694.3	691.5
165°	705.1	703.4	702.3	705.7	703.4
167.5°	714.8	712.5	712.5	715.9	712.5
170°	722.7	719.9	720.5	723.9	719.9
172.5°	728.4	726.1	726.1	730.1	726.1
175°	733.5	730.7	730.1	734.1	730.1
177.5°	735.8	733.0	733.0	736.9	732.4
180°	734.7	734.7	734.7	734.7	734.7

(END OF REPORT)