

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008339

Luminaire Tested: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008339
REPORT IS A COMBINATION OF REPORTS P987989 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7094.0 lumens
Efficiency: N/A
Efficacy: 79.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008339

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008339

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47			42
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41			36
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35			31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22			19
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	19			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	18	21	18	16			14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26631	26631	26631
5°	26675	25336	25148
10°	26411	24030	23237
15°	26047	22487	21058
20°	25567	20734	18779
25°	25077	18934	16694
30°	24414	17182	14417
35°	23768	15415	12462
40°	23111	13678	10448
45°	22344	11888	8691
50°	21553	10159	7075
55°	20731	8433	5617
60°	19773	6744	4250
65°	18674	5141	3455
70°	17340	3730	2747
75°	15669	2845	2098
80°	13253	1926	1409
85°	9252	881	680

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22344 cd/sqm

TEST NUMBER: P1008339

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	157.7	2.2
10°-20°	432.8	6.1
20°-30°	607.7	8.6
30°-40°	662.4	9.3
40°-50°	608.8	8.6
50°-60°	478.1	6.7
60°-70°	311.2	4.4
70°-80°	160.2	2.3
80°-90°	43.1	0.6
90°-100°	40.9	0.6
100°-110°	152.3	2.1
110°-120°	403.9	5.7
120°-130°	669.8	9.4
130°-140°	711.5	10.0
140°-150°	661.3	9.3
150°-160°	531.6	7.5
160°-170°	342.6	4.8
170°-180°	117.9	1.7
0°-30°	1198.2	16.9
0°-40°	1860.7	26.2
0°-60°	2947.6	41.6
0°-90°	3462.2	48.8
90°-120°	597.0	8.4
90°-150°	2639.6	37.2
90°-180°	3632.0	51.2
0°-180°	7094.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1682	1682	1682	1682	1682	
5°	1682	1675	1655	1669	1664	160
15°	1600	1583	1532	1503	1488	451
25°	1452	1404	1303	1241	1218	668
35°	1252	1174	1040	944	910	783
45°	1023	921	761	653	617	790
55°	778	659	495	404	374	695
65°	525	402	265	213	209	521
75°	280	174	122	111	110	296
85°	66	34	29	29	29	75
90°	1	11	18	22	24	7
95°	58	29	35	39	38	69
105°	272	299	55	64	68	291
115°	515	531	553	138	74	507
125°	729	740	758	764	766	650
135°	902	916	924	933	931	697
145°	1046	1045	1060	1067	1062	654
155°	1152	1144	1155	1160	1153	531
165°	1214	1208	1211	1217	1211	343
175°	1242	1235	1237	1243	1234	118
180°	1239	1239	1239	1239	1239	

TEST NUMBER: P1008339

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1682.4	1682.4	1682.4	1682.4	1682.4
2.5°	1690.0	1682.4	1665.6	1680.8	1677.8
5°	1682.4	1674.8	1655.0	1668.7	1664.1
7.5°	1668.7	1659.5	1638.2	1644.3	1636.7
10°	1650.4	1639.7	1609.3	1604.7	1595.6
12.5°	1627.6	1613.9	1572.7	1563.6	1546.9
15°	1600.1	1583.4	1531.6	1502.7	1487.5
17.5°	1568.2	1543.8	1479.9	1446.4	1422.0
20°	1531.6	1501.2	1425.1	1387.0	1353.5
22.5°	1492.1	1457.0	1368.7	1317.0	1294.1
25°	1452.5	1403.7	1303.3	1240.8	1218.0
27.5°	1405.3	1353.5	1242.4	1170.8	1135.8
30°	1355.0	1297.2	1175.4	1097.7	1056.6
32.5°	1306.3	1236.3	1111.4	1020.1	982.0
35°	1251.5	1173.8	1039.9	944.0	910.5
37.5°	1198.2	1114.5	972.9	867.8	829.8
40°	1141.9	1050.5	902.8	794.7	755.2
42.5°	1084.0	986.6	832.8	720.1	682.1
45°	1023.1	921.1	761.3	653.2	616.6
47.5°	965.3	857.2	692.7	584.6	551.1
50°	901.3	793.2	625.7	520.7	488.7
52.5°	838.9	724.7	561.8	461.3	432.4
55°	778.0	659.2	494.8	403.5	374.5
57.5°	715.6	593.8	435.4	350.2	325.8
60°	651.6	529.8	373.0	295.4	271.0
62.5°	589.2	467.4	319.7	246.6	234.5
65°	525.3	401.9	264.9	213.2	208.6
67.5°	464.4	341.0	213.2	187.3	182.7
70°	400.4	281.7	176.6	161.4	155.3
72.5°	339.5	226.9	147.7	135.5	132.5
75°	280.1	173.6	121.8	111.1	109.6
77.5°	220.8	123.3	95.9	89.8	86.8
80°	166.0	88.3	73.1	67.0	67.0
82.5°	115.7	59.4	50.2	47.2	47.2
85°	65.5	33.5	28.9	28.9	28.9
87.5°	24.4	12.2	12.2	10.7	10.7
90°	0.9	10.8	17.9	22.4	24.2
92.5°	22.4	18.8	21.5	23.3	24.2
95°	58.3	28.7	35.0	39.4	38.5
97.5°	104.9	31.4	45.7	48.4	49.3
100°	158.7	35.9	51.1	58.3	60.1
102.5°	217.8	216.0	52.9	62.7	65.4
105°	272.5	299.4	54.7	64.5	68.1
107.5°	336.2	358.6	56.5	66.3	69.9
110°	397.1	415.9	156.9	67.2	70.8

TEST NUMBER: P1008339

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	454.5	470.6	455.4	69.0	71.7
115°	515.4	530.7	553.1	138.0	73.5
117.5°	568.3	586.2	601.5	473.3	238.4
120°	627.5	640.9	657.1	667.8	546.8
122.5°	677.7	692.0	710.0	715.3	716.2
125°	728.8	740.4	757.5	763.7	766.4
127.5°	775.4	787.9	801.4	810.4	811.2
130°	819.3	833.7	843.5	853.4	852.5
132.5°	864.1	875.8	885.6	893.7	892.8
135°	901.8	916.1	924.2	933.2	931.4
137.5°	941.2	952.0	960.9	969.9	967.2
140°	979.8	986.9	996.8	1004.9	1000.4
142.5°	1012.0	1018.3	1030.0	1037.1	1032.7
145°	1046.1	1045.2	1060.4	1066.7	1062.2
147.5°	1075.7	1073.0	1088.2	1092.7	1089.1
150°	1104.4	1098.1	1112.4	1117.8	1113.3
152.5°	1128.6	1121.4	1134.8	1140.2	1134.0
155°	1151.9	1143.8	1154.6	1159.9	1152.8
157.5°	1170.7	1163.5	1171.6	1177.9	1170.7
160°	1186.8	1181.5	1186.8	1192.2	1185.9
162.5°	1201.2	1195.8	1200.3	1206.6	1198.5
165°	1213.7	1208.4	1211.0	1217.3	1211.0
167.5°	1223.6	1218.2	1220.9	1227.2	1219.1
170°	1231.7	1226.3	1228.1	1234.3	1226.3
172.5°	1237.0	1231.7	1233.5	1239.7	1231.7
175°	1241.5	1235.2	1237.0	1243.3	1234.3
177.5°	1243.3	1237.0	1237.9	1244.2	1236.1
180°	1238.8	1238.8	1238.8	1238.8	1238.8

(END OF REPORT)