

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008341

Luminaire Tested: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008341
REPORT IS A COMBINATION OF REPORTS P987991 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7187.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008341

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008341

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	98	94	90	87	90	87	83	81	73	71	69	61	59	58	49	48	47			42
2	90	82	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41			36
3	82	73	66	60	75	68	61	56	57	53	49	48	45	42	39	37	35			31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31			27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27			24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	29	26	24			21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22			19
8	55	43	35	30	51	40	33	29	35	29	26	30	26	22	25	22	19			17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18			16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	18	21	18	16			14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	26984	26984	26984
5°	27028	25673	25482
10°	26762	24349	23545
15°	26394	22786	21338
20°	25908	21009	19029
25°	25410	19186	16916
30°	24739	17410	14609
35°	24083	15619	12627
40°	23419	13860	10586
45°	22642	12045	8806
50°	21840	10295	7169
55°	21005	8545	5692
60°	20037	6834	4306
65°	18919	5209	3501
70°	17570	3780	2785
75°	15881	2882	2126
80°	13429	1953	1427
85°	9365	893	689

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 22642 cd/sqm

TEST NUMBER: P1008341

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.8	2.2
10°-20°	438.6	6.1
20°-30°	615.8	8.6
30°-40°	671.2	9.3
40°-50°	616.9	8.6
50°-60°	484.5	6.7
60°-70°	315.4	4.4
70°-80°	162.4	2.3
80°-90°	43.7	0.6
90°-100°	41.4	0.6
100°-110°	154.2	2.1
110°-120°	409.1	5.7
120°-130°	678.5	9.4
130°-140°	720.7	10.0
140°-150°	669.9	9.3
150°-160°	538.5	7.5
160°-170°	347.0	4.8
170°-180°	119.4	1.7
0°-30°	1214.2	16.9
0°-40°	1885.4	26.2
0°-60°	2986.8	41.6
0°-90°	3508.2	48.8
90°-120°	604.7	8.4
90°-150°	2673.8	37.2
90°-180°	3679.0	51.2
0°-180°	7187.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1705	1697	1677	1691	1686	162
15°	1621	1604	1552	1523	1507	457
25°	1472	1422	1321	1257	1234	677
35°	1268	1190	1054	956	923	794
45°	1037	933	771	662	625	801
55°	788	668	501	409	380	704
65°	532	407	268	216	211	528
75°	284	176	123	113	111	300
85°	66	34	29	29	29	76
90°	1	11	18	23	24	7
95°	59	29	35	40	39	70
105°	276	303	55	65	69	295
115°	522	538	560	140	74	514
125°	738	750	767	774	776	658
135°	913	928	936	945	943	706
145°	1060	1059	1074	1080	1076	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1008341

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1704.7	1704.7	1704.7	1704.7	1704.7
2.5°	1712.4	1704.7	1687.8	1703.2	1700.1
5°	1704.7	1697.0	1677.0	1690.8	1686.2
7.5°	1690.8	1681.6	1660.0	1666.2	1658.4
10°	1672.3	1661.5	1630.7	1626.1	1616.8
12.5°	1649.2	1635.3	1593.7	1584.4	1567.4
15°	1621.4	1604.5	1552.0	1522.7	1507.3
17.5°	1589.0	1564.3	1499.5	1465.6	1440.9
20°	1552.0	1521.1	1444.0	1405.4	1371.5
22.5°	1511.9	1476.4	1386.9	1334.5	1311.3
25°	1471.8	1422.4	1320.6	1257.3	1234.2
27.5°	1424.0	1371.5	1258.9	1186.4	1150.9
30°	1373.0	1314.4	1191.0	1112.3	1070.7
32.5°	1323.7	1252.7	1126.2	1033.6	995.1
35°	1268.1	1189.5	1053.7	956.5	922.6
37.5°	1214.1	1129.3	985.8	879.4	840.8
40°	1157.1	1064.5	914.8	805.3	765.2
42.5°	1098.4	999.7	843.9	729.7	691.1
45°	1036.7	933.4	771.4	661.8	624.8
47.5°	978.1	868.6	701.9	592.4	558.5
50°	913.3	803.8	634.1	527.6	495.2
52.5°	850.1	734.3	569.3	467.5	438.1
55°	788.3	668.0	501.4	408.8	379.5
57.5°	725.1	601.7	441.2	354.8	330.1
60°	660.3	536.9	378.0	299.3	274.6
62.5°	597.0	473.6	324.0	249.9	237.6
65°	532.2	407.3	268.4	216.0	211.4
67.5°	470.5	345.6	216.0	189.8	185.1
70°	405.7	285.4	179.0	163.5	157.4
72.5°	344.0	229.9	149.6	137.3	134.2
75°	283.9	175.9	123.4	112.6	111.1
77.5°	223.7	125.0	97.2	91.0	87.9
80°	168.2	89.5	74.1	67.9	67.9
82.5°	117.2	60.2	50.9	47.8	47.8
85°	66.3	33.9	29.3	29.3	29.3
87.5°	24.7	12.3	12.3	10.8	10.8
90°	0.9	10.9	18.2	22.7	24.5
92.5°	22.7	19.1	21.8	23.6	24.5
95°	59.0	29.1	35.4	40.0	39.0
97.5°	106.2	31.8	46.3	49.0	49.9
100°	160.7	36.3	51.8	59.0	60.8
102.5°	220.6	218.8	53.6	63.6	66.3
105°	276.0	303.3	55.4	65.4	69.0
107.5°	340.5	363.2	57.2	67.2	70.8
110°	402.2	421.3	158.9	68.1	71.7



TEST NUMBER: P1008341

CATALOG NUMBER: S122RDIP-B1005D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.4	476.7	461.3	69.9	72.6
115°	522.1	537.5	560.2	139.8	74.5
117.5°	575.7	593.8	609.3	479.4	241.5
120°	635.6	649.2	665.6	676.5	553.9
122.5°	686.4	701.0	719.1	724.6	725.5
125°	738.2	750.0	767.3	773.6	776.3
127.5°	785.4	798.1	811.8	820.8	821.7
130°	829.9	844.4	854.4	864.4	863.5
132.5°	875.3	887.1	897.1	905.3	904.4
135°	913.4	928.0	936.1	945.2	943.4
137.5°	953.4	964.3	973.4	982.5	979.7
140°	992.4	999.7	1009.7	1017.9	1013.3
142.5°	1025.1	1031.5	1043.3	1050.6	1046.0
145°	1059.6	1058.7	1074.2	1080.5	1076.0
147.5°	1089.6	1086.9	1102.3	1106.9	1103.2
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)