

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001962

Luminaire Tested: SA4XXDIP-B795D810UB30-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001962
REPORT IS A COMBINATION OF REPORTS P996587 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB30-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5997.0 lumens
Efficiency: N/A
Efficacy: 105.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001962

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001962

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	72	69	66	59	57	56	48	47	46
2	88	80	73	68	81	74	68	63	62	58	54	52	48	46	42	40	38
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	31
4	73	61	53	47	67	57	50	44	48	43	38	40	36	32	33	29	27
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	26	23	20
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	19	16
9	49	36	29	24	45	34	27	22	29	23	20	25	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7788	7788	7788
5°	7809	7585	7599
10°	7758	7435	7414
15°	7686	7268	7206
20°	7578	7086	7005
25°	7457	6886	6787
30°	7325	6687	6565
35°	7177	6485	6367
40°	7059	6289	6162
45°	6882	6107	5982
50°	6732	5899	5791
55°	6577	5698	5572
60°	6336	5450	5365
65°	6071	5181	5115
70°	5749	4874	4828
75°	5300	4533	4554
80°	4796	4186	4267
85°	4126	3836	4035

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6882 cd/sqm

TEST NUMBER: P1001962

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.5	1.5
10°-20°	259.3	4.3
20°-30°	392.0	6.5
30°-40°	474.3	7.9
40°-50°	501.4	8.4
50°-60°	471.9	7.9
60°-70°	391.5	6.5
70°-80°	274.8	4.6
80°-90°	157.0	2.6
90°-100°	156.6	2.6
100°-110°	261.0	4.4
110°-120°	373.2	6.2
120°-130°	457.6	7.6
130°-140°	496.1	8.3
140°-150°	478.9	8.0
150°-160°	400.9	6.7
160°-170°	266.7	4.4
170°-180°	93.4	1.6
0°-30°	741.8	12.4
0°-40°	1216.0	20.3
0°-60°	2189.2	36.5
0°-90°	3012.6	50.2
90°-120°	790.8	13.2
90°-150°	2223.4	37.1
90°-180°	2984.0	49.8
0°-180°	5997.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	955	955	955	955	955	
5°	956	953	945	954	953	91
15°	916	918	914	924	923	258
25°	838	845	848	860	861	386
35°	734	746	757	772	775	459
45°	612	632	652	670	676	473
55°	479	502	534	555	562	427
65°	332	366	402	429	437	329
75°	184	224	268	298	308	195
85°	57	102	150	182	192	59
90°	19	71	123	158	168	15
95°	60	102	151	182	192	61
105°	188	210	252	281	292	200
115°	339	349	382	404	411	335
125°	489	488	514	533	538	436
135°	627	632	639	655	659	486
145°	761	763	763	769	771	476
155°	870	870	870	873	870	401
165°	947	945	944	948	945	267
175°	986	982	981	986	981	94
180°	987	987	987	987	987	

TEST NUMBER: P1001962

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	955.0	955.0	955.0	955.0	955.0
2.5°	959.3	956.1	947.5	955.0	953.9
5°	956.1	952.9	945.4	953.9	952.9
7.5°	949.7	947.5	941.1	950.7	949.7
10°	941.1	940.0	934.7	944.3	943.2
12.5°	929.3	929.3	926.1	934.7	934.7
15°	916.5	917.6	914.4	924.0	922.9
17.5°	899.4	902.6	901.5	911.2	910.1
20°	881.2	884.4	885.5	896.2	896.2
22.5°	860.9	865.2	867.3	878.0	880.1
25°	838.4	844.9	848.1	859.8	860.9
27.5°	813.8	823.5	827.7	838.4	839.5
30°	789.2	797.8	805.3	817.0	819.2
32.5°	762.5	773.2	781.8	795.7	797.8
35°	733.6	746.5	757.2	772.1	775.3
37.5°	704.8	719.7	732.6	747.5	750.7
40°	677.0	690.9	705.8	721.9	726.1
42.5°	644.9	660.9	679.1	697.3	700.5
45°	611.7	632.0	652.4	670.5	675.9
47.5°	580.7	601.0	624.5	642.7	649.1
50°	546.5	570.0	593.5	614.9	621.3
52.5°	512.3	535.8	563.6	585.0	591.4
55°	479.1	501.6	533.6	555.0	561.5
57.5°	441.7	469.5	500.5	526.2	531.5
60°	405.3	433.1	468.4	493.0	501.6
62.5°	370.0	401.0	436.3	460.9	469.5
65°	331.5	365.7	402.1	428.8	437.4
67.5°	295.2	331.5	370.0	396.8	405.3
70°	257.7	294.1	334.7	363.6	371.1
72.5°	221.4	258.8	302.6	330.5	339.0
75°	183.9	223.5	268.4	298.4	308.0
77.5°	148.7	190.4	237.4	267.4	278.1
80°	116.6	159.3	206.4	238.5	247.0
82.5°	84.5	129.4	176.5	209.6	219.2
85°	56.7	101.6	149.7	181.8	192.5
87.5°	35.3	79.1	126.2	157.2	166.8
90°	19.4	70.6	122.7	158.3	168.3
92.5°	35.8	83.3	133.1	165.3	174.6
95°	59.7	101.9	151.0	182.2	191.8
97.5°	86.1	123.2	173.2	204.1	213.7
100°	118.7	149.5	198.1	228.5	235.9
102.5°	153.8	178.1	224.8	254.9	264.2
105°	187.5	209.6	252.3	281.3	292.2
107.5°	224.9	243.9	282.0	311.9	318.6
110°	262.1	278.5	315.2	338.3	349.1

TEST NUMBER: P1001962

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	300.7	313.5	347.2	370.7	379.3
115°	339.3	348.9	381.6	404.4	411.1
117.5°	376.7	383.1	414.4	434.6	440.8
120°	413.0	419.3	448.0	465.6	475.6
122.5°	451.9	452.7	480.8	499.9	503.6
125°	489.1	488.0	513.9	532.8	537.7
127.5°	523.4	524.6	544.5	562.2	568.9
130°	559.0	560.2	577.3	595.0	598.4
132.5°	596.4	596.8	609.0	625.6	631.3
135°	627.4	631.9	639.4	655.0	659.2
137.5°	663.2	664.5	670.2	684.1	690.1
140°	699.1	699.6	700.6	713.8	718.4
142.5°	730.9	732.5	730.6	742.4	746.6
145°	760.7	762.7	763.4	769.1	771.1
147.5°	791.3	794.0	793.2	793.5	797.0
150°	818.7	820.7	820.7	820.7	819.9
152.5°	843.6	845.1	845.9	848.2	845.9
155°	870.3	870.3	869.5	872.6	869.5
157.5°	893.2	891.7	891.7	894.0	891.7
160°	913.1	912.3	911.5	913.8	910.0
162.5°	931.4	929.1	928.3	932.9	929.1
165°	947.4	945.1	943.6	948.2	945.1
167.5°	960.4	957.3	957.3	961.9	957.3
170°	971.1	967.3	968.0	972.6	967.3
172.5°	978.7	975.7	975.7	981.0	975.7
175°	985.6	981.8	981.0	986.4	981.0
177.5°	988.6	984.8	984.8	990.2	984.1
180°	987.1	987.1	987.1	987.1	987.1

(END OF REPORT)