

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008350

Luminaire Tested: S122RDIP-B290D1080UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008350
REPORT IS A COMBINATION OF REPORTS P988030 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D1080UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5312.0 lumens
Efficiency: N/A
Efficacy: 110.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008350

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008350

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28	19		
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	25	24	24	16		
2	83	76	70	66	73	67	63	59	51	48	45	36	34	32	22	21	20	14		
3	76	67	60	55	67	59	54	49	45	41	38	32	29	28	20	18	17	12		
4	69	59	52	46	61	53	46	42	40	36	32	28	26	24	18	16	15	10		
5	63	53	45	39	56	47	40	36	36	31	28	25	23	20	16	14	13	9		
6	58	47	39	34	51	42	35	31	32	28	24	23	20	18	14	13	12	8		
7	54	42	35	30	47	38	31	27	29	25	21	21	18	16	13	12	10	7		
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	10	9	7		
9	46	35	28	23	41	31	25	21	24	20	17	17	15	13	11	10	8	6		
10	43	32	25	20	38	28	23	19	22	18	15	16	13	11	10	9	8	6		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7736	7736	7736
5°	7748	7359	7305
10°	7672	6979	6750
15°	7566	6532	6117
20°	7427	6022	5454
25°	7284	5499	4849
30°	7092	4991	4187
35°	6903	4477	3620
40°	6713	3973	3034
45°	6491	3452	2524
50°	6261	2952	2056
55°	6022	2449	1632
60°	5744	1958	1234
65°	5425	1492	1004
70°	5037	1083	798
75°	4554	827	609
80°	3848	559	410
85°	2684	256	198

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6491 cd/sqm

TEST NUMBER: P1008350

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.8	0.9
10°-20°	125.7	2.4
20°-30°	176.5	3.3
30°-40°	192.4	3.6
40°-50°	176.8	3.3
50°-60°	138.9	2.6
60°-70°	90.4	1.7
70°-80°	46.5	0.9
80°-90°	14.5	0.3
90°-100°	48.4	0.9
100°-110°	180.5	3.4
110°-120°	478.7	9.0
120°-130°	793.9	14.9
130°-140°	843.3	15.9
140°-150°	783.8	14.8
150°-160°	630.1	11.9
160°-170°	406.0	7.6
170°-180°	139.7	2.6
0°-30°	348.0	6.6
0°-40°	540.4	10.2
0°-60°	856.2	16.1
0°-90°	1007.6	19.0
90°-120°	707.6	13.3
90°-150°	3128.5	58.9
90°-180°	4304.0	81.0
0°-180°	5312.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	489	489	489	489	489	
5°	489	486	481	485	483	46
15°	465	460	445	436	432	131
25°	422	408	378	360	354	194
35°	364	341	302	274	264	228
45°	297	268	221	190	179	230
55°	226	192	144	117	109	202
65°	153	117	77	62	61	151
75°	81	50	35	32	32	86
85°	19	10	8	8	8	22
90°	1	13	21	27	29	5
95°	69	34	41	47	46	82
105°	323	355	65	76	81	345
115°	611	629	656	164	87	601
125°	864	878	898	905	908	770
135°	1069	1086	1095	1106	1104	826
145°	1240	1239	1257	1264	1259	775
155°	1365	1356	1368	1375	1366	629
165°	1438	1432	1435	1443	1435	406
175°	1471	1464	1466	1474	1463	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P1008350

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	488.7	488.7	488.7	488.7	488.7
2.5°	490.9	488.7	483.8	488.2	487.3
5°	488.7	486.5	480.7	484.7	483.4
7.5°	484.7	482.0	475.8	477.6	475.4
10°	479.4	476.3	467.4	466.1	463.5
12.5°	472.7	468.8	456.8	454.2	449.3
15°	464.8	459.9	444.9	436.5	432.1
17.5°	455.5	448.4	429.8	420.1	413.0
20°	444.9	436.0	413.9	402.9	393.1
22.5°	433.4	423.2	397.6	382.5	375.9
25°	421.9	407.7	378.5	360.4	353.8
27.5°	408.2	393.1	360.9	340.1	329.9
30°	393.6	376.8	341.4	318.8	306.9
32.5°	379.4	359.1	322.8	296.3	285.2
35°	363.5	341.0	302.0	274.2	264.5
37.5°	348.0	323.7	282.6	252.1	241.0
40°	331.7	305.1	262.2	230.8	219.3
42.5°	314.9	286.6	241.9	209.2	198.1
45°	297.2	267.5	221.1	189.7	179.1
47.5°	280.4	249.0	201.2	169.8	160.1
50°	261.8	230.4	181.8	151.2	142.0
52.5°	243.7	210.5	163.2	134.0	125.6
55°	226.0	191.5	143.7	117.2	108.8
57.5°	207.8	172.5	126.5	101.7	94.6
60°	189.3	153.9	108.3	85.8	78.7
62.5°	171.1	135.8	92.9	71.6	68.1
65°	152.6	116.7	76.9	61.9	60.6
67.5°	134.9	99.1	61.9	54.4	53.1
70°	116.3	81.8	51.3	46.9	45.1
72.5°	98.6	65.9	42.9	39.4	38.5
75°	81.4	50.4	35.4	32.3	31.8
77.5°	64.1	35.8	27.9	26.1	25.2
80°	48.2	25.6	21.2	19.5	19.5
82.5°	33.6	17.2	14.6	13.7	13.7
85°	19.0	9.7	8.4	8.4	8.4
87.5°	7.1	3.5	3.5	3.1	3.1
90°	1.1	12.7	21.2	26.6	28.7
92.5°	26.6	22.3	25.5	27.6	28.7
95°	69.1	34.0	41.4	46.7	45.7
97.5°	124.3	37.2	54.2	57.4	58.4
100°	188.0	42.5	60.6	69.1	71.2
102.5°	258.2	256.0	62.7	74.4	77.6
105°	323.0	354.8	64.8	76.5	80.7
107.5°	398.4	425.0	66.9	78.6	82.9
110°	470.6	493.0	185.9	79.7	83.9

TEST NUMBER: P1008350

CATALOG NUMBER: S122RDIP-B290D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	538.6	557.8	539.7	81.8	85.0
115°	610.9	628.9	655.5	163.6	87.1
117.5°	673.6	694.8	712.9	561.0	282.6
120°	743.7	759.6	778.8	791.5	648.1
122.5°	803.2	820.2	841.4	847.8	848.9
125°	863.7	877.6	897.7	905.2	908.4
127.5°	919.0	933.9	949.8	960.4	961.5
130°	971.0	988.0	999.7	1011.4	1010.4
132.5°	1024.2	1038.0	1049.7	1059.2	1058.2
135°	1068.8	1085.8	1095.3	1106.0	1103.8
137.5°	1115.5	1128.3	1138.9	1149.5	1146.3
140°	1161.2	1169.7	1181.4	1191.0	1185.7
142.5°	1199.5	1206.9	1220.7	1229.2	1223.9
145°	1239.8	1238.8	1256.8	1264.3	1259.0
147.5°	1274.9	1271.7	1289.8	1295.1	1290.8
150°	1308.9	1301.5	1318.5	1324.8	1319.5
152.5°	1337.6	1329.1	1345.0	1351.4	1344.0
155°	1365.2	1355.6	1368.4	1374.8	1366.3
157.5°	1387.5	1379.0	1388.6	1396.0	1387.5
160°	1406.6	1400.3	1406.6	1413.0	1405.6
162.5°	1423.6	1417.3	1422.6	1430.0	1420.4
165°	1438.5	1432.1	1435.3	1442.8	1435.3
167.5°	1450.2	1443.8	1447.0	1454.4	1444.9
170°	1459.8	1453.4	1455.5	1462.9	1453.4
172.5°	1466.1	1459.8	1461.9	1469.3	1459.8
175°	1471.4	1464.0	1466.1	1473.6	1462.9
177.5°	1473.6	1466.1	1467.2	1474.6	1465.1
180°	1468.3	1468.3	1468.3	1468.3	1468.3

(END OF REPORT)