

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001966

Luminaire Tested: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001966
REPORT IS A COMBINATION OF REPORTS P996591 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F4
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6263.7 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001966

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1001966

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60
1	99	94	90	87	92	88	84	81	75	73	71	64	62	60	53	52	51
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	47	45	43
3	82	72	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	31
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	27
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	21
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10881	10881	10881
5°	10890	10568	10581
10°	10798	10275	10203
15°	10643	9926	9777
20°	10445	9549	9334
25°	10223	9150	8859
30°	9954	8719	8338
35°	9676	8278	7833
40°	9387	7803	7296
45°	9083	7327	6794
50°	8747	6865	6238
55°	8380	6326	5687
60°	8007	5735	5111
65°	7578	5126	4464
70°	7086	4390	3770
75°	6349	3540	3019
80°	5408	2559	2125
85°	4199	1425	1142

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9083 cd/sqm

TEST NUMBER: P1001966

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.8	2.0
10°-20°	354.3	5.7
20°-30°	521.5	8.3
30°-40°	606.2	9.7
40°-50°	606.2	9.7
50°-60°	530.2	8.5
60°-70°	393.6	6.3
70°-80°	223.3	3.6
80°-90°	65.4	1.0
90°-100°	288.8	4.6
100°-110°	587.3	9.4
110°-120°	523.5	8.4
120°-130°	439.8	7.0
130°-140°	367.0	5.9
140°-150°	280.3	4.5
150°-160°	197.0	3.1
160°-170°	115.9	1.8
170°-180°	37.7	0.6
0°-30°	1001.6	16.0
0°-40°	1607.8	25.7
0°-60°	2744.1	43.8
0°-90°	3426.5	54.7
90°-120°	1399.6	22.3
90°-150°	2486.6	39.7
90°-180°	2837.0	45.3
0°-180°	6263.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1334	1334	1334	1334	1334	
5°	1333	1329	1317	1329	1327	127
15°	1269	1265	1249	1255	1252	358
25°	1149	1142	1127	1128	1124	529
35°	989	982	967	959	954	618
45°	807	800	783	771	768	622
55°	610	607	592	580	573	547
65°	414	408	398	387	382	410
75°	220	215	210	205	204	234
85°	58	58	56	56	54	62
90°	1	6	14	15	16	5
95°	25	79	622	308	186	28
105°	89	129	501	1079	1075	95
115°	157	197	447	858	1032	156
125°	219	260	444	731	823	195
135°	260	310	441	648	736	201
145°	300	344	438	547	601	188
155°	341	369	426	483	503	157
165°	372	383	409	433	439	105
175°	388	389	392	397	396	37
180°	389	389	389	389	389	

TEST NUMBER: P1001966

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1334.4	1334.4	1334.4	1334.4	1334.4
2.5°	1338.7	1335.5	1323.7	1334.4	1333.3
5°	1333.3	1329.1	1317.3	1329.1	1326.9
7.5°	1323.7	1319.4	1306.6	1316.2	1315.2
10°	1309.8	1305.5	1291.6	1300.2	1298.0
12.5°	1291.6	1287.4	1272.4	1282.0	1278.8
15°	1269.2	1264.9	1248.9	1255.3	1252.1
17.5°	1243.5	1238.2	1223.2	1227.5	1225.3
20°	1214.6	1209.3	1193.3	1196.5	1194.3
22.5°	1183.6	1176.2	1160.1	1166.5	1162.3
25°	1149.4	1141.9	1127.0	1128.0	1123.8
27.5°	1110.9	1103.4	1089.5	1087.4	1082.1
30°	1072.4	1063.9	1050.0	1045.7	1040.4
32.5°	1031.8	1024.3	1009.4	1004.0	998.7
35°	989.0	981.6	966.6	959.1	953.8
37.5°	944.1	937.7	921.7	914.2	906.7
40°	900.3	891.7	875.7	865.0	859.7
42.5°	853.2	849.0	830.8	818.0	814.8
45°	807.3	799.8	782.7	770.9	767.7
47.5°	759.2	753.8	737.8	724.9	716.4
50°	710.0	705.7	690.7	675.8	669.3
52.5°	661.9	656.5	640.5	627.6	619.1
55°	610.5	607.3	592.4	579.5	573.1
57.5°	562.4	559.2	544.2	531.4	525.0
60°	512.2	506.8	492.9	483.3	477.9
62.5°	463.0	458.7	443.7	435.2	429.8
65°	413.8	408.4	397.8	387.1	381.7
67.5°	363.5	359.3	348.6	337.9	336.8
70°	317.6	310.1	301.5	293.0	289.8
72.5°	268.4	260.9	254.5	248.1	244.9
75°	220.3	214.9	209.6	205.3	204.2
77.5°	173.2	171.1	165.7	164.7	161.5
80°	131.5	128.3	126.2	124.0	123.0
82.5°	90.9	89.8	89.8	88.7	87.7
85°	57.7	57.7	55.6	55.6	54.5
87.5°	27.8	26.7	25.7	25.7	25.7
90°	0.8	6.1	13.7	15.3	16.0
92.5°	10.7	58.8	299.4	99.0	69.5
95°	25.2	79.4	622.5	308.2	186.4
97.5°	42.0	87.8	666.0	629.4	447.6
100°	58.0	99.3	614.1	870.8	700.4
102.5°	73.3	113.0	549.2	1022.0	920.4
105°	89.4	129.4	501.0	1078.8	1074.6
107.5°	106.9	146.2	469.7	1061.6	1148.0
110°	124.5	163.1	455.2	1000.6	1149.5

TEST NUMBER: P1001966

CATALOG NUMBER: SA4XXDIP-B795D810UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	141.3	179.9	448.3	925.7	1104.4
115°	157.3	197.4	446.8	858.5	1031.9
117.5°	174.1	213.9	446.0	805.8	960.8
120°	190.9	229.9	446.0	770.3	902.8
122.5°	206.2	245.6	445.3	747.0	857.0
125°	219.2	260.5	444.5	730.6	823.4
127.5°	231.4	274.2	443.0	714.9	802.0
130°	241.4	287.6	442.2	696.2	783.6
132.5°	251.3	299.0	441.5	674.0	763.0
135°	260.4	310.1	440.7	648.4	736.3
137.5°	269.6	319.6	440.7	621.0	705.0
140°	279.5	328.5	439.9	594.2	670.6
142.5°	290.2	336.4	439.9	569.4	633.9
145°	300.2	343.7	438.4	546.9	601.1
147.5°	311.6	350.5	436.1	528.2	570.5
150°	322.3	357.0	433.8	511.0	545.3
152.5°	332.2	363.2	430.0	496.4	522.4
155°	341.4	368.6	426.2	482.7	503.3
157.5°	350.6	373.5	422.4	469.7	485.8
160°	359.0	377.7	417.8	456.8	469.7
162.5°	366.6	381.2	413.2	444.2	454.4
165°	372.0	383.4	408.6	432.7	439.2
167.5°	378.1	385.3	404.0	422.8	427.0
170°	381.9	386.8	399.5	412.8	415.5
172.5°	385.7	388.0	394.9	404.0	404.0
175°	388.0	388.8	391.8	397.2	395.6
177.5°	389.5	388.8	389.5	392.2	389.5
180°	388.8	388.8	388.8	388.8	388.8

(END OF REPORT)