

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001971

Luminaire Tested: SA4XXDIP-B795D810UB35-4F0-XX-W2A-D1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001971
REPORT IS A COMBINATION OF REPORTS P996596 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB35-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6023.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001971

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001971

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	72	69	66	59	57	56	48	47	46
2	88	80	73	68	81	74	68	63	62	58	54	52	48	46	42	40	38
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	31
4	73	61	53	47	67	57	50	44	48	43	38	40	36	32	33	29	27
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	26	23	20
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	19	16
9	49	36	29	24	45	34	27	22	29	23	20	25	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7821	7821	7821
5°	7843	7617	7631
10°	7791	7467	7446
15°	7718	7299	7237
20°	7611	7116	7034
25°	7489	6915	6816
30°	7357	6715	6593
35°	7208	6512	6395
40°	7089	6317	6190
45°	6911	6133	6008
50°	6761	5924	5816
55°	6605	5723	5595
60°	6364	5473	5387
65°	6097	5203	5138
70°	5774	4896	4849
75°	5323	4553	4573
80°	4816	4204	4286
85°	4141	3854	4052

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6911 cd/sqm

TEST NUMBER: P1001971

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.9	1.5
10°-20°	260.4	4.3
20°-30°	393.7	6.5
30°-40°	476.3	7.9
40°-50°	503.5	8.4
50°-60°	473.9	7.9
60°-70°	393.2	6.5
70°-80°	276.0	4.6
80°-90°	157.7	2.6
90°-100°	157.2	2.6
100°-110°	262.1	4.4
110°-120°	374.8	6.2
120°-130°	459.6	7.6
130°-140°	498.3	8.3
140°-150°	481.0	8.0
150°-160°	402.7	6.7
160°-170°	267.9	4.4
170°-180°	93.8	1.6
0°-30°	744.9	12.4
0°-40°	1221.2	20.3
0°-60°	2198.6	36.5
0°-90°	3025.5	50.2
90°-120°	794.2	13.2
90°-150°	2233.1	37.1
90°-180°	2997.0	49.8
0°-180°	6023.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	959	959	959	959	959	
5°	960	957	949	958	957	91
15°	920	922	918	928	927	259
25°	842	848	852	864	865	388
35°	737	750	760	776	779	461
45°	614	635	655	673	679	475
55°	481	504	536	557	564	429
65°	333	367	404	431	439	330
75°	185	224	270	300	309	196
85°	57	102	150	183	193	59
90°	20	71	123	159	169	15
95°	60	102	152	183	193	61
105°	188	210	253	282	293	200
115°	341	350	383	406	413	337
125°	491	490	516	535	540	438
135°	630	635	642	658	662	488
145°	764	766	767	772	774	478
155°	874	874	873	876	873	402
165°	952	949	948	952	949	268
175°	990	986	985	991	985	94
180°	991	991	991	991	991	

TEST NUMBER: P1001971

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	959.1	959.1	959.1	959.1	959.1
2.5°	963.4	960.2	951.6	959.1	958.0
5°	960.2	957.0	949.4	958.0	957.0
7.5°	953.7	951.6	945.1	954.8	953.7
10°	945.1	944.1	938.7	948.4	947.3
12.5°	933.3	933.3	930.1	938.7	938.7
15°	920.4	921.5	918.3	928.0	926.9
17.5°	903.3	906.5	905.4	915.1	914.0
20°	885.0	888.2	889.3	900.0	900.0
22.5°	864.6	868.9	871.0	881.8	883.9
25°	842.0	848.5	851.7	863.5	864.6
27.5°	817.3	827.0	831.3	842.0	843.1
30°	792.6	801.2	808.7	820.6	822.7
32.5°	765.8	776.5	785.1	799.1	801.2
35°	736.8	749.7	760.4	775.5	778.7
37.5°	707.8	722.8	735.7	750.7	754.0
40°	679.9	693.8	708.9	725.0	729.3
42.5°	647.6	663.8	682.0	700.3	703.5
45°	614.3	634.8	655.2	673.4	678.8
47.5°	583.2	603.6	627.2	645.5	651.9
50°	548.8	572.5	596.1	617.6	624.0
52.5°	514.5	538.1	566.0	587.5	593.9
55°	481.2	503.7	535.9	557.4	563.9
57.5°	443.6	471.5	502.6	528.4	533.8
60°	407.1	435.0	470.4	495.1	503.7
62.5°	371.6	402.8	438.2	462.9	471.5
65°	332.9	367.3	403.8	430.7	439.3
67.5°	296.4	332.9	371.6	398.5	407.1
70°	258.8	295.4	336.2	365.2	372.7
72.5°	222.3	259.9	304.0	331.9	340.5
75°	184.7	224.5	269.6	299.7	309.3
77.5°	149.3	191.2	238.4	268.5	279.2
80°	117.1	160.0	207.3	239.5	248.1
82.5°	84.8	130.0	177.2	210.5	220.2
85°	56.9	102.0	150.4	182.6	193.3
87.5°	35.4	79.5	126.7	157.9	167.5
90°	19.5	70.8	123.2	159.0	169.1
92.5°	36.0	83.6	133.6	166.0	175.4
95°	60.0	102.3	151.7	183.0	192.7
97.5°	86.5	123.7	174.0	204.9	214.6
100°	119.1	150.1	198.9	229.5	237.0
102.5°	154.4	178.8	225.8	256.0	265.4
105°	188.4	210.5	253.4	282.5	293.4
107.5°	225.9	244.9	283.3	313.2	320.0
110°	263.2	279.7	316.5	339.7	350.6

TEST NUMBER: P1001971

CATALOG NUMBER: SA4XXDIP-B795D810UB35-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	301.9	314.8	348.7	372.4	381.0
115°	340.7	350.4	383.3	406.1	412.8
117.5°	378.3	384.8	416.2	436.5	442.8
120°	414.9	421.1	449.9	467.6	477.7
122.5°	454.0	454.7	483.0	502.1	505.8
125°	491.2	490.1	516.2	535.1	540.0
127.5°	525.7	526.9	546.9	564.6	571.5
130°	561.4	562.6	579.8	597.7	601.0
132.5°	599.0	599.4	611.6	628.3	634.0
135°	630.1	634.7	642.3	658.0	662.1
137.5°	666.1	667.4	673.3	687.1	693.2
140°	702.2	702.7	703.7	716.9	721.6
142.5°	734.1	735.7	733.8	745.6	749.9
145°	764.0	766.0	766.8	772.4	774.4
147.5°	794.7	797.4	796.7	797.0	800.5
150°	822.3	824.3	824.3	824.3	823.5
152.5°	847.3	848.8	849.6	851.9	849.6
155°	874.1	874.1	873.4	876.4	873.4
157.5°	897.1	895.6	895.6	897.9	895.6
160°	917.1	916.3	915.5	917.8	914.0
162.5°	935.5	933.2	932.4	937.0	933.2
165°	951.6	949.3	947.7	952.3	949.3
167.5°	964.6	961.5	961.5	966.1	961.5
170°	975.3	971.5	972.3	976.9	971.5
172.5°	983.0	979.9	979.9	985.3	979.9
175°	989.9	986.1	985.3	990.7	985.3
177.5°	993.0	989.1	989.1	994.5	988.4
180°	991.4	991.4	991.4	991.4	991.4

(END OF REPORT)