

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008379

Luminaire Tested: S122RDIP-B290D725UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008379
REPORT IS A COMBINATION OF REPORTS P988149 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B290D725UB2750-4F0-XX-W2A-F_2700K
Description: Define 2 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3804.0 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008379

CATALOG NUMBER: S122RDIP-B290D725UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1008379

CATALOG NUMBER: S122RDIP-B290D725UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	91	91	91	91	70	70	70	51	51	51	34	34	34			26
1	93	89	85	82	83	79	76	73	62	60	58	46	44	43	31	30	29			23
2	85	78	72	67	75	70	65	61	54	51	48	40	38	36	27	26	25			19
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	24	23	22			17
4	71	61	53	47	63	54	48	43	43	38	35	32	29	27	22	20	19			15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17			13
6	60	48	41	35	53	44	37	32	34	30	26	26	23	20	18	16	15			11
7	55	44	36	31	49	39	33	28	31	26	23	24	20	18	17	15	13			10
8	51	39	32	27	46	36	29	25	28	24	20	22	18	16	15	13	12			9
9	48	36	29	24	42	33	26	22	26	21	18	20	17	14	14	12	11			8
10	44	33	26	21	40	30	24	20	24	19	16	18	15	13	13	11	10			8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7666	7666	7666
5°	7679	7293	7239
10°	7603	6918	6689
15°	7498	6473	6062
20°	7360	5968	5406
25°	7218	5451	4805
30°	7029	4945	4151
35°	6843	4437	3587
40°	6653	3938	3008
45°	6432	3421	2502
50°	6206	2924	2037
55°	5969	2427	1617
60°	5693	1942	1223
65°	5375	1481	994
70°	4993	1073	791
75°	4509	820	605
80°	3816	553	406
85°	2656	253	195

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6432 cd/sqm

TEST NUMBER: P1008379

CATALOG NUMBER: S122RDIP-B290D725UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	45.4	1.2
10°-20°	124.6	3.3
20°-30°	174.9	4.6
30°-40°	190.7	5.0
40°-50°	175.3	4.6
50°-60°	137.6	3.6
60°-70°	89.6	2.4
70°-80°	46.1	1.2
80°-90°	13.5	0.4
90°-100°	31.6	0.8
100°-110°	117.7	3.1
110°-120°	312.1	8.2
120°-130°	517.6	13.6
130°-140°	549.8	14.5
140°-150°	511.0	13.4
150°-160°	410.8	10.8
160°-170°	264.7	7.0
170°-180°	91.1	2.4
0°-30°	344.9	9.1
0°-40°	535.6	14.1
0°-60°	848.5	22.3
0°-90°	997.7	26.2
90°-120°	461.3	12.1
90°-150°	2039.7	53.6
90°-180°	2806.0	73.8
0°-180°	3804.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	484	484	484	484	484	
5°	484	482	476	480	479	46
15°	461	456	441	433	428	130
25°	418	404	375	357	351	192
35°	360	338	299	272	262	225
45°	294	265	219	188	178	227
55°	224	190	142	116	108	200
65°	151	116	76	61	60	150
75°	81	50	35	32	32	85
85°	19	10	8	8	8	22
90°	1	8	14	17	19	4
95°	45	22	27	30	30	53
105°	211	231	42	50	53	225
115°	398	410	427	107	57	392
125°	563	572	585	590	592	502
135°	697	708	714	721	720	538
145°	808	808	819	824	821	506
155°	890	884	892	896	891	410
165°	938	934	936	941	936	265
175°	959	954	956	961	954	91
180°	957	957	957	957	957	

TEST NUMBER: P1008379

CATALOG NUMBER: S122RDIP-B290D725UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	484.3	484.3	484.3	484.3	484.3
2.5°	486.5	484.3	479.5	483.8	483.0
5°	484.3	482.1	476.4	480.3	479.0
7.5°	480.3	477.7	471.6	473.3	471.1
10°	475.1	472.0	463.3	461.9	459.3
12.5°	468.5	464.6	452.7	450.1	445.3
15°	460.6	455.8	440.9	432.6	428.2
17.5°	451.4	444.4	426.0	416.4	409.3
20°	440.9	432.1	410.2	399.3	389.6
22.5°	429.5	419.4	394.0	379.1	372.5
25°	418.1	404.1	375.2	357.2	350.6
27.5°	404.5	389.6	357.6	337.0	326.9
30°	390.1	373.4	338.3	316.0	304.2
32.5°	376.0	355.9	319.9	293.6	282.7
35°	360.3	337.9	299.3	271.7	262.1
37.5°	344.9	320.8	280.1	249.8	238.9
40°	328.7	302.4	259.9	228.8	217.4
42.5°	312.0	284.0	239.7	207.3	196.3
45°	294.5	265.2	219.1	188.0	177.5
47.5°	277.9	246.7	199.4	168.3	158.7
50°	259.5	228.3	180.1	149.9	140.7
52.5°	241.5	208.6	161.7	132.8	124.5
55°	224.0	189.8	142.4	116.1	107.8
57.5°	206.0	170.9	125.3	100.8	93.8
60°	187.6	152.5	107.4	85.0	78.0
62.5°	169.6	134.5	92.0	71.0	67.5
65°	151.2	115.7	76.3	61.4	60.0
67.5°	133.7	98.2	61.4	53.9	52.6
70°	115.3	81.1	50.8	46.5	44.7
72.5°	97.7	65.3	42.5	39.0	38.1
75°	80.6	50.0	35.1	32.0	31.6
77.5°	63.5	35.5	27.6	25.9	25.0
80°	47.8	25.4	21.0	19.3	19.3
82.5°	33.3	17.1	14.5	13.6	13.6
85°	18.8	9.6	8.3	8.3	8.3
87.5°	7.0	3.5	3.5	3.1	3.1
90°	0.7	8.3	13.9	17.3	18.7
92.5°	17.3	14.5	16.6	18.0	18.7
95°	45.0	22.2	27.0	30.5	29.8
97.5°	81.0	24.2	35.3	37.4	38.1
100°	122.6	27.7	39.5	45.0	46.4
102.5°	168.3	166.9	40.9	48.5	50.6
105°	210.6	231.3	42.3	49.9	52.6
107.5°	259.7	277.1	43.6	51.3	54.0
110°	306.8	321.4	121.2	51.9	54.7

TEST NUMBER: P1008379

CATALOG NUMBER: S122RDIP-B290D725UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	351.2	363.6	351.9	53.3	55.4
115°	398.3	410.1	427.4	106.7	56.8
117.5°	439.1	453.0	464.8	365.7	184.2
120°	484.9	495.2	507.7	516.0	422.5
122.5°	523.6	534.7	548.6	552.7	553.4
125°	563.1	572.1	585.3	590.1	592.2
127.5°	599.1	608.8	619.2	626.2	626.9
130°	633.1	644.2	651.8	659.4	658.7
132.5°	667.7	676.7	684.3	690.6	689.9
135°	696.8	707.9	714.1	721.1	719.7
137.5°	727.3	735.6	742.5	749.5	747.4
140°	757.1	762.6	770.2	776.5	773.0
142.5°	782.0	786.9	795.9	801.4	797.9
145°	808.3	807.6	819.4	824.3	820.8
147.5°	831.2	829.1	840.9	844.3	841.6
150°	853.3	848.5	859.6	863.7	860.3
152.5°	872.1	866.5	876.9	881.1	876.2
155°	890.1	883.8	892.1	896.3	890.8
157.5°	904.6	899.1	905.3	910.1	904.6
160°	917.1	912.9	917.1	921.2	916.4
162.5°	928.2	924.0	927.5	932.3	926.1
165°	937.9	933.7	935.8	940.6	935.8
167.5°	945.5	941.3	943.4	948.2	942.0
170°	951.7	947.6	948.9	953.8	947.6
172.5°	955.9	951.7	953.1	957.9	951.7
175°	959.3	954.5	955.9	960.7	953.8
177.5°	960.7	955.9	956.6	961.4	955.2
180°	957.2	957.2	957.2	957.2	957.2

(END OF REPORT)