

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001983

Luminaire Tested: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001983
REPORT IS A COMBINATION OF REPORTS P996608 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6132.0 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001983

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001983

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	47	42	45	40	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10821	10821	10821
5°	10830	10510	10523
10°	10738	10218	10146
15°	10584	9871	9722
20°	10387	9495	9283
25°	10166	9099	8810
30°	9899	8671	8291
35°	9623	8232	7789
40°	9335	7759	7255
45°	9032	7286	6756
50°	8697	6827	6204
55°	8334	6291	5655
60°	7961	5703	5084
65°	7536	5096	4439
70°	7045	4367	3750
75°	6311	3519	3003
80°	5380	2545	2113
85°	4177	1417	1136

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9032 cd/sqm

TEST NUMBER: P1001983

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	125.1	2.0
10°-20°	352.4	5.7
20°-30°	518.6	8.5
30°-40°	602.8	9.8
40°-50°	602.8	9.8
50°-60°	527.2	8.6
60°-70°	391.4	6.4
70°-80°	222.1	3.6
80°-90°	65.7	1.1
90°-100°	64.0	1.0
100°-110°	191.7	3.1
110°-120°	325.6	5.3
120°-130°	429.4	7.0
130°-140°	482.3	7.9
140°-150°	474.0	7.7
150°-160°	398.7	6.5
160°-170°	265.3	4.3
170°-180°	92.9	1.5
0°-30°	996.1	16.2
0°-40°	1598.9	26.1
0°-60°	2728.9	44.5
0°-90°	3408.1	55.6
90°-120°	581.3	9.5
90°-150°	1967.0	32.1
90°-180°	2724.0	44.4
0°-180°	6132.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1327	1327	1327	1327	1327	
5°	1326	1322	1310	1322	1320	126
15°	1262	1258	1242	1248	1245	356
25°	1143	1136	1121	1122	1118	526
35°	984	976	961	954	948	615
45°	803	795	778	767	763	619
55°	607	604	589	576	570	544
65°	412	406	396	385	380	407
75°	219	214	208	204	203	232
85°	57	57	55	55	54	62
90°	2	11	17	21	23	7
95°	46	52	58	60	60	49
105°	177	178	181	183	185	188
115°	331	331	330	329	328	326
125°	482	482	481	480	478	430
135°	622	626	626	625	623	481
145°	756	758	759	758	756	473
155°	866	866	865	868	865	398
165°	942	940	938	943	940	266
175°	980	976	976	981	976	93
180°	982	982	982	982	982	

TEST NUMBER: P1001983

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1327.0	1327.0	1327.0	1327.0	1327.0
2.5°	1331.3	1328.1	1316.4	1327.0	1325.9
5°	1325.9	1321.7	1310.0	1321.7	1319.6
7.5°	1316.4	1312.1	1299.4	1308.9	1307.9
10°	1302.5	1298.3	1284.5	1293.0	1290.8
12.5°	1284.5	1280.2	1265.3	1274.9	1271.7
15°	1262.1	1257.9	1241.9	1248.3	1245.1
17.5°	1236.6	1231.3	1216.4	1220.7	1218.5
20°	1207.9	1202.6	1186.6	1189.8	1187.7
22.5°	1177.1	1169.6	1153.7	1160.1	1155.8
25°	1143.0	1135.6	1120.7	1121.8	1117.5
27.5°	1104.8	1097.3	1083.5	1081.4	1076.1
30°	1066.5	1058.0	1044.2	1039.9	1034.6
32.5°	1026.1	1018.6	1003.8	998.4	993.1
35°	983.6	976.1	961.2	953.8	948.5
37.5°	938.9	932.5	916.6	909.1	901.7
40°	895.3	886.8	870.8	860.2	854.9
42.5°	848.5	844.3	826.2	813.4	810.2
45°	802.8	795.3	778.3	766.6	763.4
47.5°	754.9	749.6	733.7	720.9	712.4
50°	706.0	701.8	686.9	672.0	665.6
52.5°	658.2	652.9	636.9	624.2	615.7
55°	607.1	604.0	589.1	576.3	569.9
57.5°	559.3	556.1	541.2	528.5	522.1
60°	509.3	504.0	490.2	480.6	475.3
62.5°	460.4	456.2	441.3	432.8	427.4
65°	411.5	406.2	395.5	384.9	379.6
67.5°	361.5	357.3	346.6	336.0	334.9
70°	315.8	308.4	299.9	291.3	288.2
72.5°	266.9	259.4	253.1	246.7	243.5
75°	219.0	213.7	208.4	204.2	203.1
77.5°	172.3	170.1	164.8	163.7	160.6
80°	130.8	127.6	125.5	123.3	122.3
82.5°	90.4	89.3	89.3	88.3	87.2
85°	57.4	57.4	55.3	55.3	54.2
87.5°	27.6	26.6	25.5	25.5	25.5
90°	2.3	10.6	16.7	21.3	22.8
92.5°	19.7	29.6	33.4	35.7	36.4
95°	45.6	52.4	57.7	60.0	60.0
97.5°	72.9	79.0	85.0	88.1	88.1
100°	106.3	109.3	116.2	117.7	117.7
102.5°	141.2	142.0	148.1	150.3	151.1
105°	176.9	177.7	180.7	183.0	185.3
107.5°	214.1	214.9	215.6	218.7	217.9
110°	252.1	253.6	252.8	251.3	253.6

TEST NUMBER: P1001983

CATALOG NUMBER: SA4XXDIP-B795D810UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	291.6	291.6	290.0	290.0	290.0
115°	331.0	331.0	329.5	328.8	328.0
117.5°	368.2	368.2	367.5	365.2	362.9
120°	405.4	408.5	406.2	402.4	403.9
122.5°	444.2	444.9	444.2	441.9	438.1
125°	482.1	482.1	481.4	479.8	478.3
127.5°	516.3	518.6	517.1	515.5	514.8
130°	552.7	555.0	555.0	553.5	550.5
132.5°	589.9	591.5	590.7	589.2	588.4
135°	621.8	626.4	626.4	624.9	622.6
137.5°	657.5	659.8	661.3	659.0	659.8
140°	693.2	694.7	694.7	694.0	693.2
142.5°	725.8	727.4	726.6	726.6	726.6
145°	755.5	758.5	759.3	758.5	756.2
147.5°	785.8	789.6	788.9	788.1	787.3
150°	813.2	816.2	816.2	816.2	815.4
152.5°	839.0	840.5	841.3	843.5	841.3
155°	865.6	865.6	864.8	867.8	864.8
157.5°	888.3	886.8	886.8	889.1	886.8
160°	908.1	907.3	906.5	908.8	905.0
162.5°	926.3	924.0	923.3	927.8	924.0
165°	942.2	940.0	938.4	943.0	940.0
167.5°	955.1	952.1	952.1	956.7	952.1
170°	965.8	962.0	962.7	967.3	962.0
172.5°	973.4	970.3	970.3	975.6	970.3
175°	980.2	976.4	975.6	981.0	975.6
177.5°	983.2	979.4	979.4	984.8	978.7
180°	981.7	981.7	981.7	981.7	981.7

(END OF REPORT)