

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001989

Luminaire Tested: SA4XXDIP-B795D810UB50-4F0-XX-W2A-D1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001989
REPORT IS A COMBINATION OF REPORTS P996614 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB50-4F0-XX-W2A-D1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5766.0 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001989

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-D1

Luminous Intensity Polar Plot



TEST NUMBER: P1001989

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	97	92	88	84	89	85	81	78	72	69	66	59	57	56	48	47	46
2	88	80	73	68	81	74	68	63	62	58	54	52	48	46	42	40	38
3	80	70	62	56	73	64	58	52	54	49	45	45	41	38	37	34	31
4	73	61	53	47	67	57	50	44	48	43	38	40	36	32	33	29	27
5	67	55	46	40	61	51	43	37	43	37	33	36	31	28	29	26	23
6	61	49	40	34	56	45	38	32	39	33	28	32	28	24	26	23	20
7	57	44	36	30	52	41	34	28	35	29	25	29	25	21	24	21	18
8	53	40	32	27	48	37	30	25	32	26	22	27	22	19	22	19	16
9	49	36	29	24	45	34	27	22	29	23	20	25	20	17	20	17	14
10	46	33	26	21	42	31	24	20	27	21	18	23	18	15	19	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7486	7486	7486
5°	7507	7291	7304
10°	7458	7147	7127
15°	7388	6986	6927
20°	7285	6812	6733
25°	7168	6619	6524
30°	7042	6428	6311
35°	6899	6234	6121
40°	6785	6046	5924
45°	6616	5870	5750
50°	6471	5671	5567
55°	6323	5478	5355
60°	6090	5239	5157
65°	5836	4980	4918
70°	5528	4686	4641
75°	5095	4357	4378
80°	4611	4024	4103
85°	3966	3687	3878

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6616 cd/sqm

TEST NUMBER: P1001989

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.0	1.5
10°-20°	249.2	4.3
20°-30°	376.8	6.5
30°-40°	455.9	7.9
40°-50°	482.0	8.4
50°-60°	453.6	7.9
60°-70°	376.4	6.5
70°-80°	264.1	4.6
80°-90°	150.9	2.6
90°-100°	150.5	2.6
100°-110°	251.0	4.4
110°-120°	358.9	6.2
120°-130°	440.0	7.6
130°-140°	477.1	8.3
140°-150°	460.5	8.0
150°-160°	385.5	6.7
160°-170°	256.5	4.4
170°-180°	89.8	1.6
0°-30°	713.1	12.4
0°-40°	1169.0	20.3
0°-60°	2104.5	36.5
0°-90°	2896.0	50.2
90°-120°	760.4	13.2
90°-150°	2138.1	37.1
90°-180°	2870.0	49.8
0°-180°	5766.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	918	918	918	918	918	
5°	919	916	909	917	916	87
15°	881	882	879	888	887	248
25°	806	812	815	827	828	371
35°	705	718	728	742	745	442
45°	588	608	627	645	650	454
55°	461	482	513	534	540	410
65°	319	352	386	412	420	316
75°	177	215	258	287	296	188
85°	54	98	144	175	185	57
90°	19	68	118	152	162	14
95°	58	98	145	175	184	58
105°	180	202	243	270	281	192
115°	326	336	367	389	395	322
125°	470	469	494	512	517	419
135°	603	608	615	630	634	467
145°	732	734	734	740	742	458
155°	837	837	836	839	836	385
165°	911	909	908	912	909	257
175°	948	944	943	949	943	90
180°	949	949	949	949	949	

TEST NUMBER: P1001989

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	918.0	918.0	918.0	918.0	918.0
2.5°	922.2	919.1	910.9	918.0	917.0
5°	919.1	916.0	908.8	917.0	916.0
7.5°	912.9	910.9	904.7	913.9	912.9
10°	904.7	903.7	898.5	907.8	906.7
12.5°	893.4	893.4	890.3	898.5	898.5
15°	881.0	882.1	879.0	888.2	887.2
17.5°	864.6	867.7	866.6	875.9	874.9
20°	847.1	850.2	851.2	861.5	861.5
22.5°	827.6	831.7	833.7	844.0	846.1
25°	806.0	812.2	815.2	826.6	827.6
27.5°	782.3	791.6	795.7	806.0	807.0
30°	758.7	766.9	774.1	785.4	787.5
32.5°	733.0	743.3	751.5	764.9	766.9
35°	705.2	717.6	727.9	742.3	745.3
37.5°	677.5	691.9	704.2	718.6	721.7
40°	650.8	664.1	678.5	693.9	698.0
42.5°	619.9	635.3	652.8	670.3	673.4
45°	588.0	607.6	627.1	644.6	649.7
47.5°	558.2	577.8	600.4	617.9	624.0
50°	525.3	547.9	570.6	591.1	597.3
52.5°	492.4	515.1	541.8	562.3	568.5
55°	460.6	482.2	513.0	533.6	539.7
57.5°	424.6	451.3	481.1	505.8	510.9
60°	389.6	416.4	450.3	473.9	482.2
62.5°	355.7	385.5	419.4	443.1	451.3
65°	318.7	351.6	386.5	412.2	420.5
67.5°	283.7	318.7	355.7	381.4	389.6
70°	247.8	282.7	321.8	349.5	356.7
72.5°	212.8	248.8	290.9	317.7	325.9
75°	176.8	214.9	258.0	286.8	296.1
77.5°	142.9	183.0	228.2	257.0	267.3
80°	112.1	153.2	198.4	229.3	237.5
82.5°	81.2	124.4	169.6	201.5	210.7
85°	54.5	97.7	143.9	174.8	185.0
87.5°	33.9	76.1	121.3	151.1	160.4
90°	18.6	67.9	118.0	152.2	161.8
92.5°	34.5	80.0	127.9	158.9	167.8
95°	57.5	98.0	145.2	175.2	184.4
97.5°	82.8	118.5	166.5	196.2	205.5
100°	114.1	143.7	190.4	219.7	226.9
102.5°	147.9	171.2	216.2	245.1	254.0
105°	180.4	201.6	242.6	270.5	280.9
107.5°	216.3	234.5	271.2	299.8	306.3
110°	252.0	267.8	303.1	325.2	335.7

TEST NUMBER: P1001989

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-D1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	289.1	301.4	334.0	356.6	364.8
115°	326.3	335.5	366.9	388.8	395.3
117.5°	362.3	368.4	398.5	417.9	423.9
120°	397.2	403.2	430.8	447.7	457.4
122.5°	434.6	435.3	462.4	480.8	484.3
125°	470.3	469.3	494.3	512.3	517.0
127.5°	503.3	504.6	523.6	540.6	547.1
130°	537.6	538.8	555.2	572.2	575.5
132.5°	573.6	574.0	585.6	601.6	607.0
135°	603.4	607.8	615.0	629.9	633.9
137.5°	637.9	639.0	644.6	657.9	663.7
140°	672.4	672.8	673.9	686.4	690.9
142.5°	702.9	704.4	702.6	713.9	718.0
145°	731.5	733.5	734.2	739.7	741.6
147.5°	760.9	763.6	762.8	763.1	766.5
150°	787.3	789.3	789.3	789.3	788.5
152.5°	811.3	812.7	813.5	815.7	813.5
155°	837.0	837.0	836.2	839.2	836.2
157.5°	859.0	857.5	857.5	859.7	857.5
160°	878.1	877.4	876.6	878.8	875.2
162.5°	895.7	893.5	892.8	897.2	893.5
165°	911.1	908.9	907.5	911.9	908.9
167.5°	923.6	920.7	920.7	925.1	920.7
170°	933.9	930.2	930.9	935.4	930.2
172.5°	941.2	938.3	938.3	943.4	938.3
175°	947.8	944.2	943.4	948.6	943.4
177.5°	950.8	947.1	947.1	952.2	946.4
180°	949.3	949.3	949.3	949.3	949.3

(END OF REPORT)