

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1001992

Luminaire Tested: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1001992
REPORT IS A COMBINATION OF REPORTS P996617 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F1
Description: Define 4 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5929.0 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1001992

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1001992

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	47	52	47	42	45	40	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	51	43	37	59	48	41	35	42	36	32	36	32	28	31	27	24
7	59	46	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10462	10462	10462
5°	10470	10161	10174
10°	10382	9879	9810
15°	10233	9543	9399
20°	10043	9181	8975
25°	9829	8797	8518
30°	9571	8383	8016
35°	9303	7958	7531
40°	9025	7503	7014
45°	8733	7044	6532
50°	8409	6600	5998
55°	8058	6082	5467
60°	7697	5514	4915
65°	7285	4927	4292
70°	6811	4222	3625
75°	6104	3403	2904
80°	5199	2460	2042
85°	4039	1371	1098

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8733 cd/sqm

TEST NUMBER: P1001992

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	120.9	2.0
10°-20°	340.7	5.7
20°-30°	501.4	8.5
30°-40°	582.8	9.8
40°-50°	582.8	9.8
50°-60°	509.7	8.6
60°-70°	378.4	6.4
70°-80°	214.7	3.6
80°-90°	63.5	1.1
90°-100°	61.9	1.0
100°-110°	185.3	3.1
110°-120°	314.8	5.3
120°-130°	415.2	7.0
130°-140°	466.4	7.9
140°-150°	458.4	7.7
150°-160°	385.5	6.5
160°-170°	256.5	4.3
170°-180°	89.8	1.5
0°-30°	963.0	16.2
0°-40°	1545.9	26.1
0°-60°	2638.4	44.5
0°-90°	3295.0	55.6
90°-120°	562.1	9.5
90°-150°	1902.1	32.1
90°-180°	2634.0	44.4
0°-180°	5929.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1283	1283	1283	1283	1283	
5°	1282	1278	1266	1278	1276	122
15°	1220	1216	1201	1207	1204	344
25°	1105	1098	1084	1085	1080	509
35°	951	944	929	922	917	595
45°	776	769	752	741	738	598
55°	587	584	570	557	551	526
65°	398	393	382	372	367	394
75°	212	207	202	197	196	225
85°	56	56	54	54	52	60
90°	2	10	16	21	22	7
95°	44	51	56	58	58	48
105°	171	172	175	177	179	181
115°	320	320	319	318	317	316
125°	466	466	466	464	462	416
135°	601	606	606	604	602	465
145°	730	734	734	734	731	457
155°	837	837	836	839	836	385
165°	911	909	908	912	909	257
175°	948	944	943	949	943	90
180°	949	949	949	949	949	

TEST NUMBER: P1001992

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1283.0	1283.0	1283.0	1283.0	1283.0
2.5°	1287.1	1284.0	1272.7	1283.0	1281.9
5°	1281.9	1277.8	1266.5	1277.8	1275.8
7.5°	1272.7	1268.6	1256.2	1265.5	1264.5
10°	1259.3	1255.2	1241.9	1250.1	1248.0
12.5°	1241.9	1237.7	1223.3	1232.6	1229.5
15°	1220.3	1216.2	1200.7	1206.9	1203.8
17.5°	1195.6	1190.5	1176.1	1180.2	1178.1
20°	1167.8	1162.7	1147.3	1150.4	1148.3
22.5°	1138.0	1130.8	1115.4	1121.6	1117.5
25°	1105.1	1097.9	1083.5	1084.6	1080.5
27.5°	1068.1	1060.9	1047.6	1045.5	1040.4
30°	1031.1	1022.9	1009.5	1005.4	1000.3
32.5°	992.0	984.8	970.5	965.3	960.2
35°	950.9	943.7	929.3	922.1	917.0
37.5°	907.7	901.6	886.2	879.0	871.8
40°	865.6	857.4	842.0	831.7	826.5
42.5°	820.4	816.3	798.8	786.4	783.4
45°	776.2	769.0	752.5	741.2	738.1
47.5°	729.9	724.8	709.3	697.0	688.8
50°	682.6	678.5	664.1	649.7	643.5
52.5°	636.3	631.2	615.8	603.4	595.2
55°	587.0	583.9	569.5	557.2	551.0
57.5°	540.7	537.7	523.3	510.9	504.8
60°	492.4	487.3	473.9	464.7	459.5
62.5°	445.1	441.0	426.6	418.4	413.3
65°	397.8	392.7	382.4	372.1	367.0
67.5°	349.5	345.4	335.1	324.9	323.8
70°	305.3	298.1	289.9	281.7	278.6
72.5°	258.0	250.8	244.7	238.5	235.4
75°	211.8	206.6	201.5	197.4	196.4
77.5°	166.5	164.5	159.3	158.3	155.2
80°	126.4	123.4	121.3	119.3	118.2
82.5°	87.4	86.4	86.4	85.3	84.3
85°	55.5	55.5	53.5	53.5	52.4
87.5°	26.7	25.7	24.7	24.7	24.7
90°	2.2	10.3	16.2	20.6	22.0
92.5°	19.1	28.6	32.3	34.5	35.2
95°	44.1	50.7	55.8	58.0	58.0
97.5°	70.5	76.4	82.2	85.2	85.2
100°	102.8	105.7	112.3	113.8	113.8
102.5°	136.6	137.3	143.2	145.4	146.1
105°	171.1	171.8	174.7	176.9	179.1
107.5°	207.0	207.8	208.5	211.4	210.7
110°	243.8	245.2	244.5	243.0	245.2

TEST NUMBER: P1001992

CATALOG NUMBER: SA4XXDIP-B795D810UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	281.9	281.9	280.5	280.5	280.5
115°	320.1	320.1	318.6	317.9	317.2
117.5°	356.1	356.1	355.3	353.1	350.9
120°	392.1	395.0	392.8	389.1	390.6
122.5°	429.5	430.2	429.5	427.3	423.6
125°	466.2	466.2	465.5	464.0	462.5
127.5°	499.2	501.5	500.0	498.5	497.8
130°	534.5	536.7	536.7	535.2	532.3
132.5°	570.5	571.9	571.2	569.7	569.0
135°	601.3	605.7	605.7	604.2	602.0
137.5°	635.8	638.0	639.5	637.3	638.0
140°	670.3	671.8	671.8	671.0	670.3
142.5°	701.9	703.4	702.6	702.6	702.6
145°	730.5	733.5	734.2	733.5	731.3
147.5°	759.9	763.6	762.8	762.1	761.4
150°	786.3	789.3	789.3	789.3	788.5
152.5°	811.3	812.7	813.5	815.7	813.5
155°	837.0	837.0	836.2	839.2	836.2
157.5°	859.0	857.5	857.5	859.7	857.5
160°	878.1	877.4	876.6	878.8	875.2
162.5°	895.7	893.5	892.8	897.2	893.5
165°	911.1	908.9	907.5	911.9	908.9
167.5°	923.6	920.7	920.7	925.1	920.7
170°	933.9	930.2	930.9	935.4	930.2
172.5°	941.2	938.3	938.3	943.4	938.3
175°	947.8	944.2	943.4	948.6	943.4
177.5°	950.8	947.1	947.1	952.2	946.4
180°	949.3	949.3	949.3	949.3	949.3

(END OF REPORT)