

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000273

Luminaire Tested: SA4XXDP-B1020DB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000273
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDP-B1020DB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Direct Recessed with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4402.0 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000273

CATALOG NUMBER: SA4XXDP-B1020DB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000273

CATALOG NUMBER: SA4XXDP-B1020DB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	109	104	100	96	106	102	98	95	98	95	92		94	91	89		90
2	99	91	84	79	97	89	83	78	86	80	76		82	78	74		79
3	91	80	72	66	88	79	71	65	76	69	64		73	67	63		70
4	83	71	63	56	81	70	62	56	67	60	55		65	59	54		63
5	77	64	55	48	74	63	54	48	61	53	48		59	52	47		57
6	71	58	49	42	69	57	48	42	55	47	42		53	47	41		52
7	66	52	44	38	64	52	43	37	50	43	37		49	42	37		47
8	61	48	39	34	60	47	39	34	46	39	33		45	38	33		43
9	57	44	36	30	56	43	36	30	42	35	30		41	35	30		40
10	54	41	33	28	52	40	33	28	39	32	27		38	32	27		37

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13985	13985	13985
5°	14028	13859	13960
10°	13939	13746	13814
15°	13771	13550	13585
20°	13547	13308	13320
25°	13292	13032	12995
30°	12979	12707	12590
35°	12655	12367	12203
40°	12317	11981	11762
45°	11965	11600	11379
50°	11576	11263	10914
55°	11156	10823	10472
60°	10736	10332	10019
65°	10261	9864	9466
70°	9730	9239	8879
75°	8919	8488	8270
80°	7936	7617	7420
85°	6942	6690	6559

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11965 cd/sqm

TEST NUMBER: P1000273

CATALOG NUMBER: SA4XXDP-B1020DB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	161.6	3.7
10°-20°	455.4	10.3
20°-30°	670.3	15.2
30°-40°	779.1	17.7
40°-50°	779.0	17.7
50°-60°	681.4	15.5
60°-70°	505.9	11.5
70°-80°	287.0	6.5
80°-90°	82.2	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1287.3	29.2
0°-40°	2066.5	46.9
0°-60°	3526.9	80.1
0°-90°	4402.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4402.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1715	1715	1715	1715	1715	
5°	1714	1708	1693	1708	1705	163
15°	1631	1626	1605	1613	1609	460
25°	1477	1468	1448	1450	1444	680
35°	1271	1262	1242	1233	1226	795
45°	1038	1028	1006	991	987	800
55°	785	781	761	745	737	703
65°	532	525	511	498	491	526
75°	283	276	269	264	262	300
85°	74	74	72	72	70	85
90°	0	0	0	0	0	

TEST NUMBER: P1000273

CATALOG NUMBER: SA4XXDP-B1020DB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1715.0	1715.0	1715.0	1715.0	1715.0
2.5°	1720.5	1716.4	1701.3	1715.0	1713.7
5°	1713.7	1708.2	1693.1	1708.2	1705.4
7.5°	1701.3	1695.8	1679.3	1691.7	1690.3
10°	1683.4	1677.9	1660.1	1671.1	1668.3
12.5°	1660.1	1654.6	1635.3	1647.7	1643.6
15°	1631.2	1625.7	1605.1	1613.4	1609.2
17.5°	1598.2	1591.4	1572.1	1577.6	1574.9
20°	1561.1	1554.3	1533.6	1537.8	1535.0
22.5°	1521.3	1511.7	1491.0	1499.3	1493.8
25°	1477.3	1467.7	1448.4	1449.8	1444.3
27.5°	1427.8	1418.2	1400.3	1397.6	1390.7
30°	1378.4	1367.4	1349.5	1344.0	1337.1
32.5°	1326.1	1316.5	1297.3	1290.4	1283.5
35°	1271.2	1261.5	1242.3	1232.7	1225.8
37.5°	1213.5	1205.2	1184.6	1175.0	1165.4
40°	1157.1	1146.1	1125.5	1111.8	1104.9
42.5°	1096.6	1091.1	1067.8	1051.3	1047.2
45°	1037.5	1027.9	1005.9	990.8	986.7
47.5°	975.7	968.8	948.2	931.7	920.7
50°	912.5	907.0	887.8	868.5	860.3
52.5°	850.7	843.8	823.2	806.7	795.7
55°	784.7	780.6	761.3	744.8	736.6
57.5°	722.8	718.7	699.5	683.0	674.7
60°	658.3	651.4	633.5	621.2	614.3
62.5°	595.0	589.5	570.3	559.3	552.4
65°	531.8	525.0	511.2	497.5	490.6
67.5°	467.2	461.7	448.0	434.3	432.9
70°	408.1	398.5	387.5	376.5	372.4
72.5°	344.9	335.3	327.1	318.8	314.7
75°	283.1	276.2	269.4	263.9	262.5
77.5°	222.6	219.9	213.0	211.6	207.5
80°	169.0	164.9	162.2	159.4	158.0
82.5°	116.8	115.4	115.4	114.1	112.7
85°	74.2	74.2	71.5	71.5	70.1
87.5°	35.7	34.4	33.0	33.0	33.0
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)