

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008441

Luminaire Tested: S122RDIP-B485D925UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008441
REPORT IS A COMBINATION OF REPORTS P988391 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B485D925UB2750-4F0-XX-W2A-F_3500K
Description: Define 2 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5379.0 lumens
Efficiency: N/A
Efficacy: 102.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008441

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008441

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	32
1	94	90	86	83	84	81	78	75	64	62	60	49	48	47	35	34	34	34	34	34	27
2	86	79	73	68	77	71	66	62	57	53	50	44	41	39	31	30	29	29	29	29	23
3	78	69	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25	25	25	25	20
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22	22	22	22	18
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19	19	19	19	15
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17	17	17	17	14
7	56	44	37	32	50	40	34	29	33	28	24	26	22	20	19	17	15	15	15	15	12
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14	14	14	14	11
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12	12	12	12	10
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13069	13069	13069
5°	13090	12434	12342
10°	12961	11793	11403
15°	12784	11036	10334
20°	12548	10176	9216
25°	12306	9292	8192
30°	11982	8432	7075
35°	11665	7564	6115
40°	11342	6713	5127
45°	10966	5834	4265
50°	10577	4986	3472
55°	10174	4138	2757
60°	9704	3310	2086
65°	9165	2523	1696
70°	8510	1831	1348
75°	7692	1397	1030
80°	6499	946	692
85°	4534	433	334

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10966 cd/sqm

TEST NUMBER: P1008441

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.4	1.4
10°-20°	212.4	3.9
20°-30°	298.2	5.5
30°-40°	325.1	6.0
40°-50°	298.8	5.6
50°-60°	234.7	4.4
60°-70°	152.7	2.8
70°-80°	78.6	1.5
80°-90°	22.3	0.4
90°-100°	41.4	0.8
100°-110°	154.2	2.9
110°-120°	409.1	7.6
120°-130°	678.5	12.6
130°-140°	720.7	13.4
140°-150°	669.9	12.5
150°-160°	538.5	10.0
160°-170°	347.0	6.5
170°-180°	119.4	2.2
0°-30°	588.0	10.9
0°-40°	913.1	17.0
0°-60°	1446.5	26.9
0°-90°	1700.2	31.6
90°-120°	604.7	11.2
90°-150°	2673.8	49.7
90°-180°	3679.0	68.4
0°-180°	5379.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	826	826	826	826	826	
5°	826	822	812	819	817	78
15°	785	777	752	738	730	221
25°	713	689	640	609	598	328
35°	614	576	510	463	447	384
45°	502	452	374	320	303	388
55°	382	324	243	198	184	341
65°	258	197	130	105	102	256
75°	138	85	60	54	54	145
85°	32	16	14	14	14	37
90°	1	11	18	23	24	5
95°	59	29	35	40	39	70
105°	276	303	55	65	69	295
115°	522	538	560	140	74	514
125°	738	750	767	774	776	658
135°	913	928	936	945	943	706
145°	1060	1059	1074	1080	1076	663
155°	1167	1159	1170	1175	1168	538
165°	1229	1224	1227	1233	1227	347
175°	1258	1251	1253	1259	1250	120
180°	1255	1255	1255	1255	1255	

TEST NUMBER: P1008441

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	825.6	825.6	825.6	825.6	825.6
2.5°	829.4	825.6	817.4	824.9	823.4
5°	825.6	821.9	812.2	818.9	816.7
7.5°	818.9	814.4	804.0	806.9	803.2
10°	809.9	804.7	789.8	787.5	783.0
12.5°	798.7	792.0	771.8	767.3	759.1
15°	785.3	777.1	751.7	737.5	730.0
17.5°	769.6	757.6	726.2	709.8	697.9
20°	751.7	736.7	699.4	680.7	664.2
22.5°	732.2	715.0	671.7	646.3	635.1
25°	712.8	688.9	639.6	608.9	597.7
27.5°	689.6	664.2	609.7	574.6	557.4
30°	665.0	636.6	576.8	538.7	518.5
32.5°	641.1	606.7	545.4	500.6	481.9
35°	614.2	576.1	510.3	463.2	446.8
37.5°	588.0	546.9	477.4	425.9	407.2
40°	560.4	515.5	443.1	390.0	370.6
42.5°	532.0	484.2	408.7	353.4	334.7
45°	502.1	452.0	373.6	320.5	302.6
47.5°	473.7	420.7	340.0	286.9	270.5
50°	442.3	389.3	307.1	255.5	239.8
52.5°	411.7	355.7	275.7	226.4	212.2
55°	381.8	323.5	242.8	198.0	183.8
57.5°	351.2	291.4	213.7	171.8	159.9
60°	319.8	260.0	183.1	145.0	133.0
62.5°	289.2	229.4	156.9	121.0	115.1
65°	257.8	197.3	130.0	104.6	102.4
67.5°	227.9	167.4	104.6	91.9	89.7
70°	196.5	138.2	86.7	79.2	76.2
72.5°	166.6	111.3	72.5	66.5	65.0
75°	137.5	85.2	59.8	54.5	53.8
77.5°	108.3	60.5	47.1	44.1	42.6
80°	81.4	43.3	35.9	32.9	32.9
82.5°	56.8	29.1	24.7	23.2	23.2
85°	32.1	16.4	14.2	14.2	14.2
87.5°	12.0	6.0	6.0	5.2	5.2
90°	0.9	10.9	18.2	22.7	24.5
92.5°	22.7	19.1	21.8	23.6	24.5
95°	59.0	29.1	35.4	40.0	39.0
97.5°	106.2	31.8	46.3	49.0	49.9
100°	160.7	36.3	51.8	59.0	60.8
102.5°	220.6	218.8	53.6	63.6	66.3
105°	276.0	303.3	55.4	65.4	69.0
107.5°	340.5	363.2	57.2	67.2	70.8
110°	402.2	421.3	158.9	68.1	71.7

TEST NUMBER: P1008441

CATALOG NUMBER: S122RDIP-B485D925UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	460.4	476.7	461.3	69.9	72.6
115°	522.1	537.5	560.2	139.8	74.5
117.5°	575.7	593.8	609.3	479.4	241.5
120°	635.6	649.2	665.6	676.5	553.9
122.5°	686.4	701.0	719.1	724.6	725.5
125°	738.2	750.0	767.3	773.6	776.3
127.5°	785.4	798.1	811.8	820.8	821.7
130°	829.9	844.4	854.4	864.4	863.5
132.5°	875.3	887.1	897.1	905.3	904.4
135°	913.4	928.0	936.1	945.2	943.4
137.5°	953.4	964.3	973.4	982.5	979.7
140°	992.4	999.7	1009.7	1017.9	1013.3
142.5°	1025.1	1031.5	1043.3	1050.6	1046.0
145°	1059.6	1058.7	1074.2	1080.5	1076.0
147.5°	1089.6	1086.9	1102.3	1106.9	1103.2
150°	1118.7	1112.3	1126.8	1132.3	1127.7
152.5°	1143.2	1135.9	1149.5	1155.0	1148.6
155°	1166.8	1158.6	1169.5	1175.0	1167.7
157.5°	1185.8	1178.6	1186.8	1193.1	1185.8
160°	1202.2	1196.7	1202.2	1207.6	1201.3
162.5°	1216.7	1211.3	1215.8	1222.2	1214.0
165°	1229.4	1224.0	1226.7	1233.1	1226.7
167.5°	1239.4	1234.0	1236.7	1243.1	1234.9
170°	1247.6	1242.1	1244.0	1250.3	1242.1
172.5°	1253.0	1247.6	1249.4	1255.8	1247.6
175°	1257.6	1251.2	1253.0	1259.4	1250.3
177.5°	1259.4	1253.0	1253.9	1260.3	1252.1
180°	1254.9	1254.9	1254.9	1254.9	1254.9

(END OF REPORT)