

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000329

Luminaire Tested: SA4XXDP-B350DB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000329
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-16)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDP-B350DB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct Recessed with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1409.0 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000329

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000329

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	92
1	105	100	95	91	102	97	93	89	91	88	84	86	83	80	81	79	77	77	77	74
2	95	86	79	73	92	84	77	71	79	73	68	74	70	66	70	67	63	63	63	60
3	87	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	49	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	28
8	58	44	35	29	56	43	35	29	41	33	28	39	32	28	37	31	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	29	25	34	29	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3370	3370	3370
5°	3386	3349	3375
10°	3373	3349	3380
15°	3348	3341	3372
20°	3309	3325	3365
25°	3264	3302	3352
30°	3216	3281	3338
35°	3161	3262	3340
40°	3118	3251	3345
45°	3053	3256	3373
50°	3000	3258	3411
55°	2947	3283	3455
60°	2861	3306	3539
65°	2769	3357	3653
70°	2658	3455	3829
75°	2508	3661	4200
80°	2367	4194	5020
85°	2292	6063	7794

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 13498 cd/sqm

TEST NUMBER: P1000329

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	2.8
10°-20°	112.2	8.0
20°-30°	169.6	12.0
30°-40°	205.2	14.6
40°-50°	217.0	15.4
50°-60°	204.2	14.5
60°-70°	169.4	12.0
70°-80°	118.9	8.4
80°-90°	67.0	4.8
90°-100°	39.9	2.8
100°-110°	29.6	2.1
110°-120°	19.8	1.4
120°-130°	11.2	0.8
130°-140°	4.8	0.3
140°-150°	1.0	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	321.0	22.8
0°-40°	526.2	37.3
0°-60°	947.4	67.2
0°-90°	1302.8	92.5
90°-120°	89.3	6.3
90°-150°	106.3	7.5
90°-180°	106.0	7.5
0°-180°	1409.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	413	413	413	413	413	
5°	414	412	409	413	412	39
15°	397	397	396	400	399	112
25°	363	366	367	372	372	167
35°	318	323	328	334	336	199
45°	265	274	282	290	292	205
55°	207	217	231	240	243	185
65°	144	158	174	186	189	142
75°	80	97	116	129	133	85
85°	24	44	65	79	83	26
90°	7	26	46	59	63	5
95°	6	21	40	53	57	5
105°	4	13	30	42	46	5
115°	3	7	22	32	35	3
125°	2	1	13	22	24	2
135°	1	1	4	12	14	1
145°	0	0	0	3	5	0
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1000329

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	413.3	413.3	413.3	413.3	413.3
2.5°	415.1	413.7	410.0	413.3	412.8
5°	413.7	412.3	409.1	412.8	412.3
7.5°	411.0	410.0	407.3	411.4	411.0
10°	407.3	406.8	404.5	408.6	408.2
12.5°	402.2	402.2	400.8	404.5	404.5
15°	396.6	397.1	395.7	399.8	399.4
17.5°	389.2	390.6	390.1	394.3	393.8
20°	381.3	382.7	383.2	387.8	387.8
22.5°	372.5	374.4	375.3	379.9	380.9
25°	362.8	365.6	367.0	372.1	372.5
27.5°	352.2	356.3	358.2	362.8	363.3
30°	341.5	345.2	348.5	353.6	354.5
32.5°	330.0	334.6	338.3	344.3	345.2
35°	317.5	323.0	327.7	334.1	335.5
37.5°	305.0	311.5	317.0	323.5	324.9
40°	292.9	299.0	305.4	312.4	314.2
42.5°	279.1	286.0	293.9	301.7	303.1
45°	264.7	273.5	282.3	290.2	292.5
47.5°	251.3	260.1	270.3	278.1	280.9
50°	236.5	246.7	256.8	266.1	268.9
52.5°	221.7	231.9	243.9	253.1	255.9
55°	207.3	217.0	230.9	240.2	243.0
57.5°	191.1	203.2	216.6	227.7	230.0
60°	175.4	187.4	202.7	213.3	217.0
62.5°	160.1	173.5	188.8	199.5	203.2
65°	143.5	158.3	174.0	185.6	189.3
67.5°	127.7	143.5	160.1	171.7	175.4
70°	111.5	127.3	144.9	157.3	160.6
72.5°	95.8	112.0	131.0	143.0	146.7
75°	79.6	96.7	116.2	129.1	133.3
77.5°	64.3	82.4	102.7	115.7	120.3
80°	50.4	69.0	89.3	103.2	106.9
82.5°	36.6	56.0	76.4	90.7	94.9
85°	24.5	44.0	64.8	78.7	83.3
87.5°	15.3	34.2	54.6	68.0	72.2
90°	7.4	25.9	45.8	59.2	62.9
92.5°	6.9	23.1	43.0	56.0	59.7
95°	6.0	21.3	40.3	52.8	56.9
97.5°	5.6	19.0	37.9	50.0	54.1
100°	5.1	17.1	35.2	47.7	50.9
102.5°	5.1	15.3	32.9	44.9	48.6
105°	4.2	13.4	30.5	42.1	45.8
107.5°	4.2	12.0	28.2	39.8	43.0
110°	3.7	10.2	26.4	37.0	40.7



TEST NUMBER: P1000329

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	3.2	8.8	24.1	34.2	37.9
115°	2.8	6.9	21.8	31.9	35.2
117.5°	2.8	5.6	19.4	29.2	32.9
120°	2.3	3.7	17.1	26.4	30.1
122.5°	2.3	2.3	14.8	24.1	27.3
125°	1.9	1.4	13.0	21.8	24.5
127.5°	1.9	1.4	10.6	19.0	22.2
130°	1.4	0.9	8.3	16.7	19.4
132.5°	1.4	0.9	6.5	14.3	17.1
135°	0.9	0.9	4.2	11.6	14.3
137.5°	0.9	0.5	2.3	9.3	11.6
140°	0.9	0.5	0.9	6.9	9.3
142.5°	0.5	0.5	0.0	5.1	6.9
145°	0.5	0.0	0.0	2.8	4.6
147.5°	0.5	0.0	0.0	0.5	2.3
150°	0.5	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)