

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000334

Luminaire Tested: SA4XXDP-B350DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000334
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDP-B350DB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Direct Recessed with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1482.0 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 13
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000334

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1000334

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84						
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73	70						
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	60						
4	83	71	63	56	81	70	62	56	67	60	55	65	59	54	63	58	53	51						
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44						
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39						
7	66	52	44	38	64	52	43	37	50	43	37	49	42	37	47	41	37	35						
8	61	48	39	34	60	47	39	34	46	39	33	45	38	33	43	37	33	31						
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28						
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25						

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4708	4708	4708
5°	4722	4666	4700
10°	4693	4628	4651
15°	4636	4562	4574
20°	4561	4480	4485
25°	4475	4387	4375
30°	4369	4278	4239
35°	4261	4163	4108
40°	4147	4033	3960
45°	4028	3906	3831
50°	3897	3792	3674
55°	3756	3644	3526
60°	3614	3479	3373
65°	3454	3321	3188
70°	3276	3111	2990
75°	3003	2858	2785
80°	2672	2564	2498
85°	2339	2255	2208

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4028 cd/sqm

TEST NUMBER: P1000334

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.4	3.7
10°-20°	153.3	10.3
20°-30°	225.7	15.2
30°-40°	262.3	17.7
40°-50°	262.3	17.7
50°-60°	229.4	15.5
60°-70°	170.3	11.5
70°-80°	96.6	6.5
80°-90°	27.7	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	433.4	29.2
0°-40°	695.7	46.9
0°-60°	1187.4	80.1
0°-90°	1482.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1482.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	577	577	577	577	577	
5°	577	575	570	575	574	55
15°	549	547	540	543	542	155
25°	497	494	488	488	486	229
35°	428	425	418	415	413	268
45°	349	346	339	334	332	269
55°	264	263	256	251	248	237
65°	179	177	172	168	165	177
75°	95	93	91	89	88	101
85°	25	25	24	24	24	28
90°	0	0	0	0	0	

TEST NUMBER: P1000334

CATALOG NUMBER: SA4XXDP-B350DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	577.4	577.4	577.4	577.4	577.4
2.5°	579.2	577.9	572.8	577.4	576.9
5°	576.9	575.1	570.0	575.1	574.2
7.5°	572.8	570.9	565.4	569.5	569.1
10°	566.8	564.9	558.9	562.6	561.7
12.5°	558.9	557.0	550.6	554.7	553.3
15°	549.2	547.3	540.4	543.2	541.8
17.5°	538.1	535.8	529.3	531.1	530.2
20°	525.6	523.3	516.3	517.7	516.8
22.5°	512.2	508.9	502.0	504.8	502.9
25°	497.4	494.1	487.6	488.1	486.3
27.5°	480.7	477.5	471.4	470.5	468.2
30°	464.0	460.3	454.3	452.5	450.2
32.5°	446.5	443.2	436.7	434.4	432.1
35°	428.0	424.7	418.2	415.0	412.7
37.5°	408.5	405.8	398.8	395.6	392.3
40°	389.6	385.9	378.9	374.3	372.0
42.5°	369.2	367.3	359.5	353.9	352.5
45°	349.3	346.1	338.7	333.6	332.2
47.5°	328.5	326.2	319.2	313.7	310.0
50°	307.2	305.4	298.9	292.4	289.6
52.5°	286.4	284.1	277.1	271.6	267.9
55°	264.2	262.8	256.3	250.8	248.0
57.5°	243.4	242.0	235.5	229.9	227.2
60°	221.6	219.3	213.3	209.1	206.8
62.5°	200.3	198.5	192.0	188.3	186.0
65°	179.0	176.7	172.1	167.5	165.2
67.5°	157.3	155.5	150.8	146.2	145.7
70°	137.4	134.2	130.5	126.8	125.4
72.5°	116.1	112.9	110.1	107.3	105.9
75°	95.3	93.0	90.7	88.8	88.4
77.5°	75.0	74.0	71.7	71.2	69.9
80°	56.9	55.5	54.6	53.7	53.2
82.5°	39.3	38.9	38.9	38.4	37.9
85°	25.0	25.0	24.1	24.1	23.6
87.5°	12.0	11.6	11.1	11.1	11.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)