

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000365

Luminaire Tested: SA4XXDP-B575DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000365
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDP-B575DB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct Recessed with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2468.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 24
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000365

CATALOG NUMBER: SA4XXDP-B575DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1000365

CATALOG NUMBER: SA4XXDP-B575DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20							
RC	80				70				50				30				10				0			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																								
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						
1	109	104	100	96	106	102	98	95	98	95	92	94	91	89	90	88	86	84						
2	99	91	84	79	97	89	83	78	86	80	76	82	78	74	79	76	73	70						
3	91	80	72	66	88	79	71	65	76	69	64	73	67	63	70	66	62	60						
4	83	71	63	56	81	70	62	56	67	60	55	65	59	54	63	58	53	51						
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44						
6	71	58	49	42	69	57	48	42	55	47	42	53	47	41	52	46	41	39						
7	66	52	44	38	64	52	43	37	50	43	37	49	42	37	47	41	37	35						
8	61	48	39	34	60	47	39	34	46	39	33	45	38	33	43	37	33	31						
9	57	44	36	30	56	43	36	30	42	35	30	41	35	30	40	34	30	28						
10	54	41	33	28	52	40	33	28	39	32	27	38	32	27	37	31	27	25						

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7841	7841	7841
5°	7865	7770	7827
10°	7815	7706	7745
15°	7720	7597	7616
20°	7596	7461	7468
25°	7453	7307	7286
30°	7277	7124	7059
35°	7095	6934	6842
40°	6905	6717	6595
45°	6708	6504	6380
50°	6490	6314	6119
55°	6254	6068	5872
60°	6020	5793	5617
65°	5754	5530	5308
70°	5455	5181	4978
75°	5000	4757	4638
80°	4452	4269	4161
85°	3892	3752	3677

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6708 cd/sqm

TEST NUMBER: P1000365

CATALOG NUMBER: SA4XXDP-B575DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.6	3.7
10°-20°	255.3	10.3
20°-30°	375.8	15.2
30°-40°	436.8	17.7
40°-50°	436.8	17.7
50°-60°	382.0	15.5
60°-70°	283.6	11.5
70°-80°	160.9	6.5
80°-90°	46.1	1.9
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	721.7	29.2
0°-40°	1158.6	46.9
0°-60°	1977.4	80.1
0°-90°	2468.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2468.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	962	962	962	962	962	
5°	961	958	949	958	956	91
15°	914	912	900	904	902	258
25°	828	823	812	813	810	381
35°	713	707	696	691	687	446
45°	582	576	564	556	553	448
55°	440	438	427	418	413	394
65°	298	294	287	279	275	295
75°	159	155	151	148	147	168
85°	42	42	40	40	39	47
90°	0	0	0	0	0	



TEST NUMBER: P1000365

CATALOG NUMBER: SA4XXDP-B575DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	961.5	961.5	961.5	961.5	961.5
2.5°	964.6	962.3	953.8	961.5	960.8
5°	960.8	957.7	949.2	957.7	956.2
7.5°	953.8	950.8	941.5	948.4	947.7
10°	943.8	940.7	930.7	936.9	935.4
12.5°	930.7	927.6	916.9	923.8	921.5
15°	914.5	911.5	899.9	904.5	902.2
17.5°	896.1	892.2	881.4	884.5	883.0
20°	875.3	871.4	859.8	862.2	860.6
22.5°	852.9	847.5	836.0	840.6	837.5
25°	828.3	822.9	812.1	812.8	809.8
27.5°	800.5	795.1	785.1	783.6	779.7
30°	772.8	766.6	756.6	753.5	749.7
32.5°	743.5	738.1	727.3	723.5	719.6
35°	712.7	707.3	696.5	691.1	687.3
37.5°	680.3	675.7	664.1	658.8	653.4
40°	648.7	642.6	631.0	623.3	619.5
42.5°	614.8	611.8	598.7	589.4	587.1
45°	581.7	576.3	564.0	555.5	553.2
47.5°	547.0	543.2	531.6	522.4	516.2
50°	511.6	508.5	497.7	486.9	482.3
52.5°	476.9	473.1	461.5	452.3	446.1
55°	439.9	437.6	426.8	417.6	413.0
57.5°	405.3	403.0	392.2	382.9	378.3
60°	369.1	365.2	355.2	348.3	344.4
62.5°	333.6	330.5	319.7	313.6	309.7
65°	298.2	294.3	286.6	278.9	275.1
67.5°	262.0	258.9	251.2	243.5	242.7
70°	228.8	223.4	217.3	211.1	208.8
72.5°	193.4	188.0	183.4	178.7	176.4
75°	158.7	154.9	151.0	147.9	147.2
77.5°	124.8	123.3	119.4	118.7	116.3
80°	94.8	92.5	90.9	89.4	88.6
82.5°	65.5	64.7	64.7	63.9	63.2
85°	41.6	41.6	40.1	40.1	39.3
87.5°	20.0	19.3	18.5	18.5	18.5
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)