

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000387

Luminaire Tested: SA4XXDP-B795DB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000387
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-16)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXDP-B795DB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct Recessed with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3228.0 lumens
Efficiency: N/A
Efficacy: 89.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000387

CATALOG NUMBER: SA4XXDP-B795DB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1000387

CATALOG NUMBER: SA4XXDP-B795DB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	117	117	117	117	114	114	114	114	107	107	107	101	101	101	95	95	95	95	95	95	92
1	105	100	95	91	102	97	93	89	91	88	84	86	83	80	81	79	77	77	77	77	74
2	95	86	79	73	92	84	77	71	79	73	68	74	70	66	70	67	63	63	63	63	60
3	87	75	67	60	83	73	65	59	69	62	57	65	60	55	62	57	53	53	53	53	50
4	79	66	57	50	76	65	56	49	61	54	48	58	52	47	55	49	45	45	45	45	43
5	73	59	50	43	70	58	49	42	55	47	41	52	45	40	49	44	39	39	39	39	37
6	67	53	44	37	64	52	43	37	49	42	36	47	40	35	45	39	34	34	34	34	32
7	62	48	39	33	60	47	38	32	45	37	32	43	36	31	41	35	30	30	30	30	28
8	58	44	35	29	56	43	35	29	41	33	28	39	32	28	37	31	27	27	27	27	25
9	54	40	32	26	52	39	31	26	38	30	25	36	29	25	34	29	24	24	24	24	22
10	50	37	29	24	49	36	29	23	35	28	23	33	27	23	32	26	22	22	22	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7759	7672	7733
10°	7725	7673	7743
15°	7671	7653	7725
20°	7581	7618	7710
25°	7479	7565	7679
30°	7368	7518	7647
35°	7240	7472	7652
40°	7144	7449	7663
45°	6994	7458	7728
50°	6873	7465	7815
55°	6753	7522	7913
60°	6553	7574	8110
65°	6342	7691	8366
70°	6092	7913	8772
75°	5747	8384	9619
80°	5429	9608	11500
85°	5258	13885	17852

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 87.5°

Luminance: 30921 cd/sqm

TEST NUMBER: P1000387

CATALOG NUMBER: SA4XXDP-B795DB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	2.8
10°-20°	257.0	8.0
20°-30°	388.6	12.0
30°-40°	470.2	14.6
40°-50°	497.1	15.4
50°-60°	467.8	14.5
60°-70°	388.2	12.0
70°-80°	272.4	8.4
80°-90°	153.6	4.8
90°-100°	91.4	2.8
100°-110°	67.7	2.1
110°-120°	45.4	1.4
120°-130°	25.6	0.8
130°-140°	11.1	0.3
140°-150°	2.2	0.1
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	735.4	22.8
0°-40°	1205.6	37.3
0°-60°	2170.4	67.2
0°-90°	2984.6	92.5
90°-120°	204.6	6.3
90°-150°	243.4	7.5
90°-180°	243.0	7.5
0°-180°	3228.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	17	59	105	136	144	12
95°	14	49	92	121	130	11
105°	10	31	70	96	105	11
115°	6	16	50	73	81	7
125°	4	3	30	50	56	4
135°	2	2	10	26	33	2
145°	1	0	0	6	11	1
155°	0	0	0	0	0	0
165°	0	0	0	0	0	0
175°	0	0	0	0	0	0
180°	0	0	0	0	0	0

TEST NUMBER: P1000387

CATALOG NUMBER: SA4XXDP-B795DB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	17.0	59.4	105.0	135.7	144.2
92.5°	15.9	53.0	98.6	128.3	136.8
95°	13.8	48.8	92.2	120.9	130.4
97.5°	12.7	43.5	86.9	114.5	124.0
100°	11.7	39.2	80.6	109.2	116.6
102.5°	11.7	35.0	75.3	102.8	111.3
105°	9.5	30.7	70.0	96.5	105.0
107.5°	9.5	27.6	64.7	91.2	98.6
110°	8.5	23.3	60.4	84.8	93.3



TEST NUMBER: P1000387

CATALOG NUMBER: SA4XXDP-B795DB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	7.4	20.1	55.1	78.5	86.9
115°	6.4	15.9	49.8	73.2	80.6
117.5°	6.4	12.7	44.5	66.8	75.3
120°	5.3	8.5	39.2	60.4	68.9
122.5°	5.3	5.3	33.9	55.1	62.6
125°	4.2	3.2	29.7	49.8	56.2
127.5°	4.2	3.2	24.4	43.5	50.9
130°	3.2	2.1	19.1	38.2	44.5
132.5°	3.2	2.1	14.8	32.9	39.2
135°	2.1	2.1	9.5	26.5	32.9
137.5°	2.1	1.1	5.3	21.2	26.5
140°	2.1	1.1	2.1	15.9	21.2
142.5°	1.1	1.1	0.0	11.7	15.9
145°	1.1	0.0	0.0	6.4	10.6
147.5°	1.1	0.0	0.0	1.1	5.3
150°	1.1	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)