

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008520

Luminaire Tested: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008520
REPORT IS A COMBINATION OF REPORTS P988711 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5118.0 lumens
Efficiency: N/A
Efficacy: 82.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 62.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008520

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008520

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47
3	84	75	68	62	78	70	64	59	62	57	53	53	50	47	46	43	41
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	41	38	36
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	25	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21
10	50	38	30	26	46	36	29	25	32	27	23	28	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23074	23074	23074
5°	23112	21953	21790
10°	22884	20821	20133
15°	22570	19484	18246
20°	22154	17965	16272
25°	21727	16405	14465
30°	21155	14887	12491
35°	20594	13356	10797
40°	20025	11853	9052
45°	19361	10300	7531
50°	18676	8803	6131
55°	17962	7306	4867
60°	17133	5843	3682
65°	16179	4454	2993
70°	15028	3231	2381
75°	13577	2464	1818
80°	11481	1668	1219
85°	8009	765	590

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19361 cd/sqm

TEST NUMBER: P1008520

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.6	2.7
10°-20°	375.1	7.3
20°-30°	526.6	10.3
30°-40°	574.0	11.2
40°-50°	527.5	10.3
50°-60°	414.3	8.1
60°-70°	269.7	5.3
70°-80°	138.8	2.7
80°-90°	36.7	0.7
90°-100°	23.8	0.5
100°-110°	88.8	1.7
110°-120°	235.6	4.6
120°-130°	390.8	7.6
130°-140°	415.1	8.1
140°-150°	385.8	7.5
150°-160°	310.2	6.1
160°-170°	199.9	3.9
170°-180°	68.8	1.3
0°-30°	1038.2	20.3
0°-40°	1612.2	31.5
0°-60°	2554.0	49.9
0°-90°	2999.3	58.6
90°-120°	348.3	6.8
90°-150°	1539.9	30.1
90°-180°	2119.0	41.4
0°-180°	5118.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1446	1442	138
15°	1386	1372	1327	1302	1289	391
25°	1258	1216	1129	1075	1055	579
35°	1084	1017	901	818	789	679
45°	886	798	660	566	534	685
55°	674	571	429	350	324	602
65°	455	348	230	185	181	451
75°	243	150	106	96	95	257
85°	57	29	25	25	25	65
90°	0	6	10	13	14	5
95°	34	17	20	23	22	40
105°	159	175	32	38	40	170
115°	301	310	323	80	43	296
125°	425	432	442	446	447	379
135°	526	534	539	544	543	406
145°	610	610	619	622	620	382
155°	672	667	674	677	672	310
165°	708	705	706	710	706	200
175°	724	721	722	725	720	69
180°	723	723	723	723	723	

TEST NUMBER: P1008520

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1457.7	1457.7	1457.7	1457.7	1457.7
2.5°	1464.3	1457.7	1443.2	1456.4	1453.8
5°	1457.7	1451.1	1434.0	1445.9	1441.9
7.5°	1445.9	1437.9	1419.5	1424.7	1418.1
10°	1430.0	1420.8	1394.4	1390.4	1382.5
12.5°	1410.2	1398.4	1362.7	1354.8	1340.3
15°	1386.5	1372.0	1327.1	1302.1	1288.9
17.5°	1358.8	1337.7	1282.3	1253.2	1232.1
20°	1327.1	1300.7	1234.8	1201.8	1172.8
22.5°	1292.8	1262.5	1186.0	1141.1	1121.3
25°	1258.5	1216.3	1129.2	1075.2	1055.4
27.5°	1217.6	1172.8	1076.5	1014.5	984.1
30°	1174.1	1124.0	1018.4	951.1	915.5
32.5°	1131.9	1071.2	963.0	883.9	850.9
35°	1084.4	1017.1	901.0	817.9	788.9
37.5°	1038.2	965.7	843.0	751.9	719.0
40°	989.4	910.3	782.3	688.6	654.3
42.5°	939.3	854.8	721.6	624.0	591.0
45°	886.5	798.1	659.6	565.9	534.3
47.5°	836.4	742.7	600.2	506.6	477.6
50°	781.0	687.3	542.2	451.2	423.5
52.5°	726.9	627.9	486.8	399.7	374.7
55°	674.1	571.2	428.7	349.6	324.5
57.5°	620.0	514.5	377.3	303.4	282.3
60°	564.6	459.1	323.2	255.9	234.8
62.5°	510.5	405.0	277.0	213.7	203.2
65°	455.1	348.3	229.5	184.7	180.7
67.5°	402.4	295.5	184.7	162.3	158.3
70°	347.0	244.1	153.0	139.8	134.6
72.5°	294.2	196.6	128.0	117.4	114.8
75°	242.7	150.4	105.5	96.3	95.0
77.5°	191.3	106.9	83.1	77.8	75.2
80°	143.8	76.5	63.3	58.0	58.0
82.5°	100.3	51.4	43.5	40.9	40.9
85°	56.7	29.0	25.1	25.1	25.1
87.5°	21.1	10.6	10.6	9.2	9.2
90°	0.5	6.3	10.5	13.1	14.1
92.5°	13.1	11.0	12.6	13.6	14.1
95°	34.0	16.7	20.4	23.0	22.5
97.5°	61.2	18.3	26.7	28.2	28.8
100°	92.6	20.9	29.8	34.0	35.0
102.5°	127.1	126.0	30.9	36.6	38.2
105°	159.0	174.7	31.9	37.7	39.7
107.5°	196.1	209.2	32.9	38.7	40.8
110°	231.7	242.6	91.5	39.2	41.3

TEST NUMBER: P1008520

CATALOG NUMBER: S122RDIP-B865D530UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	265.1	274.5	265.7	40.3	41.8
115°	300.7	309.6	322.7	80.5	42.9
117.5°	331.5	342.0	350.9	276.1	139.1
120°	366.1	373.9	383.3	389.6	319.0
122.5°	395.3	403.7	414.2	417.3	417.8
125°	425.2	432.0	441.9	445.5	447.1
127.5°	452.3	459.7	467.5	472.7	473.3
130°	478.0	486.3	492.1	497.8	497.3
132.5°	504.1	510.9	516.7	521.4	520.9
135°	526.1	534.4	539.2	544.4	543.3
137.5°	549.1	555.4	560.6	565.8	564.3
140°	571.6	575.8	581.5	586.2	583.6
142.5°	590.4	594.1	600.9	605.0	602.4
145°	610.3	609.8	618.6	622.3	619.7
147.5°	627.5	626.0	634.9	637.5	635.4
150°	644.3	640.6	649.0	652.1	649.5
152.5°	658.4	654.2	662.0	665.2	661.5
155°	672.0	667.3	673.6	676.7	672.5
157.5°	683.0	678.8	683.5	687.1	683.0
160°	692.4	689.2	692.4	695.5	691.9
162.5°	700.7	697.6	700.2	703.9	699.2
165°	708.1	704.9	706.5	710.2	706.5
167.5°	713.8	710.7	712.2	715.9	711.2
170°	718.5	715.4	716.4	720.1	715.4
172.5°	721.7	718.5	719.6	723.2	718.5
175°	724.3	720.6	721.7	725.3	720.1
177.5°	725.3	721.7	722.2	725.8	721.1
180°	722.7	722.7	722.7	722.7	722.7

(END OF REPORT)