

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000418

Luminaire Tested: SA4XXRDP-B1020DB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000418
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXRDP-B1020DB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Regressed Direct Recessed with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4165.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 46.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000418

CATALOG NUMBER: SA4XXRDP-B1020DB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1000418

CATALOG NUMBER: SA4XXRDP-B1020DB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	110	105	101	98	107	103	99	96	99	96	93		95	92	90		91	89	87		85
2	100	93	86	81	98	91	85	80	87	82	78		84	80	76		81	78	74		72
3	92	82	74	68	89	80	73	67	77	71	66		75	69	65		72	68	64		62
4	84	73	65	58	82	72	64	58	69	62	57		67	61	56		65	60	56		54
5	78	66	57	51	76	65	56	50	62	55	50		61	54	49		59	53	49		47
6	72	59	51	45	70	58	50	44	57	49	44		55	49	44		53	48	43		41
7	67	54	46	40	65	53	45	40	52	45	39		50	44	39		49	43	39		37
8	63	50	41	36	61	49	41	36	48	40	35		46	40	35		45	39	35		33
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42	36	32		30
10	55	42	35	29	54	42	34	29	41	34	29		40	33	29		39	33	29		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14699	14699	14699
5°	14732	14552	14642
10°	14640	14377	14377
15°	14472	14076	13971
20°	14241	13678	13426
25°	13946	13213	12878
30°	13659	12723	12190
35°	13341	12215	11500
40°	12958	11636	10755
45°	12606	11062	9996
50°	12204	10400	9192
55°	11773	9713	8320
60°	11300	8959	7429
65°	10865	8015	6551
70°	10233	6976	5562
75°	9436	5785	4521
80°	8232	4410	4147
85°	6970	4004	3742

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12606 cd/sqm

TEST NUMBER: P1000418

CATALOG NUMBER: SA4XXRDP-B1020DB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.5	4.1
10°-20°	472.6	11.3
20°-30°	682.3	16.4
30°-40°	773.3	18.6
40°-50°	746.6	17.9
50°-60°	620.7	14.9
60°-70°	428.4	10.3
70°-80°	216.5	5.2
80°-90°	55.0	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1324.4	31.8
0°-40°	2097.7	50.4
0°-60°	3465.1	83.2
0°-90°	4165.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4165.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1803	1803	1803	1803	1803	
5°	1800	1794	1778	1792	1789	171
15°	1714	1702	1667	1664	1655	483
25°	1550	1525	1468	1445	1431	714
35°	1340	1296	1227	1180	1155	838
45°	1093	1042	959	892	867	843
55°	828	773	683	611	585	741
65°	563	504	415	356	340	556
75°	300	248	184	152	144	316
85°	74	47	43	40	40	86
90°	0	0	0	0	0	

TEST NUMBER: P1000418

CATALOG NUMBER: SA4XXRDP-B1020DB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1802.6	1802.6	1802.6	1802.6	1802.6
2.5°	1808.1	1802.6	1787.4	1802.6	1801.2
5°	1799.8	1794.3	1777.7	1791.5	1788.8
7.5°	1787.4	1781.9	1761.2	1770.8	1766.7
10°	1768.1	1761.2	1736.3	1741.8	1736.3
12.5°	1743.2	1734.9	1704.6	1707.3	1699.0
15°	1714.2	1701.8	1667.3	1664.5	1654.9
17.5°	1681.1	1663.2	1623.1	1616.2	1602.4
20°	1641.1	1623.1	1576.2	1565.2	1547.2
22.5°	1596.9	1576.2	1525.1	1507.2	1493.4
25°	1550.0	1525.1	1468.5	1445.1	1431.3
27.5°	1501.7	1471.3	1412.0	1384.4	1365.0
30°	1450.6	1416.1	1351.2	1316.7	1294.6
32.5°	1396.8	1356.7	1289.1	1247.7	1227.0
35°	1340.2	1296.0	1227.0	1180.1	1155.2
37.5°	1280.8	1235.3	1159.4	1108.3	1083.5
40°	1217.3	1171.8	1093.1	1035.2	1010.3
42.5°	1156.6	1108.3	1025.5	966.1	939.9
45°	1093.1	1042.1	959.2	891.6	866.8
47.5°	1028.3	975.8	890.2	819.8	792.2
50°	962.0	908.2	819.8	750.8	724.6
52.5°	894.4	841.9	750.8	680.4	652.8
55°	828.1	772.9	683.2	611.4	585.2
57.5°	763.3	705.3	617.0	543.8	524.5
60°	692.9	637.7	549.3	477.6	455.5
62.5°	629.4	571.4	480.3	415.4	398.9
65°	563.1	503.8	415.4	356.1	339.5
67.5°	494.1	437.5	354.7	302.3	282.9
70°	429.2	371.3	292.6	247.1	233.3
72.5°	360.2	309.2	236.0	198.8	186.3
75°	299.5	248.4	183.6	151.8	143.5
77.5°	236.0	191.8	136.6	114.6	111.8
80°	175.3	135.3	93.9	89.7	88.3
82.5°	122.8	87.0	67.6	64.9	63.5
85°	74.5	46.9	42.8	40.0	40.0
87.5°	31.7	20.7	19.3	17.9	19.3
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)