

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1000499

Luminaire Tested: SA4XXRDP-B795DB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/2/2025

Test Information

Test Method: LM-79-2019
Report Number: P1000499
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-26)
Test Lab: INNOVATION CENTER
Issue Date: 5/2/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: SA4XXRDP-B795DB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Regressed Direct Recessed with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3208.0 lumens
Efficiency: N/A
Efficacy: 89.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular (W 0.33' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 35.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1000499

CATALOG NUMBER: SA4XXRDP-B795DB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1000499

CATALOG NUMBER: SA4XXRDP-B795DB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	110	105	101	98	107	103	99	96	99	96	93		95	92	90		91	89	87		85
2	100	93	86	81	98	91	85	80	87	82	78		84	80	76		81	78	74		72
3	92	82	74	68	89	80	73	67	77	71	66		75	69	65		72	68	64		62
4	84	73	65	58	82	72	64	58	69	62	57		67	61	56		65	60	56		54
5	78	66	57	51	76	65	56	50	62	55	50		61	54	49		59	53	49		47
6	72	59	51	45	70	58	50	44	57	49	44		55	49	44		53	48	43		41
7	67	54	46	40	65	53	45	40	52	45	39		50	44	39		49	43	39		37
8	63	50	41	36	61	49	41	36	48	40	35		46	40	35		45	39	35		33
9	59	46	38	32	57	45	37	32	44	37	32		43	36	32		42	36	32		30
10	55	42	35	29	54	42	34	29	41	34	29		40	33	29		39	33	29		27

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11322	11322	11322
5°	11348	11208	11277
10°	11276	11074	11074
15°	11146	10841	10760
20°	10969	10535	10341
25°	10741	10177	9919
30°	10520	9800	9390
35°	10275	9408	8858
40°	9981	8963	8284
45°	9710	8520	7699
50°	9400	8011	7080
55°	9068	7481	6408
60°	8704	6900	5721
65°	8368	6174	5046
70°	7882	5374	4284
75°	7269	4455	3485
80°	6340	3395	3193
85°	5370	3088	2882

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 9710 cd/sqm

TEST NUMBER: P1000499

CATALOG NUMBER: SA4XXRDP-B795DB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.6	4.1
10°-20°	364.0	11.3
20°-30°	525.5	16.4
30°-40°	595.6	18.6
40°-50°	575.1	17.9
50°-60°	478.1	14.9
60°-70°	330.0	10.3
70°-80°	166.8	5.2
80°-90°	42.3	1.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1020.1	31.8
0°-40°	1615.7	50.4
0°-60°	2668.9	83.2
0°-90°	3208.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3208.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1388	1388	1388	1388	1388	
5°	1386	1382	1369	1380	1378	132
15°	1320	1311	1284	1282	1275	372
25°	1194	1175	1131	1113	1102	550
35°	1032	998	945	909	890	645
45°	842	803	739	687	668	649
55°	638	595	526	471	451	571
65°	434	388	320	274	262	428
75°	231	191	141	117	111	243
85°	57	36	33	31	31	66
90°	0	0	0	0	0	



TEST NUMBER: P1000499

CATALOG NUMBER: SA4XXRDP-B795DB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1388.4	1388.4	1388.4	1388.4	1388.4
2.5°	1392.6	1388.4	1376.7	1388.4	1387.3
5°	1386.3	1382.0	1369.2	1379.9	1377.7
7.5°	1376.7	1372.4	1356.5	1363.9	1360.7
10°	1361.8	1356.5	1337.4	1341.6	1337.4
12.5°	1342.7	1336.3	1312.9	1315.0	1308.6
15°	1320.3	1310.8	1284.2	1282.1	1274.6
17.5°	1294.8	1281.0	1250.2	1244.9	1234.2
20°	1264.0	1250.2	1214.0	1205.5	1191.7
22.5°	1230.0	1214.0	1174.7	1160.9	1150.3
25°	1193.8	1174.7	1131.1	1113.0	1102.4
27.5°	1156.6	1133.2	1087.5	1066.3	1051.4
30°	1117.3	1090.7	1040.8	1014.2	997.2
32.5°	1075.8	1045.0	992.9	961.0	945.1
35°	1032.2	998.2	945.1	908.9	889.8
37.5°	986.5	951.5	893.0	853.7	834.5
40°	937.6	902.6	842.0	797.3	778.2
42.5°	890.9	853.7	789.9	744.2	724.0
45°	842.0	802.6	738.8	686.7	667.6
47.5°	792.0	751.6	685.7	631.5	610.2
50°	741.0	699.5	631.5	578.3	558.1
52.5°	688.9	648.5	578.3	524.1	502.8
55°	637.8	595.3	526.2	470.9	450.7
57.5°	587.9	543.2	475.2	418.9	404.0
60°	533.7	491.1	423.1	367.8	350.8
62.5°	484.8	440.1	370.0	320.0	307.2
65°	433.7	388.0	320.0	274.3	261.5
67.5°	380.6	337.0	273.2	232.8	217.9
70°	330.6	286.0	225.4	190.3	179.7
72.5°	277.5	238.1	181.8	153.1	143.5
75°	230.7	191.4	141.4	116.9	110.6
77.5°	181.8	147.8	105.2	88.2	86.1
80°	135.0	104.2	72.3	69.1	68.0
82.5°	94.6	67.0	52.1	50.0	48.9
85°	57.4	36.1	33.0	30.8	30.8
87.5°	24.5	15.9	14.9	13.8	14.9
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)