

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008556

Luminaire Tested: S122DIP-B1005D1080UB30-4F0-XX-W2A-D

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008556
REPORT IS A COMBINATION OF REPORTS P983545 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB30-4F0-XX-W2A-D
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8351.0 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008556

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-D

Luminous Intensity Polar Plot



TEST NUMBER: P1008556

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	90	86	82	86	82	79	75	68	65	63	54	52	51	42	41	39
2	86	78	71	66	78	71	65	61	59	54	51	47	44	41	36	34	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	17	15
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16776	16776	16776
5°	16852	16061	15970
10°	16739	15504	15278
15°	16503	14928	14568
20°	16206	14325	13895
25°	15911	13746	13284
30°	15499	13158	12680
35°	15081	12591	12236
40°	14643	12101	11794
45°	14224	11657	11410
50°	13774	11247	11030
55°	13302	10812	10643
60°	12723	10358	10237
65°	12122	9838	9768
70°	11442	9278	9266
75°	10567	8720	8791
80°	9197	8135	8300
85°	7811	7586	7873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14224 cd/sqm

TEST NUMBER: P1008556

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.5	1.2
10°-20°	288.2	3.5
20°-30°	436.6	5.2
30°-40°	531.7	6.4
40°-50°	572.0	6.9
50°-60°	555.5	6.7
60°-70°	485.2	5.8
70°-80°	373.4	4.5
80°-90°	252.7	3.0
90°-100°	221.0	2.6
100°-110°	306.5	3.7
110°-120°	561.9	6.7
120°-130°	840.2	10.1
130°-140°	862.7	10.3
140°-150°	787.0	9.4
150°-160°	630.1	7.5
160°-170°	406.0	4.9
170°-180°	139.7	1.7
0°-30°	825.2	9.9
0°-40°	1356.9	16.2
0°-60°	2484.5	29.8
0°-90°	3595.7	43.1
90°-120°	1089.3	13.0
90°-150°	3579.3	42.9
90°-180°	4755.0	56.9
0°-180°	8351.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1060	1060	1060	1060	1060	
5°	1063	1058	1049	1058	1057	101
15°	1014	1017	1017	1031	1029	286
25°	922	932	946	965	969	424
35°	794	820	849	883	894	496
45°	651	693	746	794	810	503
55°	499	554	634	690	710	447
65°	341	416	507	570	590	339
75°	189	275	373	439	459	200
85°	55	150	249	313	335	58
90°	16	117	224	291	311	15
95°	81	118	218	282	299	91
105°	331	407	197	262	284	354
115°	617	652	748	302	242	607
125°	867	881	950	999	1016	774
135°	1070	1087	1112	1155	1165	827
145°	1240	1239	1257	1274	1276	776
155°	1365	1356	1368	1375	1366	629
165°	1438	1432	1435	1443	1435	406
175°	1471	1464	1466	1474	1463	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P1008556

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-D

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1067.5	1062.9	1052.2	1059.8	1056.8
5°	1062.9	1058.3	1049.1	1058.3	1056.8
7.5°	1055.2	1052.2	1044.5	1055.2	1053.7
10°	1046.0	1042.9	1038.3	1050.6	1049.1
12.5°	1030.7	1032.2	1029.1	1041.4	1039.9
15°	1013.8	1016.8	1016.8	1030.7	1029.1
17.5°	992.3	998.4	1003.0	1016.8	1016.8
20°	970.8	978.4	984.6	1001.5	1001.5
22.5°	947.7	956.9	966.1	983.0	986.1
25°	921.6	932.4	946.2	964.6	969.2
27.5°	890.9	907.8	923.1	946.2	949.3
30°	860.2	880.1	900.1	924.7	929.3
32.5°	826.4	849.4	874.0	903.2	912.4
35°	794.1	820.2	849.4	883.2	894.0
37.5°	758.8	788.0	824.8	861.7	872.5
40°	723.5	757.3	798.7	838.7	852.5
42.5°	689.7	723.5	772.6	817.2	831.0
45°	651.3	692.7	746.5	794.1	809.5
47.5°	614.4	658.9	720.4	769.5	786.4
50°	576.0	623.6	692.7	745.0	761.9
52.5°	539.1	589.8	663.6	717.3	735.7
55°	499.2	554.5	634.4	689.7	709.6
57.5°	460.8	522.2	602.1	662.0	682.0
60°	419.3	485.4	572.9	631.3	652.8
62.5°	382.5	451.6	539.1	602.1	622.1
65°	341.0	416.3	506.9	569.9	589.8
67.5°	304.1	382.5	474.6	537.6	559.1
70°	264.2	344.1	439.3	505.3	523.8
72.5°	227.3	310.3	407.0	471.6	494.6
75°	188.9	274.9	373.3	439.3	459.3
77.5°	152.1	241.2	341.0	407.0	428.5
80°	115.2	208.9	308.7	373.3	394.8
82.5°	84.5	176.6	278.0	342.5	362.5
85°	55.3	150.5	248.8	313.3	334.8
87.5°	33.8	126.0	224.3	287.2	307.2
90°	16.5	117.1	224.0	290.8	311.3
92.5°	40.4	117.5	214.4	276.4	296.0
95°	81.4	118.5	218.0	281.7	299.1
97.5°	135.1	114.0	220.1	280.1	299.6
100°	198.8	110.1	214.2	279.5	298.5
102.5°	267.4	315.9	205.5	272.5	292.6
105°	330.7	407.0	196.9	262.4	283.5
107.5°	406.1	469.5	188.2	252.2	273.4
110°	476.7	529.9	298.0	241.0	262.1

TEST NUMBER: P1008556

CATALOG NUMBER: S122DIP-B1005D1080UB30-4F0-XX-W2A-D

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	544.7	588.5	641.1	232.3	252.4
115°	617.0	651.9	747.7	301.8	242.2
117.5°	678.2	711.7	794.3	688.5	425.4
120°	748.3	770.4	851.0	906.7	780.2
122.5°	807.8	826.3	904.4	952.2	967.2
125°	866.8	880.7	949.9	998.9	1015.9
127.5°	922.1	935.4	992.8	1041.8	1056.7
130°	974.1	989.5	1033.5	1082.1	1093.3
132.5°	1027.3	1039.5	1074.3	1119.1	1130.4
135°	1070.3	1087.3	1112.2	1155.2	1165.2
137.5°	1117.0	1129.8	1148.1	1187.9	1195.5
140°	1162.7	1169.7	1184.5	1218.6	1222.6
142.5°	1201.0	1206.9	1220.7	1247.6	1250.0
145°	1239.8	1238.8	1256.8	1273.5	1275.9
147.5°	1274.9	1271.7	1289.8	1296.6	1296.9
150°	1308.9	1301.5	1318.5	1324.8	1319.5
152.5°	1337.6	1329.1	1345.0	1351.4	1344.0
155°	1365.2	1355.6	1368.4	1374.8	1366.3
157.5°	1387.5	1379.0	1388.6	1396.0	1387.5
160°	1406.6	1400.3	1406.6	1413.0	1405.6
162.5°	1423.6	1417.3	1422.6	1430.0	1420.4
165°	1438.5	1432.1	1435.3	1442.8	1435.3
167.5°	1450.2	1443.8	1447.0	1454.4	1444.9
170°	1459.8	1453.4	1455.5	1462.9	1453.4
172.5°	1466.1	1459.8	1461.9	1469.3	1459.8
175°	1471.4	1464.0	1466.1	1473.6	1462.9
177.5°	1473.6	1466.1	1467.2	1474.6	1465.1
180°	1468.3	1468.3	1468.3	1468.3	1468.3

(END OF REPORT)