

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331626-830

Luminaire Tested: **SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331626-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2920.6 lumens
Efficiency: N/A
Efficacy: 114.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331626-830
CATALOG NUMBER: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331626-830

CATALOG NUMBER: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	33
1	94	90	87	83	85	82	78	76	65	63	61	50	49	48	37	36	35	29
2	86	79	73	68	78	72	67	63	58	54	51	45	42	40	33	31	30	25
3	79	70	63	57	71	63	57	53	51	47	43	40	37	34	29	27	26	21
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	23	18
5	66	55	47	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16
6	61	50	42	36	55	45	38	34	37	32	28	29	25	23	22	19	18	14
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	18	16	13
8	52	41	33	28	47	37	31	26	30	26	22	24	21	18	18	16	14	12
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	13	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7640	7640	7640
5°	7669	7543	7585
10°	7609	7420	7356
15°	7522	7199	6992
20°	7400	6887	6541
25°	7277	6531	6102
30°	7105	6162	5541
35°	6936	5765	5048
40°	6768	5351	4477
45°	6572	4889	3959
50°	6365	4421	3451
55°	6159	3916	2967
60°	5916	3387	2464
65°	5643	2846	2239
70°	5316	2346	2058
75°	4916	2133	1921
80°	4342	1906	1757
85°	3409	1501	1501



TEST NUMBER: P331626-830

CATALOG NUMBER: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	1.5
10°-20°	121.6	4.2
20°-30°	170.8	5.8
30°-40°	186.2	6.4
40°-50°	171.2	5.9
50°-60°	134.5	4.6
60°-70°	87.7	3.0
70°-80°	45.2	1.5
80°-90°	14.2	0.5
90°-100°	111.8	3.8
100°-110°	379.3	13.0
110°-120°	402.9	13.8
120°-130°	331.7	11.4
130°-140°	266.3	9.1
140°-150°	201.3	6.9
150°-160°	141.4	4.8
160°-170°	83.3	2.9
170°-180°	27.1	0.9
0°-30°	336.6	11.5
0°-40°	522.8	17.9
0°-60°	828.5	28.4
0°-90°	975.6	33.4
90°-120°	893.9	30.6
90°-150°	1693.2	58.0
90°-180°	1945.0	66.6
0°-180°	2920.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	473	473	473	473	473	
5°	473	471	465	469	468	45
15°	450	445	431	423	418	127
25°	408	394	367	350	342	188
35°	352	329	292	266	256	220
45°	288	258	214	185	173	222
55°	219	185	139	114	105	195
65°	148	113	74	61	59	146
75°	79	50	34	31	31	83
85°	18	10	8	8	8	22
90°	1	7	18	17	18	2
95°	19	46	211	80	61	20
105°	66	99	398	712	606	70
115°	116	146	333	688	797	115
125°	161	191	320	557	647	143
135°	189	226	317	468	536	146
145°	216	248	315	391	428	136
155°	246	265	306	346	360	113
165°	268	276	293	311	316	75
175°	279	279	282	285	284	26
180°	280	280	280	280	280	



TEST NUMBER: P331626-830

CATALOG NUMBER: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	474.9	474.5	474.1	473.7	473.3	472.7	471.8	471.1	470.2	469.4	470.1
5°	473.2	472.7	472.2	471.7	471.3	470.3	469.1	467.9	466.7	465.4	466.3
7.5°	468.3	467.7	467.0	466.5	465.9	464.9	463.4	461.9	460.5	459.1	459.3
10°	464.1	463.4	462.8	462.1	461.5	460.1	458.3	456.4	454.5	452.6	452.3
12.5°	459.0	458.2	457.3	456.6	455.7	454.1	451.7	449.2	446.8	444.3	443.8
15°	450.0	448.9	447.9	446.9	445.8	443.7	440.5	437.2	433.9	430.7	429.0
17.5°	438.9	437.3	435.7	434.1	432.5	429.7	425.6	421.4	417.3	413.1	410.9
20°	430.7	428.9	427.0	425.0	423.1	419.8	415.0	410.3	405.6	400.8	398.4
22.5°	421.9	419.7	417.5	415.5	413.3	409.5	404.2	398.8	393.5	388.1	385.0
25°	408.5	405.4	402.4	399.4	396.3	391.6	385.3	379.1	372.8	366.6	362.6
27.5°	392.4	389.1	385.8	382.5	379.1	373.9	366.8	359.8	352.7	345.6	341.1
30°	381.1	377.5	373.8	370.2	366.6	361.0	353.4	345.8	338.2	330.5	325.7
32.5°	370.1	365.9	361.7	357.4	353.2	347.2	339.5	331.7	324.0	316.1	310.7
35°	351.9	347.1	342.2	337.4	332.5	325.9	317.5	309.2	300.9	292.5	286.4
37.5°	333.8	328.5	323.1	317.8	312.5	305.4	296.4	287.5	278.6	269.7	263.1
40°	321.1	315.5	309.7	304.0	298.3	290.9	281.6	272.4	263.2	253.9	247.1
42.5°	308.1	302.1	296.1	290.1	284.1	276.3	266.7	257.2	247.7	238.2	231.2
45°	287.8	281.3	274.9	268.6	262.2	254.0	244.0	234.0	224.0	214.1	207.4
47.5°	267.9	261.1	254.4	247.6	240.8	232.3	222.0	211.7	201.3	191.1	184.4
50°	253.4	246.8	240.0	233.2	226.5	217.8	207.4	196.9	186.4	176.0	169.4
52.5°	239.4	232.3	225.4	218.3	211.2	202.6	192.3	182.1	171.8	161.6	155.2
55°	218.8	211.4	204.0	196.5	189.1	180.3	169.9	159.7	149.4	139.1	133.5
57.5°	197.7	190.0	182.4	174.8	167.2	158.4	148.5	138.7	128.8	118.9	113.7
60°	183.2	175.7	168.1	160.4	152.8	144.1	134.3	124.5	114.7	104.9	100.0
62.5°	169.2	161.6	154.0	146.4	138.7	130.3	120.9	111.6	102.3	92.9	88.3
65°	147.7	140.0	132.3	124.6	116.9	108.8	100.2	91.6	83.0	74.5	71.3
67.5°	127.0	119.3	111.7	104.1	96.4	88.7	81.0	73.3	65.6	57.9	56.4
70°	112.6	105.2	97.7	90.4	82.9	76.0	69.4	62.8	56.3	49.7	48.7
72.5°	98.9	91.8	84.6	77.6	70.4	64.3	59.0	53.7	48.4	43.2	42.3
75°	78.8	72.1	65.5	58.8	52.1	47.2	43.9	40.7	37.5	34.2	33.6
77.5°	59.0	53.2	47.3	41.5	35.6	32.0	30.3	28.8	27.2	25.7	25.4
80°	46.7	41.8	36.9	32.1	27.2	24.3	23.4	22.4	21.5	20.5	20.2
82.5°	35.3	31.6	27.8	24.0	20.3	18.0	17.3	16.7	16.0	15.5	15.2
85°	18.4	16.4	14.4	12.4	10.5	9.2	9.0	8.7	8.4	8.1	8.1
87.5°	5.6	5.3	5.1	4.7	4.3	4.3	4.9	5.7	6.3	6.4	6.2
90°	0.6	2.2	4.3	5.4	6.4	8.1	10.7	14.5	17.7	18.3	17.7
92.5°	6.6	9.4	13.3	15.7	19.3	24.4	36.6	53.6	68.9	69.8	59.0
95°	18.9	20.9	26.3	31.2	39.8	52.7	77.4	124.1	186.5	210.8	184.4
97.5°	30.6	33.6	39.2	46.6	56.5	71.1	102.2	167.3	270.9	359.7	377.3
100°	41.4	43.0	47.9	56.5	67.2	82.3	110.7	176.3	292.4	424.6	502.0
102.5°	51.3	52.5	57.3	65.9	77.1	92.1	118.5	176.7	284.3	426.8	548.5
105°	65.6	67.8	71.4	79.6	91.3	106.4	131.7	179.6	268.2	398.3	541.3
107.5°	81.1	82.8	86.4	93.9	105.6	120.7	145.2	186.9	260.2	367.8	494.1
110°	91.3	93.5	96.8	103.8	115.0	130.6	154.3	192.9	258.5	353.2	464.4



TEST NUMBER: P331626-830

CATALOG NUMBER: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	100.9	103.0	106.6	113.2	124.0	140.1	162.9	199.4	259.0	343.7	443.7
115°	115.6	118.3	121.5	127.9	138.6	153.2	176.3	209.1	261.3	333.3	418.2
117.5°	130.8	133.0	136.2	141.9	152.2	167.3	188.7	219.4	265.1	328.2	402.1
120°	140.3	142.4	145.6	150.5	161.3	176.3	197.3	226.3	267.7	325.2	393.5
122.5°	149.3	151.1	154.3	159.6	170.3	185.8	205.5	232.3	270.7	323.5	386.2
125°	161.3	162.9	166.1	172.6	183.3	198.3	217.7	241.9	275.2	320.4	375.7
127.5°	170.7	172.9	177.4	184.5	194.8	210.3	229.1	250.8	279.8	318.6	366.1
130°	176.3	178.4	183.8	191.3	202.1	217.2	236.0	256.4	283.2	317.6	359.6
132.5°	181.4	184.1	189.8	197.8	209.0	224.0	242.0	262.0	286.7	317.3	354.4
135°	189.2	191.3	197.8	205.9	218.2	233.3	250.5	269.3	290.8	316.6	347.2
137.5°	196.5	199.1	205.6	214.1	226.4	240.3	257.4	274.8	294.5	316.5	342.1
140°	202.1	204.2	210.8	219.3	231.1	245.2	261.3	277.9	296.1	316.0	339.2
142.5°	207.7	209.4	215.5	224.0	235.4	248.5	264.3	280.5	297.5	316.0	336.2
145°	216.1	218.2	223.6	231.7	242.4	254.2	268.7	283.8	298.9	315.0	332.2
147.5°	225.1	226.7	231.9	239.3	248.3	258.7	272.4	285.7	299.3	313.0	328.1
150°	231.1	232.7	237.0	244.0	252.1	261.7	274.1	286.5	298.9	311.8	324.7
152.5°	237.1	237.9	242.2	248.4	256.0	264.8	275.9	286.9	298.0	309.6	321.7
155°	245.6	246.2	249.4	255.3	261.3	269.3	278.4	287.6	296.7	305.9	316.0
157.5°	252.7	253.3	255.9	261.0	265.8	272.5	280.2	287.6	294.3	302.0	310.8
160°	257.5	258.0	260.1	264.5	268.7	274.7	281.2	287.6	292.9	299.4	306.9
162.5°	262.2	261.8	264.0	267.5	271.4	276.0	281.5	287.1	291.6	297.3	303.5
165°	267.7	267.1	268.2	271.5	274.1	277.4	282.2	286.0	289.2	292.9	297.7
167.5°	272.2	271.5	272.5	274.6	276.5	278.5	282.1	285.2	286.7	289.2	292.2
170°	275.2	274.1	274.7	276.3	277.4	279.0	281.6	284.4	285.4	287.0	289.2
172.5°	276.9	276.3	276.0	277.6	278.2	279.4	281.3	283.0	283.7	284.5	286.2
175°	279.0	278.4	277.9	279.0	279.0	279.5	280.6	281.6	281.2	281.6	282.2
177.5°	279.9	279.1	278.6	279.5	279.5	279.5	279.9	280.8	279.9	279.5	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5



TEST NUMBER: P331626-830

CATALOG NUMBER: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	473.2	473.2	473.2	473.2	473.2	473.2	473.2	473.2
2.5°	470.9	471.6	472.4	472.7	472.6	472.4	472.2	472.1
5°	467.1	468.0	468.8	469.1	468.8	468.5	468.3	468.0
7.5°	459.6	459.9	460.1	460.0	459.5	458.9	458.5	458.0
10°	452.0	451.8	451.5	451.0	450.4	449.9	449.3	448.7
12.5°	443.4	442.8	442.3	441.6	440.6	439.7	438.8	437.8
15°	427.2	425.3	423.5	422.2	421.2	420.2	419.2	418.3
17.5°	408.8	406.6	404.5	402.7	401.0	399.4	397.7	396.1
20°	396.1	393.6	391.2	389.0	386.9	384.8	382.8	380.7
22.5°	382.0	378.9	375.9	373.5	371.9	370.4	368.8	367.3
25°	358.7	354.8	350.9	348.3	346.9	345.3	343.9	342.5
27.5°	336.5	332.0	327.4	324.0	321.8	319.5	317.3	315.0
30°	320.8	316.0	311.1	307.5	304.8	302.3	299.7	297.2
32.5°	305.1	299.5	294.0	290.0	287.7	285.2	282.8	280.4
35°	280.5	274.5	268.4	264.4	262.3	260.2	258.2	256.1
37.5°	256.5	249.9	243.3	238.7	236.4	233.9	231.6	229.1
40°	240.4	233.7	226.9	222.3	219.8	217.4	214.8	212.4
42.5°	224.1	217.2	210.2	205.6	203.1	200.8	198.3	196.0
45°	200.6	193.8	187.1	182.6	180.3	178.0	175.7	173.4
47.5°	177.6	170.9	164.2	159.8	157.7	155.6	153.5	151.5
50°	162.9	156.3	149.7	145.4	143.5	141.5	139.4	137.4
52.5°	148.9	142.6	136.3	132.1	130.4	128.5	126.6	124.8
55°	127.7	122.1	116.3	112.5	110.7	109.0	107.2	105.4
57.5°	108.5	103.2	98.0	94.6	93.1	91.6	90.1	88.5
60°	95.2	90.4	85.5	82.3	80.8	79.3	77.8	76.3
62.5°	83.7	79.1	74.5	71.6	70.7	69.8	68.9	68.0
65°	68.1	64.8	61.5	59.8	59.5	59.2	58.9	58.6
67.5°	55.0	53.4	51.9	51.1	50.7	50.4	50.1	49.9
70°	47.8	46.8	45.9	45.2	44.8	44.4	44.0	43.6
72.5°	41.6	40.7	40.0	39.5	39.2	39.0	38.7	38.5
75°	32.9	32.2	31.6	31.2	31.1	31.0	30.9	30.8
77.5°	24.9	24.5	24.1	23.9	23.8	23.6	23.5	23.3
80°	19.8	19.4	19.0	18.9	18.9	18.9	18.9	18.9
82.5°	15.0	14.7	14.5	14.4	14.4	14.4	14.4	14.4
85°	8.1	8.1	8.1	8.1	8.1	8.1	8.1	8.1
87.5°	6.0	5.7	5.8	5.9	5.9	5.9	5.9	5.9
90°	17.2	16.1	17.2	17.7	17.7	17.7	17.7	17.7
92.5°	46.8	40.2	35.7	32.3	32.0	30.3	30.6	29.8
95°	140.8	108.0	85.5	73.6	66.6	62.4	60.7	61.3
97.5°	328.7	268.9	210.8	171.9	146.2	133.0	125.2	120.6
100°	490.8	424.1	350.4	285.4	240.8	217.7	202.1	192.5
102.5°	597.0	581.9	528.1	459.1	410.7	371.2	351.8	338.7
105°	653.1	713.8	720.9	703.0	669.8	636.4	613.3	605.8
107.5°	612.7	704.2	760.1	786.1	790.2	788.4	783.8	773.8
110°	577.9	674.0	742.8	786.9	810.0	820.3	825.1	824.5



TEST NUMBER: P331626-830

CATALOG NUMBER: SA2XXRDIP-C290D530U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	546.0	638.4	711.9	762.4	794.6	811.6	820.8	823.7
115°	506.9	589.7	660.1	715.5	753.6	778.4	792.3	797.1
117.5°	477.4	550.1	614.0	665.9	704.8	730.9	745.6	749.7
120°	462.8	529.4	586.4	635.4	673.0	698.2	713.8	719.2
122.5°	451.2	512.3	566.2	610.4	644.1	669.0	682.9	687.4
125°	434.3	489.7	537.0	577.3	608.5	628.9	642.3	646.7
127.5°	417.6	467.8	512.4	549.6	576.7	595.9	607.5	611.0
130°	406.9	453.2	495.6	531.0	557.4	575.7	586.4	590.7
132.5°	396.6	439.4	478.4	511.7	537.6	555.9	565.8	569.7
135°	382.2	417.6	453.2	483.2	506.3	524.1	533.8	535.9
137.5°	370.7	400.4	428.5	454.8	475.8	491.1	499.5	502.8
140°	363.4	389.2	413.9	437.5	454.8	468.7	476.7	480.0
142.5°	357.3	379.3	400.6	420.4	436.7	449.4	456.6	457.2
145°	348.8	366.6	383.2	398.9	411.7	420.8	426.2	427.8
147.5°	342.3	356.3	369.3	380.7	391.3	398.6	402.3	403.2
150°	337.5	349.4	360.7	370.3	378.4	384.8	388.0	388.6
152.5°	332.8	343.8	353.4	361.7	368.1	373.7	376.1	376.2
155°	326.3	334.9	342.9	348.8	354.8	358.5	360.7	359.6
157.5°	318.7	325.8	332.6	337.2	341.4	344.6	345.5	345.5
160°	313.9	319.8	325.7	329.5	333.3	335.9	336.5	336.5
162.5°	309.2	314.2	319.3	322.2	325.9	327.8	328.3	327.9
165°	302.1	305.9	309.6	311.8	313.9	316.0	316.0	315.6
167.5°	295.3	298.2	300.8	302.7	303.7	304.9	304.8	304.2
170°	291.9	293.5	295.7	296.7	297.3	298.9	298.3	297.3
172.5°	288.0	289.2	290.9	291.5	292.1	292.8	292.3	291.6
175°	283.8	284.4	284.9	285.4	285.4	286.0	285.4	284.4
177.5°	280.8	280.8	281.3	281.3	281.3	281.3	280.8	279.9
180°	279.5	279.5	279.5	279.5	279.5	279.5	279.5	279.5

(END OF REPORT)