

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331360-840

Luminaire Tested: **SA2XXDIP-C675D925U840-4F0-1E-UDD-D**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331360-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U840-4F0-1E-UDD-D
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6452.3 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331360-840
CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-D

Luminous Intensity Polar Plot





TEST NUMBER: P331360-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-D

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	37
1	94	89	85	81	85	81	77	74	65	63	60	51	49	47	38	36	35	29
2	85	77	71	65	77	70	64	60	56	52	49	44	41	39	32	31	29	24
3	77	67	60	54	69	61	55	49	49	45	41	38	35	32	28	26	24	19
4	70	59	51	45	63	54	47	41	44	38	34	34	30	27	25	23	20	16
5	64	53	44	38	58	48	41	35	39	33	29	30	26	23	22	20	18	14
6	59	47	39	33	53	43	36	30	35	29	25	27	23	20	20	18	15	12
7	55	42	34	29	49	39	31	26	31	26	22	25	21	18	18	16	14	11
8	51	38	30	25	46	35	28	23	29	23	19	23	19	16	17	14	12	9
9	47	35	27	22	42	32	25	21	26	21	17	21	17	14	16	13	11	8
10	44	32	25	20	40	29	23	18	24	19	15	19	15	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11485	11485	11485
5°	11541	11055	11013
10°	11469	10729	10608
15°	11310	10384	10181
20°	11112	10013	9772
25°	10913	9655	9399
30°	10635	9288	9023
35°	10355	8933	8760
40°	10057	8630	8496
45°	9777	8361	8270
50°	9476	8116	8048
55°	9160	7855	7822
60°	8770	7583	7583
65°	8367	7262	7299
70°	7917	6920	6990
75°	7339	6581	6708
80°	6436	6238	6424
85°	5566	5939	6199



TEST NUMBER: P331360-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-D

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.4	1.0
10°-20°	193.3	3.0
20°-30°	292.9	4.5
30°-40°	356.7	5.5
40°-50°	383.8	5.9
50°-60°	372.7	5.8
60°-70°	325.4	5.0
70°-80°	250.5	3.9
80°-90°	171.3	2.7
90°-100°	158.4	2.5
100°-110°	240.5	3.7
110°-120°	472.7	7.3
120°-130°	719.2	11.1
130°-140°	744.8	11.5
140°-150°	682.3	10.6
150°-160°	546.8	8.5
160°-170°	352.3	5.5
170°-180°	121.3	1.9
0°-30°	553.6	8.6
0°-40°	910.3	14.1
0°-60°	1666.8	25.8
0°-90°	2414.1	37.4
90°-120°	871.5	13.5
90°-150°	3017.8	46.8
90°-180°	4038.0	62.6
0°-180°	6452.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	711	711	711	711	711	
5°	713	710	704	710	709	68
15°	680	682	682	691	691	192
25°	618	626	635	647	651	284
35°	533	551	570	592	600	333
45°	437	465	501	532	543	337
55°	335	373	426	462	476	299
65°	229	280	340	381	396	227
75°	127	185	250	293	308	134
85°	37	101	167	209	225	40
90°	11	81	154	199	215	10
95°	68	89	154	196	210	80
105°	286	329	145	189	206	305
115°	534	564	631	254	180	526
125°	752	766	814	847	861	671
135°	929	944	962	992	1000	717
145°	1076	1076	1091	1103	1104	673
155°	1185	1178	1188	1193	1186	546
165°	1249	1244	1246	1252	1246	353
175°	1277	1271	1273	1278	1270	122
180°	1275	1275	1275	1275	1275	



TEST NUMBER: P331360-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3
2.5°	715.5	714.9	714.4	713.8	713.3	712.4	711.0	709.7	708.5	707.2	708.1
5°	713.4	712.7	712.1	711.3	710.6	709.6	708.2	706.9	705.5	704.1	705.5
7.5°	707.0	706.5	706.1	705.6	705.2	704.4	703.4	702.3	701.3	700.2	701.9
10°	702.1	701.6	701.1	700.6	700.2	699.6	698.9	698.3	697.6	696.9	698.7
12.5°	693.8	693.9	694.0	694.1	694.2	694.0	693.5	693.0	692.5	692.0	693.8
15°	680.4	680.9	681.4	681.8	682.3	682.5	682.5	682.5	682.5	682.5	684.5
17.5°	663.1	664.1	665.0	666.0	666.9	667.8	668.5	669.2	669.9	670.8	672.9
20°	651.6	652.7	653.8	655.0	656.1	657.1	658.0	659.0	659.9	660.9	663.4
22.5°	639.1	640.5	641.9	643.2	644.5	645.8	647.1	648.3	649.6	651.0	653.5
25°	618.5	620.2	621.8	623.4	625.0	626.8	628.8	631.0	633.0	635.0	637.8
27.5°	593.8	596.4	599.1	601.7	604.3	606.8	609.3	611.7	614.1	616.5	620.0
30°	577.3	580.3	583.3	586.2	589.3	592.2	595.2	598.1	601.2	604.1	607.7
32.5°	559.2	562.5	565.8	569.2	572.6	576.0	579.6	583.0	586.5	590.1	594.3
35°	533.0	536.8	540.8	544.6	548.6	552.7	557.0	561.4	565.7	570.1	575.1
37.5°	504.5	509.1	513.5	518.0	522.5	527.6	533.2	538.9	544.4	550.1	555.7
40°	485.5	490.6	495.6	500.7	505.7	511.3	517.6	523.7	529.9	536.0	542.0
42.5°	467.5	472.4	477.5	482.5	487.6	493.6	500.8	507.9	514.9	522.1	528.6
45°	437.1	443.3	449.5	455.7	461.8	469.0	477.0	485.0	493.0	501.0	508.2
47.5°	407.2	413.9	420.7	427.4	434.1	442.2	451.6	461.0	470.4	479.8	487.3
50°	386.6	393.7	400.8	407.9	415.0	423.7	434.0	444.3	454.6	464.9	472.7
52.5°	366.8	374.3	381.7	389.2	396.7	405.9	416.7	427.6	438.4	449.3	457.3
55°	335.1	343.3	351.5	359.8	368.0	378.1	390.0	401.9	413.8	425.8	434.0
57.5°	303.7	313.1	322.3	331.6	340.9	351.6	363.8	375.9	388.1	400.2	409.1
60°	281.4	291.2	301.1	311.0	320.8	332.3	345.4	358.4	371.4	384.6	393.2
62.5°	261.7	271.9	282.1	292.3	302.6	314.2	327.2	340.2	353.4	366.4	375.7
65°	228.8	240.0	251.4	262.6	273.8	286.1	299.6	313.2	326.7	340.2	349.6
67.5°	198.7	210.5	222.3	234.0	245.7	258.4	272.3	286.1	299.9	313.8	323.3
70°	177.3	189.2	201.2	213.1	225.0	238.0	252.3	266.4	280.6	294.9	304.7
72.5°	157.5	169.8	182.1	194.4	206.6	219.9	234.4	248.7	263.2	277.5	287.2
75°	126.8	139.7	152.5	165.3	178.1	191.9	206.5	221.2	235.8	250.5	260.3
77.5°	97.1	110.6	124.0	137.3	150.8	165.0	179.9	194.8	209.6	224.5	234.4
80°	77.4	91.3	105.2	119.3	133.2	147.6	162.6	177.4	192.3	207.2	216.8
82.5°	60.8	74.6	88.4	102.2	116.0	130.4	145.5	160.6	175.6	190.8	200.4
85°	37.2	51.3	65.5	79.7	93.9	108.4	123.0	137.6	152.4	167.0	176.6
87.5°	20.4	34.5	48.6	62.7	76.9	91.4	106.3	121.4	136.3	151.3	160.9
90°	11.2	26.8	42.3	57.9	73.4	89.3	105.6	121.9	138.3	154.5	164.7
92.5°	28.1	40.3	52.4	64.6	76.7	90.3	105.2	120.2	135.1	150.1	159.6
95°	68.2	72.2	76.2	80.2	84.2	93.8	109.0	124.2	139.4	154.5	164.3
97.5°	126.2	116.7	107.2	97.8	88.3	91.8	108.3	124.8	141.3	157.8	167.1
100°	170.5	150.9	131.3	111.7	92.1	90.4	106.7	123.0	139.4	155.6	165.8
102.5°	218.3	220.2	222.0	223.8	225.5	218.1	201.4	184.7	168.0	151.4	161.8
105°	285.5	298.3	311.1	323.9	336.7	321.0	277.0	233.0	188.9	144.9	155.2
107.5°	363.3	373.7	384.0	394.2	404.5	381.7	326.1	270.3	214.7	159.0	164.4
110°	412.7	421.6	430.5	439.4	448.3	428.7	380.7	332.6	284.7	236.6	223.5



TEST NUMBER: P331360-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	459.9	467.6	475.2	482.9	490.6	492.4	488.5	484.5	480.6	476.6	409.2
115°	534.4	540.5	546.4	552.5	558.5	569.2	584.6	600.1	615.5	631.0	542.9
117.5°	600.0	605.5	611.1	616.6	622.2	631.5	644.5	657.6	670.7	683.7	667.5
120°	648.7	652.7	656.7	660.7	664.7	673.1	685.9	698.8	711.7	724.5	733.4
122.5°	690.0	693.7	697.2	700.8	704.5	712.6	725.2	737.8	750.4	763.1	770.8
125°	751.8	754.6	757.2	759.9	762.5	769.5	780.7	791.9	803.1	814.4	822.0
127.5°	808.9	811.6	814.4	817.1	819.8	825.6	834.4	843.2	852.0	860.8	868.6
130°	845.1	848.1	851.1	854.2	857.3	862.3	869.4	876.5	883.5	890.6	898.3
132.5°	881.9	884.5	887.1	889.6	892.2	896.5	902.4	908.4	914.3	920.3	927.6
135°	928.9	932.1	935.4	938.7	942.0	945.7	949.8	953.9	958.1	962.2	969.1
137.5°	977.3	979.7	981.9	984.1	986.3	989.1	992.2	995.2	998.4	1001.5	1007.6
140°	1009.2	1010.5	1011.9	1013.3	1014.7	1016.8	1019.6	1022.3	1024.9	1027.6	1033.2
142.5°	1035.7	1036.9	1038.1	1039.5	1040.7	1042.6	1045.3	1047.9	1050.7	1053.3	1057.9
145°	1076.3	1076.1	1075.9	1075.7	1075.5	1077.1	1080.7	1084.1	1087.6	1091.1	1093.9
147.5°	1112.7	1111.9	1111.2	1110.3	1109.5	1110.9	1114.3	1117.8	1121.3	1124.7	1125.9
150°	1136.3	1134.9	1133.4	1132.0	1130.5	1131.5	1134.8	1138.0	1141.3	1144.6	1145.8
152.5°	1156.2	1154.6	1153.0	1151.4	1149.8	1150.5	1153.7	1156.8	1159.9	1163.1	1164.3
155°	1185.2	1183.4	1181.4	1179.6	1177.8	1178.1	1180.5	1183.1	1185.5	1187.9	1189.1
157.5°	1207.8	1206.3	1204.8	1203.2	1201.6	1201.7	1203.5	1205.2	1206.9	1208.6	1210.0
160°	1221.1	1219.9	1218.7	1217.4	1216.2	1216.2	1217.4	1218.7	1219.9	1221.1	1222.3
162.5°	1232.9	1231.7	1230.5	1229.2	1228.0	1227.9	1229.0	1230.0	1231.1	1232.2	1233.6
165°	1248.8	1247.6	1246.4	1245.1	1243.9	1243.5	1244.2	1244.8	1245.5	1246.1	1247.5
167.5°	1260.6	1259.4	1258.2	1256.9	1255.7	1255.4	1256.0	1256.5	1257.1	1257.7	1259.1
170°	1267.3	1266.0	1264.8	1263.5	1262.3	1261.9	1262.3	1262.7	1263.1	1263.5	1265.0
172.5°	1271.6	1270.4	1269.2	1268.0	1266.8	1266.4	1266.8	1267.2	1267.6	1268.0	1269.4
175°	1277.4	1276.0	1274.6	1273.0	1271.6	1271.1	1271.5	1271.9	1272.3	1272.7	1274.2
177.5°	1278.3	1277.2	1276.1	1274.9	1273.7	1273.2	1273.4	1273.5	1273.7	1273.8	1275.1
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7



TEST NUMBER: P331360-840
 CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	711.3	711.3	711.3	711.3	711.3	711.3	711.3	711.3
2.5°	709.0	709.9	710.8	711.1	710.7	710.4	710.0	709.7
5°	706.9	708.2	709.6	710.2	709.9	709.7	709.5	709.2
7.5°	703.5	705.2	706.8	707.5	707.3	707.0	706.8	706.6
10°	700.5	702.4	704.3	705.0	704.8	704.6	704.4	704.1
12.5°	695.6	697.4	699.3	700.0	699.8	699.6	699.4	699.1
15°	686.6	688.6	690.7	691.7	691.5	691.2	690.9	690.7
17.5°	675.0	677.2	679.3	680.4	680.4	680.4	680.4	680.4
20°	665.9	668.4	670.9	672.2	672.2	672.2	672.2	672.2
22.5°	656.0	658.5	661.0	662.5	662.8	663.2	663.6	663.9
25°	640.6	643.3	646.0	647.7	648.4	649.1	649.8	650.6
27.5°	623.5	626.9	630.5	632.4	632.9	633.4	633.9	634.4
30°	611.5	615.1	618.7	621.0	621.7	622.4	623.0	623.7
32.5°	598.5	602.8	606.9	609.7	611.0	612.2	613.4	614.6
35°	580.2	585.2	590.3	593.6	595.2	596.8	598.3	600.0
37.5°	561.3	566.8	572.5	576.1	577.8	579.5	581.2	582.9
40°	548.0	553.9	559.9	563.9	565.9	568.0	570.1	572.2
42.5°	535.0	541.6	548.1	552.4	554.4	556.5	558.6	560.6
45°	515.2	522.3	529.5	534.1	536.4	538.8	541.0	543.3
47.5°	494.6	502.1	509.5	514.4	516.9	519.5	522.0	524.5
50°	480.5	488.3	496.1	501.3	503.8	506.3	508.8	511.3
52.5°	465.2	473.2	481.2	486.6	489.2	491.9	494.6	497.4
55°	442.2	450.5	458.8	464.3	467.4	470.3	473.3	476.3
57.5°	418.0	426.9	435.8	441.7	444.7	447.8	450.8	453.8
60°	401.9	410.6	419.4	425.4	428.5	431.7	434.9	438.2
62.5°	384.9	394.2	403.4	409.6	412.5	415.6	418.6	421.6
65°	359.0	368.4	377.8	384.0	387.0	389.9	392.9	395.9
67.5°	332.8	342.2	351.7	358.1	361.1	364.3	367.4	370.5
70°	314.6	324.4	334.3	340.5	343.3	346.1	348.8	351.5
72.5°	296.9	306.5	316.2	322.7	326.0	329.3	332.5	335.9
75°	270.2	280.0	289.9	296.3	299.3	302.3	305.3	308.2
77.5°	244.2	254.0	263.8	270.2	273.5	276.7	279.8	283.1
80°	226.4	236.1	245.7	252.2	255.3	258.5	261.8	265.0
82.5°	210.0	219.5	229.2	235.5	238.5	241.6	244.6	247.6
85°	186.2	195.9	205.5	211.9	215.1	218.3	221.6	224.7
87.5°	170.5	180.0	189.6	195.8	198.8	201.9	204.9	207.8
90°	174.9	185.1	195.3	202.0	205.1	208.2	211.5	214.6
92.5°	169.1	178.6	188.1	194.4	197.3	200.4	203.4	206.3
95°	174.0	183.7	193.5	199.5	202.2	204.7	207.2	209.7
97.5°	176.4	185.7	195.0	201.2	204.1	207.0	210.0	213.0
100°	175.9	186.0	196.1	202.7	205.6	208.5	211.5	214.4
102.5°	172.2	182.7	193.1	199.9	202.9	206.0	209.1	212.2
105°	165.4	175.7	186.0	192.8	196.1	199.4	202.9	206.2
107.5°	169.8	175.2	180.6	184.9	188.3	191.7	195.0	198.3
110°	210.4	197.1	184.0	179.0	182.4	185.8	189.1	192.5



TEST NUMBER: P331360-840

CATALOG NUMBER: SA2XXDIP-C675D925U840-4F0-1E-UDD-D

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	341.7	274.3	206.8	174.7	177.8	181.1	184.2	187.4
115°	454.8	366.9	278.8	228.7	216.4	204.2	192.0	179.8
117.5°	651.4	635.2	619.0	587.8	541.7	495.5	449.4	403.2
120°	742.3	751.1	760.0	751.8	726.7	701.6	676.4	651.3
122.5°	778.5	786.2	794.0	796.2	792.9	789.7	786.5	783.3
125°	829.6	837.3	844.9	850.0	852.7	855.4	858.1	860.7
127.5°	876.4	884.1	891.9	896.9	899.0	901.2	903.3	905.4
130°	906.1	913.8	921.6	926.2	927.9	929.5	931.2	932.8
132.5°	934.7	942.0	949.3	953.7	955.3	956.9	958.6	960.2
135°	975.9	982.8	989.7	993.8	995.2	996.6	998.0	999.5
137.5°	1013.9	1020.2	1026.3	1029.9	1030.8	1031.6	1032.5	1033.3
140°	1038.6	1044.2	1049.7	1052.7	1053.0	1053.3	1053.7	1054.0
142.5°	1062.6	1067.1	1071.8	1074.2	1074.3	1074.5	1074.7	1074.8
145°	1096.7	1099.5	1102.4	1103.8	1103.9	1104.0	1104.2	1104.3
147.5°	1127.1	1128.4	1129.6	1130.1	1129.8	1129.5	1129.2	1128.9
150°	1147.0	1148.3	1149.5	1149.6	1148.6	1147.5	1146.5	1145.5
152.5°	1165.5	1166.7	1167.9	1167.9	1166.5	1165.2	1163.9	1162.5
155°	1190.4	1191.6	1192.9	1192.7	1191.0	1189.3	1187.7	1186.1
157.5°	1211.3	1212.7	1214.2	1214.1	1212.4	1210.8	1209.2	1207.7
160°	1223.6	1224.9	1226.1	1226.0	1224.5	1223.0	1221.6	1220.2
162.5°	1235.0	1236.4	1237.8	1237.6	1235.9	1234.1	1232.3	1230.5
165°	1248.9	1250.3	1251.7	1251.7	1250.3	1248.9	1247.5	1246.1
167.5°	1260.5	1261.9	1263.4	1263.1	1261.3	1259.5	1257.7	1255.8
170°	1266.5	1267.9	1269.3	1269.1	1267.3	1265.4	1263.5	1261.7
172.5°	1270.8	1272.3	1273.7	1273.5	1271.6	1269.8	1268.0	1266.2
175°	1275.7	1277.1	1278.5	1278.2	1276.2	1274.1	1272.0	1270.0
177.5°	1276.2	1277.4	1278.5	1278.3	1276.9	1275.4	1273.8	1272.4
180°	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7	1274.7

(END OF REPORT)