

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008575

Luminaire Tested: S122DIP-B1005D1080UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008575
REPORT IS A COMBINATION OF REPORTS P983567 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB40-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7869.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008575

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008575

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	107	107	107	107	99	99	99	99	84	84	84		70	70	70		57
1	98	94	90	86	91	87	83	80	74	71	69		62	60	58		51
2	89	82	76	71	82	76	71	66	65	61	57		54	51	49		45
3	81	72	65	59	75	67	60	55	57	52	48		48	44	41		40
4	75	64	56	50	69	59	52	47	51	45	41		43	39	35		35
5	68	57	49	43	63	53	46	40	45	40	35		38	34	31		32
6	63	51	43	37	58	47	40	35	41	35	31		35	30	27		29
7	58	46	38	32	54	43	36	31	37	31	27		32	27	24		26
8	54	42	34	29	50	39	32	27	34	28	24		29	24	21		24
9	50	38	31	26	47	36	29	24	31	26	22		27	22	19		22
10	47	35	28	23	44	33	26	22	29	23	20		25	20	17		21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25142	25142	25142
5°	25183	23965	23795
10°	24979	22873	22420
15°	24613	21773	20971
20°	24118	20575	19601
25°	23625	19325	18232
30°	23005	18152	16796
35°	22421	16912	15385
40°	21698	15689	14051
45°	20979	14475	12743
50°	20197	13242	11386
55°	19372	11922	10101
60°	18443	10493	8766
65°	17426	9040	7360
70°	16136	7451	5944
75°	14354	5744	4590
80°	12191	3903	2954
85°	8843	1817	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20979 cd/sqm

TEST NUMBER: P1008575

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	1.9
10°-20°	420.6	5.3
20°-30°	618.1	7.9
30°-40°	717.9	9.1
40°-50°	717.0	9.1
50°-60°	625.2	7.9
60°-70°	462.2	5.9
70°-80°	261.5	3.3
80°-90°	72.9	0.9
90°-100°	84.6	1.1
100°-110°	269.0	3.4
110°-120°	460.3	5.8
120°-130°	605.3	7.7
130°-140°	679.5	8.6
140°-150°	666.3	8.5
150°-160°	558.9	7.1
160°-170°	370.7	4.7
170°-180°	129.6	1.6
0°-30°	1188.2	15.1
0°-40°	1906.1	24.2
0°-60°	3248.3	41.3
0°-90°	4044.9	51.4
90°-120°	813.9	10.3
90°-150°	2764.9	35.1
90°-180°	3824.0	48.6
0°-180°	7869.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1588	1588	1588	1588	1588	
5°	1588	1582	1565	1578	1575	151
15°	1512	1503	1483	1489	1481	426
25°	1368	1356	1330	1333	1330	630
35°	1181	1165	1141	1132	1124	737
45°	961	950	927	910	904	741
55°	727	718	700	681	674	650
65°	490	481	466	452	444	485
75°	257	254	246	237	240	274
85°	63	61	60	55	54	70
90°	1	15	40	38	39	8
95°	60	72	74	74	72	67
105°	248	252	254	256	256	262
115°	462	469	466	465	462	457
125°	672	682	679	675	674	600
135°	869	882	884	883	880	672
145°	1055	1063	1070	1071	1066	659
155°	1206	1210	1213	1219	1215	555
165°	1312	1311	1311	1319	1314	370
175°	1366	1362	1360	1368	1361	130
180°	1368	1368	1368	1368	1368	

TEST NUMBER: P1008575

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1588.3	1588.3	1588.3	1588.3	1588.3
2.5°	1597.5	1589.9	1573.1	1588.3	1585.3
5°	1588.3	1582.2	1565.4	1577.7	1574.6
7.5°	1577.7	1568.5	1551.7	1563.9	1560.9
10°	1560.9	1550.2	1531.8	1544.1	1539.5
12.5°	1537.9	1528.8	1510.5	1518.1	1515.0
15°	1512.0	1502.8	1483.0	1489.1	1481.4
17.5°	1479.9	1470.7	1450.9	1458.5	1450.9
20°	1444.8	1435.6	1414.2	1418.8	1412.7
22.5°	1409.7	1395.9	1376.1	1376.1	1373.0
25°	1368.4	1356.2	1330.2	1333.3	1330.2
27.5°	1322.6	1311.9	1292.1	1287.5	1279.8
30°	1276.8	1264.6	1241.7	1237.1	1231.0
32.5°	1227.9	1218.7	1194.3	1185.1	1179.0
35°	1180.6	1165.3	1140.9	1131.7	1124.1
37.5°	1127.1	1113.4	1088.9	1078.2	1070.6
40°	1072.1	1059.9	1035.5	1021.7	1015.6
42.5°	1018.7	1006.5	982.0	966.8	957.6
45°	960.6	950.0	927.0	910.2	904.1
47.5°	904.1	893.4	869.0	852.2	843.0
50°	844.6	836.9	815.6	794.2	786.5
52.5°	786.5	775.8	756.0	739.2	728.5
55°	727.0	717.8	699.5	681.2	673.5
57.5°	667.4	659.8	639.9	621.6	615.5
60°	607.8	601.7	580.4	563.6	559.0
62.5°	549.8	539.1	523.8	508.6	502.5
65°	490.2	481.1	465.8	452.1	444.4
67.5°	429.2	421.5	407.8	397.1	391.0
70°	372.6	366.5	352.8	342.1	336.0
72.5°	314.6	308.5	300.9	290.2	285.6
75°	256.6	253.5	245.9	236.7	239.8
77.5°	204.7	198.5	195.5	190.9	186.3
80°	152.7	151.2	148.1	143.6	140.5
82.5°	103.9	103.9	102.3	96.2	96.2
85°	62.6	61.1	59.6	55.0	53.5
87.5°	27.5	24.4	21.4	16.8	15.3
90°	1.2	15.0	40.4	38.1	39.2
92.5°	25.4	34.6	35.8	36.9	36.9
95°	60.0	71.6	73.9	73.9	71.6
97.5°	100.4	110.8	115.4	115.4	115.4
100°	146.6	155.8	159.3	159.3	158.1
102.5°	195.1	202.0	206.6	207.8	206.6
105°	248.2	251.6	253.9	256.2	256.2
107.5°	301.3	305.9	305.9	307.0	301.3
110°	352.0	359.0	359.0	359.0	355.5



TEST NUMBER: P1008575

CATALOG NUMBER: S122DIP-B1005D1080UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	407.5	414.4	413.2	409.8	407.5
115°	461.7	468.6	466.3	465.2	461.7
117.5°	516.0	525.2	519.4	516.0	512.5
120°	570.2	579.4	570.2	570.2	566.7
122.5°	619.8	631.4	625.6	622.1	619.8
125°	671.8	682.2	678.7	675.2	674.1
127.5°	722.6	735.3	730.6	726.0	722.6
130°	769.9	784.9	782.6	780.3	775.7
132.5°	823.0	834.5	835.7	829.9	826.5
135°	869.2	881.9	884.2	883.0	879.5
137.5°	919.9	930.3	932.6	931.5	926.9
140°	965.0	975.4	981.1	981.1	976.5
142.5°	1011.1	1021.5	1025.0	1026.1	1021.5
145°	1055.0	1063.1	1070.0	1071.2	1066.5
147.5°	1094.2	1104.6	1109.2	1111.6	1106.9
150°	1134.6	1141.6	1146.2	1149.6	1146.2
152.5°	1170.4	1177.3	1183.1	1187.7	1183.1
155°	1206.2	1209.7	1213.1	1218.9	1215.4
157.5°	1237.4	1239.7	1242.0	1250.1	1244.3
160°	1265.1	1267.4	1268.5	1275.5	1270.8
162.5°	1290.5	1290.5	1291.6	1299.7	1293.9
165°	1312.4	1311.2	1311.2	1319.3	1313.5
167.5°	1332.0	1328.6	1328.6	1336.6	1330.9
170°	1347.0	1343.6	1342.4	1350.5	1343.6
172.5°	1357.4	1353.9	1352.8	1360.9	1353.9
175°	1365.5	1362.0	1359.7	1367.8	1360.9
177.5°	1370.1	1366.6	1364.3	1371.3	1364.3
180°	1367.8	1367.8	1367.8	1367.8	1367.8

(END OF REPORT)