

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331764-840

Luminaire Tested: **SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331764-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7767.8 lumens
Efficiency: N/A
Efficacy: 108.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331764-840
CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331764-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	45	39
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25
5	69	57	50	44	63	53	46	41	45	40	36	37	34	30	30	28	25	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27611	27611	27611
5°	27716	27266	27417
10°	27506	26820	26591
15°	27189	26024	25275
20°	26751	24890	23639
25°	26302	23599	22057
30°	25682	22275	20025
35°	25074	20834	18242
40°	24464	19344	16179
45°	23749	17671	14312
50°	23016	15978	12479
55°	22261	14159	10716
60°	21390	12245	8896
65°	20397	10288	8103
70°	19218	8478	7449
75°	17767	7723	6949
80°	15676	6908	6332
85°	12338	5446	5446



TEST NUMBER: P331764-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.1	2.1
10°-20°	439.5	5.7
20°-30°	617.2	7.9
30°-40°	673.0	8.7
40°-50°	618.8	8.0
50°-60°	486.0	6.3
60°-70°	316.9	4.1
70°-80°	163.4	2.1
80°-90°	47.9	0.6
90°-100°	243.9	3.1
100°-110°	827.7	10.7
110°-120°	879.3	11.3
120°-130°	723.9	9.3
130°-140°	581.3	7.5
140°-150°	439.3	5.7
150°-160°	308.7	4.0
160°-170°	181.7	2.3
170°-180°	59.1	0.8
0°-30°	1216.8	15.7
0°-40°	1889.8	24.3
0°-60°	2994.7	38.6
0°-90°	3522.8	45.4
90°-120°	1951.0	25.1
90°-150°	3695.4	47.6
90°-180°	4245.0	54.6
0°-180°	7767.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1710	1710	1710	1710	1710	
5°	1710	1702	1682	1695	1692	162
15°	1627	1608	1557	1528	1512	458
25°	1476	1424	1325	1264	1238	679
35°	1272	1190	1057	963	926	796
45°	1040	933	774	668	627	803
55°	791	668	503	414	381	706
65°	534	408	269	219	212	529
75°	285	180	124	114	111	301
85°	67	36	29	29	29	78
90°	1	16	40	38	39	5
95°	41	101	460	174	134	44
105°	143	216	869	1554	1322	152
115°	252	319	727	1501	1740	250
125°	352	416	699	1216	1411	312
135°	413	493	691	1022	1170	319
145°	472	542	687	854	934	296
155°	536	579	668	755	785	247
165°	584	602	639	678	689	165
175°	609	609	615	622	621	58
180°	610	610	610	610	610	



TEST NUMBER: P331764-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1716.4	1715.0	1713.5	1712.2	1710.8	1708.6	1705.6	1702.6	1699.6	1696.6	1699.3
5°	1710.1	1708.4	1706.7	1705.0	1703.2	1700.2	1695.7	1691.2	1686.8	1682.3	1685.4
7.5°	1692.5	1690.4	1688.3	1686.1	1683.9	1680.3	1675.1	1669.8	1664.7	1659.4	1660.3
10°	1677.7	1675.3	1672.8	1670.4	1668.0	1663.3	1656.5	1649.6	1642.7	1635.9	1634.9
12.5°	1659.1	1656.1	1653.1	1650.2	1647.3	1641.3	1632.5	1623.8	1615.0	1606.2	1604.3
15°	1626.6	1622.8	1619.0	1615.2	1611.4	1603.7	1592.1	1580.3	1568.6	1556.9	1550.4
17.5°	1586.6	1580.8	1575.1	1569.3	1563.6	1553.2	1538.1	1523.2	1508.1	1493.2	1485.4
20°	1556.9	1550.0	1543.2	1536.3	1529.4	1517.4	1500.2	1483.0	1465.8	1448.6	1440.0
22.5°	1524.7	1517.0	1509.3	1501.7	1493.9	1480.4	1461.0	1441.6	1422.2	1402.8	1391.7
25°	1476.4	1465.4	1454.4	1443.4	1432.4	1415.6	1392.9	1370.2	1347.5	1324.7	1310.7
27.5°	1418.3	1406.3	1394.3	1382.4	1370.4	1351.6	1326.1	1300.4	1274.9	1249.3	1232.8
30°	1377.5	1364.3	1351.3	1338.2	1325.1	1304.8	1277.3	1249.8	1222.3	1194.8	1177.2
32.5°	1337.8	1322.5	1307.3	1292.0	1276.7	1255.1	1227.0	1198.9	1170.8	1142.8	1122.8
35°	1272.1	1254.7	1237.1	1219.5	1202.0	1178.1	1147.8	1117.6	1087.3	1057.0	1035.4
37.5°	1206.6	1187.3	1168.0	1148.7	1129.5	1103.8	1071.5	1039.3	1006.9	974.7	950.9
40°	1160.7	1140.1	1119.4	1098.8	1078.2	1051.2	1017.8	984.5	951.1	917.8	893.3
42.5°	1113.7	1092.0	1070.3	1048.4	1026.7	998.7	964.2	929.7	895.2	860.8	835.6
45°	1040.1	1016.9	993.9	970.9	947.9	918.3	882.1	846.1	809.9	773.9	749.4
47.5°	968.2	943.8	919.4	894.9	870.5	839.7	802.4	765.1	727.8	690.5	666.3
50°	916.3	891.8	867.4	842.9	818.5	787.4	749.6	711.8	673.9	636.1	612.4
52.5°	865.5	839.9	814.5	788.9	763.4	732.2	695.1	658.1	621.1	584.1	561.2
55°	790.8	764.1	737.2	710.3	683.6	651.6	614.4	577.2	540.2	503.0	482.3
57.5°	714.4	686.9	659.3	631.9	604.3	572.7	537.0	501.3	465.6	429.9	411.0
60°	662.4	634.9	607.3	579.9	552.3	520.9	485.4	450.0	414.5	379.2	361.6
62.5°	611.7	584.1	556.6	529.1	501.6	470.9	437.2	403.3	369.6	335.9	319.1
65°	533.9	506.0	478.3	450.4	422.5	393.1	362.1	331.2	300.2	269.3	257.6
67.5°	459.0	431.4	403.7	376.1	348.4	320.6	292.9	265.0	237.1	209.2	203.9
70°	407.1	380.2	353.4	326.6	299.7	274.5	250.7	227.0	203.3	179.6	176.1
72.5°	357.5	331.7	306.1	280.3	254.6	232.2	213.2	194.1	175.0	156.0	153.1
75°	284.8	260.6	236.6	212.6	188.4	170.6	158.9	147.2	135.5	123.8	121.4
77.5°	213.3	192.2	171.1	150.0	128.8	115.4	109.8	104.1	98.5	92.9	91.5
80°	168.6	151.2	133.6	116.0	98.6	88.1	84.6	81.2	77.8	74.3	72.9
82.5°	127.8	114.1	100.5	86.7	73.1	65.0	62.7	60.4	58.1	55.7	54.9
85°	66.6	59.3	52.1	44.8	37.7	33.5	32.5	31.5	30.4	29.4	29.4
87.5°	20.0	18.6	17.3	15.6	13.8	13.4	14.6	16.3	17.7	17.9	17.4
90°	1.2	4.6	9.4	11.7	14.0	17.6	23.4	31.7	38.7	39.9	38.7
92.5°	14.3	20.6	29.1	34.2	42.2	53.2	79.8	117.0	150.4	152.5	128.9
95°	41.1	45.7	57.5	68.1	86.8	114.9	169.0	270.9	407.1	459.9	402.4
97.5°	66.9	73.2	85.6	101.6	123.2	155.1	222.9	365.1	591.3	785.1	823.5
100°	90.3	93.8	104.4	123.2	146.6	179.5	241.7	384.8	638.1	926.8	1095.7
102.5°	111.9	114.5	125.0	143.8	168.2	201.1	258.5	385.8	620.4	931.5	1197.1
105°	143.1	147.8	156.0	173.6	199.4	232.3	287.4	391.8	585.4	869.3	1181.3
107.5°	176.9	180.7	188.6	204.8	230.5	263.5	317.0	408.0	568.0	802.6	1078.3
110°	199.4	204.1	211.2	226.4	251.1	285.1	336.7	421.1	564.3	770.7	1013.6



TEST NUMBER: P331764-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	220.0	224.8	232.8	247.0	270.7	305.7	355.5	435.3	565.2	750.1	968.6
115°	252.3	258.1	265.1	279.2	302.7	334.4	384.8	456.4	570.2	727.3	912.7
117.5°	285.6	290.2	297.3	309.7	332.2	365.1	411.7	478.9	578.6	716.3	877.5
120°	306.2	310.8	317.9	328.5	351.9	384.8	430.5	493.9	584.2	709.7	858.7
122.5°	325.9	329.6	336.7	348.2	371.6	405.5	448.4	507.1	590.8	706.0	842.7
125°	351.9	355.5	362.5	376.6	400.0	432.9	475.1	528.0	600.7	699.2	820.0
127.5°	372.5	377.3	387.2	402.6	425.2	458.9	500.0	547.3	610.8	695.2	798.9
130°	384.8	389.5	401.2	417.7	441.1	473.9	515.0	559.6	618.2	693.3	784.9
132.5°	396.1	401.7	414.3	431.7	456.2	489.0	528.2	571.8	625.7	692.4	773.6
135°	412.9	417.7	431.7	449.3	476.3	509.2	546.6	587.7	634.7	690.9	757.8
137.5°	428.9	434.5	448.6	467.4	494.1	524.6	561.7	600.0	642.7	690.7	746.8
140°	441.1	445.8	459.9	478.7	504.4	534.9	570.2	606.5	646.4	689.8	740.2
142.5°	453.3	457.1	470.2	489.0	513.8	542.5	576.7	612.2	649.2	689.8	733.7
145°	471.6	476.3	488.1	505.6	529.1	554.9	586.5	619.5	652.3	687.4	725.0
147.5°	491.3	494.8	506.0	522.3	541.8	564.7	594.5	623.4	653.2	683.3	716.1
150°	504.4	508.0	517.4	532.6	550.2	571.3	598.3	625.3	652.3	680.4	708.5
152.5°	517.6	519.3	528.6	542.0	558.7	577.8	602.1	626.2	650.4	675.7	702.0
155°	536.1	537.2	544.3	557.2	570.2	587.7	607.6	627.6	647.5	667.5	689.8
157.5°	551.6	552.8	558.5	569.7	580.0	594.8	611.7	627.6	642.2	659.0	678.3
160°	561.9	563.1	567.7	577.1	586.5	599.5	613.6	627.6	639.3	653.5	669.8
162.5°	572.3	571.6	576.2	583.7	592.2	602.3	614.5	626.7	636.5	648.7	662.4
165°	584.2	583.1	585.4	592.4	598.3	605.3	615.9	624.1	631.2	639.3	649.9
167.5°	594.1	592.7	594.8	599.3	603.5	607.9	615.6	622.5	625.7	631.2	637.7
170°	600.7	598.3	599.5	603.0	605.3	608.8	614.7	620.6	622.9	626.4	631.2
172.5°	604.4	603.0	602.3	605.8	607.2	609.8	613.8	617.7	619.1	620.9	624.6
175°	608.8	607.6	606.5	608.8	608.8	610.1	612.4	614.7	613.6	614.7	615.9
177.5°	611.0	609.0	608.1	610.1	610.1	610.1	611.0	612.9	611.0	610.1	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1



TEST NUMBER: P331764-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1	1710.1
2.5°	1702.0	1704.8	1707.6	1708.6	1708.1	1707.6	1707.0	1706.5
5°	1688.5	1691.6	1694.7	1695.7	1694.7	1693.6	1692.6	1691.6
7.5°	1661.1	1662.0	1662.9	1662.5	1660.7	1658.9	1657.2	1655.4
10°	1633.8	1632.7	1631.7	1630.2	1628.1	1626.1	1624.0	1621.9
12.5°	1602.5	1600.5	1598.7	1596.1	1592.7	1589.2	1585.8	1582.4
15°	1543.9	1537.3	1530.8	1525.8	1522.4	1518.9	1515.5	1512.1
17.5°	1477.6	1469.9	1462.1	1455.2	1449.4	1443.4	1437.4	1431.6
20°	1431.4	1422.8	1414.2	1406.1	1398.6	1391.0	1383.4	1375.8
22.5°	1380.7	1369.6	1358.5	1350.1	1344.5	1338.9	1333.2	1327.6
25°	1296.6	1282.5	1268.4	1258.8	1253.5	1248.4	1243.2	1238.1
27.5°	1216.4	1199.9	1183.5	1171.1	1163.0	1154.8	1146.6	1138.4
30°	1159.7	1142.2	1124.6	1111.3	1102.0	1092.7	1083.4	1074.1
32.5°	1102.8	1082.8	1062.7	1048.3	1039.7	1030.9	1022.1	1013.4
35°	1013.7	992.1	970.4	955.7	948.2	940.6	933.0	925.5
37.5°	927.0	903.1	879.2	862.9	854.3	845.7	837.0	828.3
40°	868.9	844.4	820.1	803.4	794.5	785.5	776.6	767.6
42.5°	810.3	785.1	759.8	742.9	734.2	725.5	716.9	708.2
45°	725.0	700.5	676.1	659.8	651.6	643.3	635.0	626.8
47.5°	642.0	617.7	593.4	577.5	570.1	562.6	555.0	547.5
50°	588.7	564.9	541.2	525.6	518.5	511.2	504.0	496.8
52.5°	538.3	515.3	492.5	477.7	471.0	464.3	457.7	451.0
55°	461.7	441.1	420.4	406.9	400.3	393.7	387.3	380.7
57.5°	392.1	373.1	354.3	342.0	336.6	331.0	325.6	320.0
60°	344.1	326.6	309.0	297.5	292.0	286.5	280.9	275.5
62.5°	302.5	285.7	269.0	258.9	255.7	252.4	249.0	245.8
65°	245.9	234.2	222.5	216.1	215.1	214.1	213.1	212.1
67.5°	198.5	193.2	187.7	184.5	183.5	182.4	181.3	180.2
70°	172.7	169.3	165.8	163.4	162.0	160.6	159.3	157.8
72.5°	150.3	147.3	144.4	142.6	141.8	141.0	140.1	139.3
75°	119.0	116.6	114.2	112.8	112.5	112.1	111.8	111.4
77.5°	90.1	88.8	87.4	86.3	85.8	85.3	84.7	84.2
80°	71.5	70.2	68.8	68.1	68.1	68.1	68.1	68.1
82.5°	54.0	53.2	52.4	52.0	52.0	52.0	52.0	52.0
85°	29.4	29.4	29.4	29.4	29.4	29.4	29.4	29.4
87.5°	16.9	16.2	16.4	16.4	16.4	16.4	16.4	16.4
90°	37.6	35.2	37.6	38.7	38.7	38.7	38.7	38.7
92.5°	102.3	87.8	77.9	70.6	69.7	65.9	66.9	65.0
95°	307.4	235.8	186.5	160.7	145.4	136.1	132.6	133.7
97.5°	717.2	586.8	459.9	375.2	319.1	290.2	273.1	263.3
100°	1071.1	925.6	764.9	622.9	525.5	475.1	441.1	420.0
102.5°	1302.9	1270.0	1152.5	1002.1	896.3	810.2	767.7	739.1
105°	1425.3	1557.9	1573.2	1534.5	1461.7	1389.0	1338.6	1322.1
107.5°	1337.2	1536.8	1658.8	1715.6	1724.7	1720.7	1710.6	1688.8
110°	1261.1	1471.1	1621.2	1717.5	1767.9	1790.2	1800.8	1799.6



TEST NUMBER: P331764-840

CATALOG NUMBER: SA2XXRDIP-C1005D1080U840-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1191.6	1393.2	1553.7	1664.0	1734.1	1771.4	1791.4	1797.7
115°	1106.3	1287.0	1440.6	1561.5	1644.8	1698.7	1729.2	1739.8
117.5°	1042.0	1200.6	1340.0	1453.3	1538.2	1595.2	1627.4	1636.3
120°	1010.1	1155.5	1279.9	1386.6	1468.7	1523.9	1557.9	1569.6
122.5°	984.7	1118.0	1235.8	1332.2	1405.8	1460.1	1490.4	1500.2
125°	947.9	1068.7	1171.9	1259.9	1328.0	1372.6	1401.9	1411.3
127.5°	911.5	1020.9	1118.2	1199.4	1258.8	1300.5	1325.9	1333.4
130°	888.1	989.0	1081.7	1159.0	1216.6	1256.5	1279.9	1289.3
132.5°	865.6	959.0	1044.1	1116.8	1173.4	1213.3	1234.9	1243.2
135°	834.0	911.5	989.0	1054.6	1105.1	1143.8	1164.9	1169.6
137.5°	809.0	873.7	935.2	992.5	1038.4	1071.8	1090.4	1097.3
140°	793.0	849.4	903.3	954.9	992.5	1023.0	1040.6	1047.6
142.5°	779.9	827.8	874.2	917.4	953.0	980.8	996.4	997.8
145°	761.3	800.1	836.5	870.5	898.6	918.6	930.3	933.8
147.5°	747.1	777.6	806.0	830.8	854.0	870.0	878.0	880.1
150°	736.7	762.5	787.2	808.3	825.9	840.0	847.0	848.2
152.5°	726.4	750.3	771.2	789.5	803.3	815.6	820.7	820.9
155°	712.1	730.8	748.4	761.3	774.3	782.4	787.2	784.9
157.5°	695.4	711.1	725.9	736.0	745.2	751.9	754.1	754.1
160°	685.1	698.0	710.9	719.1	727.3	733.2	734.4	734.4
162.5°	674.8	685.8	696.8	703.2	711.3	715.4	716.5	715.6
165°	659.3	667.5	675.7	680.4	685.1	689.8	689.8	688.6
167.5°	644.5	650.9	656.5	660.8	662.8	665.4	665.2	663.8
170°	637.0	640.6	645.2	647.5	648.7	652.3	651.1	648.7
172.5°	628.5	631.2	634.9	636.3	637.5	639.1	637.9	636.5
175°	619.5	620.6	621.8	622.9	622.9	624.1	622.9	620.6
177.5°	612.9	612.9	613.8	613.8	613.8	613.8	612.9	611.0
180°	610.1	610.1	610.1	610.1	610.1	610.1	610.1	610.1

(END OF REPORT)