

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P332939-840

Luminaire Tested: **SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P332939-840
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-18,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4
Description: DEFINE 4 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 795 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 810 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6295.0 lumens
Efficiency: N/A
Efficacy: 137.1 lumens/watt
Spacing Criteria (0/90/45): 1.28 / 1.23 / 1.39
Luminous Opening: Rectangular (W 4' x L: 0.33' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P332939-840
CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	46	44	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38	34
4	76	66	58	52	70	61	54	49	53	48	44	45	41	38	38	35	33	29
5	70	59	51	45	65	55	48	42	48	42	38	41	37	33	35	31	29	26
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26	23
7	60	48	40	34	55	45	38	33	39	34	29	34	29	26	29	26	23	20
8	56	43	36	31	52	41	34	29	36	30	26	31	27	23	27	23	21	18
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19	17
10	48	37	29	25	45	34	28	24	30	25	21	26	22	19	23	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	10761	10761	10761	10761
5°	12482	10794	9541	10794
10°	14767	10747	8515	10747
15°	17057	10647	7317	10647
20°	18991	10511	6617	10511
25°	19605	10377	6143	10377
30°	17162	10213	5857	10213
35°	13360	9973	5685	9973
40°	10019	9695	5593	9695
45°	7911	9252	5543	9252
50°	6678	8743	5383	8743
55°	5820	8179	5095	8179
60°	5238	7597	4510	7597
65°	4617	6967	3878	6967
70°	4157	6314	3498	6314
75°	3484	5596	2982	5596
80°	2947	4770	2799	4770
85°	2492	3733	2492	3733



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	2.1
10°-20°	389.6	6.2
20°-30°	609.4	9.7
30°-40°	677.4	10.8
40°-50°	601.0	9.5
50°-60°	468.4	7.4
60°-70°	306.6	4.9
70°-80°	150.8	2.4
80°-90°	39.4	0.6
90°-100°	290.3	4.6
100°-110°	604.2	9.6
110°-120°	541.2	8.6
120°-130°	455.2	7.2
130°-140°	379.6	6.0
140°-150°	290.0	4.6
150°-160°	203.8	3.2
160°-170°	119.9	1.9
170°-180°	39.0	0.6
0°-30°	1128.1	17.9
0°-40°	1805.6	28.7
0°-60°	2875.0	45.7
0°-90°	3371.8	53.6
90°-120°	1435.7	22.8
90°-150°	2560.4	40.7
90°-180°	2923.0	46.4
0°-180°	6295.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1333	1333	1333	1333	1333	
5°	1540	1332	1177	1332	1540	156
15°	2041	1274	876	1274	2041	580
25°	2201	1165	690	1165	2201	976
35°	1356	1012	577	1012	1356	850
45°	693	810	486	810	693	549
55°	414	581	362	581	414	376
65°	242	365	203	365	242	243
75°	112	179	96	179	112	123
85°	27	40	27	40	27	31
90°	17	1	17	1	17	15
95°	193	26	193	26	193	299
105°	1111	92	1111	92	1111	1098
115°	1067	163	1067	163	1067	1059
125°	851	227	851	227	851	774
135°	761	269	761	269	761	588
145°	622	310	622	310	622	394
155°	520	353	520	353	520	243
165°	454	385	454	385	454	130
175°	409	401	409	401	409	40
180°	402	402	402	402	402	



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1406.0	1410.0	1406.0	1405.6	1401.4	1400.1	1398.4	1392.8	1382.4	1376.4	1377.8
5°	1540.3	1553.8	1546.3	1545.2	1533.4	1521.6	1514.0	1496.8	1478.5	1466.2	1456.0
7.5°	1695.7	1703.4	1698.7	1691.1	1672.0	1661.2	1643.8	1621.1	1588.4	1563.4	1540.4
10°	1801.4	1807.9	1805.6	1791.7	1777.8	1749.3	1733.1	1701.5	1660.1	1627.4	1596.8
12.5°	1905.3	1912.3	1893.3	1894.0	1867.5	1845.1	1819.6	1779.7	1731.9	1689.7	1651.3
15°	2040.9	2032.4	2032.4	2021.5	1992.1	1960.9	1934.6	1892.7	1832.5	1782.0	1728.9
17.5°	2147.1	2150.0	2145.7	2120.3	2097.1	2064.9	2016.6	1967.7	1911.9	1844.1	1789.8
20°	2210.6	2210.6	2205.8	2188.6	2158.6	2124.2	2072.0	2018.9	1948.0	1879.8	1818.6
22.5°	2236.4	2238.2	2232.4	2218.3	2191.2	2157.7	2113.3	2059.3	1986.2	1909.5	1833.6
25°	2201.0	2211.2	2212.2	2208.5	2200.4	2180.0	2141.9	2086.6	2021.0	1937.8	1856.1
27.5°	2020.7	2033.6	2044.9	2063.5	2088.2	2101.0	2102.7	2074.7	2017.5	1937.3	1855.2
30°	1841.1	1851.9	1886.7	1932.4	1967.9	2000.1	2028.0	2035.6	2003.4	1931.4	1844.9
32.5°	1641.7	1656.4	1691.3	1740.4	1799.5	1854.0	1916.7	1948.7	1947.9	1904.7	1824.7
35°	1355.6	1366.3	1398.6	1450.2	1521.1	1602.2	1701.5	1778.8	1831.5	1827.7	1778.8
37.5°	1093.3	1105.4	1138.0	1180.7	1249.5	1349.9	1446.0	1552.6	1649.9	1704.6	1688.3
40°	950.7	951.2	982.9	1026.9	1091.4	1178.9	1283.6	1401.8	1510.3	1598.9	1616.1
42.5°	838.1	838.2	859.1	906.6	953.0	1035.4	1135.4	1252.7	1379.7	1482.1	1527.6
45°	692.9	697.7	714.9	743.4	779.8	849.7	929.7	1038.7	1181.0	1302.4	1378.2
47.5°	586.7	593.8	604.7	627.9	657.0	703.6	769.7	867.7	983.5	1117.0	1224.8
50°	531.7	532.8	546.7	559.7	584.9	622.0	679.9	761.5	867.9	996.3	1116.1
52.5°	484.4	484.2	492.6	509.0	529.5	558.4	605.2	679.5	773.9	888.9	1012.5
55°	413.5	416.3	422.7	435.6	451.1	471.6	508.6	564.5	638.6	736.9	849.1
57.5°	359.6	361.0	366.1	371.5	385.9	400.7	428.5	467.3	529.8	610.3	714.9
60°	324.4	325.0	326.6	334.6	345.9	359.8	378.6	411.4	464.0	537.7	620.4
62.5°	290.0	290.9	293.5	299.3	308.1	317.7	337.4	363.8	407.3	470.2	544.7
65°	241.7	242.3	246.0	248.1	255.1	263.7	278.2	295.9	326.0	378.6	435.0
67.5°	202.0	202.0	202.2	205.1	209.8	215.6	224.3	238.4	261.2	293.5	343.2
70°	176.1	176.1	177.2	178.8	181.6	186.3	191.2	202.0	218.6	244.9	283.1
72.5°	152.1	152.5	153.6	153.9	155.3	159.3	162.9	169.8	182.1	202.0	232.8
75°	111.7	113.3	116.0	118.2	120.9	120.3	124.1	128.4	132.1	143.9	161.7
77.5°	83.1	82.3	82.6	84.4	84.7	85.3	88.0	91.3	94.1	99.7	106.0
80°	63.4	63.4	65.0	65.5	65.0	65.5	68.2	69.8	70.9	73.0	79.0
82.5°	47.9	48.8	48.3	48.8	49.1	49.6	51.9	52.2	53.3	54.1	56.7
85°	26.9	27.4	28.0	26.9	26.9	26.9	28.0	28.5	29.6	29.0	30.1
87.5°	12.7	12.3	12.9	12.7	13.0	12.6	12.9	13.6	12.5	13.1	12.8
90°	16.6	16.6	17.4	16.6	15.8	15.8	15.0	14.2	13.4	14.2	12.6
92.5°	60.8	60.8	63.5	67.8	77.1	92.9	116.7	155.1	208.6	250.4	219.2
95°	192.7	203.0	217.1	241.7	280.3	356.9	462.7	585.1	661.8	643.6	485.6
97.5°	515.0	531.4	555.1	602.7	659.3	741.7	819.0	864.4	831.3	677.8	454.5
100°	724.1	730.4	754.1	802.2	871.0	929.4	968.1	952.3	837.0	634.9	412.2
102.5°	906.1	911.1	936.0	971.0	1013.1	1037.4	1026.2	947.9	789.6	581.2	383.7
105°	1111.1	1115.8	1126.8	1133.2	1131.6	1099.1	1021.0	884.4	703.6	518.0	359.3
107.5°	1187.1	1185.1	1177.2	1159.2	1120.1	1049.8	939.7	794.3	634.1	482.6	354.9
110°	1188.4	1181.3	1167.1	1133.9	1077.8	991.0	876.5	739.9	599.4	470.6	356.1



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1151.1	1139.6	1119.7	1079.5	1015.9	929.1	820.9	700.1	579.8	464.9	359.9
115°	1066.8	1060.5	1035.2	987.8	925.4	849.6	757.3	660.1	561.4	461.9	367.2
117.5°	981.4	976.4	950.9	911.1	857.9	793.6	720.9	640.6	553.2	461.1	375.0
120°	933.3	924.6	904.1	869.4	824.4	768.3	705.2	631.7	548.8	461.1	380.6
122.5°	895.4	886.8	869.4	839.7	801.6	752.6	695.0	624.1	543.7	460.5	386.3
125°	851.2	846.5	831.5	808.6	777.0	733.6	679.1	611.2	535.3	459.6	394.9
127.5°	825.4	820.6	808.0	787.6	755.9	714.6	660.2	595.4	524.1	457.9	401.6
130°	810.2	805.5	792.8	773.1	740.6	698.8	645.1	582.8	517.3	457.2	406.7
132.5°	793.1	788.4	776.4	754.1	722.4	680.5	628.0	569.5	510.9	456.6	411.1
135°	761.2	756.5	743.9	721.8	690.1	650.7	602.5	551.2	501.4	455.7	417.7
137.5°	721.8	716.0	705.6	683.8	654.3	618.6	578.0	534.6	493.2	455.4	421.6
140°	693.3	687.0	675.9	658.5	631.0	597.7	562.2	525.1	488.8	454.8	424.9
142.5°	663.0	658.5	648.7	632.7	608.1	579.5	549.0	516.2	485.0	454.8	427.4
145°	621.5	617.5	609.6	596.2	576.4	554.3	530.7	503.8	478.5	453.2	428.8
147.5°	584.6	583.2	577.2	565.7	551.2	533.8	514.8	493.5	472.7	450.4	429.6
150°	563.8	563.0	558.3	548.1	535.3	521.2	505.3	487.2	468.3	448.5	429.6
152.5°	544.8	544.0	541.2	532.8	522.1	510.4	495.8	480.3	463.2	445.4	428.3
155°	520.4	520.4	518.0	511.7	503.8	494.3	482.5	469.8	455.7	440.6	426.4
157.5°	498.9	498.9	497.5	492.7	486.8	479.2	469.2	458.6	447.9	435.8	424.3
160°	485.6	485.6	484.8	480.1	475.3	469.1	460.4	451.7	442.2	431.9	422.4
162.5°	473.0	473.6	472.8	468.1	464.6	459.0	452.1	444.7	437.2	428.2	420.6
165°	454.0	454.8	455.7	452.4	449.3	445.4	439.8	435.0	428.8	422.4	417.0
167.5°	439.0	439.7	439.8	437.8	436.2	433.8	429.4	425.8	421.2	416.8	413.1
170°	429.6	429.6	430.3	429.6	428.0	425.7	422.4	420.1	416.2	412.9	410.6
172.5°	420.1	421.3	422.1	421.3	420.4	418.7	416.8	415.1	411.7	409.2	408.1
175°	409.0	410.6	412.2	410.6	410.6	410.6	409.0	408.3	406.7	405.1	405.1
177.5°	402.5	403.8	405.1	404.5	405.1	404.5	404.5	403.8	403.1	402.5	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332939-840
 CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1373.4	1367.5	1364.4	1357.6	1349.4	1345.0	1341.2	1335.6	1328.3	1320.6	1314.9
5°	1443.1	1430.3	1414.1	1394.8	1377.7	1361.0	1346.5	1332.0	1315.3	1298.1	1280.9
7.5°	1514.7	1489.3	1462.0	1430.3	1399.5	1371.4	1345.6	1320.9	1292.9	1268.0	1245.2
10°	1564.5	1530.1	1492.0	1451.8	1411.5	1376.5	1342.2	1311.0	1276.7	1246.1	1220.2
12.5°	1604.9	1564.5	1518.6	1468.4	1420.1	1377.9	1338.3	1297.7	1258.6	1225.4	1191.0
15°	1671.9	1616.6	1554.9	1494.7	1431.9	1374.4	1321.2	1273.9	1229.4	1182.7	1149.9
17.5°	1718.0	1652.3	1577.3	1505.0	1430.8	1363.0	1301.7	1245.4	1194.0	1146.2	1107.2
20°	1745.6	1673.0	1589.7	1507.6	1424.3	1351.8	1285.8	1223.5	1170.3	1118.7	1078.4
22.5°	1761.0	1680.7	1589.7	1503.7	1417.4	1339.0	1266.5	1201.5	1143.7	1092.1	1047.5
25°	1766.0	1680.0	1587.1	1488.2	1393.7	1310.5	1235.3	1165.0	1100.4	1048.9	1001.7
27.5°	1759.1	1657.9	1562.7	1461.3	1363.7	1276.0	1197.1	1123.2	1058.6	1003.3	954.8
30°	1748.8	1640.2	1538.2	1432.9	1334.1	1249.8	1166.5	1095.6	1028.5	971.1	922.2
32.5°	1726.4	1618.8	1508.9	1401.2	1301.0	1214.2	1135.2	1063.9	998.0	939.3	887.4
35°	1682.1	1573.2	1453.9	1343.2	1245.0	1154.7	1080.7	1011.9	949.1	886.2	831.4
37.5°	1623.9	1512.5	1393.8	1272.6	1174.3	1089.1	1021.1	956.5	895.2	837.9	777.2
40°	1568.8	1467.3	1344.8	1224.6	1123.6	1041.4	978.6	920.0	858.3	801.3	740.6
42.5°	1502.2	1415.7	1292.0	1171.2	1071.6	992.4	933.9	876.7	820.4	765.3	702.0
45°	1391.1	1325.5	1209.5	1093.5	993.1	914.6	860.9	810.4	761.0	708.4	648.8
47.5°	1263.6	1219.3	1119.1	1000.4	907.5	836.9	785.0	743.8	702.0	649.3	597.0
50°	1175.2	1146.7	1050.0	941.5	852.9	787.9	734.8	696.1	661.2	610.7	563.9
52.5°	1080.7	1065.5	983.8	880.1	794.5	730.7	685.3	650.6	615.2	573.3	529.6
55°	936.6	944.7	875.5	785.8	705.2	651.5	610.2	581.1	551.1	515.6	481.8
57.5°	789.5	818.9	772.4	693.7	618.1	568.6	537.5	513.0	487.8	458.4	429.5
60°	701.5	726.1	699.8	630.6	564.5	518.3	489.3	470.5	445.2	418.4	396.4
62.5°	615.5	642.0	626.3	570.4	509.1	469.3	443.7	426.3	407.5	384.1	361.1
65°	507.6	524.7	517.3	478.6	435.0	401.2	377.6	364.7	347.5	330.3	309.9
67.5°	388.7	421.9	417.6	397.0	359.4	333.0	317.5	306.1	290.4	277.7	263.8
70°	319.5	350.2	349.6	333.0	312.6	287.9	277.1	267.5	253.5	241.2	229.8
72.5°	261.6	289.6	293.8	281.0	267.0	248.3	238.0	231.4	217.8	209.3	200.3
75°	183.2	203.6	208.9	208.9	202.5	192.8	183.7	179.4	169.8	162.2	156.8
77.5°	120.1	133.0	141.4	143.3	144.3	141.1	133.5	130.5	123.1	120.4	115.2
80°	84.8	93.4	103.1	106.3	109.1	108.0	104.7	102.6	95.6	92.9	90.8
82.5°	58.7	63.4	71.3	78.4	77.7	80.5	77.7	75.9	70.7	69.7	67.6
85°	30.6	31.1	32.2	37.1	39.8	40.8	41.4	40.3	38.7	38.7	34.9
87.5°	12.5	12.1	12.0	12.0	12.3	13.8	14.6	14.7	13.8	13.0	11.8
90°	11.0	11.0	6.4	6.4	5.6	4.7	2.3	0.8	2.3	4.7	5.6
92.5°	159.5	98.3	58.1	41.7	30.2	20.5	13.1	9.0	13.1	20.5	30.2
95°	296.9	167.4	98.7	65.5	46.6	36.4	28.4	26.1	28.4	36.4	46.6
97.5°	266.9	160.0	107.0	79.3	63.0	53.5	46.8	46.8	46.8	53.5	63.0
100°	251.2	161.9	115.3	90.0	75.0	65.5	60.0	60.0	60.0	65.5	75.0
102.5°	246.7	168.1	126.0	102.0	87.7	78.8	73.9	72.6	73.9	78.8	87.7
105°	248.7	183.2	145.3	122.4	108.2	98.7	94.7	92.4	94.7	98.7	108.2
107.5°	260.4	200.8	166.0	143.4	129.8	119.7	115.7	114.2	115.7	119.7	129.8
110°	269.2	214.0	179.3	157.9	143.7	134.2	130.3	128.8	130.3	134.2	143.7



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	278.7	226.6	193.2	171.8	157.6	148.8	144.2	142.6	144.2	148.8	157.6
115°	293.8	246.4	214.8	193.5	178.4	170.6	165.0	162.7	165.0	170.6	178.4
117.5°	309.0	265.5	235.5	213.4	199.3	190.7	185.7	183.5	185.7	190.7	199.3
120°	319.8	278.7	248.7	226.6	213.2	204.5	198.9	197.4	198.9	204.5	213.2
122.5°	329.9	291.3	261.4	239.8	225.2	217.1	211.7	210.1	211.7	217.1	225.2
125°	345.1	308.7	280.3	258.2	243.2	234.5	229.7	226.6	229.7	234.5	243.2
127.5°	358.2	324.9	297.4	275.1	259.4	249.5	243.9	241.4	243.9	249.5	259.4
130°	366.4	335.6	308.7	285.9	270.8	259.0	252.7	249.5	252.7	259.0	270.8
132.5°	374.6	344.5	317.6	296.0	279.7	268.5	260.2	257.7	260.2	268.5	279.7
135°	385.4	356.9	330.8	310.3	293.8	280.3	272.5	269.2	272.5	280.3	293.8
137.5°	392.9	366.4	342.0	322.4	305.3	292.5	283.8	280.8	283.8	292.5	305.3
140°	398.0	372.7	349.0	330.0	313.5	300.0	291.3	289.0	291.3	300.0	313.5
142.5°	401.7	378.4	355.4	337.0	321.0	308.3	300.2	297.8	300.2	308.3	321.0
145°	405.9	384.6	364.1	346.7	331.6	320.6	312.7	310.3	312.7	320.6	331.6
147.5°	409.5	390.9	371.6	356.0	343.5	332.1	325.2	324.4	325.2	332.1	343.5
150°	411.4	394.0	376.7	361.6	349.8	340.3	334.1	333.3	334.1	340.3	349.8
152.5°	412.6	396.6	381.1	367.4	356.8	347.9	341.6	341.4	341.6	347.9	356.8
155°	413.7	400.3	386.9	375.1	366.4	358.5	353.8	352.9	353.8	358.5	366.4
157.5°	413.7	403.0	391.6	382.3	374.8	368.6	364.2	364.2	364.2	368.6	374.8
160°	413.7	404.2	394.9	386.2	379.8	374.3	371.1	371.1	371.1	374.3	379.8
162.5°	413.7	405.6	396.7	389.9	384.3	379.3	376.8	377.5	376.8	379.3	384.3
165°	412.2	405.9	398.8	394.0	390.1	386.2	384.6	384.6	384.6	386.2	390.1
167.5°	410.3	405.8	400.5	396.9	394.7	391.6	390.9	391.6	390.9	391.6	394.7
170°	409.0	405.1	401.1	398.8	397.2	394.9	394.0	394.9	394.0	394.9	397.2
172.5°	407.8	404.5	401.7	400.0	399.1	397.4	397.2	398.0	397.2	397.4	399.1
175°	405.9	403.5	401.9	401.9	401.1	400.3	400.3	401.1	400.3	400.3	401.1
177.5°	403.8	402.5	401.9	401.9	401.9	401.3	401.9	402.5	401.9	401.3	401.9
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1309.0	1304.6	1299.1	1292.6	1285.0	1278.1	1275.1	1277.6	1278.9	1275.5	1275.1
5°	1269.1	1255.7	1245.0	1228.8	1216.0	1205.2	1197.7	1194.5	1195.6	1187.0	1184.8
7.5°	1224.4	1208.4	1190.8	1171.7	1153.9	1138.1	1129.8	1125.3	1116.2	1112.3	1105.7
10°	1195.6	1174.1	1156.9	1134.3	1113.9	1095.1	1086.0	1078.4	1069.3	1065.0	1055.9
12.5°	1165.9	1140.9	1122.1	1098.6	1077.8	1055.1	1046.4	1032.5	1018.2	1009.2	997.4
15°	1124.1	1094.1	1071.0	1043.0	1018.3	992.5	969.5	943.6	934.0	913.6	901.8
17.5°	1075.2	1044.7	1016.1	978.7	940.6	908.6	883.9	859.2	844.4	831.4	825.4
20°	1043.0	1015.1	975.3	931.8	889.4	853.9	834.0	818.0	801.8	792.7	786.3
22.5°	1012.5	976.8	930.7	883.7	841.3	813.5	796.7	780.1	767.1	758.4	749.7
25°	961.4	914.6	865.8	812.0	783.0	758.9	740.6	727.2	719.1	707.9	703.6
27.5°	908.9	852.2	798.3	762.2	732.1	709.9	694.0	683.9	673.7	666.5	661.0
30°	868.5	811.0	762.7	728.3	697.7	679.4	666.5	654.7	646.6	640.8	636.4
32.5°	828.5	771.0	730.4	693.5	669.3	651.5	637.7	628.9	622.6	615.0	612.4
35°	770.7	719.7	684.3	651.0	626.2	610.2	599.4	590.3	584.9	582.7	581.1
37.5°	715.2	673.4	635.3	607.9	585.9	573.3	560.6	556.1	552.4	548.6	550.3
40°	679.9	640.8	606.9	577.9	560.2	546.2	538.7	533.3	530.1	530.1	530.1
42.5°	649.4	611.1	578.1	552.1	534.4	522.6	514.2	509.7	508.6	508.2	510.8
45°	602.1	566.6	533.3	511.8	496.8	484.9	480.2	476.4	476.4	478.6	479.1
47.5°	555.1	521.9	495.2	471.1	457.4	450.0	445.8	443.8	444.0	446.3	448.7
50°	526.3	493.6	467.3	445.8	432.9	425.9	422.1	421.1	422.1	422.1	425.9
52.5°	494.9	465.6	439.8	421.7	407.1	400.5	398.5	397.0	397.7	399.4	401.0
55°	449.0	422.7	398.0	380.8	370.0	365.8	360.9	361.4	360.4	361.4	361.4
57.5°	402.9	379.3	356.3	342.6	333.3	327.0	321.7	323.3	321.6	321.4	320.5
60°	373.2	347.5	329.2	316.9	306.1	300.7	295.9	297.0	295.4	294.3	292.2
62.5°	341.0	319.5	302.2	290.2	281.7	275.4	270.5	269.5	265.8	262.1	257.4
65°	294.3	276.6	261.1	249.7	241.7	236.8	233.1	229.8	221.8	213.2	208.9
67.5°	248.9	236.1	221.6	212.1	205.5	199.1	192.0	186.5	178.9	174.2	171.6
70°	219.6	207.3	195.0	185.8	178.8	173.0	164.9	161.2	155.7	153.6	150.9
72.5°	191.8	180.3	168.7	160.5	153.1	148.5	142.1	138.4	136.0	135.1	132.5
75°	149.4	140.2	131.6	124.1	118.2	114.9	112.3	109.6	108.5	103.6	101.0
77.5°	109.0	102.9	97.6	92.2	88.0	85.8	80.7	77.6	75.7	73.5	72.9
80°	84.8	80.6	75.2	72.0	66.0	63.9	61.8	61.2	60.7	60.2	59.6
82.5°	63.8	59.5	54.1	52.2	50.6	49.3	48.0	47.5	47.0	47.3	47.2
85°	32.2	30.1	30.1	29.6	29.0	28.5	28.0	28.0	27.4	28.0	27.4
87.5°	12.0	11.6	12.5	11.6	12.4	12.7	12.1	12.3	12.9	12.2	12.2
90°	6.4	6.4	11.0	11.0	12.6	14.2	13.4	14.2	15.0	15.8	15.8
92.5°	41.7	58.1	98.3	159.5	219.2	250.4	208.6	155.1	116.7	92.9	77.1
95°	65.5	98.7	167.4	296.9	485.6	643.6	661.8	585.1	462.7	356.9	280.3
97.5°	79.3	107.0	160.0	266.9	454.5	677.8	831.3	864.4	819.0	741.7	659.3
100°	90.0	115.3	161.9	251.2	412.2	634.9	837.0	952.3	968.1	929.4	871.0
102.5°	102.0	126.0	168.1	246.7	383.7	581.2	789.6	947.9	1026.2	1037.4	1013.1
105°	122.4	145.3	183.2	248.7	359.3	518.0	703.6	884.4	1021.0	1099.1	1131.6
107.5°	143.4	166.0	200.8	260.4	354.9	482.6	634.1	794.3	939.7	1049.8	1120.1
110°	157.9	179.3	214.0	269.2	356.1	470.6	599.4	739.9	876.5	991.0	1077.8



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	171.8	193.2	226.6	278.7	359.9	464.9	579.8	700.1	820.9	929.1	1015.9
115°	193.5	214.8	246.4	293.8	367.2	461.9	561.4	660.1	757.3	849.6	925.4
117.5°	213.4	235.5	265.5	309.0	375.0	461.1	553.2	640.6	720.9	793.6	857.9
120°	226.6	248.7	278.7	319.8	380.6	461.1	548.8	631.7	705.2	768.3	824.4
122.5°	239.8	261.4	291.3	329.9	386.3	460.5	543.7	624.1	695.0	752.6	801.6
125°	258.2	280.3	308.7	345.1	394.9	459.6	535.3	611.2	679.1	733.6	777.0
127.5°	275.1	297.4	324.9	358.2	401.6	457.9	524.1	595.4	660.2	714.6	755.9
130°	285.9	308.7	335.6	366.4	406.7	457.2	517.3	582.8	645.1	698.8	740.6
132.5°	296.0	317.6	344.5	374.6	411.1	456.6	510.9	569.5	628.0	680.5	722.4
135°	310.3	330.8	356.9	385.4	417.7	455.7	501.4	551.2	602.5	650.7	690.1
137.5°	322.4	342.0	366.4	392.9	421.6	455.4	493.2	534.6	578.0	618.6	654.3
140°	330.0	349.0	372.7	398.0	424.9	454.8	488.8	525.1	562.2	597.7	631.0
142.5°	337.0	355.4	378.4	401.7	427.4	454.8	485.0	516.2	549.0	579.5	608.1
145°	346.7	364.1	384.6	405.9	428.8	453.2	478.5	503.8	530.7	554.3	576.4
147.5°	356.0	371.6	390.9	409.5	429.6	450.4	472.7	493.5	514.8	533.8	551.2
150°	361.6	376.7	394.0	411.4	429.6	448.5	468.3	487.2	505.3	521.2	535.3
152.5°	367.4	381.1	396.6	412.6	428.3	445.4	463.2	480.3	495.8	510.4	522.1
155°	375.1	386.9	400.3	413.7	426.4	440.6	455.7	469.8	482.5	494.3	503.8
157.5°	382.3	391.6	403.0	413.7	424.3	435.8	447.9	458.6	469.2	479.2	486.8
160°	386.2	394.9	404.2	413.7	422.4	431.9	442.2	451.7	460.4	469.1	475.3
162.5°	389.9	396.7	405.6	413.7	420.6	428.2	437.2	444.7	452.1	459.0	464.6
165°	394.0	398.8	405.9	412.2	417.0	422.4	428.8	435.0	439.8	445.4	449.3
167.5°	396.9	400.5	405.8	410.3	413.1	416.8	421.2	425.8	429.4	433.8	436.2
170°	398.8	401.1	405.1	409.0	410.6	412.9	416.2	420.1	422.4	425.7	428.0
172.5°	400.0	401.7	404.5	407.8	408.1	409.2	411.7	415.1	416.8	418.7	420.4
175°	401.9	401.9	403.5	405.9	405.1	405.1	406.7	408.3	409.0	410.6	410.6
177.5°	401.9	401.9	402.5	403.8	402.5	402.5	403.1	403.8	404.5	404.5	405.1
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1272.4	1273.3	1270.3	1269.4	1270.3	1273.3	1272.4	1275.1	1275.5	1278.9	1277.6
5°	1180.5	1179.4	1176.8	1177.3	1176.8	1179.4	1180.5	1184.8	1187.0	1195.6	1194.5
7.5°	1101.9	1097.7	1098.8	1094.6	1098.8	1097.7	1101.9	1105.7	1112.3	1116.2	1125.3
10°	1053.8	1047.8	1043.0	1038.7	1043.0	1047.8	1053.8	1055.9	1065.0	1069.3	1078.4
12.5°	988.1	983.0	976.4	977.8	976.4	983.0	988.1	997.4	1009.2	1018.2	1032.5
15°	894.7	886.8	873.8	875.5	873.8	886.8	894.7	901.8	913.6	934.0	943.6
17.5°	815.9	816.0	810.0	811.4	810.0	816.0	815.9	825.4	831.4	844.4	859.2
20°	775.0	771.2	771.7	770.2	771.7	771.2	775.0	786.3	792.7	801.8	818.0
22.5°	746.7	742.0	738.3	735.0	738.3	742.0	746.7	749.7	758.4	767.1	780.1
25°	698.7	695.5	690.6	689.6	690.6	695.5	698.7	703.6	707.9	719.1	727.2
27.5°	656.6	656.0	654.1	651.6	654.1	656.0	656.6	661.0	666.5	673.7	683.9
30°	632.2	631.1	630.0	628.3	630.0	631.1	632.2	636.4	640.8	646.6	654.7
32.5°	610.3	609.6	608.5	608.6	608.5	609.6	610.3	612.4	615.0	622.6	628.9
35°	579.0	578.5	577.3	576.8	577.3	578.5	579.0	581.1	582.7	584.9	590.3
37.5°	549.8	551.2	550.5	550.4	550.5	551.2	549.8	550.3	548.6	552.4	556.1
40°	529.6	530.1	531.2	530.7	531.2	530.1	529.6	530.1	530.1	530.1	533.3
42.5°	512.8	512.9	514.4	512.6	514.4	512.9	512.8	510.8	508.2	508.6	509.7
45°	482.8	486.0	485.5	485.5	485.5	486.0	482.8	479.1	478.6	476.4	476.4
47.5°	450.1	452.8	453.6	453.5	453.6	452.8	450.1	448.7	446.3	444.0	443.8
50°	428.6	427.5	429.1	428.6	429.1	427.5	428.6	425.9	422.1	422.1	421.1
52.5°	402.4	402.6	402.5	401.9	402.5	402.6	402.4	401.0	399.4	397.7	397.0
55°	362.0	362.5	361.4	362.0	361.4	362.5	362.0	361.4	361.4	360.4	361.4
57.5°	318.2	315.6	316.7	315.4	316.7	315.6	318.2	320.5	321.4	321.6	323.3
60°	286.8	282.5	281.4	279.3	281.4	282.5	286.8	292.2	294.3	295.4	297.0
62.5°	251.6	248.5	244.9	246.6	244.9	248.5	251.6	257.4	262.1	265.8	269.5
65°	204.6	202.5	200.9	203.0	200.9	202.5	204.6	208.9	213.2	221.8	229.8
67.5°	169.4	168.2	168.2	167.1	168.2	168.2	169.4	171.6	174.2	178.9	186.5
70°	150.9	149.4	149.4	148.2	149.4	149.4	150.9	150.9	153.6	155.7	161.2
72.5°	132.0	130.4	130.9	130.2	130.9	130.4	132.0	132.5	135.1	136.0	138.4
75°	97.8	95.0	95.0	95.6	95.0	95.0	97.8	101.0	103.6	108.5	109.6
77.5°	72.9	72.4	73.1	72.2	73.1	72.4	72.9	72.9	73.5	75.7	77.6
80°	59.6	59.1	58.6	60.2	58.6	59.1	59.6	59.6	60.2	60.7	61.2
82.5°	46.3	46.2	46.0	48.2	46.0	46.2	46.3	47.2	47.3	47.0	47.5
85°	28.0	26.9	28.0	26.9	28.0	26.9	28.0	27.4	28.0	27.4	28.0
87.5°	13.2	12.9	12.3	12.7	12.3	12.9	13.2	12.2	12.2	12.9	12.3
90°	16.6	17.4	16.6	16.6	16.6	17.4	16.6	15.8	15.8	15.0	14.2
92.5°	67.8	63.5	60.8	60.8	60.8	63.5	67.8	77.1	92.9	116.7	155.1
95°	241.7	217.1	203.0	192.7	203.0	217.1	241.7	280.3	356.9	462.7	585.1
97.5°	602.7	555.1	531.4	515.0	531.4	555.1	602.7	659.3	741.7	819.0	864.4
100°	802.2	754.1	730.4	724.1	730.4	754.1	802.2	871.0	929.4	968.1	952.3
102.5°	971.0	936.0	911.1	906.1	911.1	936.0	971.0	1013.1	1037.4	1026.2	947.9
105°	1133.2	1126.8	1115.8	1111.1	1115.8	1126.8	1133.2	1131.6	1099.1	1021.0	884.4
107.5°	1159.2	1177.2	1185.1	1187.1	1185.1	1177.2	1159.2	1120.1	1049.8	939.7	794.3
110°	1133.9	1167.1	1181.3	1188.4	1181.3	1167.1	1133.9	1077.8	991.0	876.5	739.9



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1079.5	1119.7	1139.6	1151.1	1139.6	1119.7	1079.5	1015.9	929.1	820.9	700.1
115°	987.8	1035.2	1060.5	1066.8	1060.5	1035.2	987.8	925.4	849.6	757.3	660.1
117.5°	911.1	950.9	976.4	981.4	976.4	950.9	911.1	857.9	793.6	720.9	640.6
120°	869.4	904.1	924.6	933.3	924.6	904.1	869.4	824.4	768.3	705.2	631.7
122.5°	839.7	869.4	886.8	895.4	886.8	869.4	839.7	801.6	752.6	695.0	624.1
125°	808.6	831.5	846.5	851.2	846.5	831.5	808.6	777.0	733.6	679.1	611.2
127.5°	787.6	808.0	820.6	825.4	820.6	808.0	787.6	755.9	714.6	660.2	595.4
130°	773.1	792.8	805.5	810.2	805.5	792.8	773.1	740.6	698.8	645.1	582.8
132.5°	754.1	776.4	788.4	793.1	788.4	776.4	754.1	722.4	680.5	628.0	569.5
135°	721.8	743.9	756.5	761.2	756.5	743.9	721.8	690.1	650.7	602.5	551.2
137.5°	683.8	705.6	716.0	721.8	716.0	705.6	683.8	654.3	618.6	578.0	534.6
140°	658.5	675.9	687.0	693.3	687.0	675.9	658.5	631.0	597.7	562.2	525.1
142.5°	632.7	648.7	658.5	663.0	658.5	648.7	632.7	608.1	579.5	549.0	516.2
145°	596.2	609.6	617.5	621.5	617.5	609.6	596.2	576.4	554.3	530.7	503.8
147.5°	565.7	577.2	583.2	584.6	583.2	577.2	565.7	551.2	533.8	514.8	493.5
150°	548.1	558.3	563.0	563.8	563.0	558.3	548.1	535.3	521.2	505.3	487.2
152.5°	532.8	541.2	544.0	544.8	544.0	541.2	532.8	522.1	510.4	495.8	480.3
155°	511.7	518.0	520.4	520.4	520.4	518.0	511.7	503.8	494.3	482.5	469.8
157.5°	492.7	497.5	498.9	498.9	498.9	497.5	492.7	486.8	479.2	469.2	458.6
160°	480.1	484.8	485.6	485.6	485.6	484.8	480.1	475.3	469.1	460.4	451.7
162.5°	468.1	472.8	473.6	473.0	473.6	472.8	468.1	464.6	459.0	452.1	444.7
165°	452.4	455.7	454.8	454.0	454.8	455.7	452.4	449.3	445.4	439.8	435.0
167.5°	437.8	439.8	439.7	439.0	439.7	439.8	437.8	436.2	433.8	429.4	425.8
170°	429.6	430.3	429.6	429.6	429.6	430.3	429.6	428.0	425.7	422.4	420.1
172.5°	421.3	422.1	421.3	420.1	421.3	422.1	421.3	420.4	418.7	416.8	415.1
175°	410.6	412.2	410.6	409.0	410.6	412.2	410.6	410.6	410.6	409.0	408.3
177.5°	404.5	405.1	403.8	402.5	403.8	405.1	404.5	405.1	404.5	404.5	403.8
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1275.1	1278.1	1285.0	1292.6	1299.1	1304.6	1309.0	1314.9	1320.6	1328.3	1335.6
5°	1197.7	1205.2	1216.0	1228.8	1245.0	1255.7	1269.1	1280.9	1298.1	1315.3	1332.0
7.5°	1129.8	1138.1	1153.9	1171.7	1190.8	1208.4	1224.4	1245.2	1268.0	1292.9	1320.9
10°	1086.0	1095.1	1113.9	1134.3	1156.9	1174.1	1195.6	1220.2	1246.1	1276.7	1311.0
12.5°	1046.4	1055.1	1077.8	1098.6	1122.1	1140.9	1165.9	1191.0	1225.4	1258.6	1297.7
15°	969.5	992.5	1018.3	1043.0	1071.0	1094.1	1124.1	1149.9	1182.7	1229.4	1273.9
17.5°	883.9	908.6	940.6	978.7	1016.1	1044.7	1075.2	1107.2	1146.2	1194.0	1245.4
20°	834.0	853.9	889.4	931.8	975.3	1015.1	1043.0	1078.4	1118.7	1170.3	1223.5
22.5°	796.7	813.5	841.3	883.7	930.7	976.8	1012.5	1047.5	1092.1	1143.7	1201.5
25°	740.6	758.9	783.0	812.0	865.8	914.6	961.4	1001.7	1048.9	1100.4	1165.0
27.5°	694.0	709.9	732.1	762.2	798.3	852.2	908.9	954.8	1003.3	1058.6	1123.2
30°	666.5	679.4	697.7	728.3	762.7	811.0	868.5	922.2	971.1	1028.5	1095.6
32.5°	637.7	651.5	669.3	693.5	730.4	771.0	828.5	887.4	939.3	998.0	1063.9
35°	599.4	610.2	626.2	651.0	684.3	719.7	770.7	831.4	886.2	949.1	1011.9
37.5°	560.6	573.3	585.9	607.9	635.3	673.4	715.2	777.2	837.9	895.2	956.5
40°	538.7	546.2	560.2	577.9	606.9	640.8	679.9	740.6	801.3	858.3	920.0
42.5°	514.2	522.6	534.4	552.1	578.1	611.1	649.4	702.0	765.3	820.4	876.7
45°	480.2	484.9	496.8	511.8	533.3	566.6	602.1	648.8	708.4	761.0	810.4
47.5°	445.8	450.0	457.4	471.1	495.2	521.9	555.1	597.0	649.3	702.0	743.8
50°	422.1	425.9	432.9	445.8	467.3	493.6	526.3	563.9	610.7	661.2	696.1
52.5°	398.5	400.5	407.1	421.7	439.8	465.6	494.9	529.6	573.3	615.2	650.6
55°	360.9	365.8	370.0	380.8	398.0	422.7	449.0	481.8	515.6	551.1	581.1
57.5°	321.7	327.0	333.3	342.6	356.3	379.3	402.9	429.5	458.4	487.8	513.0
60°	295.9	300.7	306.1	316.9	329.2	347.5	373.2	396.4	418.4	445.2	470.5
62.5°	270.5	275.4	281.7	290.2	302.2	319.5	341.0	361.1	384.1	407.5	426.3
65°	233.1	236.8	241.7	249.7	261.1	276.6	294.3	309.9	330.3	347.5	364.7
67.5°	192.0	199.1	205.5	212.1	221.6	236.1	248.9	263.8	277.7	290.4	306.1
70°	164.9	173.0	178.8	185.8	195.0	207.3	219.6	229.8	241.2	253.5	267.5
72.5°	142.1	148.5	153.1	160.5	168.7	180.3	191.8	200.3	209.3	217.8	231.4
75°	112.3	114.9	118.2	124.1	131.6	140.2	149.4	156.8	162.2	169.8	179.4
77.5°	80.7	85.8	88.0	92.2	97.6	102.9	109.0	115.2	120.4	123.1	130.5
80°	61.8	63.9	66.0	72.0	75.2	80.6	84.8	90.8	92.9	95.6	102.6
82.5°	48.0	49.3	50.6	52.2	54.1	59.5	63.8	67.6	69.7	70.7	75.9
85°	28.0	28.5	29.0	29.6	30.1	30.1	32.2	34.9	38.7	38.7	40.3
87.5°	12.1	12.7	12.4	11.6	12.5	11.6	12.0	11.8	13.0	13.8	14.7
90°	13.4	14.2	12.6	11.0	11.0	6.4	6.4	5.6	4.7	2.3	0.8
92.5°	208.6	250.4	219.2	159.5	98.3	58.1	41.7	30.2	20.5	13.1	9.0
95°	661.8	643.6	485.6	296.9	167.4	98.7	65.5	46.6	36.4	28.4	26.1
97.5°	831.3	677.8	454.5	266.9	160.0	107.0	79.3	63.0	53.5	46.8	46.8
100°	837.0	634.9	412.2	251.2	161.9	115.3	90.0	75.0	65.5	60.0	60.0
102.5°	789.6	581.2	383.7	246.7	168.1	126.0	102.0	87.7	78.8	73.9	72.6
105°	703.6	518.0	359.3	248.7	183.2	145.3	122.4	108.2	98.7	94.7	92.4
107.5°	634.1	482.6	354.9	260.4	200.8	166.0	143.4	129.8	119.7	115.7	114.2
110°	599.4	470.6	356.1	269.2	214.0	179.3	157.9	143.7	134.2	130.3	128.8



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	579.8	464.9	359.9	278.7	226.6	193.2	171.8	157.6	148.8	144.2	142.6
115°	561.4	461.9	367.2	293.8	246.4	214.8	193.5	178.4	170.6	165.0	162.7
117.5°	553.2	461.1	375.0	309.0	265.5	235.5	213.4	199.3	190.7	185.7	183.5
120°	548.8	461.1	380.6	319.8	278.7	248.7	226.6	213.2	204.5	198.9	197.4
122.5°	543.7	460.5	386.3	329.9	291.3	261.4	239.8	225.2	217.1	211.7	210.1
125°	535.3	459.6	394.9	345.1	308.7	280.3	258.2	243.2	234.5	229.7	226.6
127.5°	524.1	457.9	401.6	358.2	324.9	297.4	275.1	259.4	249.5	243.9	241.4
130°	517.3	457.2	406.7	366.4	335.6	308.7	285.9	270.8	259.0	252.7	249.5
132.5°	510.9	456.6	411.1	374.6	344.5	317.6	296.0	279.7	268.5	260.2	257.7
135°	501.4	455.7	417.7	385.4	356.9	330.8	310.3	293.8	280.3	272.5	269.2
137.5°	493.2	455.4	421.6	392.9	366.4	342.0	322.4	305.3	292.5	283.8	280.8
140°	488.8	454.8	424.9	398.0	372.7	349.0	330.0	313.5	300.0	291.3	289.0
142.5°	485.0	454.8	427.4	401.7	378.4	355.4	337.0	321.0	308.3	300.2	297.8
145°	478.5	453.2	428.8	405.9	384.6	364.1	346.7	331.6	320.6	312.7	310.3
147.5°	472.7	450.4	429.6	409.5	390.9	371.6	356.0	343.5	332.1	325.2	324.4
150°	468.3	448.5	429.6	411.4	394.0	376.7	361.6	349.8	340.3	334.1	333.3
152.5°	463.2	445.4	428.3	412.6	396.6	381.1	367.4	356.8	347.9	341.6	341.4
155°	455.7	440.6	426.4	413.7	400.3	386.9	375.1	366.4	358.5	353.8	352.9
157.5°	447.9	435.8	424.3	413.7	403.0	391.6	382.3	374.8	368.6	364.2	364.2
160°	442.2	431.9	422.4	413.7	404.2	394.9	386.2	379.8	374.3	371.1	371.1
162.5°	437.2	428.2	420.6	413.7	405.6	396.7	389.9	384.3	379.3	376.8	377.5
165°	428.8	422.4	417.0	412.2	405.9	398.8	394.0	390.1	386.2	384.6	384.6
167.5°	421.2	416.8	413.1	410.3	405.8	400.5	396.9	394.7	391.6	390.9	391.6
170°	416.2	412.9	410.6	409.0	405.1	401.1	398.8	397.2	394.9	394.0	394.9
172.5°	411.7	409.2	408.1	407.8	404.5	401.7	400.0	399.1	397.4	397.2	398.0
175°	406.7	405.1	405.1	405.9	403.5	401.9	401.9	401.1	400.3	400.3	401.1
177.5°	403.1	402.5	402.5	403.8	402.5	401.9	401.9	401.9	401.3	401.9	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1341.2	1345.0	1349.4	1357.6	1364.4	1367.5	1373.4	1377.8	1376.4	1382.4	1392.8
5°	1346.5	1361.0	1377.7	1394.8	1414.1	1430.3	1443.1	1456.0	1466.2	1478.5	1496.8
7.5°	1345.6	1371.4	1399.5	1430.3	1462.0	1489.3	1514.7	1540.4	1563.4	1588.4	1621.1
10°	1342.2	1376.5	1411.5	1451.8	1492.0	1530.1	1564.5	1596.8	1627.4	1660.1	1701.5
12.5°	1338.3	1377.9	1420.1	1468.4	1518.6	1564.5	1604.9	1651.3	1689.7	1731.9	1779.7
15°	1321.2	1374.4	1431.9	1494.7	1554.9	1616.6	1671.9	1728.9	1782.0	1832.5	1892.7
17.5°	1301.7	1363.0	1430.8	1505.0	1577.3	1652.3	1718.0	1789.8	1844.1	1911.9	1967.7
20°	1285.8	1351.8	1424.3	1507.6	1589.7	1673.0	1745.6	1818.6	1879.8	1948.0	2018.9
22.5°	1266.5	1339.0	1417.4	1503.7	1589.7	1680.7	1761.0	1833.6	1909.5	1986.2	2059.3
25°	1235.3	1310.5	1393.7	1488.2	1587.1	1680.0	1766.0	1856.1	1937.8	2021.0	2086.6
27.5°	1197.1	1276.0	1363.7	1461.3	1562.7	1657.9	1759.1	1855.2	1937.3	2017.5	2074.7
30°	1166.5	1249.8	1334.1	1432.9	1538.2	1640.2	1748.8	1844.9	1931.4	2003.4	2035.6
32.5°	1135.2	1214.2	1301.0	1401.2	1508.9	1618.8	1726.4	1824.7	1904.7	1947.9	1948.7
35°	1080.7	1154.7	1245.0	1343.2	1453.9	1573.2	1682.1	1778.8	1827.7	1831.5	1778.8
37.5°	1021.1	1089.1	1174.3	1272.6	1393.8	1512.5	1623.9	1688.3	1704.6	1649.9	1552.6
40°	978.6	1041.4	1123.6	1224.6	1344.8	1467.3	1568.8	1616.1	1598.9	1510.3	1401.8
42.5°	933.9	992.4	1071.6	1171.2	1292.0	1415.7	1502.2	1527.6	1482.1	1379.7	1252.7
45°	860.9	914.6	993.1	1093.5	1209.5	1325.5	1391.1	1378.2	1302.4	1181.0	1038.7
47.5°	785.0	836.9	907.5	1000.4	1119.1	1219.3	1263.6	1224.8	1117.0	983.5	867.7
50°	734.8	787.9	852.9	941.5	1050.0	1146.7	1175.2	1116.1	996.3	867.9	761.5
52.5°	685.3	730.7	794.5	880.1	983.8	1065.5	1080.7	1012.5	888.9	773.9	679.5
55°	610.2	651.5	705.2	785.8	875.5	944.7	936.6	849.1	736.9	638.6	564.5
57.5°	537.5	568.6	618.1	693.7	772.4	818.9	789.5	714.9	610.3	529.8	467.3
60°	489.3	518.3	564.5	630.6	699.8	726.1	701.5	620.4	537.7	464.0	411.4
62.5°	443.7	469.3	509.1	570.4	626.3	642.0	615.5	544.7	470.2	407.3	363.8
65°	377.6	401.2	435.0	478.6	517.3	524.7	507.6	435.0	378.6	326.0	295.9
67.5°	317.5	333.0	359.4	397.0	417.6	421.9	388.7	343.2	293.5	261.2	238.4
70°	277.1	287.9	312.6	333.0	349.6	350.2	319.5	283.1	244.9	218.6	202.0
72.5°	238.0	248.3	267.0	281.0	293.8	289.6	261.6	232.8	202.0	182.1	169.8
75°	183.7	192.8	202.5	208.9	208.9	203.6	183.2	161.7	143.9	132.1	128.4
77.5°	133.5	141.1	144.3	143.3	141.4	133.0	120.1	106.0	99.7	94.1	91.3
80°	104.7	108.0	109.1	106.3	103.1	93.4	84.8	79.0	73.0	70.9	69.8
82.5°	77.7	80.5	77.7	78.4	71.3	63.4	58.7	56.7	54.1	53.3	52.2
85°	41.4	40.8	39.8	37.1	32.2	31.1	30.6	30.1	29.0	29.6	28.5
87.5°	14.6	13.8	12.3	12.0	12.0	12.1	12.5	12.8	13.1	12.5	13.6
90°	2.3	4.7	5.6	6.4	6.4	11.0	11.0	12.6	14.2	13.4	14.2
92.5°	13.1	20.5	30.2	41.7	58.1	98.3	159.5	219.2	250.4	208.6	155.1
95°	28.4	36.4	46.6	65.5	98.7	167.4	296.9	485.6	643.6	661.8	585.1
97.5°	46.8	53.5	63.0	79.3	107.0	160.0	266.9	454.5	677.8	831.3	864.4
100°	60.0	65.5	75.0	90.0	115.3	161.9	251.2	412.2	634.9	837.0	952.3
102.5°	73.9	78.8	87.7	102.0	126.0	168.1	246.7	383.7	581.2	789.6	947.9
105°	94.7	98.7	108.2	122.4	145.3	183.2	248.7	359.3	518.0	703.6	884.4
107.5°	115.7	119.7	129.8	143.4	166.0	200.8	260.4	354.9	482.6	634.1	794.3
110°	130.3	134.2	143.7	157.9	179.3	214.0	269.2	356.1	470.6	599.4	739.9



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	144.2	148.8	157.6	171.8	193.2	226.6	278.7	359.9	464.9	579.8	700.1
115°	165.0	170.6	178.4	193.5	214.8	246.4	293.8	367.2	461.9	561.4	660.1
117.5°	185.7	190.7	199.3	213.4	235.5	265.5	309.0	375.0	461.1	553.2	640.6
120°	198.9	204.5	213.2	226.6	248.7	278.7	319.8	380.6	461.1	548.8	631.7
122.5°	211.7	217.1	225.2	239.8	261.4	291.3	329.9	386.3	460.5	543.7	624.1
125°	229.7	234.5	243.2	258.2	280.3	308.7	345.1	394.9	459.6	535.3	611.2
127.5°	243.9	249.5	259.4	275.1	297.4	324.9	358.2	401.6	457.9	524.1	595.4
130°	252.7	259.0	270.8	285.9	308.7	335.6	366.4	406.7	457.2	517.3	582.8
132.5°	260.2	268.5	279.7	296.0	317.6	344.5	374.6	411.1	456.6	510.9	569.5
135°	272.5	280.3	293.8	310.3	330.8	356.9	385.4	417.7	455.7	501.4	551.2
137.5°	283.8	292.5	305.3	322.4	342.0	366.4	392.9	421.6	455.4	493.2	534.6
140°	291.3	300.0	313.5	330.0	349.0	372.7	398.0	424.9	454.8	488.8	525.1
142.5°	300.2	308.3	321.0	337.0	355.4	378.4	401.7	427.4	454.8	485.0	516.2
145°	312.7	320.6	331.6	346.7	364.1	384.6	405.9	428.8	453.2	478.5	503.8
147.5°	325.2	332.1	343.5	356.0	371.6	390.9	409.5	429.6	450.4	472.7	493.5
150°	334.1	340.3	349.8	361.6	376.7	394.0	411.4	429.6	448.5	468.3	487.2
152.5°	341.6	347.9	356.8	367.4	381.1	396.6	412.6	428.3	445.4	463.2	480.3
155°	353.8	358.5	366.4	375.1	386.9	400.3	413.7	426.4	440.6	455.7	469.8
157.5°	364.2	368.6	374.8	382.3	391.6	403.0	413.7	424.3	435.8	447.9	458.6
160°	371.1	374.3	379.8	386.2	394.9	404.2	413.7	422.4	431.9	442.2	451.7
162.5°	376.8	379.3	384.3	389.9	396.7	405.6	413.7	420.6	428.2	437.2	444.7
165°	384.6	386.2	390.1	394.0	398.8	405.9	412.2	417.0	422.4	428.8	435.0
167.5°	390.9	391.6	394.7	396.9	400.5	405.8	410.3	413.1	416.8	421.2	425.8
170°	394.0	394.9	397.2	398.8	401.1	405.1	409.0	410.6	412.9	416.2	420.1
172.5°	397.2	397.4	399.1	400.0	401.7	404.5	407.8	408.1	409.2	411.7	415.1
175°	400.3	400.3	401.1	401.9	401.9	403.5	405.9	405.1	405.1	406.7	408.3
177.5°	401.9	401.3	401.9	401.9	401.9	402.5	403.8	402.5	402.5	403.1	403.8
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9	401.9



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0	1333.0
2.5°	1398.4	1400.1	1401.4	1405.6	1406.0	1410.0	1406.0
5°	1514.0	1521.6	1533.4	1545.2	1546.3	1553.8	1540.3
7.5°	1643.8	1661.2	1672.0	1691.1	1698.7	1703.4	1695.7
10°	1733.1	1749.3	1777.8	1791.7	1805.6	1807.9	1801.4
12.5°	1819.6	1845.1	1867.5	1894.0	1893.3	1912.3	1905.3
15°	1934.6	1960.9	1992.1	2021.5	2032.4	2032.4	2040.9
17.5°	2016.6	2064.9	2097.1	2120.3	2145.7	2150.0	2147.1
20°	2072.0	2124.2	2158.6	2188.6	2205.8	2210.6	2210.6
22.5°	2113.3	2157.7	2191.2	2218.3	2232.4	2238.2	2236.4
25°	2141.9	2180.0	2200.4	2208.5	2212.2	2211.2	2201.0
27.5°	2102.7	2101.0	2088.2	2063.5	2044.9	2033.6	2020.7
30°	2028.0	2000.1	1967.9	1932.4	1886.7	1851.9	1841.1
32.5°	1916.7	1854.0	1799.5	1740.4	1691.3	1656.4	1641.7
35°	1701.5	1602.2	1521.1	1450.2	1398.6	1366.3	1355.6
37.5°	1446.0	1349.9	1249.5	1180.7	1138.0	1105.4	1093.3
40°	1283.6	1178.9	1091.4	1026.9	982.9	951.2	950.7
42.5°	1135.4	1035.4	953.0	906.6	859.1	838.2	838.1
45°	929.7	849.7	779.8	743.4	714.9	697.7	692.9
47.5°	769.7	703.6	657.0	627.9	604.7	593.8	586.7
50°	679.9	622.0	584.9	559.7	546.7	532.8	531.7
52.5°	605.2	558.4	529.5	509.0	492.6	484.2	484.4
55°	508.6	471.6	451.1	435.6	422.7	416.3	413.5
57.5°	428.5	400.7	385.9	371.5	366.1	361.0	359.6
60°	378.6	359.8	345.9	334.6	326.6	325.0	324.4
62.5°	337.4	317.7	308.1	299.3	293.5	290.9	290.0
65°	278.2	263.7	255.1	248.1	246.0	242.3	241.7
67.5°	224.3	215.6	209.8	205.1	202.2	202.0	202.0
70°	191.2	186.3	181.6	178.8	177.2	176.1	176.1
72.5°	162.9	159.3	155.3	153.9	153.6	152.5	152.1
75°	124.1	120.3	120.9	118.2	116.0	113.3	111.7
77.5°	88.0	85.3	84.7	84.4	82.6	82.3	83.1
80°	68.2	65.5	65.0	65.5	65.0	63.4	63.4
82.5°	51.9	49.6	49.1	48.8	48.3	48.8	47.9
85°	28.0	26.9	26.9	26.9	28.0	27.4	26.9
87.5°	12.9	12.6	13.0	12.7	12.9	12.3	12.7
90°	15.0	15.8	15.8	16.6	17.4	16.6	16.6
92.5°	116.7	92.9	77.1	67.8	63.5	60.8	60.8
95°	462.7	356.9	280.3	241.7	217.1	203.0	192.7
97.5°	819.0	741.7	659.3	602.7	555.1	531.4	515.0
100°	968.1	929.4	871.0	802.2	754.1	730.4	724.1
102.5°	1026.2	1037.4	1013.1	971.0	936.0	911.1	906.1
105°	1021.0	1099.1	1131.6	1133.2	1126.8	1115.8	1111.1
107.5°	939.7	1049.8	1120.1	1159.2	1177.2	1185.1	1187.1
110°	876.5	991.0	1077.8	1133.9	1167.1	1181.3	1188.4



TEST NUMBER: P332939-840

CATALOG NUMBER: SA4XXRDIP-C795D810U840-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	820.9	929.1	1015.9	1079.5	1119.7	1139.6	1151.1
115°	757.3	849.6	925.4	987.8	1035.2	1060.5	1066.8
117.5°	720.9	793.6	857.9	911.1	950.9	976.4	981.4
120°	705.2	768.3	824.4	869.4	904.1	924.6	933.3
122.5°	695.0	752.6	801.6	839.7	869.4	886.8	895.4
125°	679.1	733.6	777.0	808.6	831.5	846.5	851.2
127.5°	660.2	714.6	755.9	787.6	808.0	820.6	825.4
130°	645.1	698.8	740.6	773.1	792.8	805.5	810.2
132.5°	628.0	680.5	722.4	754.1	776.4	788.4	793.1
135°	602.5	650.7	690.1	721.8	743.9	756.5	761.2
137.5°	578.0	618.6	654.3	683.8	705.6	716.0	721.8
140°	562.2	597.7	631.0	658.5	675.9	687.0	693.3
142.5°	549.0	579.5	608.1	632.7	648.7	658.5	663.0
145°	530.7	554.3	576.4	596.2	609.6	617.5	621.5
147.5°	514.8	533.8	551.2	565.7	577.2	583.2	584.6
150°	505.3	521.2	535.3	548.1	558.3	563.0	563.8
152.5°	495.8	510.4	522.1	532.8	541.2	544.0	544.8
155°	482.5	494.3	503.8	511.7	518.0	520.4	520.4
157.5°	469.2	479.2	486.8	492.7	497.5	498.9	498.9
160°	460.4	469.1	475.3	480.1	484.8	485.6	485.6
162.5°	452.1	459.0	464.6	468.1	472.8	473.6	473.0
165°	439.8	445.4	449.3	452.4	455.7	454.8	454.0
167.5°	429.4	433.8	436.2	437.8	439.8	439.7	439.0
170°	422.4	425.7	428.0	429.6	430.3	429.6	429.6
172.5°	416.8	418.7	420.4	421.3	422.1	421.3	420.1
175°	409.0	410.6	410.6	410.6	412.2	410.6	409.0
177.5°	404.5	404.5	405.1	404.5	405.1	403.8	402.5
180°	401.9	401.9	401.9	401.9	401.9	401.9	401.9

(END OF REPORT)