

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008606

Luminaire Tested: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008606
REPORT IS A COMBINATION OF REPORTS P983613 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D330UB35-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5722.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81				77
1	105	100	97	93	100	96	93	90	88	85	83	80	78	76	73	72	70				67
2	96	89	83	78	91	85	79	75	78	73	70	71	68	65	65	63	60				57
3	88	79	71	66	84	75	69	64	69	64	60	64	59	56	58	55	52				49
4	81	70	62	56	77	67	60	55	62	56	52	57	53	49	53	49	46				43
5	75	63	55	49	71	61	53	48	56	50	45	52	47	43	48	44	40				38
6	69	57	49	43	66	55	48	42	51	45	40	47	42	38	44	39	36				34
7	64	52	44	38	61	50	43	37	47	40	36	43	38	34	40	36	32				30
8	60	48	40	34	57	46	39	34	43	37	32	40	35	31	37	33	29				27
9	56	44	36	31	54	42	35	30	40	33	29	37	32	28	35	30	27				25
10	53	40	33	28	50	39	32	28	37	31	27	34	29	25	32	28	24				23

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	31769	31769	31769	31769
5°	31845	33874	31967	26949
10°	31476	36978	31673	22219
15°	30711	39004	31139	18715
20°	30233	36622	30233	16267
25°	29270	31461	29403	14546
30°	27685	24732	28213	13176
35°	26279	17101	26719	12055
40°	24665	12912	24947	11162
45°	22674	10611	23046	10198
50°	20953	9313	20991	9335
55°	18991	7935	19113	8399
60°	16899	6629	17133	7330
65°	15027	5391	15300	6259
70°	13161	4230	13494	5049
75°	11048	3070	11479	3662
80°	8622	1947	9237	2174
85°	5664	981	6102	727

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 32840 cd/sqm

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	3.3
10°-20°	556.4	9.7
20°-30°	807.5	14.1
30°-40°	851.2	14.9
40°-50°	753.3	13.2
50°-60°	601.5	10.5
60°-70°	408.5	7.1
70°-80°	209.0	3.7
80°-90°	50.6	0.9
90°-100°	72.4	1.3
100°-110°	254.9	4.5
110°-120°	267.7	4.7
120°-130°	220.2	3.8
130°-140°	176.9	3.1
140°-150°	133.6	2.3
150°-160°	93.9	1.6
160°-170°	55.3	1.0
170°-180°	18.0	0.3
0°-30°	1555.0	27.2
0°-40°	2406.3	42.1
0°-60°	3761.0	65.7
0°-90°	4429.2	77.4
90°-120°	594.9	10.4
90°-150°	1125.6	19.7
90°-180°	1293.0	22.6
0°-180°	5722.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	2007	2007	2007	2007	2007	
5°	2008	2242	2016	1783	2008	190
15°	1887	2755	1913	1322	1887	533
25°	1695	2295	1703	1061	1695	775
35°	1384	1250	1407	881	1384	866
45°	1038	753	1055	724	1038	805
55°	713	529	717	560	713	636
65°	423	326	430	378	423	420
75°	198	160	205	191	198	212
85°	40	42	43	31	40	47
90°	0	12	0	12	0	3
95°	12	41	12	41	12	13
105°	44	402	44	402	44	46
115°	77	529	77	529	77	76
125°	107	430	107	430	107	95
135°	126	356	126	356	126	97
145°	144	284	144	284	144	90
155°	163	239	163	239	163	75
165°	178	210	178	210	178	50
175°	185	189	185	189	185	18
180°	186	186	186	186	186	

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2017.8	2022.4	2030.1	2031.7	2047.1	2059.4	2073.3	2073.3	2077.9	2076.4	2064.1
5°	2008.5	2022.4	2042.5	2059.4	2087.2	2099.5	2118.0	2131.9	2144.3	2153.5	2152.0
7.5°	1993.1	2017.8	2047.1	2079.5	2116.5	2138.1	2164.3	2189.0	2206.0	2221.4	2232.2
10°	1966.9	2008.5	2048.6	2091.8	2139.6	2169.0	2199.8	2232.2	2258.4	2287.7	2315.5
12.5°	1931.4	1991.5	2040.9	2098.0	2156.6	2189.0	2238.4	2263.1	2314.0	2388.0	2408.1
15°	1886.6	1968.4	2014.7	2087.2	2164.3	2190.6	2258.4	2298.5	2403.4	2449.7	2505.2
17.5°	1845.0	1936.0	1997.7	2081.0	2156.6	2207.5	2273.9	2355.6	2443.5	2509.9	2571.6
20°	1811.1	1899.0	1973.0	2065.6	2161.2	2226.0	2295.4	2394.2	2489.8	2557.7	2605.5
22.5°	1733.9	1846.5	1932.9	2036.3	2152.0	2241.5	2307.8	2415.8	2519.1	2560.8	2602.4
25°	1695.4	1792.5	1892.8	2010.1	2145.8	2252.3	2309.3	2429.7	2520.7	2536.1	2545.4
27.5°	1624.4	1733.9	1851.2	1985.4	2144.3	2233.7	2306.2	2415.8	2488.3	2477.5	2449.7
30°	1536.5	1670.7	1800.3	1945.3	2122.7	2219.9	2287.7	2388.0	2425.0	2369.5	2320.1
32.5°	1471.7	1598.2	1741.6	1909.8	2098.0	2190.6	2256.9	2335.6	2343.3	2243.0	2159.7
35°	1383.7	1524.1	1686.1	1863.5	2056.3	2139.6	2201.3	2249.2	2212.1	2071.8	1973.0
37.5°	1305.1	1443.9	1616.7	1797.2	1999.3	2081.0	2130.4	2138.1	2047.1	1923.7	1778.7
40°	1218.7	1362.2	1542.6	1732.4	1936.0	2007.0	2037.8	2014.7	1883.6	1740.1	1572.0
42.5°	1132.3	1274.2	1468.6	1663.0	1855.8	1916.0	1928.3	1865.1	1704.6	1536.5	1342.1
45°	1038.2	1186.3	1380.7	1576.6	1763.2	1797.2	1798.7	1707.7	1518.0	1342.1	1161.6
47.5°	961.1	1098.4	1291.2	1487.1	1644.5	1667.6	1658.3	1553.4	1346.7	1149.3	991.9
50°	876.2	1007.3	1198.6	1391.5	1525.7	1531.8	1508.7	1359.1	1157.0	976.5	851.5
52.5°	785.2	917.9	1093.7	1278.8	1399.2	1389.9	1345.2	1184.7	995.0	845.4	749.7
55°	712.7	829.9	995.0	1175.5	1260.3	1234.1	1184.7	1021.2	871.6	745.1	661.8
57.5°	632.5	735.8	897.8	1055.2	1104.5	1079.8	1030.5	877.8	738.9	643.3	587.7
60°	556.9	651.0	792.9	924.0	962.6	936.4	879.3	742.0	641.7	561.5	519.9
62.5°	487.5	569.2	688.0	808.3	823.8	797.5	748.2	637.1	550.7	487.5	456.6
65°	422.7	499.8	595.5	686.5	700.4	672.6	621.7	541.5	469.0	428.9	399.5
67.5°	359.4	421.1	506.0	572.3	580.0	553.8	512.2	447.4	402.6	359.4	337.8
70°	303.9	350.2	416.5	470.5	473.6	448.9	427.3	368.7	334.8	303.9	286.9
72.5°	249.9	282.3	333.2	373.3	374.9	359.4	339.4	302.4	273.0	251.5	234.5
75°	197.5	225.2	256.1	291.6	290.0	277.7	262.2	239.1	214.4	200.5	192.8
77.5°	151.2	168.1	192.8	216.0	216.0	209.8	200.5	183.6	168.1	154.3	146.6
80°	108.0	118.8	138.8	146.6	149.6	148.1	140.4	128.0	121.9	111.1	108.0
82.5°	69.4	77.1	86.4	94.1	98.7	95.6	94.1	87.9	78.7	75.6	72.5
85°	40.1	43.2	47.8	52.4	54.0	52.4	55.5	50.9	46.3	46.3	44.7
87.5°	17.0	18.5	21.6	21.6	23.1	23.1	21.6	23.1	23.1	21.6	20.1
90°	0.4	1.4	2.9	3.6	4.3	4.8	5.4	7.1	9.6	11.8	12.1
92.5°	5.4	7.5	10.4	12.1	15.0	17.0	18.9	28.6	42.1	54.3	55.0
95°	12.5	13.9	17.5	20.7	26.4	30.7	35.0	51.4	82.5	123.9	139.9
97.5°	18.6	20.7	24.6	29.3	35.7	40.5	45.3	66.4	109.6	176.4	228.1
100°	27.5	28.6	31.8	37.5	44.6	49.6	54.6	73.5	117.1	194.2	282.0
102.5°	35.7	36.4	39.6	45.3	52.8	57.8	62.8	80.0	117.5	187.4	283.8
105°	43.6	45.0	47.5	52.8	60.7	65.7	70.7	87.5	119.2	178.1	264.5
107.5°	52.1	53.2	55.7	60.7	68.5	73.5	78.5	95.0	123.2	173.1	246.7
110°	60.7	62.1	64.3	68.9	76.4	81.6	86.8	102.5	128.2	171.7	234.5

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	68.5	70.0	72.5	76.8	83.9	89.2	94.6	109.6	133.5	172.1	226.7
115°	76.8	78.5	80.7	85.0	92.1	96.9	101.7	117.1	138.9	173.5	221.3
117.5°	85.3	86.8	88.9	92.8	99.6	104.6	109.6	123.9	144.6	175.6	218.5
120°	93.2	94.6	96.7	100.0	107.1	112.1	117.1	131.0	150.3	177.8	216.0
122.5°	100.7	101.7	103.9	107.5	114.6	119.8	125.0	137.8	155.3	180.3	214.6
125°	107.1	108.2	110.3	114.6	121.7	126.7	131.7	144.6	160.7	182.8	212.8
127.5°	112.5	113.9	116.7	121.4	128.2	133.4	138.5	151.0	165.6	185.3	211.7
130°	117.1	118.5	122.1	127.1	134.2	139.2	144.2	156.7	170.3	188.1	211.0
132.5°	121.4	123.2	127.1	132.4	139.9	144.9	149.9	161.7	174.9	191.0	210.6
135°	125.7	127.1	131.4	136.7	144.9	149.9	154.9	166.4	178.9	193.1	210.3
137.5°	129.6	131.4	135.7	141.4	149.6	154.2	158.9	170.3	182.1	195.3	210.3
140°	134.2	135.7	139.9	145.7	153.5	158.2	162.8	173.5	184.6	196.7	209.9
142.5°	138.9	139.9	143.9	149.6	157.1	161.4	165.6	176.0	186.7	197.8	209.9
145°	143.5	144.9	148.5	153.9	161.0	165.0	168.9	178.5	188.5	198.5	209.2
147.5°	148.5	149.6	153.2	158.2	164.2	167.8	171.4	180.6	189.6	198.8	208.1
150°	153.5	154.6	157.4	162.1	167.4	170.6	173.9	182.1	190.3	198.5	207.1
152.5°	158.5	158.9	161.7	165.6	170.6	173.5	176.4	183.5	190.6	197.8	205.3
155°	163.1	163.5	165.6	169.6	173.5	176.2	178.9	184.9	191.0	197.1	203.1
157.5°	167.1	167.4	169.2	172.8	176.0	178.3	180.6	186.0	191.0	195.6	201.0
160°	171.0	171.4	172.8	175.6	178.5	180.4	182.4	186.7	191.0	194.6	198.8
162.5°	174.9	174.6	176.0	178.1	180.6	182.0	183.5	187.1	190.6	193.5	197.1
165°	177.8	177.4	178.1	180.3	182.1	183.1	184.2	187.4	189.9	192.1	194.6
167.5°	180.3	179.9	180.6	182.1	183.5	184.2	184.9	187.4	189.6	190.6	192.4
170°	182.8	182.1	182.4	183.5	184.2	184.8	185.3	187.1	188.9	189.6	190.6
172.5°	184.2	183.9	183.5	184.6	184.9	185.2	185.6	186.7	187.8	188.1	188.5
175°	185.3	184.9	184.6	185.3	185.3	185.4	185.6	186.4	187.1	186.7	187.1
177.5°	186.0	185.3	184.9	185.6	185.6	185.6	185.6	186.0	186.7	186.0	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2085.7	2087.2	2090.3	2105.7	2113.4	2115.0	2108.8	2122.7	2127.3	2122.7	2119.6
5°	2184.4	2193.6	2212.1	2232.2	2230.7	2232.2	2241.5	2250.7	2253.8	2241.5	2246.1
7.5°	2270.8	2289.3	2309.3	2340.2	2340.2	2355.6	2361.8	2369.5	2388.0	2378.8	2375.7
10°	2369.5	2394.2	2431.2	2480.6	2482.1	2497.5	2513.0	2537.6	2545.4	2539.2	2542.3
12.5°	2492.9	2540.7	2543.8	2597.8	2622.5	2625.6	2650.3	2645.6	2661.1	2661.1	2687.3
15°	2546.9	2620.9	2662.6	2715.0	2730.5	2712.0	2732.0	2753.6	2755.2	2755.2	2753.6
17.5°	2644.1	2673.4	2715.0	2742.8	2749.0	2749.0	2750.5	2759.8	2753.6	2741.3	2750.5
20°	2664.1	2676.5	2691.9	2688.8	2691.9	2676.5	2661.1	2645.6	2647.2	2639.5	2662.6
22.5°	2627.1	2624.0	2588.6	2565.4	2565.4	2534.6	2505.2	2491.4	2477.5	2482.1	2489.8
25°	2534.6	2486.7	2443.5	2409.6	2401.9	2352.5	2312.4	2300.1	2276.9	2295.4	2298.5
27.5°	2386.5	2332.5	2263.1	2233.7	2193.6	2173.6	2145.8	2108.8	2061.0	2088.7	2084.1
30°	2227.6	2147.4	2090.3	2019.3	1956.1	1951.4	1899.0	1837.3	1812.6	1812.6	1826.5
32.5°	2050.2	1943.7	1860.4	1760.2	1698.4	1672.2	1609.0	1547.3	1561.2	1514.9	1531.8
35°	1843.5	1703.1	1598.2	1501.0	1454.7	1423.9	1342.1	1308.2	1271.1	1249.5	1289.6
37.5°	1646.0	1484.0	1349.8	1243.4	1226.4	1170.9	1115.3	1093.7	1072.1	1081.4	1079.8
40°	1405.3	1261.9	1141.6	1058.3	1028.9	1002.7	965.7	939.5	925.6	933.3	934.8
42.5°	1187.8	1067.5	978.0	919.4	894.7	876.2	857.7	836.1	831.5	831.5	837.7
45°	1019.7	921.0	860.8	813.0	799.1	785.2	771.3	762.1	759.0	752.8	757.4
47.5°	885.5	806.8	769.8	734.3	718.9	715.8	703.4	698.8	692.6	691.1	692.6
50°	772.9	723.5	689.6	669.5	658.7	654.1	647.9	638.7	635.6	643.3	640.2
52.5°	694.2	647.9	629.4	609.3	603.2	597.0	587.7	589.3	587.7	584.7	584.7
55°	615.5	586.2	567.7	552.3	550.7	544.6	536.8	533.8	532.2	529.1	533.8
57.5°	552.3	529.1	512.2	498.3	492.1	492.1	484.4	478.2	478.2	476.7	478.2
60°	489.0	465.9	455.1	441.2	436.6	435.0	430.4	427.3	422.7	422.7	422.7
62.5°	430.4	411.9	399.5	387.2	388.7	381.0	374.9	371.8	371.8	373.3	373.3
65°	374.9	362.5	347.1	336.3	333.2	331.7	328.6	327.0	322.4	325.5	325.5
67.5°	324.0	307.0	297.7	293.1	288.5	286.9	283.8	280.8	279.2	277.7	280.8
70°	273.0	259.2	251.5	248.4	243.7	242.2	240.7	236.0	237.6	239.1	240.7
72.5°	226.8	214.4	212.9	203.6	203.6	203.6	197.5	200.5	199.0	195.9	199.0
75°	178.9	172.8	169.7	165.1	166.6	165.1	163.5	158.9	158.9	160.4	162.0
77.5°	141.9	135.8	134.2	129.6	126.5	129.6	126.5	125.0	125.0	126.5	126.5
80°	104.9	101.8	97.2	97.2	97.2	95.6	95.6	95.6	94.1	92.6	94.1
82.5°	69.4	69.4	67.9	66.3	67.9	64.8	66.3	66.3	66.3	66.3	66.3
85°	44.7	43.2	43.2	41.7	41.7	41.7	43.2	40.1	40.1	41.7	41.7
87.5°	20.1	20.1	20.1	21.6	20.1	20.1	20.1	21.6	20.1	20.1	20.1
90°	11.8	11.4	10.7	11.4	11.6	11.8	11.8	11.8	11.8	11.8	11.8
92.5°	46.1	36.1	30.7	26.8	25.4	23.9	23.6	22.1	22.5	21.8	22.5
95°	122.5	93.5	71.8	56.8	52.8	48.9	44.3	41.4	40.3	40.7	40.3
97.5°	229.9	191.4	152.8	116.7	106.0	95.3	81.4	74.3	70.3	68.2	70.3
100°	333.4	325.9	281.7	232.8	211.2	189.6	159.9	144.6	134.2	127.8	134.2
102.5°	372.0	414.1	412.7	380.2	357.0	333.8	301.0	272.0	258.5	249.2	258.5
105°	359.5	433.8	474.1	478.7	472.8	467.0	444.8	422.7	407.3	402.3	407.3
107.5°	333.1	412.7	472.7	507.7	514.8	521.9	521.6	518.4	513.7	505.5	513.7
110°	308.4	383.8	447.7	493.4	508.0	522.7	538.0	544.8	548.0	547.6	548.0

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	291.3	357.4	418.0	467.7	485.0	502.3	525.1	537.6	544.4	546.9	544.4
115°	277.7	336.7	391.6	438.4	456.8	475.2	500.5	516.9	526.2	529.4	526.2
117.5°	268.5	319.5	368.8	412.3	429.8	447.3	473.4	490.9	500.5	503.0	500.5
120°	261.3	307.4	351.6	389.5	405.8	422.0	447.0	463.7	474.1	477.7	474.1
122.5°	255.3	297.7	337.4	372.7	387.0	401.3	423.0	439.5	448.4	451.2	448.4
125°	249.5	288.5	325.2	356.6	370.0	383.4	404.1	417.7	426.6	429.5	426.6
127.5°	244.2	279.2	313.1	343.1	355.6	368.1	386.3	399.1	407.0	409.1	407.0
130°	238.8	270.3	301.0	329.2	341.0	352.7	370.2	382.3	389.5	392.3	389.5
132.5°	234.5	261.7	289.5	314.9	325.8	336.7	353.8	365.9	372.4	374.9	372.4
135°	230.6	253.8	277.4	301.0	311.0	320.9	336.3	348.1	354.5	355.9	354.5
137.5°	227.8	247.4	267.8	287.0	296.0	304.9	319.5	329.9	335.6	337.7	335.6
140°	225.3	241.3	258.5	274.9	282.8	290.6	302.0	311.3	316.7	318.8	316.7
142.5°	222.8	236.3	250.3	263.8	270.0	276.3	287.0	295.2	299.9	299.9	299.9
145°	220.6	231.7	243.5	254.5	259.7	264.9	273.5	279.5	283.1	284.2	283.1
147.5°	218.5	228.1	237.8	246.7	250.6	254.5	262.0	267.0	269.5	270.3	269.5
150°	215.6	224.2	232.1	239.5	242.8	246.0	251.3	255.6	257.8	258.1	257.8
152.5°	213.1	220.3	227.4	233.5	236.2	238.8	242.8	246.3	247.8	247.8	247.8
155°	209.9	216.7	222.4	227.8	229.8	231.7	235.6	238.1	239.5	238.8	239.5
157.5°	207.1	212.4	217.4	222.1	223.7	225.3	228.1	230.3	231.0	231.0	231.0
160°	203.8	208.5	212.4	216.3	217.6	218.8	221.3	223.1	223.5	223.5	223.5
162.5°	201.0	204.6	207.8	211.0	211.9	212.8	215.3	216.3	216.7	216.3	216.7
165°	197.8	200.6	203.1	205.6	206.4	207.1	208.5	209.9	209.9	209.6	209.9
167.5°	194.6	196.7	198.8	200.6	201.4	202.1	202.8	203.5	203.5	203.1	203.5
170°	192.1	193.9	194.9	196.4	196.8	197.1	197.4	198.5	198.1	197.4	198.1
172.5°	189.6	190.6	191.4	192.4	192.6	192.8	193.1	193.5	193.1	192.8	193.1
175°	187.4	188.5	188.9	189.2	189.4	189.6	189.6	189.9	189.6	188.9	189.6
177.5°	186.0	186.7	186.7	187.1	187.1	187.1	187.1	187.1	186.7	186.0	186.7
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2127.3	2116.5	2107.2	2108.8	2116.5	2110.3	2094.9	2074.9	2067.1	2057.9	2067.1
5°	2255.3	2246.1	2227.6	2229.1	2224.5	2218.3	2193.6	2162.8	2162.8	2138.1	2135.0
7.5°	2381.8	2368.0	2355.6	2352.5	2335.6	2323.2	2301.6	2258.4	2241.5	2212.1	2195.2
10°	2523.8	2513.0	2499.1	2482.1	2472.9	2451.3	2415.8	2352.5	2321.7	2281.6	2252.3
12.5°	2667.2	2665.7	2634.8	2600.9	2599.3	2565.4	2540.7	2455.9	2414.2	2360.2	2290.8
15°	2758.2	2750.5	2733.6	2716.6	2721.2	2684.2	2628.7	2528.4	2500.6	2435.8	2361.8
17.5°	2756.7	2756.7	2752.1	2749.0	2744.4	2733.6	2702.7	2636.4	2591.6	2509.9	2440.5
20°	2668.8	2688.8	2693.5	2691.9	2707.3	2715.0	2713.5	2671.9	2636.4	2563.9	2492.9
22.5°	2492.9	2539.2	2559.2	2571.6	2604.0	2620.9	2661.1	2645.6	2636.4	2582.4	2522.2
25°	2329.4	2344.8	2405.0	2408.1	2452.8	2494.5	2534.6	2560.8	2594.7	2574.7	2523.8
27.5°	2118.0	2153.5	2196.7	2229.1	2238.4	2323.2	2389.6	2438.9	2516.0	2522.2	2505.2
30°	1878.9	1895.9	1966.9	2010.1	2059.4	2121.1	2216.8	2301.6	2371.0	2434.3	2455.9
32.5°	1587.4	1656.8	1698.4	1750.9	1794.1	1903.6	2020.9	2130.4	2210.6	2317.0	2363.3
35°	1320.5	1374.5	1445.5	1467.1	1545.7	1638.3	1791.0	1931.4	2053.3	2161.2	2255.3
37.5°	1099.9	1143.1	1218.7	1252.6	1298.9	1417.7	1545.7	1720.0	1866.6	1999.3	2116.5
40°	948.7	981.1	1038.2	1049.0	1087.6	1195.5	1298.9	1462.4	1656.8	1835.7	1963.8
42.5°	845.4	860.8	899.4	913.2	937.9	1010.4	1103.0	1257.3	1437.7	1622.9	1803.3
45°	771.3	782.1	805.3	817.6	848.5	880.8	956.4	1079.8	1221.8	1408.4	1602.8
47.5°	705.0	718.9	728.1	735.8	752.8	788.3	837.7	928.7	1064.4	1235.7	1423.9
50°	649.5	654.1	671.0	672.6	683.4	706.5	752.8	808.3	916.3	1055.2	1237.2
52.5°	593.9	598.5	609.3	620.1	624.8	643.3	674.1	720.4	800.6	910.2	1072.1
55°	538.4	544.6	555.4	563.1	567.7	583.1	601.6	646.4	709.6	786.7	919.4
57.5°	482.8	496.7	499.8	504.4	512.2	529.1	546.1	572.3	621.7	692.6	789.8
60°	430.4	435.0	445.8	450.5	458.2	467.4	489.0	509.1	544.6	600.1	688.0
62.5°	376.4	387.2	391.8	396.5	402.6	413.4	427.3	448.9	479.8	524.5	593.9
65°	330.1	331.7	340.9	347.1	353.3	361.0	374.9	394.9	413.4	455.1	506.0
67.5°	285.4	288.5	291.6	297.7	305.4	313.2	325.5	336.3	359.4	387.2	427.3
70°	242.2	242.2	249.9	254.5	253.0	262.2	271.5	283.8	300.8	327.0	359.4
72.5°	203.6	202.1	208.3	209.8	212.9	219.1	225.2	237.6	246.8	266.9	291.6
75°	162.0	165.1	168.1	168.1	172.8	177.4	183.6	189.7	200.5	212.9	231.4
77.5°	128.0	128.0	131.1	132.7	137.3	135.8	141.9	148.1	155.8	166.6	180.5
80°	94.1	97.2	97.2	97.2	98.7	100.3	106.4	111.1	115.7	123.4	129.6
82.5°	66.3	66.3	69.4	69.4	69.4	72.5	72.5	74.0	77.1	81.8	86.4
85°	41.7	41.7	41.7	43.2	41.7	43.2	46.3	44.7	46.3	49.4	49.4
87.5°	20.1	20.1	20.1	20.1	20.1	21.6	20.1	21.6	23.1	23.1	23.1
90°	11.8	11.8	11.8	11.6	11.4	10.7	11.4	11.8	12.1	11.8	9.6
92.5°	22.1	23.6	23.9	25.4	26.8	30.7	36.1	46.1	55.0	54.3	42.1
95°	41.4	44.3	48.9	52.8	56.8	71.8	93.5	122.5	139.9	123.9	82.5
97.5°	74.3	81.4	95.3	106.0	116.7	152.8	191.4	229.9	228.1	176.4	109.6
100°	144.6	159.9	189.6	211.2	232.8	281.7	325.9	333.4	282.0	194.2	117.1
102.5°	272.0	301.0	333.8	357.0	380.2	412.7	414.1	372.0	283.8	187.4	117.5
105°	422.7	444.8	467.0	472.8	478.7	474.1	433.8	359.5	264.5	178.1	119.2
107.5°	518.4	521.6	521.9	514.8	507.7	472.7	412.7	333.1	246.7	173.1	123.2
110°	544.8	538.0	522.7	508.0	493.4	447.7	383.8	308.4	234.5	171.7	128.2

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	537.6	525.1	502.3	485.0	467.7	418.0	357.4	291.3	226.7	172.1	133.5
115°	516.9	500.5	475.2	456.8	438.4	391.6	336.7	277.7	221.3	173.5	138.9
117.5°	490.9	473.4	447.3	429.8	412.3	368.8	319.5	268.5	218.5	175.6	144.6
120°	463.7	447.0	422.0	405.8	389.5	351.6	307.4	261.3	216.0	177.8	150.3
122.5°	439.5	423.0	401.3	387.0	372.7	337.4	297.7	255.3	214.6	180.3	155.3
125°	417.7	404.1	383.4	370.0	356.6	325.2	288.5	249.5	212.8	182.8	160.7
127.5°	399.1	386.3	368.1	355.6	343.1	313.1	279.2	244.2	211.7	185.3	165.6
130°	382.3	370.2	352.7	341.0	329.2	301.0	270.3	238.8	211.0	188.1	170.3
132.5°	365.9	353.8	336.7	325.8	314.9	289.5	261.7	234.5	210.6	191.0	174.9
135°	348.1	336.3	320.9	311.0	301.0	277.4	253.8	230.6	210.3	193.1	178.9
137.5°	329.9	319.5	304.9	296.0	287.0	267.8	247.4	227.8	210.3	195.3	182.1
140°	311.3	302.0	290.6	282.8	274.9	258.5	241.3	225.3	209.9	196.7	184.6
142.5°	295.2	287.0	276.3	270.0	263.8	250.3	236.3	222.8	209.9	197.8	186.7
145°	279.5	273.5	264.9	259.7	254.5	243.5	231.7	220.6	209.2	198.5	188.5
147.5°	267.0	262.0	254.5	250.6	246.7	237.8	228.1	218.5	208.1	198.8	189.6
150°	255.6	251.3	246.0	242.8	239.5	232.1	224.2	215.6	207.1	198.5	190.3
152.5°	246.3	242.8	238.8	236.2	233.5	227.4	220.3	213.1	205.3	197.8	190.6
155°	238.1	235.6	231.7	229.8	227.8	222.4	216.7	209.9	203.1	197.1	191.0
157.5°	230.3	228.1	225.3	223.7	222.1	217.4	212.4	207.1	201.0	195.6	191.0
160°	223.1	221.3	218.8	217.6	216.3	212.4	208.5	203.8	198.8	194.6	191.0
162.5°	216.3	215.3	212.8	211.9	211.0	207.8	204.6	201.0	197.1	193.5	190.6
165°	209.9	208.5	207.1	206.4	205.6	203.1	200.6	197.8	194.6	192.1	189.9
167.5°	203.5	202.8	202.1	201.4	200.6	198.8	196.7	194.6	192.4	190.6	189.6
170°	198.5	197.4	197.1	196.8	196.4	194.9	193.9	192.1	190.6	189.6	188.9
172.5°	193.5	193.1	192.8	192.6	192.4	191.4	190.6	189.6	188.5	188.1	187.8
175°	189.9	189.6	189.6	189.4	189.2	188.9	188.5	187.4	187.1	186.7	187.1
177.5°	187.1	187.1	187.1	187.1	187.1	186.7	186.7	186.0	185.6	186.0	186.7
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	2059.4	2051.7	2047.1	2050.2	2040.9	2017.8	2017.8	2025.5	2016.2	2007.0	1993.1
5°	2116.5	2101.1	2091.8	2090.3	2068.7	2031.7	2023.9	2016.2	1996.2	1974.6	1951.4
7.5°	2172.0	2144.3	2128.8	2118.0	2087.2	2039.4	2019.3	2002.3	1970.0	1937.6	1908.2
10°	2218.3	2178.2	2159.7	2142.7	2102.6	2042.5	2010.1	1979.2	1937.6	1895.9	1858.9
12.5°	2255.3	2209.1	2185.9	2161.2	2111.9	2033.2	1993.1	1943.7	1902.1	1846.5	1809.5
15°	2317.0	2221.4	2199.8	2176.7	2125.8	2017.8	1968.4	1912.9	1855.8	1781.8	1741.6
17.5°	2366.4	2238.4	2236.8	2187.5	2121.1	2011.6	1936.0	1863.5	1801.8	1727.8	1664.5
20°	2395.7	2264.6	2239.9	2189.0	2105.7	1970.0	1891.3	1811.1	1744.7	1655.3	1592.0
22.5°	2420.4	2301.6	2236.8	2175.1	2073.3	1956.1	1840.4	1764.8	1673.8	1576.6	1516.4
25°	2429.7	2309.3	2241.5	2170.5	2050.2	1916.0	1784.8	1703.1	1601.3	1513.3	1431.6
27.5°	2431.2	2307.8	2224.5	2150.4	2017.8	1863.5	1729.3	1642.9	1530.3	1428.5	1346.7
30°	2415.8	2290.8	2215.2	2135.0	1986.9	1815.7	1661.4	1565.8	1445.5	1343.6	1258.8
32.5°	2369.5	2256.9	2195.2	2107.2	1946.8	1749.4	1596.6	1490.2	1363.7	1263.4	1181.7
35°	2292.4	2215.2	2147.4	2065.6	1894.4	1687.6	1531.8	1406.9	1278.8	1183.2	1106.1
37.5°	2196.7	2155.1	2091.8	2011.6	1834.2	1632.1	1459.3	1320.5	1192.5	1099.9	1024.3
40°	2067.1	2077.9	2016.2	1943.7	1763.2	1556.5	1365.2	1232.6	1112.2	1025.9	951.8
42.5°	1926.8	1971.5	1936.0	1866.6	1684.6	1473.2	1295.8	1149.3	1032.0	942.6	880.8
45°	1775.6	1852.7	1831.1	1780.2	1602.8	1385.3	1197.1	1055.2	951.8	865.4	811.4
47.5°	1610.5	1720.0	1720.0	1683.0	1511.8	1297.4	1112.2	967.2	865.4	803.7	751.3
50°	1442.4	1565.8	1585.8	1561.2	1410.0	1197.1	1008.9	877.8	789.8	729.7	691.1
52.5°	1266.5	1410.0	1447.0	1434.7	1302.0	1101.4	924.0	796.0	715.8	663.3	629.4
55°	1098.4	1265.0	1305.1	1309.7	1186.3	996.5	829.9	717.3	640.2	604.7	575.4
57.5°	939.5	1099.9	1144.6	1152.4	1069.1	900.9	742.0	643.3	573.9	544.6	521.4
60°	803.7	937.9	996.5	1013.5	941.0	789.8	660.3	564.6	512.2	484.4	462.8
62.5°	692.6	800.6	862.3	867.0	834.6	692.6	575.4	495.2	450.5	425.8	415.0
65°	584.7	681.8	718.9	737.4	711.2	600.1	496.7	430.4	394.9	373.3	362.5
67.5°	498.3	560.0	590.8	615.5	589.3	506.0	422.7	368.7	342.5	320.9	314.7
70°	408.8	459.7	482.8	507.5	484.4	421.1	361.0	311.6	288.5	271.5	263.8
72.5°	327.0	367.1	388.7	404.2	390.3	337.8	288.5	254.5	237.6	225.2	220.6
75°	259.2	286.9	299.3	310.1	303.9	263.8	232.9	205.2	189.7	178.9	175.9
77.5°	197.5	217.5	231.4	234.5	226.8	200.5	174.3	157.3	145.0	138.8	135.8
80°	140.4	152.7	160.4	165.1	157.3	146.6	128.0	115.7	104.9	97.2	95.6
82.5°	94.1	100.3	106.4	104.9	101.8	92.6	81.8	75.6	71.0	64.8	64.8
85°	54.0	55.5	58.6	60.2	58.6	52.4	46.3	43.2	40.1	35.5	35.5
87.5°	23.1	24.7	24.7	26.2	23.1	23.1	20.1	17.0	17.0	15.4	13.9
90°	7.1	5.4	4.8	4.3	3.6	2.9	1.4	0.4	1.4	2.9	3.6
92.5°	28.6	18.9	17.0	15.0	12.1	10.4	7.5	5.4	7.5	10.4	12.1
95°	51.4	35.0	30.7	26.4	20.7	17.5	13.9	12.5	13.9	17.5	20.7
97.5°	66.4	45.3	40.5	35.7	29.3	24.6	20.7	18.6	20.7	24.6	29.3
100°	73.5	54.6	49.6	44.6	37.5	31.8	28.6	27.5	28.6	31.8	37.5
102.5°	80.0	62.8	57.8	52.8	45.3	39.6	36.4	35.7	36.4	39.6	45.3
105°	87.5	70.7	65.7	60.7	52.8	47.5	45.0	43.6	45.0	47.5	52.8
107.5°	95.0	78.5	73.5	68.5	60.7	55.7	53.2	52.1	53.2	55.7	60.7
110°	102.5	86.8	81.6	76.4	68.9	64.3	62.1	60.7	62.1	64.3	68.9

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	109.6	94.6	89.2	83.9	76.8	72.5	70.0	68.5	70.0	72.5	76.8
115°	117.1	101.7	96.9	92.1	85.0	80.7	78.5	76.8	78.5	80.7	85.0
117.5°	123.9	109.6	104.6	99.6	92.8	88.9	86.8	85.3	86.8	88.9	92.8
120°	131.0	117.1	112.1	107.1	100.0	96.7	94.6	93.2	94.6	96.7	100.0
122.5°	137.8	125.0	119.8	114.6	107.5	103.9	101.7	100.7	101.7	103.9	107.5
125°	144.6	131.7	126.7	121.7	114.6	110.3	108.2	107.1	108.2	110.3	114.6
127.5°	151.0	138.5	133.4	128.2	121.4	116.7	113.9	112.5	113.9	116.7	121.4
130°	156.7	144.2	139.2	134.2	127.1	122.1	118.5	117.1	118.5	122.1	127.1
132.5°	161.7	149.9	144.9	139.9	132.4	127.1	123.2	121.4	123.2	127.1	132.4
135°	166.4	154.9	149.9	144.9	136.7	131.4	127.1	125.7	127.1	131.4	136.7
137.5°	170.3	158.9	154.2	149.6	141.4	135.7	131.4	129.6	131.4	135.7	141.4
140°	173.5	162.8	158.2	153.5	145.7	139.9	135.7	134.2	135.7	139.9	145.7
142.5°	176.0	165.6	161.4	157.1	149.6	143.9	139.9	138.9	139.9	143.9	149.6
145°	178.5	168.9	165.0	161.0	153.9	148.5	144.9	143.5	144.9	148.5	153.9
147.5°	180.6	171.4	167.8	164.2	158.2	153.2	149.6	148.5	149.6	153.2	158.2
150°	182.1	173.9	170.6	167.4	162.1	157.4	154.6	153.5	154.6	157.4	162.1
152.5°	183.5	176.4	173.5	170.6	165.6	161.7	158.9	158.5	158.9	161.7	165.6
155°	184.9	178.9	176.2	173.5	169.6	165.6	163.5	163.1	163.5	165.6	169.6
157.5°	186.0	180.6	178.3	176.0	172.8	169.2	167.4	167.1	167.4	169.2	172.8
160°	186.7	182.4	180.4	178.5	175.6	172.8	171.4	171.0	171.4	172.8	175.6
162.5°	187.1	183.5	182.0	180.6	178.1	176.0	174.6	174.9	174.6	176.0	178.1
165°	187.4	184.2	183.1	182.1	180.3	178.1	177.4	177.8	177.4	178.1	180.3
167.5°	187.4	184.9	184.2	183.5	182.1	180.6	179.9	180.3	179.9	180.6	182.1
170°	187.1	185.3	184.8	184.2	183.5	182.4	182.1	182.8	182.1	182.4	183.5
172.5°	186.7	185.6	185.2	184.9	184.6	183.5	183.9	184.2	183.9	183.5	184.6
175°	186.4	185.6	185.4	185.3	185.3	184.6	184.9	185.3	184.9	184.6	185.3
177.5°	186.0	185.6	185.6	185.6	185.6	184.9	185.3	186.0	185.3	184.9	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1985.4	1993.1	1991.5	1976.1	1959.2	1945.3	1919.0	1922.1	1912.9	1914.4	1923.7
5°	1936.0	1936.0	1929.8	1908.2	1880.5	1865.1	1835.7	1828.0	1809.5	1808.0	1806.4
7.5°	1883.6	1875.9	1868.1	1837.3	1803.3	1778.7	1738.6	1729.3	1710.8	1698.4	1692.3
10°	1821.9	1811.1	1795.6	1760.2	1718.5	1687.6	1646.0	1633.7	1598.2	1582.7	1573.5
12.5°	1754.0	1747.8	1723.1	1693.8	1625.9	1592.0	1531.8	1544.2	1508.7	1477.9	1473.2
15°	1686.1	1663.0	1649.1	1601.3	1519.5	1504.1	1456.3	1431.6	1399.2	1374.5	1374.5
17.5°	1619.8	1584.3	1553.4	1502.5	1442.4	1399.2	1363.7	1351.4	1311.2	1286.6	1281.9
20°	1531.8	1491.7	1484.0	1411.5	1369.9	1322.0	1288.1	1257.3	1227.9	1217.1	1209.4
22.5°	1448.5	1402.3	1389.9	1328.2	1286.6	1238.7	1204.8	1183.2	1161.6	1153.9	1140.0
25°	1359.1	1331.3	1312.8	1246.5	1200.2	1155.4	1132.3	1116.9	1096.8	1095.3	1086.0
27.5°	1272.7	1246.5	1227.9	1164.7	1130.8	1089.1	1070.6	1053.6	1042.8	1038.2	1033.6
30°	1198.6	1169.3	1147.7	1101.4	1059.8	1025.9	1010.4	999.6	993.5	985.7	984.2
32.5°	1116.9	1099.9	1070.6	1035.1	1002.7	970.3	961.1	953.4	944.1	941.0	939.5
35°	1047.5	1024.3	1005.8	965.7	951.8	924.0	913.2	907.1	894.7	891.6	888.6
37.5°	979.6	958.0	937.9	913.2	887.0	871.6	865.4	856.2	850.0	851.5	848.5
40°	911.7	894.7	879.3	853.1	837.7	829.9	817.6	808.3	805.3	806.8	805.3
42.5°	845.4	829.9	820.7	800.6	785.2	777.5	769.8	760.5	765.1	765.1	769.8
45°	785.2	771.3	765.1	749.7	740.5	728.1	720.4	718.9	725.0	723.5	723.5
47.5°	723.5	718.9	711.2	697.3	684.9	677.2	675.7	675.7	681.8	684.9	683.4
50°	675.7	666.4	657.2	646.4	637.1	634.0	629.4	632.5	638.7	638.7	641.7
52.5°	615.5	609.3	606.3	597.0	590.8	590.8	590.8	592.4	597.0	601.6	600.1
55°	563.1	558.4	555.4	550.7	543.0	544.6	543.0	546.1	550.7	555.4	558.4
57.5°	507.5	506.0	502.9	495.2	495.2	493.6	498.3	499.8	507.5	510.6	515.2
60°	458.2	453.5	453.5	447.4	447.4	447.4	452.0	456.6	462.8	464.3	467.4
62.5°	405.7	405.7	404.2	399.5	399.5	404.2	405.7	411.9	415.0	415.0	419.6
65°	356.4	354.8	353.3	354.8	356.4	356.4	361.0	364.1	367.1	368.7	370.2
67.5°	307.0	305.4	308.5	307.0	310.1	316.2	314.7	319.3	324.0	324.0	325.5
70°	260.7	263.8	262.2	265.3	263.8	266.9	271.5	273.0	273.0	274.6	279.2
72.5°	217.5	217.5	217.5	216.0	217.5	220.6	223.7	225.2	228.3	229.9	234.5
75°	175.9	175.9	172.8	175.9	175.9	178.9	182.0	182.0	182.0	185.1	189.7
77.5°	132.7	134.2	132.7	135.8	135.8	137.3	140.4	138.8	141.9	143.5	145.0
80°	97.2	95.6	95.6	95.6	97.2	97.2	100.3	101.8	101.8	106.4	103.4
82.5°	61.7	63.2	61.7	63.2	63.2	64.8	63.2	64.8	66.3	69.4	67.9
85°	35.5	33.9	33.9	35.5	33.9	33.9	35.5	33.9	35.5	33.9	35.5
87.5°	13.9	12.3	12.3	12.3	12.3	10.8	10.8	9.3	9.3	9.3	7.7
90°	4.3	4.8	5.4	7.1	9.6	11.8	12.1	11.8	11.4	10.7	11.4
92.5°	15.0	17.0	18.9	28.6	42.1	54.3	55.0	46.1	36.1	30.7	26.8
95°	26.4	30.7	35.0	51.4	82.5	123.9	139.9	122.5	93.5	71.8	56.8
97.5°	35.7	40.5	45.3	66.4	109.6	176.4	228.1	229.9	191.4	152.8	116.7
100°	44.6	49.6	54.6	73.5	117.1	194.2	282.0	333.4	325.9	281.7	232.8
102.5°	52.8	57.8	62.8	80.0	117.5	187.4	283.8	372.0	414.1	412.7	380.2
105°	60.7	65.7	70.7	87.5	119.2	178.1	264.5	359.5	433.8	474.1	478.7
107.5°	68.5	73.5	78.5	95.0	123.2	173.1	246.7	333.1	412.7	472.7	507.7
110°	76.4	81.6	86.8	102.5	128.2	171.7	234.5	308.4	383.8	447.7	493.4

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	83.9	89.2	94.6	109.6	133.5	172.1	226.7	291.3	357.4	418.0	467.7
115°	92.1	96.9	101.7	117.1	138.9	173.5	221.3	277.7	336.7	391.6	438.4
117.5°	99.6	104.6	109.6	123.9	144.6	175.6	218.5	268.5	319.5	368.8	412.3
120°	107.1	112.1	117.1	131.0	150.3	177.8	216.0	261.3	307.4	351.6	389.5
122.5°	114.6	119.8	125.0	137.8	155.3	180.3	214.6	255.3	297.7	337.4	372.7
125°	121.7	126.7	131.7	144.6	160.7	182.8	212.8	249.5	288.5	325.2	356.6
127.5°	128.2	133.4	138.5	151.0	165.6	185.3	211.7	244.2	279.2	313.1	343.1
130°	134.2	139.2	144.2	156.7	170.3	188.1	211.0	238.8	270.3	301.0	329.2
132.5°	139.9	144.9	149.9	161.7	174.9	191.0	210.6	234.5	261.7	289.5	314.9
135°	144.9	149.9	154.9	166.4	178.9	193.1	210.3	230.6	253.8	277.4	301.0
137.5°	149.6	154.2	158.9	170.3	182.1	195.3	210.3	227.8	247.4	267.8	287.0
140°	153.5	158.2	162.8	173.5	184.6	196.7	209.9	225.3	241.3	258.5	274.9
142.5°	157.1	161.4	165.6	176.0	186.7	197.8	209.9	222.8	236.3	250.3	263.8
145°	161.0	165.0	168.9	178.5	188.5	198.5	209.2	220.6	231.7	243.5	254.5
147.5°	164.2	167.8	171.4	180.6	189.6	198.8	208.1	218.5	228.1	237.8	246.7
150°	167.4	170.6	173.9	182.1	190.3	198.5	207.1	215.6	224.2	232.1	239.5
152.5°	170.6	173.5	176.4	183.5	190.6	197.8	205.3	213.1	220.3	227.4	233.5
155°	173.5	176.2	178.9	184.9	191.0	197.1	203.1	209.9	216.7	222.4	227.8
157.5°	176.0	178.3	180.6	186.0	191.0	195.6	201.0	207.1	212.4	217.4	222.1
160°	178.5	180.4	182.4	186.7	191.0	194.6	198.8	203.8	208.5	212.4	216.3
162.5°	180.6	182.0	183.5	187.1	190.6	193.5	197.1	201.0	204.6	207.8	211.0
165°	182.1	183.1	184.2	187.4	189.9	192.1	194.6	197.8	200.6	203.1	205.6
167.5°	183.5	184.2	184.9	187.4	189.6	190.6	192.4	194.6	196.7	198.8	200.6
170°	184.2	184.8	185.3	187.1	188.9	189.6	190.6	192.1	193.9	194.9	196.4
172.5°	184.9	185.2	185.6	186.7	187.8	188.1	188.5	189.6	190.6	191.4	192.4
175°	185.3	185.4	185.6	186.4	187.1	186.7	187.1	187.4	188.5	188.9	189.2
177.5°	185.6	185.6	185.6	186.0	186.7	186.0	185.6	186.0	186.7	186.7	187.1
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1912.9	1917.5	1906.7	1903.6	1906.7	1895.9	1899.0	1902.1	1902.1	1906.7	1909.8
5°	1801.8	1795.6	1784.8	1781.8	1778.7	1783.3	1780.2	1784.8	1786.4	1797.2	1798.7
7.5°	1692.3	1683.0	1673.8	1664.5	1661.4	1653.7	1661.4	1661.4	1672.2	1669.1	1676.9
10°	1562.7	1561.2	1548.8	1544.2	1538.0	1525.7	1542.6	1538.0	1545.7	1559.6	1562.7
12.5°	1467.1	1450.1	1457.8	1436.2	1443.9	1431.6	1433.1	1433.1	1445.5	1447.0	1443.9
15°	1376.0	1362.2	1342.1	1332.8	1328.2	1322.0	1342.1	1343.6	1334.4	1356.0	1348.3
17.5°	1283.5	1283.5	1265.0	1260.3	1248.0	1254.2	1251.1	1252.6	1249.5	1265.0	1272.7
20°	1203.3	1195.5	1189.4	1190.9	1175.5	1172.4	1169.3	1172.4	1183.2	1194.0	1197.1
22.5°	1138.5	1133.8	1118.4	1121.5	1109.2	1113.8	1110.7	1118.4	1120.0	1120.0	1130.8
25°	1076.8	1070.6	1072.1	1066.0	1061.3	1061.3	1056.7	1061.3	1067.5	1070.6	1072.1
27.5°	1030.5	1025.9	1018.1	1013.5	1016.6	1008.9	1015.1	1019.7	1019.7	1016.6	1019.7
30°	974.9	978.0	978.0	962.6	968.8	965.7	970.3	973.4	973.4	974.9	971.9
32.5°	937.9	928.7	927.1	925.6	925.6	919.4	919.4	924.0	925.6	927.1	931.8
35°	888.6	888.6	880.8	885.5	879.3	880.8	879.3	880.8	883.9	879.3	883.9
37.5°	843.8	845.4	842.3	845.4	846.9	843.8	840.7	846.9	843.8	843.8	840.7
40°	805.3	803.7	805.3	805.3	805.3	806.8	803.7	803.7	803.7	800.6	797.5
42.5°	772.9	763.6	766.7	768.2	763.6	763.6	765.1	763.6	768.2	759.0	759.0
45°	726.6	723.5	725.0	725.0	728.1	723.5	726.6	728.1	723.5	722.0	718.9
47.5°	684.9	688.0	684.9	688.0	688.0	691.1	684.9	686.5	688.0	681.8	677.2
50°	643.3	643.3	647.9	646.4	647.9	644.8	644.8	643.3	644.8	641.7	637.1
52.5°	604.7	600.1	607.8	606.3	604.7	603.2	601.6	603.2	600.1	597.0	597.0
55°	556.9	556.9	561.5	563.1	563.1	560.0	556.9	558.4	556.9	555.4	553.8
57.5°	518.3	512.2	515.2	516.8	516.8	512.2	515.2	512.2	512.2	513.7	509.1
60°	469.0	469.0	465.9	470.5	470.5	467.4	467.4	469.0	465.9	464.3	462.8
62.5°	416.5	418.1	422.7	424.2	425.8	422.7	419.6	421.1	421.1	416.5	418.1
65°	371.8	374.9	381.0	379.5	376.4	377.9	374.9	376.4	371.8	373.3	368.7
67.5°	328.6	327.0	328.6	328.6	331.7	330.1	327.0	327.0	325.5	330.1	325.5
70°	282.3	282.3	282.3	282.3	283.8	285.4	282.3	279.2	280.8	277.7	276.1
72.5°	234.5	236.0	234.5	237.6	232.9	236.0	236.0	234.5	232.9	232.9	232.9
75°	189.7	192.8	188.2	189.7	188.2	191.3	189.7	189.7	186.7	185.1	186.7
77.5°	145.0	146.6	143.5	145.0	143.5	145.0	145.0	143.5	143.5	143.5	143.5
80°	103.4	104.9	103.4	101.8	100.3	103.4	100.3	101.8	103.4	101.8	104.9
82.5°	66.3	66.3	64.8	66.3	63.2	63.2	64.8	64.8	63.2	66.3	63.2
85°	32.4	32.4	35.5	32.4	30.9	30.9	30.9	32.4	30.9	33.9	32.4
87.5°	7.7	6.2	7.7	7.7	6.2	6.2	7.7	6.2	7.7	9.3	6.2
90°	11.6	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.8	11.6
92.5°	25.4	23.9	23.6	22.1	22.5	21.8	22.5	22.1	23.6	23.9	25.4
95°	52.8	48.9	44.3	41.4	40.3	40.7	40.3	41.4	44.3	48.9	52.8
97.5°	106.0	95.3	81.4	74.3	70.3	68.2	70.3	74.3	81.4	95.3	106.0
100°	211.2	189.6	159.9	144.6	134.2	127.8	134.2	144.6	159.9	189.6	211.2
102.5°	357.0	333.8	301.0	272.0	258.5	249.2	258.5	272.0	301.0	333.8	357.0
105°	472.8	467.0	444.8	422.7	407.3	402.3	407.3	422.7	444.8	467.0	472.8
107.5°	514.8	521.9	521.6	518.4	513.7	505.5	513.7	518.4	521.6	521.9	514.8
110°	508.0	522.7	538.0	544.8	548.0	547.6	548.0	544.8	538.0	522.7	508.0

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	485.0	502.3	525.1	537.6	544.4	546.9	544.4	537.6	525.1	502.3	485.0
115°	456.8	475.2	500.5	516.9	526.2	529.4	526.2	516.9	500.5	475.2	456.8
117.5°	429.8	447.3	473.4	490.9	500.5	503.0	500.5	490.9	473.4	447.3	429.8
120°	405.8	422.0	447.0	463.7	474.1	477.7	474.1	463.7	447.0	422.0	405.8
122.5°	387.0	401.3	423.0	439.5	448.4	451.2	448.4	439.5	423.0	401.3	387.0
125°	370.0	383.4	404.1	417.7	426.6	429.5	426.6	417.7	404.1	383.4	370.0
127.5°	355.6	368.1	386.3	399.1	407.0	409.1	407.0	399.1	386.3	368.1	355.6
130°	341.0	352.7	370.2	382.3	389.5	392.3	389.5	382.3	370.2	352.7	341.0
132.5°	325.8	336.7	353.8	365.9	372.4	374.9	372.4	365.9	353.8	336.7	325.8
135°	311.0	320.9	336.3	348.1	354.5	355.9	354.5	348.1	336.3	320.9	311.0
137.5°	296.0	304.9	319.5	329.9	335.6	337.7	335.6	329.9	319.5	304.9	296.0
140°	282.8	290.6	302.0	311.3	316.7	318.8	316.7	311.3	302.0	290.6	282.8
142.5°	270.0	276.3	287.0	295.2	299.9	299.9	299.9	295.2	287.0	276.3	270.0
145°	259.7	264.9	273.5	279.5	283.1	284.2	283.1	279.5	273.5	264.9	259.7
147.5°	250.6	254.5	262.0	267.0	269.5	270.3	269.5	267.0	262.0	254.5	250.6
150°	242.8	246.0	251.3	255.6	257.8	258.1	257.8	255.6	251.3	246.0	242.8
152.5°	236.2	238.8	242.8	246.3	247.8	247.8	247.8	246.3	242.8	238.8	236.2
155°	229.8	231.7	235.6	238.1	239.5	238.8	239.5	238.1	235.6	231.7	229.8
157.5°	223.7	225.3	228.1	230.3	231.0	231.0	231.0	230.3	228.1	225.3	223.7
160°	217.6	218.8	221.3	223.1	223.5	223.5	223.5	223.1	221.3	218.8	217.6
162.5°	211.9	212.8	215.3	216.3	216.7	216.3	216.7	216.3	215.3	212.8	211.9
165°	206.4	207.1	208.5	209.9	209.9	209.6	209.9	209.9	208.5	207.1	206.4
167.5°	201.4	202.1	202.8	203.5	203.5	203.1	203.5	203.5	202.8	202.1	201.4
170°	196.8	197.1	197.4	198.5	198.1	197.4	198.1	198.5	197.4	197.1	196.8
172.5°	192.6	192.8	193.1	193.5	193.1	192.8	193.1	193.5	193.1	192.8	192.6
175°	189.4	189.6	189.6	189.9	189.6	188.9	189.6	189.9	189.6	189.6	189.4
177.5°	187.1	187.1	187.1	187.1	186.7	186.0	186.7	187.1	187.1	187.1	187.1
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0	2007.0
2.5°	1905.2	1917.5	1912.9	1895.9	1916.0	1916.0	1929.8	1929.8	1946.8	1953.0	1962.2
5°	1797.2	1806.4	1814.1	1806.4	1820.3	1841.9	1854.3	1865.1	1888.2	1897.4	1911.3
7.5°	1681.5	1698.4	1706.2	1706.2	1729.3	1754.0	1778.7	1794.1	1826.5	1838.8	1852.7
10°	1568.9	1588.9	1604.3	1602.8	1641.4	1656.8	1687.6	1723.1	1755.5	1774.0	1794.1
12.5°	1450.1	1460.9	1482.5	1513.3	1522.6	1550.4	1585.8	1630.6	1689.2	1706.2	1735.5
15°	1351.4	1380.7	1397.6	1411.5	1433.1	1459.3	1497.9	1541.1	1599.7	1636.7	1667.6
17.5°	1268.1	1306.6	1317.4	1314.3	1342.1	1382.2	1426.9	1459.3	1511.8	1556.5	1585.8
20°	1200.2	1215.6	1234.1	1241.8	1263.4	1306.6	1349.8	1386.8	1430.0	1465.5	1499.4
22.5°	1132.3	1144.6	1160.1	1173.9	1190.9	1215.6	1257.3	1303.5	1345.2	1379.1	1417.7
25°	1076.8	1084.5	1098.4	1109.2	1127.7	1144.6	1173.9	1224.9	1274.2	1294.3	1328.2
27.5°	1022.8	1028.9	1038.2	1050.5	1059.8	1076.8	1103.0	1144.6	1195.5	1215.6	1261.9
30°	974.9	979.6	988.8	995.0	999.6	1019.7	1039.7	1072.1	1110.7	1138.5	1172.4
32.5°	930.2	934.8	944.1	945.6	951.8	962.6	981.1	1010.4	1044.4	1067.5	1096.8
35°	880.8	883.9	893.2	896.3	900.9	910.2	924.0	945.6	976.5	993.5	1019.7
37.5°	842.3	840.7	846.9	851.5	857.7	862.3	867.0	888.6	911.7	927.1	947.2
40°	800.6	797.5	799.1	805.3	808.3	814.5	814.5	836.1	851.5	863.9	879.3
42.5°	759.0	757.4	754.4	757.4	760.5	762.1	763.6	779.0	794.5	805.3	822.2
45°	717.3	715.8	712.7	714.2	714.2	717.3	722.0	728.1	738.9	748.2	757.4
47.5°	678.8	675.7	671.0	669.5	672.6	672.6	672.6	678.8	689.6	692.6	701.9
50°	638.7	634.0	627.9	624.8	624.8	623.2	626.3	627.9	637.1	640.2	647.9
52.5°	595.5	592.4	586.2	580.0	581.6	578.5	580.0	581.6	584.7	589.3	593.9
55°	552.3	546.1	541.5	539.9	535.3	535.3	530.7	536.8	535.3	536.8	543.0
57.5°	510.6	504.4	496.7	493.6	489.0	487.5	484.4	482.8	484.4	489.0	493.6
60°	461.2	458.2	453.5	448.9	445.8	441.2	438.1	438.1	436.6	436.6	438.1
62.5°	413.4	411.9	405.7	404.2	401.1	398.0	393.4	390.3	390.3	393.4	394.9
65°	367.1	365.6	361.0	359.4	351.7	348.6	347.1	345.6	342.5	342.5	342.5
67.5°	324.0	319.3	319.3	311.6	305.4	302.4	299.3	297.7	297.7	297.7	299.3
70°	276.1	276.1	271.5	266.9	260.7	262.2	257.6	253.0	253.0	249.9	251.5
72.5°	229.9	228.3	223.7	222.1	217.5	212.9	209.8	212.9	208.3	206.7	208.3
75°	185.1	183.6	180.5	177.4	178.9	174.3	169.7	168.1	168.1	165.1	165.1
77.5°	141.9	145.0	138.8	137.3	134.2	131.1	129.6	128.0	128.0	128.0	131.1
80°	98.7	100.3	100.3	97.2	98.7	94.1	94.1	94.1	89.5	91.0	92.6
82.5°	63.2	63.2	61.7	63.2	61.7	61.7	60.2	60.2	58.6	58.6	60.2
85°	35.5	33.9	32.4	35.5	33.9	33.9	32.4	32.4	32.4	32.4	32.4
87.5°	7.7	9.3	9.3	9.3	9.3	10.8	10.8	10.8	12.3	12.3	12.3
90°	11.4	10.7	11.4	11.8	12.1	11.8	9.6	7.1	5.4	4.8	4.3
92.5°	26.8	30.7	36.1	46.1	55.0	54.3	42.1	28.6	18.9	17.0	15.0
95°	56.8	71.8	93.5	122.5	139.9	123.9	82.5	51.4	35.0	30.7	26.4
97.5°	116.7	152.8	191.4	229.9	228.1	176.4	109.6	66.4	45.3	40.5	35.7
100°	232.8	281.7	325.9	333.4	282.0	194.2	117.1	73.5	54.6	49.6	44.6
102.5°	380.2	412.7	414.1	372.0	283.8	187.4	117.5	80.0	62.8	57.8	52.8
105°	478.7	474.1	433.8	359.5	264.5	178.1	119.2	87.5	70.7	65.7	60.7
107.5°	507.7	472.7	412.7	333.1	246.7	173.1	123.2	95.0	78.5	73.5	68.5
110°	493.4	447.7	383.8	308.4	234.5	171.7	128.2	102.5	86.8	81.6	76.4

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	467.7	418.0	357.4	291.3	226.7	172.1	133.5	109.6	94.6	89.2	83.9
115°	438.4	391.6	336.7	277.7	221.3	173.5	138.9	117.1	101.7	96.9	92.1
117.5°	412.3	368.8	319.5	268.5	218.5	175.6	144.6	123.9	109.6	104.6	99.6
120°	389.5	351.6	307.4	261.3	216.0	177.8	150.3	131.0	117.1	112.1	107.1
122.5°	372.7	337.4	297.7	255.3	214.6	180.3	155.3	137.8	125.0	119.8	114.6
125°	356.6	325.2	288.5	249.5	212.8	182.8	160.7	144.6	131.7	126.7	121.7
127.5°	343.1	313.1	279.2	244.2	211.7	185.3	165.6	151.0	138.5	133.4	128.2
130°	329.2	301.0	270.3	238.8	211.0	188.1	170.3	156.7	144.2	139.2	134.2
132.5°	314.9	289.5	261.7	234.5	210.6	191.0	174.9	161.7	149.9	144.9	139.9
135°	301.0	277.4	253.8	230.6	210.3	193.1	178.9	166.4	154.9	149.9	144.9
137.5°	287.0	267.8	247.4	227.8	210.3	195.3	182.1	170.3	158.9	154.2	149.6
140°	274.9	258.5	241.3	225.3	209.9	196.7	184.6	173.5	162.8	158.2	153.5
142.5°	263.8	250.3	236.3	222.8	209.9	197.8	186.7	176.0	165.6	161.4	157.1
145°	254.5	243.5	231.7	220.6	209.2	198.5	188.5	178.5	168.9	165.0	161.0
147.5°	246.7	237.8	228.1	218.5	208.1	198.8	189.6	180.6	171.4	167.8	164.2
150°	239.5	232.1	224.2	215.6	207.1	198.5	190.3	182.1	173.9	170.6	167.4
152.5°	233.5	227.4	220.3	213.1	205.3	197.8	190.6	183.5	176.4	173.5	170.6
155°	227.8	222.4	216.7	209.9	203.1	197.1	191.0	184.9	178.9	176.2	173.5
157.5°	222.1	217.4	212.4	207.1	201.0	195.6	191.0	186.0	180.6	178.3	176.0
160°	216.3	212.4	208.5	203.8	198.8	194.6	191.0	186.7	182.4	180.4	178.5
162.5°	211.0	207.8	204.6	201.0	197.1	193.5	190.6	187.1	183.5	182.0	180.6
165°	205.6	203.1	200.6	197.8	194.6	192.1	189.9	187.4	184.2	183.1	182.1
167.5°	200.6	198.8	196.7	194.6	192.4	190.6	189.6	187.4	184.9	184.2	183.5
170°	196.4	194.9	193.9	192.1	190.6	189.6	188.9	187.1	185.3	184.8	184.2
172.5°	192.4	191.4	190.6	189.6	188.5	188.1	187.8	186.7	185.6	185.2	184.9
175°	189.2	188.9	188.5	187.4	187.1	186.7	187.1	186.4	185.6	185.4	185.3
177.5°	187.1	186.7	186.7	186.0	185.6	186.0	186.7	186.0	185.6	185.6	185.6
180°	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6	185.6

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	2007.0	2007.0	2007.0	2007.0
2.5°	1970.0	1970.0	1993.1	2017.8
5°	1926.8	1937.6	1974.6	2008.5
7.5°	1885.1	1903.6	1949.9	1993.1
10°	1834.2	1858.9	1916.0	1966.9
12.5°	1784.8	1808.0	1874.3	1931.4
15°	1715.4	1744.7	1815.7	1886.6
17.5°	1646.0	1675.3	1761.7	1845.0
20°	1564.2	1602.8	1700.0	1811.1
22.5°	1488.6	1536.5	1644.5	1733.9
25°	1405.3	1479.4	1579.7	1695.4
27.5°	1331.3	1405.3	1507.2	1624.4
30°	1248.0	1323.6	1428.5	1536.5
32.5°	1167.8	1237.2	1339.0	1471.7
35°	1084.5	1150.8	1249.5	1383.7
37.5°	1008.9	1073.7	1181.7	1305.1
40°	934.8	1002.7	1095.3	1218.7
42.5°	865.4	925.6	1008.9	1132.3
45°	802.2	845.4	922.5	1038.2
47.5°	735.8	774.4	845.4	961.1
50°	674.1	706.5	768.2	876.2
52.5°	614.0	641.7	698.8	785.2
55°	560.0	586.2	627.9	712.7
57.5°	504.4	524.5	564.6	632.5
60°	450.5	469.0	501.4	556.9
62.5°	396.5	411.9	442.7	487.5
65°	348.6	361.0	384.1	422.7
67.5°	302.4	310.1	328.6	359.4
70°	257.6	263.8	279.2	303.9
72.5°	209.8	216.0	232.9	249.9
75°	169.7	171.2	183.6	197.5
77.5°	132.7	131.1	140.4	151.2
80°	91.0	95.6	103.4	108.0
82.5°	61.7	63.2	66.3	69.4
85°	33.9	35.5	35.5	40.1
87.5°	13.9	15.4	15.4	17.0
90°	3.6	2.9	1.4	0.4
92.5°	12.1	10.4	7.5	5.4
95°	20.7	17.5	13.9	12.5
97.5°	29.3	24.6	20.7	18.6
100°	37.5	31.8	28.6	27.5
102.5°	45.3	39.6	36.4	35.7
105°	52.8	47.5	45.0	43.6
107.5°	60.7	55.7	53.2	52.1
110°	68.9	64.3	62.1	60.7

TEST NUMBER: P1008606

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	76.8	72.5	70.0	68.5
115°	85.0	80.7	78.5	76.8
117.5°	92.8	88.9	86.8	85.3
120°	100.0	96.7	94.6	93.2
122.5°	107.5	103.9	101.7	100.7
125°	114.6	110.3	108.2	107.1
127.5°	121.4	116.7	113.9	112.5
130°	127.1	122.1	118.5	117.1
132.5°	132.4	127.1	123.2	121.4
135°	136.7	131.4	127.1	125.7
137.5°	141.4	135.7	131.4	129.6
140°	145.7	139.9	135.7	134.2
142.5°	149.6	143.9	139.9	138.9
145°	153.9	148.5	144.9	143.5
147.5°	158.2	153.2	149.6	148.5
150°	162.1	157.4	154.6	153.5
152.5°	165.6	161.7	158.9	158.5
155°	169.6	165.6	163.5	163.1
157.5°	172.8	169.2	167.4	167.1
160°	175.6	172.8	171.4	171.0
162.5°	178.1	176.0	174.6	174.9
165°	180.3	178.1	177.4	177.8
167.5°	182.1	180.6	179.9	180.3
170°	183.5	182.4	182.1	182.8
172.5°	184.6	183.5	183.9	184.2
175°	185.3	184.6	184.9	185.3
177.5°	185.6	184.9	185.3	186.0
180°	185.6	185.6	185.6	185.6

(END OF REPORT)