

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007926

Luminaire Tested: S122DIP-B1005D1080UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007926
REPORT IS A COMBINATION OF REPORTS P983534 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8386.0 lumens
Efficiency: N/A
Efficacy: 87.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007926

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007926

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50
1	95	90	86	82	86	82	79	75	68	65	63	54	52	51	42	41	39
2	86	78	71	66	78	71	65	61	59	54	51	47	44	41	36	34	32
3	78	68	60	54	71	62	55	50	51	46	42	41	37	34	32	29	27
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23
5	65	53	45	39	59	49	41	36	40	35	30	32	28	25	25	22	20
6	60	47	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	21	17	15
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	13
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	17	14	12
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16847	16847	16847
5°	16924	16128	16037
10°	16809	15569	15342
15°	16572	14992	14631
20°	16273	14385	13954
25°	15978	13805	13340
30°	15564	13214	12733
35°	15146	12644	12286
40°	14704	12153	11844
45°	14283	11705	11458
50°	13832	11295	11076
55°	13358	10856	10688
60°	12778	10401	10279
65°	12172	9879	9810
70°	11489	9316	9305
75°	10612	8755	8828
80°	9237	8169	8334
85°	7840	7620	7908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14283 cd/sqm

TEST NUMBER: P1007926

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.2
10°-20°	289.4	3.5
20°-30°	438.5	5.2
30°-40°	533.9	6.4
40°-50°	574.5	6.9
50°-60°	557.9	6.7
60°-70°	487.2	5.8
70°-80°	375.0	4.5
80°-90°	253.7	3.0
90°-100°	221.9	2.6
100°-110°	307.8	3.7
110°-120°	564.2	6.7
120°-130°	843.8	10.1
130°-140°	866.4	10.3
140°-150°	790.3	9.4
150°-160°	632.7	7.5
160°-170°	407.7	4.9
170°-180°	140.3	1.7
0°-30°	828.7	9.9
0°-40°	1362.6	16.2
0°-60°	2495.0	29.8
0°-90°	3610.9	43.1
90°-120°	1093.8	13.0
90°-150°	3594.3	42.9
90°-180°	4775.0	56.9
0°-180°	8386.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1064	1064	1064	1064	1064	
5°	1067	1063	1054	1063	1061	101
15°	1018	1021	1021	1035	1034	287
25°	926	936	950	969	973	426
35°	798	824	853	887	898	498
45°	654	696	750	798	813	505
55°	501	557	637	693	713	448
65°	342	418	509	572	592	340
75°	190	276	375	441	461	201
85°	56	151	250	315	336	59
90°	16	118	225	292	313	15
95°	82	119	219	283	300	92
105°	332	409	198	263	285	355
115°	620	655	751	303	243	609
125°	870	884	954	1003	1020	777
135°	1075	1092	1117	1160	1170	831
145°	1245	1244	1262	1279	1281	779
155°	1371	1361	1374	1380	1372	632
165°	1444	1438	1441	1449	1441	408
175°	1478	1470	1472	1480	1469	141
180°	1474	1474	1474	1474	1474	

TEST NUMBER: P1007926

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.3	1064.3	1064.3	1064.3	1064.3
2.5°	1072.0	1067.4	1056.6	1064.3	1061.2
5°	1067.4	1062.8	1053.5	1062.8	1061.2
7.5°	1059.7	1056.6	1048.9	1059.7	1058.1
10°	1050.4	1047.3	1042.7	1055.0	1053.5
12.5°	1035.0	1036.5	1033.5	1045.8	1044.2
15°	1018.0	1021.1	1021.1	1035.0	1033.5
17.5°	996.4	1002.6	1007.2	1021.1	1021.1
20°	974.8	982.6	988.7	1005.7	1005.7
22.5°	951.7	961.0	970.2	987.2	990.3
25°	925.5	936.3	950.2	968.7	973.3
27.5°	894.6	911.6	927.0	950.2	953.2
30°	863.8	883.8	903.9	928.6	933.2
32.5°	829.8	853.0	877.7	907.0	916.2
35°	797.5	823.7	853.0	886.9	897.7
37.5°	762.0	791.3	828.3	865.3	876.1
40°	726.5	760.4	802.1	842.2	856.1
42.5°	692.6	726.5	775.9	820.6	834.5
45°	654.0	695.7	749.6	797.5	812.9
47.5°	617.0	661.7	723.4	772.8	789.7
50°	578.4	626.2	695.7	748.1	765.1
52.5°	541.4	592.3	666.3	720.3	738.8
55°	501.3	556.8	637.0	692.6	712.6
57.5°	462.7	524.4	604.6	664.8	684.9
60°	421.1	487.4	575.3	634.0	655.5
62.5°	384.1	453.5	541.4	604.6	624.7
65°	342.4	418.0	509.0	572.3	592.3
67.5°	305.4	384.1	476.6	539.9	561.5
70°	265.3	345.5	441.1	507.5	526.0
72.5°	228.3	311.6	408.8	473.5	496.7
75°	189.7	276.1	374.8	441.1	461.2
77.5°	152.7	242.2	342.4	408.8	430.3
80°	115.7	209.8	310.0	374.8	396.4
82.5°	84.8	177.4	279.2	344.0	364.0
85°	55.5	151.2	249.9	314.7	336.3
87.5°	33.9	126.5	225.2	288.4	308.5
90°	16.5	117.7	224.9	292.0	312.6
92.5°	40.6	118.0	215.3	277.6	297.2
95°	81.6	118.9	219.0	282.9	300.4
97.5°	135.6	114.4	221.0	281.3	300.9
100°	199.6	110.6	215.0	280.6	299.8
102.5°	268.5	317.3	206.3	273.7	293.8
105°	332.0	408.7	197.8	263.4	284.7
107.5°	407.8	471.4	189.1	253.2	274.5
110°	478.8	532.0	299.3	242.0	263.2

TEST NUMBER: P1007926

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	547.1	590.9	643.8	233.3	253.4
115°	619.6	654.7	750.7	303.1	243.3
117.5°	681.0	714.7	797.7	691.3	427.2
120°	751.4	773.6	854.5	910.5	783.5
122.5°	811.1	829.8	908.1	956.3	971.2
125°	870.5	884.3	953.9	1003.1	1020.2
127.5°	925.9	939.3	997.0	1046.2	1061.1
130°	978.2	993.7	1037.8	1086.6	1097.9
132.5°	1031.5	1043.8	1078.8	1123.9	1135.1
135°	1074.8	1091.8	1116.9	1160.0	1170.2
137.5°	1121.7	1134.5	1153.0	1192.9	1200.5
140°	1167.6	1174.6	1189.4	1223.7	1227.6
142.5°	1206.0	1211.9	1225.8	1252.9	1255.2
145°	1245.0	1244.0	1262.1	1278.9	1281.2
147.5°	1280.2	1277.0	1295.2	1302.0	1302.4
150°	1314.4	1306.9	1324.0	1330.4	1325.0
152.5°	1343.2	1334.6	1350.6	1357.0	1349.6
155°	1370.9	1361.3	1374.1	1380.5	1372.0
157.5°	1393.3	1384.8	1394.4	1401.8	1393.3
160°	1412.5	1406.1	1412.5	1418.9	1411.4
162.5°	1429.6	1423.2	1428.5	1436.0	1426.4
165°	1444.5	1438.1	1441.3	1448.8	1441.3
167.5°	1456.3	1449.9	1453.1	1460.5	1450.9
170°	1465.9	1459.5	1461.6	1469.1	1459.5
172.5°	1472.3	1465.9	1468.0	1475.5	1465.9
175°	1477.6	1470.1	1472.3	1479.7	1469.1
177.5°	1479.7	1472.3	1473.3	1480.8	1471.2
180°	1474.4	1474.4	1474.4	1474.4	1474.4

(END OF REPORT)