

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008611

Luminaire Tested: S122DIP-B1005D330UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008611
REPORT IS A COMBINATION OF REPORTS P983618 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D330UB35-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5265.0 lumens
Efficiency: N/A
Efficacy: 74.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008611

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008611

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49
4	79	68	60	53	75	65	57	52	60	53	49	55	50	46	50	46	43
5	73	61	52	46	69	58	50	45	54	47	42	49	44	40	45	41	37
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	36	33
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26
9	54	41	33	28	52	40	33	28	37	31	26	34	29	25	32	27	24
10	51	38	31	25	48	37	30	25	34	28	24	32	27	23	30	25	22

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25392	25392	25392
5°	25433	24202	24031
10°	25225	23099	22641
15°	24856	21987	21179
20°	24357	20779	19795
25°	23859	19517	18413
30°	23232	18330	16963
35°	22644	17079	15537
40°	21913	15843	14190
45°	21189	14619	12870
50°	20396	13372	11499
55°	19564	12039	10202
60°	18629	10597	8852
65°	17601	9129	7433
70°	16296	7525	6002
75°	14494	5800	4636
80°	12311	3942	2983
85°	8927	1836	1270

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21189 cd/sqm

TEST NUMBER: P1008611

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	151.0	2.9
10°-20°	424.8	8.1
20°-30°	624.2	11.9
30°-40°	725.0	13.8
40°-50°	724.1	13.8
50°-60°	631.4	12.0
60°-70°	466.7	8.9
70°-80°	264.1	5.0
80°-90°	70.9	1.3
90°-100°	26.2	0.5
100°-110°	83.2	1.6
110°-120°	142.4	2.7
120°-130°	187.2	3.6
130°-140°	210.2	4.0
140°-150°	206.1	3.9
150°-160°	172.9	3.3
160°-170°	114.7	2.2
170°-180°	40.1	0.8
0°-30°	1200.0	22.8
0°-40°	1925.0	36.6
0°-60°	3280.5	62.3
0°-90°	4082.2	77.5
90°-120°	251.7	4.8
90°-150°	855.2	16.2
90°-180°	1183.0	22.5
0°-180°	5265.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1581	1593	1590	152
15°	1527	1518	1498	1504	1496	430
25°	1382	1370	1343	1346	1343	636
35°	1192	1177	1152	1143	1135	745
45°	970	959	936	919	913	749
55°	734	725	706	688	680	656
65°	495	486	470	456	449	490
75°	259	256	248	239	242	277
85°	63	62	60	56	54	70
90°	0	5	12	12	12	5
95°	19	22	23	23	22	21
105°	77	78	78	79	79	81
115°	143	145	144	144	143	141
125°	208	211	210	209	208	186
135°	269	273	274	273	272	208
145°	326	329	331	331	330	204
155°	373	374	375	377	376	172
165°	406	406	406	408	406	115
175°	422	421	421	423	421	40
180°	423	423	423	423	423	

TEST NUMBER: P1008611

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1613.3	1605.6	1588.6	1604.1	1601.0
5°	1604.1	1597.9	1580.9	1593.3	1590.2
7.5°	1593.3	1584.0	1567.0	1579.4	1576.3
10°	1576.3	1565.5	1547.0	1559.3	1554.7
12.5°	1553.2	1543.9	1525.4	1533.1	1530.0
15°	1526.9	1517.7	1497.6	1503.8	1496.1
17.5°	1494.6	1485.3	1465.3	1473.0	1465.3
20°	1459.1	1449.8	1428.2	1432.9	1426.7
22.5°	1423.6	1409.7	1389.7	1389.7	1386.6
25°	1382.0	1369.6	1343.4	1346.5	1343.4
27.5°	1335.7	1324.9	1304.8	1300.2	1292.5
30°	1289.4	1277.1	1253.9	1249.3	1243.2
32.5°	1240.1	1230.8	1206.1	1196.9	1190.7
35°	1192.3	1176.8	1152.2	1142.9	1135.2
37.5°	1138.3	1124.4	1099.7	1088.9	1081.2
40°	1082.7	1070.4	1045.7	1031.8	1025.7
42.5°	1028.8	1016.4	991.7	976.3	967.1
45°	970.2	959.4	936.2	919.3	913.1
47.5°	913.1	902.3	877.6	860.6	851.4
50°	852.9	845.2	823.6	802.0	794.3
52.5°	794.3	783.5	763.5	746.5	735.7
55°	734.2	724.9	706.4	687.9	680.2
57.5°	674.0	666.3	646.3	627.7	621.6
60°	613.9	607.7	586.1	569.1	564.5
62.5°	555.3	544.5	529.0	513.6	507.4
65°	495.1	485.8	470.4	456.5	448.8
67.5°	433.4	425.7	411.8	401.0	394.8
70°	376.3	370.2	356.3	345.5	339.3
72.5°	317.7	311.6	303.8	293.1	288.4
75°	259.1	256.0	248.3	239.1	242.2
77.5°	206.7	200.5	197.4	192.8	188.2
80°	154.2	152.7	149.6	145.0	141.9
82.5°	104.9	104.9	103.3	97.2	97.2
85°	63.2	61.7	60.2	55.5	54.0
87.5°	27.8	24.7	21.6	17.0	15.4
90°	0.4	4.6	12.5	11.8	12.1
92.5°	7.9	10.7	11.1	11.4	11.4
95°	18.6	22.1	22.8	22.8	22.1
97.5°	31.1	34.3	35.7	35.7	35.7
100°	45.3	48.2	49.3	49.3	48.9
102.5°	60.3	62.5	63.9	64.3	63.9
105°	76.8	77.8	78.5	79.3	79.3
107.5°	93.2	94.6	94.6	95.0	93.2
110°	108.9	111.0	111.0	111.0	110.0

TEST NUMBER: P1008611

CATALOG NUMBER: S122DIP-B1005D330UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	126.0	128.2	127.8	126.7	126.0
115°	142.8	144.9	144.2	143.9	142.8
117.5°	159.6	162.4	160.7	159.6	158.5
120°	176.4	179.2	176.4	176.4	175.3
122.5°	191.7	195.3	193.5	192.4	191.7
125°	207.8	211.0	209.9	208.9	208.5
127.5°	223.5	227.4	226.0	224.6	223.5
130°	238.1	242.8	242.1	241.3	239.9
132.5°	254.6	258.1	258.5	256.7	255.6
135°	268.8	272.8	273.5	273.1	272.0
137.5°	284.5	287.8	288.5	288.1	286.7
140°	298.5	301.7	303.5	303.5	302.0
142.5°	312.7	316.0	317.0	317.4	316.0
145°	326.3	328.8	331.0	331.3	329.9
147.5°	338.4	341.7	343.1	343.8	342.4
150°	350.9	353.1	354.5	355.6	354.5
152.5°	362.0	364.2	365.9	367.4	365.9
155°	373.1	374.1	375.2	377.0	375.9
157.5°	382.7	383.4	384.1	386.6	384.9
160°	391.3	392.0	392.4	394.5	393.1
162.5°	399.1	399.1	399.5	402.0	400.2
165°	405.9	405.6	405.6	408.1	406.3
167.5°	412.0	410.9	410.9	413.4	411.6
170°	416.6	415.6	415.2	417.7	415.6
172.5°	419.8	418.8	418.4	420.9	418.8
175°	422.3	421.3	420.6	423.1	420.9
177.5°	423.8	422.7	422.0	424.1	422.0
180°	423.1	423.1	423.1	423.1	423.1

(END OF REPORT)