

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007930

Luminaire Tested: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007930
REPORT IS A COMBINATION OF REPORTS P983538 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8371.0 lumens
Efficiency: N/A
Efficacy: 86.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007930

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007930

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	17
9	50	38	30	25	46	35	29	24	30	25	21	26	22	18	21	18	16
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25286	25286	25286
5°	25327	24101	23931
10°	25120	23004	22546
15°	24753	21896	21092
20°	24255	20693	19713
25°	23759	19436	18336
30°	23137	18254	16892
35°	22549	17008	15473
40°	21822	15778	14131
45°	21100	14558	12816
50°	20312	13317	11451
55°	19481	11990	10160
60°	18550	10553	8816
65°	17526	9093	7403
70°	16232	7493	5978
75°	14433	5777	4615
80°	12263	3926	2971
85°	8899	1826	1265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21100 cd/sqm

TEST NUMBER: P1007930

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	1.8
10°-20°	423.0	5.1
20°-30°	621.6	7.4
30°-40°	722.0	8.6
40°-50°	721.1	8.6
50°-60°	628.8	7.5
60°-70°	464.8	5.6
70°-80°	263.0	3.1
80°-90°	72.0	0.9
90°-100°	48.4	0.6
100°-110°	180.5	2.2
110°-120°	478.7	5.7
120°-130°	793.9	9.5
130°-140°	843.3	10.1
140°-150°	783.8	9.4
150°-160°	630.1	7.5
160°-170°	406.0	4.9
170°-180°	139.7	1.7
0°-30°	1195.0	14.3
0°-40°	1917.0	22.9
0°-60°	3266.8	39.0
0°-90°	4066.6	48.6
90°-120°	707.6	8.5
90°-150°	3128.5	37.4
90°-180°	4304.0	51.4
0°-180°	8371.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1597	1597	1597	1597	1597	
5°	1597	1591	1574	1587	1584	152
15°	1521	1511	1491	1498	1490	428
25°	1376	1364	1338	1341	1338	633
35°	1187	1172	1147	1138	1130	741
45°	966	955	932	915	909	746
55°	731	722	704	685	677	654
65°	493	484	468	455	447	487
75°	258	255	247	238	241	275
85°	63	61	60	55	54	70
90°	1	13	21	27	29	8
95°	69	34	41	47	46	82
105°	323	355	65	76	81	345
115°	611	629	656	164	87	601
125°	864	878	898	905	908	770
135°	1069	1086	1095	1106	1104	826
145°	1240	1239	1257	1264	1259	775
155°	1365	1356	1368	1375	1366	629
165°	1438	1432	1435	1443	1435	406
175°	1471	1464	1466	1474	1463	140
180°	1468	1468	1468	1468	1468	

TEST NUMBER: P1007930

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1597.4	1597.4	1597.4	1597.4	1597.4
2.5°	1606.6	1598.9	1582.0	1597.4	1594.3
5°	1597.4	1591.2	1574.3	1586.6	1583.6
7.5°	1586.6	1577.4	1560.5	1572.8	1569.7
10°	1569.7	1559.0	1540.6	1552.8	1548.2
12.5°	1546.7	1537.5	1519.1	1526.7	1523.7
15°	1520.6	1511.4	1491.4	1497.5	1489.9
17.5°	1488.3	1479.1	1459.1	1466.8	1459.1
20°	1453.0	1443.8	1422.3	1426.9	1420.8
22.5°	1417.7	1403.9	1383.9	1383.9	1380.8
25°	1376.2	1363.9	1337.8	1340.9	1337.8
27.5°	1330.1	1319.4	1299.4	1294.8	1287.1
30°	1284.1	1271.8	1248.7	1244.1	1238.0
32.5°	1234.9	1225.7	1201.1	1191.9	1185.8
35°	1187.3	1171.9	1147.4	1138.1	1130.5
37.5°	1133.5	1119.7	1095.1	1084.4	1076.7
40°	1078.2	1065.9	1041.4	1027.5	1021.4
42.5°	1024.5	1012.2	987.6	972.3	963.0
45°	966.1	955.4	932.3	915.4	909.3
47.5°	909.3	898.5	874.0	857.1	847.8
50°	849.4	841.7	820.2	798.7	791.0
52.5°	791.0	780.3	760.3	743.4	732.6
55°	731.1	721.9	703.5	685.0	677.4
57.5°	671.2	663.5	643.6	625.1	619.0
60°	611.3	605.2	583.7	566.8	562.2
62.5°	552.9	542.2	526.8	511.5	505.3
65°	493.0	483.8	468.5	454.6	447.0
67.5°	431.6	423.9	410.1	399.3	393.2
70°	374.8	368.6	354.8	344.1	337.9
72.5°	316.4	310.3	302.6	291.8	287.2
75°	258.0	255.0	247.3	238.1	241.1
77.5°	205.8	199.7	196.6	192.0	187.4
80°	153.6	152.1	149.0	144.4	141.3
82.5°	104.4	104.4	102.9	96.8	96.8
85°	63.0	61.4	59.9	55.3	53.8
87.5°	27.6	24.6	21.5	16.9	15.4
90°	1.1	12.7	21.2	26.6	28.7
92.5°	26.6	22.3	25.5	27.6	28.7
95°	69.1	34.0	41.4	46.7	45.7
97.5°	124.3	37.2	54.2	57.4	58.4
100°	188.0	42.5	60.6	69.1	71.2
102.5°	258.2	256.0	62.7	74.4	77.6
105°	323.0	354.8	64.8	76.5	80.7
107.5°	398.4	425.0	66.9	78.6	82.9
110°	470.6	493.0	185.9	79.7	83.9

TEST NUMBER: P1007930

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	538.6	557.8	539.7	81.8	85.0
115°	610.9	628.9	655.5	163.6	87.1
117.5°	673.6	694.8	712.9	561.0	282.6
120°	743.7	759.6	778.8	791.5	648.1
122.5°	803.2	820.2	841.4	847.8	848.9
125°	863.7	877.6	897.7	905.2	908.4
127.5°	919.0	933.9	949.8	960.4	961.5
130°	971.0	988.0	999.7	1011.4	1010.4
132.5°	1024.2	1038.0	1049.7	1059.2	1058.2
135°	1068.8	1085.8	1095.3	1106.0	1103.8
137.5°	1115.5	1128.3	1138.9	1149.5	1146.3
140°	1161.2	1169.7	1181.4	1191.0	1185.7
142.5°	1199.5	1206.9	1220.7	1229.2	1223.9
145°	1239.8	1238.8	1256.8	1264.3	1259.0
147.5°	1274.9	1271.7	1289.8	1295.1	1290.8
150°	1308.9	1301.5	1318.5	1324.8	1319.5
152.5°	1337.6	1329.1	1345.0	1351.4	1344.0
155°	1365.2	1355.6	1368.4	1374.8	1366.3
157.5°	1387.5	1379.0	1388.6	1396.0	1387.5
160°	1406.6	1400.3	1406.6	1413.0	1405.6
162.5°	1423.6	1417.3	1422.6	1430.0	1420.4
165°	1438.5	1432.1	1435.3	1442.8	1435.3
167.5°	1450.2	1443.8	1447.0	1454.4	1444.9
170°	1459.8	1453.4	1455.5	1462.9	1453.4
172.5°	1466.1	1459.8	1461.9	1469.3	1459.8
175°	1471.4	1464.0	1466.1	1473.6	1462.9
177.5°	1473.6	1466.1	1467.2	1474.6	1465.1
180°	1468.3	1468.3	1468.3	1468.3	1468.3

(END OF REPORT)