

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007933

Luminaire Tested: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007933
REPORT IS A COMBINATION OF REPORTS P983541 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8049.0 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007933

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007933

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55			49
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46			41
2	89	81	75	70	81	75	70	65	63	60	56	53	50	47	43	41	39			34
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	35	33			29
4	74	63	55	49	68	59	52	46	50	44	40	41	38	34	34	31	29			25
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25			22
6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	28	24	22			19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20			17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18			15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	18	21	18	16			14
10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14			12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1007933

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	1.8
10°-20°	406.8	5.1
20°-30°	597.8	7.4
30°-40°	694.3	8.6
40°-50°	693.4	8.6
50°-60°	604.6	7.5
60°-70°	446.9	5.6
70°-80°	252.9	3.1
80°-90°	69.2	0.9
90°-100°	46.6	0.6
100°-110°	173.5	2.2
110°-120°	460.2	5.7
120°-130°	763.3	9.5
130°-140°	810.8	10.1
140°-150°	753.6	9.4
150°-160°	605.8	7.5
160°-170°	390.4	4.9
170°-180°	134.4	1.7
0°-30°	1149.1	14.3
0°-40°	1843.4	22.9
0°-60°	3141.4	39.0
0°-90°	3910.5	48.6
90°-120°	680.3	8.5
90°-150°	3007.9	37.4
90°-180°	4139.0	51.4
0°-180°	8049.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	1	12	20	26	28	7
95°	66	33	40	45	44	79
105°	310	341	62	74	78	332
115°	587	605	630	157	84	578
125°	830	844	863	870	873	741
135°	1028	1044	1053	1063	1061	794
145°	1192	1191	1208	1216	1210	746
155°	1313	1303	1316	1322	1314	605
165°	1383	1377	1380	1387	1380	391
175°	1415	1408	1410	1417	1407	135
180°	1412	1412	1412	1412	1412	

TEST NUMBER: P1007933

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	1.0	12.3	20.4	25.5	27.6
92.5°	25.5	21.5	24.5	26.6	27.6
95°	66.4	32.7	39.8	44.9	43.9
97.5°	119.5	35.8	52.1	55.2	56.2
100°	180.8	40.9	58.2	66.4	68.4
102.5°	248.2	246.2	60.3	71.5	74.6
105°	310.5	341.2	62.3	73.5	77.6
107.5°	383.1	408.6	64.4	75.6	79.7
110°	452.5	474.0	178.8	76.6	80.7

TEST NUMBER: P1007933

CATALOG NUMBER: S122DIP-B1005D1080UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	517.9	536.3	518.9	78.7	81.7
115°	587.3	604.7	630.2	157.3	83.8
117.5°	647.6	668.0	685.4	539.3	271.7
120°	715.0	730.3	748.7	761.0	623.1
122.5°	772.2	788.6	809.0	815.1	816.2
125°	830.5	843.7	863.1	870.3	873.4
127.5°	883.6	897.9	913.2	923.4	924.4
130°	933.6	950.0	961.2	972.4	971.4
132.5°	984.7	998.0	1009.2	1018.4	1017.4
135°	1027.6	1043.9	1053.1	1063.3	1061.3
137.5°	1072.5	1084.8	1095.0	1105.2	1102.2
140°	1116.5	1124.6	1135.9	1145.1	1140.0
142.5°	1153.2	1160.4	1173.7	1181.8	1176.7
145°	1192.1	1191.0	1208.4	1215.5	1210.4
147.5°	1225.8	1222.7	1240.1	1245.2	1241.1
150°	1258.4	1251.3	1267.6	1273.8	1268.7
152.5°	1286.0	1277.9	1293.2	1299.3	1292.2
155°	1312.6	1303.4	1315.7	1321.8	1313.6
157.5°	1334.0	1325.9	1335.1	1342.2	1334.0
160°	1352.4	1346.3	1352.4	1358.6	1351.4
162.5°	1368.8	1362.6	1367.7	1374.9	1365.7
165°	1383.1	1376.9	1380.0	1387.2	1380.0
167.5°	1394.3	1388.2	1391.2	1398.4	1389.2
170°	1403.5	1397.4	1399.4	1406.6	1397.4
172.5°	1409.6	1403.5	1405.5	1412.7	1403.5
175°	1414.7	1407.6	1409.6	1416.8	1406.6
177.5°	1416.8	1409.6	1410.6	1417.8	1408.6
180°	1411.7	1411.7	1411.7	1411.7	1411.7

(END OF REPORT)