

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008639

Luminaire Tested: S122DIP-B1005D530UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008639
REPORT IS A COMBINATION OF REPORTS P983646 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB27-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6084.3 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008639

CATALOG NUMBER: S122DIP-B1005D530UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008639

CATALOG NUMBER: S122DIP-B1005D530UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66		
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56		
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47		
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40		
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34		
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26		
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23		
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21		
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19		
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25067	25067	25067
5°	25108	23894	23724
10°	24904	22805	22353
15°	24540	21709	20909
20°	24047	20514	19542
25°	23556	19269	18178
30°	22937	18098	16746
35°	22355	16861	15339
40°	21634	15642	14009
45°	20918	14433	12705
50°	20138	13201	11353
55°	19313	11886	10071
60°	18389	10461	8739
65°	17377	9013	7339
70°	16089	7428	5926
75°	14310	5728	4576
80°	12159	3892	2945
85°	8814	1811	1253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20918 cd/sqm

TEST NUMBER: P1008639

CATALOG NUMBER: S122DIP-B1005D530UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.4
10°-20°	419.4	6.9
20°-30°	616.3	10.1
30°-40°	715.8	11.8
40°-50°	714.9	11.7
50°-60°	623.3	10.2
60°-70°	460.8	7.6
70°-80°	260.7	4.3
80°-90°	70.7	1.2
90°-100°	119.4	2.0
100°-110°	403.6	6.6
110°-120°	424.3	7.0
120°-130°	348.9	5.7
130°-140°	280.4	4.6
140°-150°	211.8	3.5
150°-160°	148.9	2.4
160°-170°	87.7	1.4
170°-180°	28.5	0.5
0°-30°	1184.7	19.5
0°-40°	1900.5	31.2
0°-60°	3238.7	53.2
0°-90°	4030.9	66.2
90°-120°	947.3	15.6
90°-150°	1788.4	29.4
90°-180°	2053.0	33.7
0°-180°	6084.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1584	1584	1584	1584	1584	
5°	1584	1578	1561	1573	1570	150
15°	1508	1498	1479	1485	1477	425
25°	1364	1352	1326	1329	1326	628
35°	1177	1162	1138	1128	1121	735
45°	958	947	924	908	901	739
55°	725	716	697	679	672	648
65°	489	480	464	451	443	483
75°	256	253	245	236	239	273
85°	62	61	59	55	53	70
90°	1	8	19	18	19	5
95°	20	49	222	84	65	20
105°	69	104	420	750	638	73
115°	122	154	351	725	840	121
125°	170	201	338	587	681	151
135°	199	238	334	493	565	154
145°	228	262	332	412	451	143
155°	259	280	322	364	379	119
165°	282	291	309	327	332	80
175°	294	294	297	300	300	28
180°	294	294	294	294	294	

TEST NUMBER: P1008639

CATALOG NUMBER: S122DIP-B1005D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1583.6	1583.6	1583.6	1583.6	1583.6
2.5°	1592.8	1585.1	1568.4	1583.6	1580.6
5°	1583.6	1577.5	1560.8	1573.0	1569.9
7.5°	1573.0	1563.8	1547.1	1559.3	1556.2
10°	1556.2	1545.6	1527.3	1539.5	1534.9
12.5°	1533.4	1524.2	1506.0	1513.6	1510.5
15°	1507.5	1498.4	1478.6	1484.7	1477.0
17.5°	1475.5	1466.4	1446.6	1454.2	1446.6
20°	1440.5	1431.4	1410.0	1414.6	1408.5
22.5°	1405.5	1391.8	1372.0	1372.0	1368.9
25°	1364.4	1352.2	1326.3	1329.3	1326.3
27.5°	1318.7	1308.0	1288.2	1283.7	1276.0
30°	1273.0	1260.8	1238.0	1233.4	1227.3
32.5°	1224.3	1215.1	1190.8	1181.6	1175.5
35°	1177.1	1161.8	1137.5	1128.3	1120.7
37.5°	1123.8	1110.1	1085.7	1075.0	1067.4
40°	1068.9	1056.8	1032.4	1018.7	1012.6
42.5°	1015.7	1003.5	979.1	963.9	954.7
45°	957.8	947.1	924.3	907.5	901.4
47.5°	901.4	890.8	866.4	849.7	840.5
50°	842.1	834.4	813.1	791.8	784.2
52.5°	784.2	773.5	753.7	737.0	726.3
55°	724.8	715.7	697.4	679.1	671.5
57.5°	665.4	657.8	638.0	619.7	613.7
60°	606.0	600.0	578.6	561.9	557.3
62.5°	548.2	537.5	522.3	507.1	501.0
65°	488.8	479.7	464.4	450.7	443.1
67.5°	427.9	420.3	406.6	395.9	389.8
70°	371.5	365.5	351.7	341.1	335.0
72.5°	313.7	307.6	300.0	289.3	284.7
75°	255.8	252.8	245.2	236.0	239.1
77.5°	204.0	198.0	194.9	190.3	185.8
80°	152.3	150.7	147.7	143.1	140.1
82.5°	103.5	103.5	102.0	95.9	95.9
85°	62.4	60.9	59.4	54.8	53.3
87.5°	27.4	24.4	21.3	16.7	15.2
90°	0.6	7.6	19.3	18.4	18.7
92.5°	8.5	26.9	87.2	40.2	34.6
95°	19.8	48.7	222.0	83.8	64.6
97.5°	29.5	64.2	361.9	168.2	108.2
100°	43.6	78.8	447.5	335.0	202.8
102.5°	56.6	91.8	450.3	566.4	395.3
105°	69.1	104.2	419.7	750.2	638.3
107.5°	82.7	116.6	391.4	816.8	802.0
110°	96.3	129.4	372.1	806.0	868.9

TEST NUMBER: P1008639

CATALOG NUMBER: S122DIP-B1005D530UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	108.7	141.6	359.7	769.4	867.7
115°	121.8	153.8	351.2	724.7	840.0
117.5°	135.4	166.0	346.6	682.0	798.1
120°	147.8	177.9	342.7	643.7	757.8
122.5°	159.7	190.0	340.4	614.0	715.9
125°	169.9	201.0	337.6	587.0	681.4
127.5°	178.4	211.6	335.9	564.2	649.1
130°	185.8	220.9	334.7	540.9	622.5
132.5°	192.6	230.0	334.2	516.8	594.7
135°	199.4	237.9	333.6	493.4	564.7
137.5°	205.6	244.6	333.6	469.6	535.8
140°	213.0	251.0	333.0	448.6	505.8
142.5°	220.3	256.0	333.0	428.5	475.8
145°	227.7	261.6	331.9	412.0	450.9
147.5°	235.6	266.2	330.2	397.6	428.8
150°	243.6	270.7	328.5	385.2	409.5
152.5°	251.5	275.2	325.7	374.6	393.1
155°	258.8	279.6	322.3	364.5	378.9
157.5°	265.1	282.9	318.9	354.8	366.5
160°	271.3	286.3	315.5	345.2	354.6
162.5°	277.5	288.8	312.7	336.2	343.2
165°	282.1	290.6	308.7	327.4	332.5
167.5°	286.0	292.2	305.3	319.5	322.3
170°	290.0	293.2	302.5	312.1	313.2
172.5°	292.3	294.0	299.1	305.6	305.9
175°	294.0	294.2	296.8	300.5	299.6
177.5°	295.1	294.5	294.5	296.8	295.1
180°	294.5	294.5	294.5	294.5	294.5

(END OF REPORT)