

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007941

Luminaire Tested: S122DIP-B1005D330UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007941
REPORT IS A COMBINATION OF REPORTS P983594 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D330UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5385.0 lumens
Efficiency: N/A
Efficacy: 76.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007941

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007941

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	100	94	90	85	93	89	85	81	78	75	72	69	67	64	60	58	57	52		
2	90	81	74	68	84	77	70	65	68	63	58	59	56	52	52	49	46	42		
3	82	71	62	56	76	67	59	53	59	53	48	52	47	43	45	42	38	35		
4	74	62	53	47	69	59	51	45	52	46	40	46	41	36	40	36	33	29		
5	68	55	46	40	64	52	44	38	46	40	35	41	36	31	36	32	28	25		
6	63	50	41	34	59	47	39	33	42	35	30	37	31	27	33	28	25	22		
7	58	45	36	30	54	42	34	29	38	31	26	34	28	24	30	25	22	19		
8	54	41	32	26	50	38	31	25	34	28	23	31	25	21	27	23	19	17		
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15		
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16847	16847	16847
5°	16924	16128	16037
10°	16809	15569	15342
15°	16572	14992	14631
20°	16273	14385	13954
25°	15978	13805	13340
30°	15564	13214	12733
35°	15146	12644	12286
40°	14704	12153	11844
45°	14283	11705	11458
50°	13832	11295	11076
55°	13358	10856	10688
60°	12778	10401	10279
65°	12172	9879	9810
70°	11489	9316	9305
75°	10612	8755	8828
80°	9237	8169	8334
85°	7840	7620	7908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14283 cd/sqm

TEST NUMBER: P1007941

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.9	1.9
10°-20°	289.4	5.4
20°-30°	438.5	8.1
30°-40°	533.9	9.9
40°-50°	574.5	10.7
50°-60°	557.9	10.4
60°-70°	487.2	9.0
70°-80°	375.0	7.0
80°-90°	251.9	4.7
90°-100°	188.1	3.5
100°-110°	182.0	3.4
110°-120°	230.7	4.3
120°-130°	290.6	5.4
130°-140°	278.8	5.2
140°-150°	244.2	4.5
150°-160°	193.7	3.6
160°-170°	124.8	2.3
170°-180°	43.0	0.8
0°-30°	828.7	15.4
0°-40°	1362.6	25.3
0°-60°	2495.0	46.3
0°-90°	3609.1	67.0
90°-120°	600.8	11.2
90°-150°	1414.5	26.3
90°-180°	1776.0	33.0
0°-180°	5385.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1064	1064	1064	1064	1064	
5°	1067	1063	1054	1063	1061	101
15°	1018	1021	1021	1035	1034	287
25°	926	936	950	969	973	426
35°	798	824	853	887	898	498
45°	654	696	750	798	813	505
55°	501	557	637	693	713	448
65°	342	418	509	572	592	340
75°	190	276	375	441	461	201
85°	56	151	250	315	336	59
90°	16	109	210	274	293	12
95°	34	95	190	250	268	35
105°	107	162	153	210	228	115
115°	194	216	294	189	183	190
125°	269	273	328	372	387	240
135°	330	335	354	389	401	255
145°	381	381	386	398	404	239
155°	420	417	421	423	420	193
165°	442	440	441	444	441	125
175°	452	450	451	453	450	43
180°	451	451	451	451	451	

TEST NUMBER: P1007941

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1064.3	1064.3	1064.3	1064.3	1064.3
2.5°	1072.0	1067.4	1056.6	1064.3	1061.2
5°	1067.4	1062.8	1053.5	1062.8	1061.2
7.5°	1059.7	1056.6	1048.9	1059.7	1058.1
10°	1050.4	1047.3	1042.7	1055.0	1053.5
12.5°	1035.0	1036.5	1033.5	1045.8	1044.2
15°	1018.0	1021.1	1021.1	1035.0	1033.5
17.5°	996.4	1002.6	1007.2	1021.1	1021.1
20°	974.8	982.6	988.7	1005.7	1005.7
22.5°	951.7	961.0	970.2	987.2	990.3
25°	925.5	936.3	950.2	968.7	973.3
27.5°	894.6	911.6	927.0	950.2	953.2
30°	863.8	883.8	903.9	928.6	933.2
32.5°	829.8	853.0	877.7	907.0	916.2
35°	797.5	823.7	853.0	886.9	897.7
37.5°	762.0	791.3	828.3	865.3	876.1
40°	726.5	760.4	802.1	842.2	856.1
42.5°	692.6	726.5	775.9	820.6	834.5
45°	654.0	695.7	749.6	797.5	812.9
47.5°	617.0	661.7	723.4	772.8	789.7
50°	578.4	626.2	695.7	748.1	765.1
52.5°	541.4	592.3	666.3	720.3	738.8
55°	501.3	556.8	637.0	692.6	712.6
57.5°	462.7	524.4	604.6	664.8	684.9
60°	421.1	487.4	575.3	634.0	655.5
62.5°	384.1	453.5	541.4	604.6	624.7
65°	342.4	418.0	509.0	572.3	592.3
67.5°	305.4	384.1	476.6	539.9	561.5
70°	265.3	345.5	441.1	507.5	526.0
72.5°	228.3	311.6	408.8	473.5	496.7
75°	189.7	276.1	374.8	441.1	461.2
77.5°	152.7	242.2	342.4	408.8	430.3
80°	115.7	209.8	310.0	374.8	396.4
82.5°	84.8	177.4	279.2	344.0	364.0
85°	55.5	151.2	249.9	314.7	336.3
87.5°	33.9	126.5	225.2	288.4	308.5
90°	15.7	108.8	210.1	273.5	292.6
92.5°	22.1	102.5	197.5	258.4	277.2
95°	33.5	95.3	190.1	250.4	268.5
97.5°	49.0	88.5	183.3	241.3	260.2
100°	68.6	81.0	172.8	232.5	250.2
102.5°	88.7	138.9	162.7	221.9	239.7
105°	107.0	161.5	152.6	210.1	228.4
107.5°	130.2	175.3	142.5	198.5	216.8
110°	150.9	188.5	169.8	186.5	204.7



TEST NUMBER: P1007941

CATALOG NUMBER: S122DIP-B1005D330UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	171.8	202.3	267.7	176.3	194.2
115°	194.0	216.4	294.0	189.1	182.6
117.5°	211.7	230.6	300.9	300.4	230.3
120°	233.2	244.3	311.9	359.0	331.9
122.5°	251.5	258.3	321.9	365.5	379.7
125°	268.6	272.9	328.4	372.4	387.2
127.5°	285.6	288.6	335.2	377.0	391.2
130°	301.6	305.2	341.2	381.9	393.9
132.5°	317.9	320.6	347.4	385.8	397.8
135°	330.1	335.3	353.7	389.4	401.0
137.5°	344.4	348.3	359.4	392.0	401.8
140°	358.5	359.6	366.3	393.9	401.5
142.5°	370.2	371.0	375.3	396.4	402.4
145°	381.1	380.8	386.4	397.9	404.0
147.5°	391.9	390.9	396.5	399.6	403.0
150°	402.4	400.1	405.3	407.3	405.6
152.5°	411.2	408.6	413.5	415.4	413.1
155°	419.7	416.7	420.7	422.6	420.0
157.5°	426.5	423.9	426.9	429.1	426.5
160°	432.4	430.5	432.4	434.4	432.1
162.5°	437.6	435.7	437.3	439.6	436.7
165°	442.2	440.2	441.2	443.5	441.2
167.5°	445.8	443.8	444.8	447.1	444.2
170°	448.7	446.8	447.4	449.7	446.8
172.5°	450.7	448.7	449.4	451.7	448.7
175°	452.3	450.0	450.7	453.0	449.7
177.5°	453.0	450.7	451.0	453.3	450.4
180°	451.4	451.4	451.4	451.4	451.4

(END OF REPORT)