

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007954

Luminaire Tested: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007954
REPORT IS A COMBINATION OF REPORTS P983652 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_2700K
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6111.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 76.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007954

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007954

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	98	93	88	84	91	86	82	79	75	71	69	64	61	59	54	52	50
2	88	80	73	67	82	75	68	63	64	60	55	55	51	48	46	43	41
3	80	70	62	55	74	65	58	52	56	51	46	48	44	40	40	37	34
4	73	61	53	46	68	57	50	44	50	43	39	42	38	34	36	32	29
5	67	55	46	39	62	51	43	37	44	38	33	38	33	29	32	28	25
6	62	49	40	34	57	46	38	32	40	33	29	34	29	25	29	25	22
7	57	44	36	30	53	41	34	28	36	30	25	31	26	22	26	22	19
8	53	40	32	26	49	37	30	25	33	27	22	28	23	20	24	20	17
9	49	36	29	23	46	34	27	22	30	24	20	26	21	18	22	18	15
10	46	33	26	21	43	31	24	20	28	22	18	24	19	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16632	16632	16632
5°	16706	15921	15831
10°	16595	15371	15146
15°	16360	14799	14442
20°	16066	14201	13775
25°	15773	13627	13169
30°	15364	13044	12569
35°	14950	12483	12129
40°	14515	11997	11692
45°	14100	11555	11311
50°	13655	11149	10935
55°	13187	10718	10551
60°	12614	10269	10149
65°	12016	9752	9684
70°	11342	9198	9185
75°	10478	8643	8715
80°	9117	8066	8226
85°	7741	7522	7807

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14100 cd/sqm

TEST NUMBER: P1007954

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.6	1.6
10°-20°	285.7	4.7
20°-30°	432.8	7.1
30°-40°	527.1	8.6
40°-50°	567.1	9.3
50°-60°	550.7	9.0
60°-70°	481.0	7.9
70°-80°	370.2	6.1
80°-90°	249.2	4.1
90°-100°	194.7	3.2
100°-110°	213.0	3.5
110°-120°	316.1	5.2
120°-130°	433.4	7.1
130°-140°	430.8	7.1
140°-150°	385.8	6.3
150°-160°	307.5	5.0
160°-170°	198.2	3.2
170°-180°	68.2	1.1
0°-30°	818.1	13.4
0°-40°	1345.2	22.0
0°-60°	2463.0	40.3
0°-90°	3563.3	58.3
90°-120°	723.8	11.8
90°-150°	1973.8	32.3
90°-180°	2548.0	41.7
0°-180°	6111.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1051	1051	1051	1051	1051	
5°	1054	1049	1040	1049	1048	100
15°	1005	1008	1008	1022	1020	283
25°	914	924	938	956	961	420
35°	787	813	842	876	886	492
45°	646	687	740	787	802	498
55°	495	550	629	684	704	443
65°	338	413	502	565	585	336
75°	187	273	370	436	455	198
85°	55	149	247	311	332	58
90°	16	110	211	275	294	13
95°	46	100	195	256	274	49
105°	165	225	163	222	240	177
115°	304	330	411	217	196	299
125°	424	431	490	535	550	379
135°	523	531	551	588	600	405
145°	605	605	613	626	631	379
155°	666	662	668	671	667	307
165°	702	699	700	704	700	198
175°	718	714	716	719	714	68
180°	717	717	717	717	717	

TEST NUMBER: P1007954

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1050.7	1050.7	1050.7	1050.7	1050.7
2.5°	1058.3	1053.7	1043.1	1050.7	1047.6
5°	1053.7	1049.2	1040.0	1049.2	1047.6
7.5°	1046.1	1043.1	1035.4	1046.1	1044.6
10°	1037.0	1033.9	1029.4	1041.5	1040.0
12.5°	1021.7	1023.3	1020.2	1032.4	1030.9
15°	1005.0	1008.0	1008.0	1021.7	1020.2
17.5°	983.7	989.8	994.3	1008.0	1008.0
20°	962.4	970.0	976.1	992.8	992.8
22.5°	939.5	948.7	957.8	974.5	977.6
25°	913.6	924.3	938.0	956.3	960.8
27.5°	883.2	899.9	915.2	938.0	941.0
30°	852.7	872.5	892.3	916.7	921.2
32.5°	819.2	842.1	866.4	895.4	904.5
35°	787.2	813.1	842.1	875.6	886.2
37.5°	752.2	781.2	817.7	854.2	864.9
40°	717.2	750.7	791.8	831.4	845.1
42.5°	683.7	717.2	765.9	810.1	823.8
45°	645.6	686.7	740.0	787.2	802.5
47.5°	609.1	653.2	714.2	762.9	779.6
50°	571.0	618.2	686.7	738.5	755.3
52.5°	534.5	584.7	657.8	711.1	729.4
55°	494.9	549.7	628.9	683.7	703.5
57.5°	456.8	517.7	596.9	656.3	676.1
60°	415.7	481.2	568.0	625.8	647.2
62.5°	379.2	447.7	534.5	596.9	616.7
65°	338.0	412.7	502.5	564.9	584.7
67.5°	301.5	379.2	470.5	533.0	554.3
70°	261.9	341.1	435.5	501.0	519.2
72.5°	225.4	307.6	403.5	467.5	490.3
75°	187.3	272.6	370.0	435.5	455.3
77.5°	150.7	239.1	338.0	403.5	424.8
80°	114.2	207.1	306.1	370.0	391.3
82.5°	83.7	175.1	275.6	339.6	359.4
85°	54.8	149.2	246.7	310.6	332.0
87.5°	33.5	124.9	222.3	284.7	304.5
90°	15.7	109.7	211.4	274.9	294.2
92.5°	26.7	105.3	199.7	260.2	279.0
95°	45.9	100.3	195.3	255.8	273.5
97.5°	71.4	94.2	190.9	248.8	267.6
100°	102.5	87.7	181.9	242.3	260.1
102.5°	135.1	184.4	172.2	232.7	251.1
105°	165.2	225.0	162.6	221.5	240.4
107.5°	202.0	251.6	153.0	210.5	229.2
110°	235.8	277.1	201.9	198.8	217.6

TEST NUMBER: P1007954

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.0	302.7	363.9	189.1	207.5
115°	304.2	329.8	411.3	216.8	196.3
117.5°	333.3	355.8	428.6	400.2	279.5
120°	367.6	381.4	451.7	500.5	447.3
122.5°	396.6	406.4	473.1	517.3	531.5
125°	424.5	431.3	489.9	534.7	549.9
127.5°	451.5	457.3	506.1	549.4	563.6
130°	476.9	483.7	521.4	563.6	575.3
132.5°	502.8	508.1	536.7	576.3	588.0
135°	523.1	531.4	551.3	588.5	599.6
137.5°	545.9	552.2	564.9	599.1	608.2
140°	568.2	570.9	579.6	608.6	615.2
142.5°	586.9	589.0	595.8	618.2	623.2
145°	605.1	604.6	613.4	626.1	631.1
147.5°	622.2	620.6	629.5	633.6	636.1
150°	638.8	635.2	643.5	646.6	644.0
152.5°	652.8	648.6	656.4	659.5	655.9
155°	666.3	661.6	667.8	670.9	666.8
157.5°	677.2	673.0	677.7	681.3	677.2
160°	686.5	683.4	686.5	689.6	686.0
162.5°	694.8	691.7	694.3	697.9	693.2
165°	702.1	698.9	700.5	704.1	700.5
167.5°	707.8	704.6	706.2	709.8	705.2
170°	712.4	709.3	710.4	714.0	709.3
172.5°	715.5	712.4	713.5	717.1	712.4
175°	718.1	714.5	715.5	719.2	714.0
177.5°	719.2	715.5	716.1	719.7	715.0
180°	716.6	716.6	716.6	716.6	716.6

(END OF REPORT)