

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008666

Luminaire Tested: S122DIP-B1005D530UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008666
REPORT IS A COMBINATION OF REPORTS P983688 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB40-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6103.3 lumens
Efficiency: N/A
Efficacy: 79.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008666

CATALOG NUMBER: S122DIP-B1005D530UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008666

CATALOG NUMBER: S122DIP-B1005D530UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66		
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56		
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47		
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40		
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34		
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30		
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26		
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23		
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21		
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19		
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25142	25142	25142
5°	25183	23965	23795
10°	24979	22873	22420
15°	24613	21773	20971
20°	24118	20575	19601
25°	23625	19325	18232
30°	23005	18152	16796
35°	22421	16912	15385
40°	21698	15689	14051
45°	20979	14475	12743
50°	20197	13242	11386
55°	19372	11922	10101
60°	18443	10493	8766
65°	17426	9040	7360
70°	16136	7451	5944
75°	14354	5744	4590
80°	12191	3903	2954
85°	8843	1817	1258

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20979 cd/sqm

TEST NUMBER: P1008666

CATALOG NUMBER: S122DIP-B1005D530UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.5	2.4
10°-20°	420.6	6.9
20°-30°	618.1	10.1
30°-40°	717.9	11.8
40°-50°	717.0	11.7
50°-60°	625.2	10.2
60°-70°	462.2	7.6
70°-80°	261.5	4.3
80°-90°	70.9	1.2
90°-100°	119.8	2.0
100°-110°	405.0	6.6
110°-120°	425.7	7.0
120°-130°	350.1	5.7
130°-140°	281.3	4.6
140°-150°	212.5	3.5
150°-160°	149.4	2.4
160°-170°	88.0	1.4
170°-180°	28.6	0.5
0°-30°	1188.2	19.5
0°-40°	1906.1	31.2
0°-60°	3248.3	53.2
0°-90°	4042.9	66.2
90°-120°	950.6	15.6
90°-150°	1794.5	29.4
90°-180°	2060.0	33.8
0°-180°	6103.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1588	1588	1588	1588	1588	
5°	1588	1582	1565	1578	1575	151
15°	1512	1503	1483	1489	1481	426
25°	1368	1356	1330	1333	1330	630
35°	1181	1165	1141	1132	1124	737
45°	961	950	927	910	904	741
55°	727	718	700	681	674	650
65°	490	481	466	452	444	485
75°	257	254	246	237	240	274
85°	63	61	60	55	54	70
90°	1	8	19	18	19	5
95°	20	49	223	84	65	21
105°	69	105	421	753	640	74
115°	122	154	352	727	843	121
125°	170	202	339	589	684	152
135°	200	239	335	495	567	155
145°	228	263	333	413	452	143
155°	260	280	323	366	380	120
165°	283	292	310	328	334	80
175°	295	295	298	302	301	28
180°	296	296	296	296	296	

TEST NUMBER: P1008666

CATALOG NUMBER: S122DIP-B1005D530UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1588.3	1588.3	1588.3	1588.3	1588.3
2.5°	1597.5	1589.9	1573.1	1588.3	1585.3
5°	1588.3	1582.2	1565.4	1577.7	1574.6
7.5°	1577.7	1568.5	1551.7	1563.9	1560.9
10°	1560.9	1550.2	1531.8	1544.1	1539.5
12.5°	1537.9	1528.8	1510.5	1518.1	1515.0
15°	1512.0	1502.8	1483.0	1489.1	1481.4
17.5°	1479.9	1470.7	1450.9	1458.5	1450.9
20°	1444.8	1435.6	1414.2	1418.8	1412.7
22.5°	1409.7	1395.9	1376.1	1376.1	1373.0
25°	1368.4	1356.2	1330.2	1333.3	1330.2
27.5°	1322.6	1311.9	1292.1	1287.5	1279.8
30°	1276.8	1264.6	1241.7	1237.1	1231.0
32.5°	1227.9	1218.7	1194.3	1185.1	1179.0
35°	1180.6	1165.3	1140.9	1131.7	1124.1
37.5°	1127.1	1113.4	1088.9	1078.2	1070.6
40°	1072.1	1059.9	1035.5	1021.7	1015.6
42.5°	1018.7	1006.5	982.0	966.8	957.6
45°	960.6	950.0	927.0	910.2	904.1
47.5°	904.1	893.4	869.0	852.2	843.0
50°	844.6	836.9	815.6	794.2	786.5
52.5°	786.5	775.8	756.0	739.2	728.5
55°	727.0	717.8	699.5	681.2	673.5
57.5°	667.4	659.8	639.9	621.6	615.5
60°	607.8	601.7	580.4	563.6	559.0
62.5°	549.8	539.1	523.8	508.6	502.5
65°	490.2	481.1	465.8	452.1	444.4
67.5°	429.2	421.5	407.8	397.1	391.0
70°	372.6	366.5	352.8	342.1	336.0
72.5°	314.6	308.5	300.9	290.2	285.6
75°	256.6	253.5	245.9	236.7	239.8
77.5°	204.7	198.5	195.5	190.9	186.3
80°	152.7	151.2	148.1	143.6	140.5
82.5°	103.9	103.9	102.3	96.2	96.2
85°	62.6	61.1	59.6	55.0	53.5
87.5°	27.5	24.4	21.4	16.8	15.3
90°	0.6	7.6	19.3	18.5	18.8
92.5°	8.5	27.0	87.5	40.4	34.7
95°	19.9	48.9	222.8	84.2	64.8
97.5°	29.6	64.5	363.2	168.8	108.6
100°	43.8	79.0	449.0	336.2	203.5
102.5°	56.8	92.0	451.8	568.3	396.7
105°	69.3	104.6	421.1	752.8	640.5
107.5°	83.0	117.0	392.7	819.6	804.8
110°	96.6	129.8	373.4	808.7	871.8

TEST NUMBER: P1008666

CATALOG NUMBER: S122DIP-B1005D530UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	109.1	142.1	360.9	772.0	870.7
115°	122.2	154.3	352.4	727.2	842.8
117.5°	135.8	166.6	347.8	684.2	800.8
120°	148.3	178.4	343.8	646.0	760.4
122.5°	160.3	190.6	341.6	616.0	718.4
125°	170.5	201.8	338.7	589.1	683.7
127.5°	179.0	212.2	337.0	566.1	651.3
130°	186.4	221.6	335.9	542.8	624.6
132.5°	193.2	230.8	335.3	518.6	596.7
135°	200.1	238.7	334.7	495.0	566.6
137.5°	206.3	245.5	334.7	471.2	537.6
140°	213.7	251.8	334.2	450.1	507.5
142.5°	221.1	256.9	334.2	430.0	477.4
145°	228.5	262.6	333.0	413.4	452.4
147.5°	236.4	267.1	331.3	399.0	430.2
150°	244.4	271.6	329.6	386.5	410.9
152.5°	252.3	276.2	326.8	376.0	394.4
155°	259.7	280.4	323.4	365.7	380.2
157.5°	266.0	283.9	320.0	356.0	367.7
160°	272.2	287.3	316.6	346.4	355.8
162.5°	278.5	289.8	313.7	337.3	344.4
165°	283.0	291.6	309.7	328.5	333.6
167.5°	287.0	293.2	306.3	320.5	323.4
170°	291.0	294.2	303.5	313.2	314.3
172.5°	293.3	295.0	300.1	306.6	306.9
175°	295.0	295.2	297.8	301.5	300.6
177.5°	296.1	295.5	295.5	297.8	296.1
180°	295.5	295.5	295.5	295.5	295.5

(END OF REPORT)