

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007963

Luminaire Tested: S122DIP-B1005D530UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007963
REPORT IS A COMBINATION OF REPORTS P983661 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5946.0 lumens
Efficiency: N/A
Efficacy: 77.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007963

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007963

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71			66
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	60			55
2	92	85	78	73	87	80	74	70	71	67	63	63	59	56	55	52	50			46
3	84	74	67	61	79	70	64	58	63	57	53	55	51	48	49	46	43			39
4	77	66	58	52	72	62	55	49	56	50	45	49	45	41	44	40	37			34
5	71	59	51	44	66	56	48	43	50	44	39	44	39	36	39	35	32			29
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	28			26
7	61	48	40	34	57	45	38	33	41	35	30	37	32	28	33	28	25			23
8	56	44	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23			20
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21			18
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19			17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1007963

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	2.4
10°-20°	406.8	6.8
20°-30°	597.8	10.1
30°-40°	694.3	11.7
40°-50°	693.4	11.7
50°-60°	604.6	10.2
60°-70°	446.9	7.5
70°-80°	252.9	4.3
80°-90°	68.0	1.1
90°-100°	22.9	0.4
100°-110°	85.4	1.4
110°-120°	226.5	3.8
120°-130°	375.7	6.3
130°-140°	399.0	6.7
140°-150°	370.9	6.2
150°-160°	298.2	5.0
160°-170°	192.1	3.2
170°-180°	66.1	1.1
0°-30°	1149.1	19.3
0°-40°	1843.4	31.0
0°-60°	3141.4	52.8
0°-90°	3909.2	65.7
90°-120°	334.8	5.6
90°-150°	1480.4	24.9
90°-180°	2037.0	34.3
0°-180°	5946.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	0	6	10	13	14	6
95°	33	16	20	22	22	39
105°	153	168	31	36	38	163
115°	289	298	310	77	41	285
125°	409	415	425	428	430	365
135°	506	514	518	523	522	391
145°	587	586	595	598	596	367
155°	646	642	648	650	646	298
165°	681	678	679	683	679	192
175°	696	693	694	697	692	66
180°	695	695	695	695	695	

TEST NUMBER: P1007963

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	0.5	6.0	10.1	12.6	13.6
92.5°	12.6	10.6	12.1	13.1	13.6
95°	32.7	16.1	19.6	22.1	21.6
97.5°	58.8	17.6	25.6	27.1	27.6
100°	89.0	20.1	28.7	32.7	33.7
102.5°	122.2	121.2	29.7	35.2	36.7
105°	152.8	167.9	30.7	36.2	38.2
107.5°	188.5	201.1	31.7	37.2	39.2
110°	222.7	233.3	88.0	37.7	39.7



TEST NUMBER: P1007963

CATALOG NUMBER: S122DIP-B1005D530UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	254.9	263.9	255.4	38.7	40.2
115°	289.1	297.6	310.2	77.4	41.2
117.5°	318.7	328.8	337.3	265.4	133.7
120°	351.9	359.4	368.5	374.5	306.7
122.5°	380.1	388.1	398.2	401.2	401.7
125°	408.7	415.2	424.8	428.3	429.8
127.5°	434.9	441.9	449.4	454.5	455.0
130°	459.5	467.5	473.1	478.6	478.1
132.5°	484.6	491.2	496.7	501.2	500.7
135°	505.7	513.8	518.3	523.3	522.3
137.5°	527.9	533.9	538.9	543.9	542.4
140°	549.5	553.5	559.0	563.5	561.0
142.5°	567.6	571.1	577.6	581.6	579.1
145°	586.7	586.2	594.7	598.2	595.7
147.5°	603.3	601.8	610.3	612.8	610.8
150°	619.3	615.8	623.9	626.9	624.4
152.5°	632.9	628.9	636.4	639.5	635.9
155°	646.0	641.5	647.5	650.5	646.5
157.5°	656.5	652.5	657.1	660.6	656.5
160°	665.6	662.6	665.6	668.6	665.1
162.5°	673.6	670.6	673.1	676.7	672.1
165°	680.7	677.7	679.2	682.7	679.2
167.5°	686.2	683.2	684.7	688.2	683.7
170°	690.7	687.7	688.7	692.2	687.7
172.5°	693.7	690.7	691.7	695.3	690.7
175°	696.3	692.7	693.7	697.3	692.2
177.5°	697.3	693.7	694.3	697.8	693.2
180°	694.8	694.8	694.8	694.8	694.8

(END OF REPORT)