

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008669

Luminaire Tested: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008669
REPORT IS A COMBINATION OF REPORTS P983691 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D530UB50-4F0-XX-W2A-A4
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6231.0 lumens
Efficiency: N/A
Efficacy: 81.2 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

Luminous Intensity Polar Plot



TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	83	83	83	73	73	73	65	65	65	68
1	102	98	95	91	97	93	90	87	83	80	78	74	72	70	65	64	63	59	58	57	59
2	94	87	81	76	88	82	77	72	74	69	66	66	62	60	58	56	54	50	49	48	50
3	86	77	70	64	81	73	66	61	65	60	56	59	55	51	52	49	47	43	42	41	43
4	79	69	61	55	75	65	58	53	59	53	49	53	48	45	47	44	41	38	37	36	38
5	73	61	53	47	69	59	51	46	53	47	42	48	43	39	43	39	36	33	32	31	33
6	68	56	47	42	64	53	46	40	48	42	37	43	39	35	39	35	32	30	29	28	30
7	63	50	43	37	59	48	41	36	44	38	33	40	35	31	36	32	29	26	25	24	26
8	58	46	38	33	55	44	37	32	40	34	30	37	32	28	33	29	26	24	23	22	24
9	55	42	35	30	52	41	34	29	37	31	27	34	29	25	31	27	24	22	21	20	22
10	51	39	32	27	48	37	31	26	34	29	25	31	27	23	29	25	22	20	19	18	20

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30413	30413	30413	30413
5°	30486	32427	30603	25799
10°	30132	35400	30321	21271
15°	29401	37339	29809	17916
20°	28943	35058	28943	15573
25°	28020	30119	28148	13925
30°	26503	23676	27007	12614
35°	25158	16372	25578	11542
40°	23613	12361	23882	10686
45°	21707	10158	22061	9762
50°	20059	8915	20095	8937
55°	18181	7596	18298	8040
60°	16177	6345	16401	7017
65°	14383	5161	14646	5992
70°	12598	4049	12919	4833
75°	10573	2940	10987	3505
80°	8255	1863	8846	2079
85°	5424	938	5848	694

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 157.5°

Vertical Angle: 45°

Luminance: 31439 cd/sqm

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.0	2.9
10°-20°	532.6	8.5
20°-30°	773.0	12.4
30°-40°	814.9	13.1
40°-50°	721.1	11.6
50°-60°	575.8	9.2
60°-70°	391.1	6.3
70°-80°	200.1	3.2
80°-90°	49.1	0.8
90°-100°	111.4	1.8
100°-110°	392.3	6.3
110°-120°	412.0	6.6
120°-130°	339.0	5.4
130°-140°	272.3	4.4
140°-150°	205.7	3.3
150°-160°	144.6	2.3
160°-170°	85.1	1.4
170°-180°	27.7	0.4
0°-30°	1488.7	23.9
0°-40°	2303.6	37.0
0°-60°	3600.5	57.8
0°-90°	4240.8	68.1
90°-120°	915.8	14.7
90°-150°	1732.7	27.8
90°-180°	1990.0	31.9
0°-180°	6231.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1921	1921	1921	1921	1921	
5°	1923	2146	1930	1707	1923	182
15°	1806	2638	1831	1266	1806	510
25°	1623	2198	1630	1016	1623	742
35°	1325	1196	1347	843	1325	829
45°	994	721	1010	693	994	771
55°	682	506	687	536	682	609
65°	405	312	412	362	405	402
75°	189	154	196	183	189	203
85°	38	40	41	30	38	45
90°	0	18	0	18	0	3
95°	19	63	19	63	19	20
105°	67	619	67	619	67	71
115°	118	815	118	815	118	117
125°	165	661	165	661	165	147
135°	193	548	193	548	193	149
145°	221	438	221	438	221	139
155°	251	368	251	368	251	116
165°	274	323	274	323	274	77
175°	285	291	285	291	285	27
180°	286	286	286	286	286	

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1931.6	1936.1	1943.5	1944.9	1959.7	1971.5	1984.8	1984.8	1989.2	1987.8	1976.0
5°	1922.8	1936.1	1955.3	1971.5	1998.1	2009.9	2027.6	2040.9	2052.7	2061.6	2060.1
7.5°	1908.0	1931.6	1959.7	1990.7	2026.2	2046.8	2071.9	2095.6	2111.8	2126.6	2136.9
10°	1882.9	1922.8	1961.2	2002.5	2048.3	2076.4	2105.9	2136.9	2162.0	2190.1	2216.7
12.5°	1848.9	1906.5	1953.8	2008.4	2064.6	2095.6	2142.8	2166.5	2215.2	2286.1	2305.3
15°	1806.1	1884.4	1928.7	1998.1	2071.9	2097.1	2162.0	2200.4	2300.8	2345.2	2398.3
17.5°	1766.2	1853.4	1912.5	1992.2	2064.6	2113.3	2176.8	2255.1	2339.2	2402.7	2461.8
20°	1733.8	1817.9	1888.8	1977.4	2069.0	2131.0	2197.5	2292.0	2383.5	2448.5	2494.3
22.5°	1659.9	1767.7	1850.4	1949.4	2060.1	2145.8	2209.3	2312.7	2411.6	2451.5	2491.4
25°	1623.0	1716.0	1812.0	1924.3	2054.2	2156.1	2210.8	2326.0	2413.1	2427.9	2436.7
27.5°	1555.1	1659.9	1772.2	1900.6	2052.7	2138.4	2207.8	2312.7	2382.1	2371.7	2345.2
30°	1470.9	1599.4	1723.4	1862.2	2032.1	2125.1	2190.1	2286.1	2321.5	2268.4	2221.1
32.5°	1408.9	1530.0	1667.3	1828.3	2008.4	2097.1	2160.6	2235.9	2243.3	2147.3	2067.5
35°	1324.7	1459.1	1614.1	1784.0	1968.6	2048.3	2107.4	2153.2	2117.7	1983.3	1888.8
37.5°	1249.4	1382.3	1547.7	1720.5	1913.9	1992.2	2039.5	2046.8	1959.7	1841.6	1702.7
40°	1166.7	1304.0	1476.8	1658.4	1853.4	1921.3	1950.8	1928.7	1803.2	1665.8	1504.9
42.5°	1084.0	1219.8	1405.9	1592.0	1776.6	1834.2	1846.0	1785.4	1631.9	1470.9	1284.8
45°	993.9	1135.7	1321.7	1509.3	1688.0	1720.5	1721.9	1634.8	1453.2	1284.8	1112.0
47.5°	920.0	1051.5	1236.1	1423.6	1574.3	1596.4	1587.6	1487.1	1289.2	1100.2	949.6
50°	838.8	964.3	1147.5	1332.1	1460.6	1466.5	1444.3	1301.1	1107.6	934.8	815.2
52.5°	751.7	878.7	1047.0	1224.3	1339.5	1330.6	1287.8	1134.2	952.5	809.3	717.7
55°	682.3	794.5	952.5	1125.3	1206.5	1181.4	1134.2	977.6	834.4	713.3	633.5
57.5°	605.5	704.4	859.5	1010.1	1057.4	1033.8	986.5	840.3	707.4	615.8	562.7
60°	533.1	623.2	759.1	884.6	921.5	896.4	841.8	710.3	614.3	537.6	497.7
62.5°	466.7	544.9	658.7	773.8	788.6	763.5	716.2	609.9	527.2	466.7	437.1
65°	404.6	478.5	570.0	657.2	670.5	643.9	595.1	518.4	448.9	410.5	382.5
67.5°	344.1	403.2	484.4	547.9	555.3	530.2	490.3	428.3	385.4	344.1	323.4
70°	290.9	335.2	398.7	450.4	453.4	429.7	409.1	353.0	320.5	290.9	274.7
72.5°	239.2	270.3	319.0	357.4	358.9	344.1	324.9	289.5	261.4	240.7	224.5
75°	189.0	215.6	245.1	279.1	277.6	265.8	251.1	228.9	205.3	192.0	184.6
77.5°	144.7	161.0	184.6	206.8	206.8	200.8	192.0	175.7	161.0	147.7	140.3
80°	103.4	113.7	132.9	140.3	143.2	141.8	134.4	122.6	116.7	106.3	103.4
82.5°	66.5	73.8	82.7	90.1	94.5	91.6	90.1	84.2	75.3	72.4	69.4
85°	38.4	41.4	45.8	50.2	51.7	50.2	53.2	48.7	44.3	44.3	42.8
87.5°	16.2	17.7	20.7	20.7	22.2	22.2	20.7	22.2	22.2	20.7	19.2
90°	0.5	2.2	4.4	5.5	6.6	7.4	8.2	11.0	14.8	18.1	18.7
92.5°	8.2	11.5	15.9	18.7	23.1	26.1	29.1	44.0	64.8	83.5	84.6
95°	19.2	21.4	26.9	31.9	40.7	47.3	53.9	79.1	127.0	190.7	215.4
97.5°	28.6	31.9	37.9	45.1	55.0	62.4	69.8	102.2	168.7	271.5	351.2
100°	42.3	44.0	48.9	57.7	68.7	76.4	84.1	113.2	180.3	299.0	434.2
102.5°	55.0	56.1	61.0	69.8	81.3	89.0	96.7	123.1	180.8	288.5	436.9
105°	67.0	69.2	73.1	81.3	93.4	101.1	108.8	134.6	183.6	274.2	407.2
107.5°	80.2	81.9	85.7	93.4	105.5	113.2	120.9	146.2	189.6	266.5	379.8
110°	93.4	95.6	98.9	106.1	117.6	125.6	133.5	157.7	197.3	264.3	361.1

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	105.5	107.7	111.6	118.2	129.1	137.4	145.6	168.7	205.5	264.9	349.0
115°	118.2	120.9	124.2	130.8	141.8	149.2	156.6	180.3	213.8	267.1	340.7
117.5°	131.3	133.5	136.8	142.9	153.3	161.0	168.7	190.7	222.6	270.4	336.3
120°	143.4	145.6	148.9	153.9	164.9	172.6	180.3	201.7	231.4	273.7	332.5
122.5°	155.0	156.6	159.9	165.4	176.4	184.4	192.4	212.1	239.1	277.5	330.3
125°	164.9	166.5	169.8	176.4	187.4	195.1	202.8	222.6	247.3	281.4	327.5
127.5°	173.1	175.3	179.7	186.9	197.3	205.2	213.2	232.5	255.0	285.2	325.9
130°	180.3	182.5	188.0	195.6	206.6	214.3	222.0	241.3	262.1	289.6	324.8
132.5°	186.9	189.6	195.6	203.9	215.4	223.1	230.8	249.0	269.3	294.0	324.2
135°	193.4	195.6	202.2	210.5	223.1	230.8	238.5	256.1	275.3	297.3	323.7
137.5°	199.5	202.2	208.8	217.6	230.3	237.4	244.6	262.1	280.3	300.6	323.7
140°	206.6	208.8	215.4	224.2	236.3	243.4	250.6	267.1	284.1	302.8	323.1
142.5°	213.8	215.4	221.5	230.3	241.8	248.4	255.0	270.9	287.4	304.5	323.1
145°	220.9	223.1	228.6	236.9	247.9	253.9	259.9	274.8	290.2	305.6	322.0
147.5°	228.6	230.3	235.8	243.5	252.8	258.3	263.8	278.1	291.8	306.1	320.4
150°	236.3	238.0	242.4	249.5	257.7	262.6	267.6	280.3	292.9	305.6	318.8
152.5°	244.0	244.6	249.0	255.0	262.7	267.1	271.5	282.5	293.5	304.5	316.0
155°	251.2	251.7	255.0	261.0	267.1	271.2	275.3	284.7	294.0	303.4	312.7
157.5°	257.2	257.7	260.5	266.0	270.9	274.5	278.1	286.3	294.0	301.2	309.4
160°	263.2	263.8	266.0	270.4	274.8	277.8	280.8	287.4	294.0	299.5	306.1
162.5°	269.3	268.7	270.9	274.2	278.1	280.3	282.5	288.0	293.5	297.9	303.4
165°	273.7	273.1	274.2	277.5	280.3	282.0	283.6	288.5	292.4	295.7	299.5
167.5°	277.5	277.0	278.1	280.3	282.5	283.6	284.7	288.5	291.8	293.5	296.2
170°	281.4	280.3	280.8	282.5	283.6	284.4	285.2	288.0	290.7	291.8	293.5
172.5°	283.6	283.0	282.5	284.1	284.7	285.2	285.8	287.4	289.1	289.6	290.2
175°	285.2	284.7	284.1	285.2	285.2	285.5	285.8	286.9	288.0	287.4	288.0
177.5°	286.3	285.2	284.7	285.8	285.8	285.8	285.8	286.3	287.4	286.3	285.8
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1996.6	1998.1	2001.1	2015.8	2023.2	2024.7	2018.8	2032.1	2036.5	2032.1	2029.1
5°	2091.1	2100.0	2117.7	2136.9	2135.4	2136.9	2145.8	2154.6	2157.6	2145.8	2150.2
7.5°	2173.8	2191.6	2210.8	2240.3	2240.3	2255.1	2261.0	2268.4	2286.1	2277.2	2274.3
10°	2268.4	2292.0	2327.4	2374.7	2376.2	2390.9	2405.7	2429.3	2436.7	2430.8	2433.8
12.5°	2386.5	2432.3	2435.2	2486.9	2510.6	2513.5	2537.1	2532.7	2547.5	2547.5	2572.6
15°	2438.2	2509.1	2549.0	2599.2	2613.9	2596.2	2615.4	2636.1	2637.6	2637.6	2636.1
17.5°	2531.2	2559.3	2599.2	2625.7	2631.7	2631.7	2633.1	2642.0	2636.1	2624.3	2633.1
20°	2550.4	2562.2	2577.0	2574.1	2577.0	2562.2	2547.5	2532.7	2534.2	2526.8	2549.0
22.5°	2515.0	2512.0	2478.1	2455.9	2455.9	2426.4	2398.3	2385.0	2371.7	2376.2	2383.5
25°	2426.4	2380.6	2339.2	2306.8	2299.4	2252.1	2213.7	2201.9	2179.8	2197.5	2200.4
27.5°	2284.6	2232.9	2166.5	2138.4	2100.0	2080.8	2054.2	2018.8	1973.0	1999.6	1995.2
30°	2132.5	2055.7	2001.1	1933.1	1872.6	1868.1	1817.9	1758.9	1735.2	1735.2	1748.5
32.5°	1962.7	1860.8	1781.0	1685.0	1626.0	1600.8	1540.3	1481.2	1494.5	1450.2	1466.5
35°	1764.8	1630.4	1530.0	1436.9	1392.6	1363.1	1284.8	1252.3	1216.9	1196.2	1234.6
37.5°	1575.7	1420.7	1292.2	1190.3	1174.1	1120.9	1067.7	1047.0	1026.4	1035.2	1033.8
40°	1345.4	1208.0	1092.8	1013.1	985.0	959.9	924.5	899.4	886.1	893.5	894.9
42.5°	1137.1	1021.9	936.3	880.2	856.5	838.8	821.1	800.4	796.0	796.0	801.9
45°	976.2	881.6	824.1	778.3	765.0	751.7	738.4	729.5	726.6	720.7	725.1
47.5°	847.7	772.4	736.9	703.0	688.2	685.2	673.4	669.0	663.1	661.6	663.1
50°	739.9	692.6	660.1	640.9	630.6	626.2	620.3	611.4	608.4	615.8	612.9
52.5°	664.6	620.3	602.5	583.3	577.4	571.5	562.7	564.1	562.7	559.7	559.7
55°	589.2	561.2	543.5	528.7	527.2	521.3	513.9	511.0	509.5	506.5	511.0
57.5°	528.7	506.5	490.3	477.0	471.1	471.1	463.7	457.8	457.8	456.3	457.8
60°	468.1	446.0	435.7	422.4	417.9	416.5	412.0	409.1	404.6	404.6	404.6
62.5°	412.0	394.3	382.5	370.7	372.2	364.8	358.9	355.9	355.9	357.4	357.4
65°	358.9	347.0	332.3	321.9	319.0	317.5	314.6	313.1	308.7	311.6	311.6
67.5°	310.1	293.9	285.0	280.6	276.2	274.7	271.7	268.8	267.3	265.8	268.8
70°	261.4	248.1	240.7	237.8	233.3	231.9	230.4	225.9	227.4	228.9	230.4
72.5°	217.1	205.3	203.8	194.9	194.9	194.9	189.0	192.0	190.5	187.6	190.5
75°	171.3	165.4	162.4	158.0	159.5	158.0	156.5	152.1	152.1	153.6	155.1
77.5°	135.9	130.0	128.5	124.1	121.1	124.1	121.1	119.6	119.6	121.1	121.1
80°	100.4	97.5	93.0	93.0	93.0	91.6	91.6	91.6	90.1	88.6	90.1
82.5°	66.5	66.5	65.0	63.5	65.0	62.0	63.5	63.5	63.5	63.5	63.5
85°	42.8	41.4	41.4	39.9	39.9	39.9	41.4	38.4	38.4	39.9	39.9
87.5°	19.2	19.2	19.2	20.7	19.2	19.2	19.2	20.7	19.2	19.2	19.2
90°	18.1	17.6	16.5	17.6	17.8	18.1	18.1	18.1	18.1	18.1	18.1
92.5°	70.9	55.5	47.3	41.2	39.0	36.8	36.3	34.1	34.6	33.5	34.6
95°	188.5	144.0	110.5	87.4	81.4	75.3	68.1	63.8	62.1	62.7	62.1
97.5°	353.9	294.6	235.2	179.7	163.2	146.7	125.3	114.3	108.3	105.0	108.3
100°	513.3	501.8	433.6	358.3	325.0	291.8	246.2	222.6	206.6	196.7	206.6
102.5°	572.7	637.5	635.3	585.3	549.6	513.9	463.3	418.8	397.9	383.6	397.9
105°	553.4	667.7	729.8	737.0	727.9	718.8	684.8	650.7	627.1	619.4	627.1
107.5°	512.8	635.3	727.6	781.5	792.5	803.5	802.9	798.0	790.8	778.2	790.8
110°	474.8	590.8	689.2	759.5	782.0	804.6	828.2	838.6	843.6	843.0	843.6

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	448.5	550.1	643.5	719.9	746.6	773.2	808.4	827.7	838.1	841.9	838.1
115°	427.6	518.2	602.9	674.9	703.2	731.5	770.5	795.8	810.1	815.0	810.1
117.5°	413.3	491.9	567.7	634.8	661.7	688.6	728.7	755.7	770.5	774.3	770.5
120°	402.3	473.2	541.3	599.6	624.6	649.6	688.1	713.9	729.8	735.3	729.8
122.5°	392.9	458.3	519.3	573.8	595.8	617.7	651.2	676.5	690.3	694.7	690.3
125°	384.2	444.1	500.7	549.0	569.6	590.2	622.1	643.0	656.7	661.1	656.7
127.5°	375.9	429.8	482.0	528.1	547.4	566.6	594.6	614.4	626.5	629.8	626.5
130°	367.7	416.0	463.3	506.7	524.8	543.0	569.9	588.6	599.6	604.0	599.6
132.5°	361.1	402.8	445.7	484.7	501.4	518.2	544.6	563.3	573.2	577.1	573.2
135°	355.0	390.7	427.0	463.3	478.7	494.1	517.7	535.8	545.7	547.9	545.7
137.5°	350.6	380.9	412.2	441.9	455.6	469.3	491.9	507.8	516.6	519.9	516.6
140°	346.8	371.5	397.9	423.2	435.3	447.4	464.9	479.2	487.5	490.8	487.5
142.5°	342.9	363.8	385.3	406.1	415.8	425.4	441.9	454.5	461.6	461.6	461.6
145°	339.6	356.7	374.8	391.8	399.8	407.8	421.0	430.3	435.8	437.5	435.8
147.5°	336.3	351.2	366.0	379.8	385.8	391.8	403.4	411.1	414.9	416.0	414.9
150°	331.9	345.1	357.2	368.8	373.8	378.7	386.9	393.5	396.8	397.3	396.8
152.5°	328.1	339.1	350.1	359.4	363.5	367.7	373.7	379.2	381.4	381.4	381.4
155°	323.1	333.6	342.4	350.6	353.6	356.7	362.7	366.6	368.8	367.7	368.8
157.5°	318.8	327.0	334.7	341.8	344.3	346.8	351.2	354.5	355.6	355.6	355.6
160°	313.8	321.0	327.0	333.0	335.0	336.9	340.7	343.5	344.0	344.0	344.0
162.5°	309.4	314.9	319.9	324.8	326.2	327.5	331.4	333.0	333.6	333.0	333.6
165°	304.5	308.9	312.7	316.6	317.7	318.8	321.0	323.1	323.1	322.6	323.1
167.5°	299.5	302.8	306.1	308.9	310.0	311.1	312.2	313.3	313.3	312.7	313.3
170°	295.7	298.4	300.1	302.3	302.8	303.4	303.9	305.6	305.0	303.9	305.0
172.5°	291.8	293.5	294.6	296.2	296.5	296.8	297.3	297.9	297.3	296.8	297.3
175°	288.5	290.2	290.7	291.3	291.6	291.8	291.8	292.4	291.8	290.7	291.8
177.5°	286.3	287.4	287.4	288.0	288.0	288.0	288.0	288.0	287.4	286.3	287.4
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	2036.5	2026.2	2017.3	2018.8	2026.2	2020.3	2005.5	1986.3	1978.9	1970.0	1978.9
5°	2159.1	2150.2	2132.5	2134.0	2129.5	2123.6	2100.0	2070.5	2070.5	2046.8	2043.9
7.5°	2280.2	2266.9	2255.1	2252.1	2235.9	2224.1	2203.4	2162.0	2145.8	2117.7	2101.5
10°	2416.0	2405.7	2392.4	2376.2	2367.3	2346.6	2312.7	2252.1	2222.6	2184.2	2156.1
12.5°	2553.4	2551.9	2522.4	2489.9	2488.4	2455.9	2432.3	2351.1	2311.2	2259.5	2193.0
15°	2640.5	2633.1	2616.9	2600.6	2605.1	2569.6	2516.5	2420.5	2393.9	2331.9	2261.0
17.5°	2639.0	2639.0	2634.6	2631.7	2627.2	2616.9	2587.3	2523.8	2481.0	2402.7	2336.3
20°	2554.9	2574.1	2578.5	2577.0	2591.8	2599.2	2597.7	2557.8	2523.8	2454.4	2386.5
22.5°	2386.5	2430.8	2450.0	2461.8	2492.8	2509.1	2547.5	2532.7	2523.8	2472.2	2414.6
25°	2230.0	2244.7	2302.3	2305.3	2348.1	2388.0	2426.4	2451.5	2484.0	2464.8	2416.0
27.5°	2027.6	2061.6	2103.0	2134.0	2142.8	2224.1	2287.6	2334.8	2408.7	2414.6	2398.3
30°	1798.7	1815.0	1882.9	1924.3	1971.5	2030.6	2122.2	2203.4	2269.8	2330.4	2351.1
32.5°	1519.6	1586.1	1626.0	1676.2	1717.5	1822.4	1934.6	2039.5	2116.2	2218.1	2262.5
35°	1264.1	1315.8	1383.8	1404.4	1479.8	1568.4	1714.6	1848.9	1965.6	2069.0	2159.1
37.5°	1053.0	1094.3	1166.7	1199.2	1243.5	1357.2	1479.8	1646.6	1786.9	1913.9	2026.2
40°	908.2	939.2	993.9	1004.2	1041.1	1144.5	1243.5	1400.0	1586.1	1757.4	1880.0
42.5°	809.3	824.1	861.0	874.3	897.9	967.3	1055.9	1203.6	1376.4	1553.6	1726.4
45°	738.4	748.7	770.9	782.7	812.2	843.3	915.6	1033.8	1169.6	1348.3	1534.4
47.5°	674.9	688.2	697.0	704.4	720.7	754.6	801.9	889.0	1019.0	1182.9	1363.1
50°	621.7	626.2	642.4	643.9	654.2	676.4	720.7	773.8	877.2	1010.1	1184.4
52.5°	568.6	573.0	583.3	593.7	598.1	615.8	645.4	689.7	766.5	871.3	1026.4
55°	515.4	521.3	531.6	539.0	543.5	558.2	576.0	618.8	679.3	753.2	880.2
57.5°	462.2	475.5	478.5	482.9	490.3	506.5	522.8	547.9	595.1	663.1	756.1
60°	412.0	416.5	426.8	431.2	438.6	447.5	468.1	487.3	521.3	574.5	658.7
62.5°	360.3	370.7	375.1	379.5	385.4	395.8	409.1	429.7	459.3	502.1	568.6
65°	316.0	317.5	326.4	332.3	338.2	345.6	358.9	378.1	395.8	435.7	484.4
67.5°	273.2	276.2	279.1	285.0	292.4	299.8	311.6	321.9	344.1	370.7	409.1
70°	231.9	231.9	239.2	243.7	242.2	251.1	259.9	271.7	288.0	313.1	344.1
72.5°	194.9	193.5	199.4	200.8	203.8	209.7	215.6	227.4	236.3	255.5	279.1
75°	155.1	158.0	161.0	161.0	165.4	169.8	175.7	181.6	192.0	203.8	221.5
77.5°	122.6	122.6	125.5	127.0	131.4	130.0	135.9	141.8	149.2	159.5	172.8
80°	90.1	93.0	93.0	93.0	94.5	96.0	101.9	106.3	110.8	118.1	124.1
82.5°	63.5	63.5	66.5	66.5	66.5	69.4	69.4	70.9	73.8	78.3	82.7
85°	39.9	39.9	39.9	41.4	39.9	41.4	44.3	42.8	44.3	47.3	47.3
87.5°	19.2	19.2	19.2	19.2	19.2	20.7	19.2	20.7	22.2	22.2	22.2
90°	18.1	18.1	18.1	17.8	17.6	16.5	17.6	18.1	18.7	18.1	14.8
92.5°	34.1	36.3	36.8	39.0	41.2	47.3	55.5	70.9	84.6	83.5	64.8
95°	63.8	68.1	75.3	81.4	87.4	110.5	144.0	188.5	215.4	190.7	127.0
97.5°	114.3	125.3	146.7	163.2	179.7	235.2	294.6	353.9	351.2	271.5	168.7
100°	222.6	246.2	291.8	325.0	358.3	433.6	501.8	513.3	434.2	299.0	180.3
102.5°	418.8	463.3	513.9	549.6	585.3	635.3	637.5	572.7	436.9	288.5	180.8
105°	650.7	684.8	718.8	727.9	737.0	729.8	667.7	553.4	407.2	274.2	183.6
107.5°	798.0	802.9	803.5	792.5	781.5	727.6	635.3	512.8	379.8	266.5	189.6
110°	838.6	828.2	804.6	782.0	759.5	689.2	590.8	474.8	361.1	264.3	197.3

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	827.7	808.4	773.2	746.6	719.9	643.5	550.1	448.5	349.0	264.9	205.5
115°	795.8	770.5	731.5	703.2	674.9	602.9	518.2	427.6	340.7	267.1	213.8
117.5°	755.7	728.7	688.6	661.7	634.8	567.7	491.9	413.3	336.3	270.4	222.6
120°	713.9	688.1	649.6	624.6	599.6	541.3	473.2	402.3	332.5	273.7	231.4
122.5°	676.5	651.2	617.7	595.8	573.8	519.3	458.3	392.9	330.3	277.5	239.1
125°	643.0	622.1	590.2	569.6	549.0	500.7	444.1	384.2	327.5	281.4	247.3
127.5°	614.4	594.6	566.6	547.4	528.1	482.0	429.8	375.9	325.9	285.2	255.0
130°	588.6	569.9	543.0	524.8	506.7	463.3	416.0	367.7	324.8	289.6	262.1
132.5°	563.3	544.6	518.2	501.4	484.7	445.7	402.8	361.1	324.2	294.0	269.3
135°	535.8	517.7	494.1	478.7	463.3	427.0	390.7	355.0	323.7	297.3	275.3
137.5°	507.8	491.9	469.3	455.6	441.9	412.2	380.9	350.6	323.7	300.6	280.3
140°	479.2	464.9	447.4	435.3	423.2	397.9	371.5	346.8	323.1	302.8	284.1
142.5°	454.5	441.9	425.4	415.8	406.1	385.3	363.8	342.9	323.1	304.5	287.4
145°	430.3	421.0	407.8	399.8	391.8	374.8	356.7	339.6	322.0	305.6	290.2
147.5°	411.1	403.4	391.8	385.8	379.8	366.0	351.2	336.3	320.4	306.1	291.8
150°	393.5	386.9	378.7	373.8	368.8	357.2	345.1	331.9	318.8	305.6	292.9
152.5°	379.2	373.7	367.7	363.5	359.4	350.1	339.1	328.1	316.0	304.5	293.5
155°	366.6	362.7	356.7	353.6	350.6	342.4	333.6	323.1	312.7	303.4	294.0
157.5°	354.5	351.2	346.8	344.3	341.8	334.7	327.0	318.8	309.4	301.2	294.0
160°	343.5	340.7	336.9	335.0	333.0	327.0	321.0	313.8	306.1	299.5	294.0
162.5°	333.0	331.4	327.5	326.2	324.8	319.9	314.9	309.4	303.4	297.9	293.5
165°	323.1	321.0	318.8	317.7	316.6	312.7	308.9	304.5	299.5	295.7	292.4
167.5°	313.3	312.2	311.1	310.0	308.9	306.1	302.8	299.5	296.2	293.5	291.8
170°	305.6	303.9	303.4	302.8	302.3	300.1	298.4	295.7	293.5	291.8	290.7
172.5°	297.9	297.3	296.8	296.5	296.2	294.6	293.5	291.8	290.2	289.6	289.1
175°	292.4	291.8	291.8	291.6	291.3	290.7	290.2	288.5	288.0	287.4	288.0
177.5°	288.0	288.0	288.0	288.0	288.0	287.4	287.4	286.3	285.8	286.3	287.4
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1971.5	1964.1	1959.7	1962.7	1953.8	1931.6	1931.6	1939.0	1930.2	1921.3	1908.0
5°	2026.2	2011.4	2002.5	2001.1	1980.4	1944.9	1937.6	1930.2	1911.0	1890.3	1868.1
7.5°	2079.3	2052.7	2038.0	2027.6	1998.1	1952.3	1933.1	1916.9	1885.9	1854.9	1826.8
10°	2123.6	2085.2	2067.5	2051.3	2012.9	1955.3	1924.3	1894.7	1854.9	1815.0	1779.5
12.5°	2159.1	2114.8	2092.6	2069.0	2021.7	1946.4	1908.0	1860.8	1820.9	1767.7	1732.3
15°	2218.1	2126.6	2105.9	2083.8	2035.0	1931.6	1884.4	1831.2	1776.6	1705.7	1667.3
17.5°	2265.4	2142.8	2141.4	2094.1	2030.6	1925.7	1853.4	1784.0	1724.9	1654.0	1593.5
20°	2293.5	2167.9	2144.3	2095.6	2015.8	1885.9	1810.6	1733.8	1670.3	1584.6	1524.1
22.5°	2317.1	2203.4	2141.4	2082.3	1984.8	1872.6	1761.8	1689.5	1602.3	1509.3	1451.7
25°	2326.0	2210.8	2145.8	2077.9	1962.7	1834.2	1708.7	1630.4	1532.9	1448.7	1370.5
27.5°	2327.4	2209.3	2129.5	2058.7	1931.6	1784.0	1655.5	1572.8	1465.0	1367.5	1289.2
30°	2312.7	2193.0	2120.7	2043.9	1902.1	1738.2	1590.5	1498.9	1383.8	1286.3	1205.1
32.5°	2268.4	2160.6	2101.5	2017.3	1863.7	1674.7	1528.5	1426.6	1305.5	1209.5	1131.2
35°	2194.5	2120.7	2055.7	1977.4	1813.5	1615.6	1466.5	1346.8	1224.3	1132.7	1058.9
37.5°	2103.0	2063.1	2002.5	1925.7	1755.9	1562.5	1397.0	1264.1	1141.6	1053.0	980.6
40°	1978.9	1989.2	1930.2	1860.8	1688.0	1490.1	1307.0	1180.0	1064.8	982.1	911.2
42.5°	1844.5	1887.3	1853.4	1786.9	1612.7	1410.3	1240.5	1100.2	988.0	902.3	843.3
45°	1699.8	1773.6	1753.0	1704.2	1534.4	1326.2	1146.0	1010.1	911.2	828.5	776.8
47.5°	1541.8	1646.6	1646.6	1611.2	1447.3	1242.0	1064.8	926.0	828.5	769.4	719.2
50°	1380.8	1498.9	1518.1	1494.5	1349.8	1146.0	965.8	840.3	756.1	698.5	661.6
52.5°	1212.4	1349.8	1385.2	1373.4	1246.4	1054.4	884.6	762.0	685.2	635.0	602.5
55°	1051.5	1211.0	1249.4	1253.8	1135.7	954.0	794.5	686.7	612.9	578.9	550.8
57.5°	899.4	1053.0	1095.8	1103.2	1023.4	862.4	710.3	615.8	549.4	521.3	499.2
60°	769.4	897.9	954.0	970.3	900.8	756.1	632.1	540.5	490.3	463.7	443.0
62.5°	663.1	766.5	825.5	830.0	798.9	663.1	550.8	474.1	431.2	407.6	397.3
65°	559.7	652.7	688.2	705.9	680.8	574.5	475.5	412.0	378.1	357.4	347.0
67.5°	477.0	536.1	565.6	589.2	564.1	484.4	404.6	353.0	327.8	307.2	301.3
70°	391.4	440.1	462.2	485.9	463.7	403.2	345.6	298.3	276.2	259.9	252.5
72.5°	313.1	351.5	372.2	386.9	373.6	323.4	276.2	243.7	227.4	215.6	211.2
75°	248.1	274.7	286.5	296.8	290.9	252.5	223.0	196.4	181.6	171.3	168.4
77.5°	189.0	208.2	221.5	224.5	217.1	192.0	166.9	150.6	138.8	132.9	130.0
80°	134.4	146.2	153.6	158.0	150.6	140.3	122.6	110.8	100.4	93.0	91.6
82.5°	90.1	96.0	101.9	100.4	97.5	88.6	78.3	72.4	67.9	62.0	62.0
85°	51.7	53.2	56.1	57.6	56.1	50.2	44.3	41.4	38.4	34.0	34.0
87.5°	22.2	23.6	23.6	25.1	22.2	22.2	19.2	16.2	16.2	14.8	13.3
90°	11.0	8.2	7.4	6.6	5.5	4.4	2.2	0.5	2.2	4.4	5.5
92.5°	44.0	29.1	26.1	23.1	18.7	15.9	11.5	8.2	11.5	15.9	18.7
95°	79.1	53.9	47.3	40.7	31.9	26.9	21.4	19.2	21.4	26.9	31.9
97.5°	102.2	69.8	62.4	55.0	45.1	37.9	31.9	28.6	31.9	37.9	45.1
100°	113.2	84.1	76.4	68.7	57.7	48.9	44.0	42.3	44.0	48.9	57.7
102.5°	123.1	96.7	89.0	81.3	69.8	61.0	56.1	55.0	56.1	61.0	69.8
105°	134.6	108.8	101.1	93.4	81.3	73.1	69.2	67.0	69.2	73.1	81.3
107.5°	146.2	120.9	113.2	105.5	93.4	85.7	81.9	80.2	81.9	85.7	93.4
110°	157.7	133.5	125.6	117.6	106.1	98.9	95.6	93.4	95.6	98.9	106.1

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	168.7	145.6	137.4	129.1	118.2	111.6	107.7	105.5	107.7	111.6	118.2
115°	180.3	156.6	149.2	141.8	130.8	124.2	120.9	118.2	120.9	124.2	130.8
117.5°	190.7	168.7	161.0	153.3	142.9	136.8	133.5	131.3	133.5	136.8	142.9
120°	201.7	180.3	172.6	164.9	153.9	148.9	145.6	143.4	145.6	148.9	153.9
122.5°	212.1	192.4	184.4	176.4	165.4	159.9	156.6	155.0	156.6	159.9	165.4
125°	222.6	202.8	195.1	187.4	176.4	169.8	166.5	164.9	166.5	169.8	176.4
127.5°	232.5	213.2	205.2	197.3	186.9	179.7	175.3	173.1	175.3	179.7	186.9
130°	241.3	222.0	214.3	206.6	195.6	188.0	182.5	180.3	182.5	188.0	195.6
132.5°	249.0	230.8	223.1	215.4	203.9	195.6	189.6	186.9	189.6	195.6	203.9
135°	256.1	238.5	230.8	223.1	210.5	202.2	195.6	193.4	195.6	202.2	210.5
137.5°	262.1	244.6	237.4	230.3	217.6	208.8	202.2	199.5	202.2	208.8	217.6
140°	267.1	250.6	243.4	236.3	224.2	215.4	208.8	206.6	208.8	215.4	224.2
142.5°	270.9	255.0	248.4	241.8	230.3	221.5	215.4	213.8	215.4	221.5	230.3
145°	274.8	259.9	253.9	247.9	236.9	228.6	223.1	220.9	223.1	228.6	236.9
147.5°	278.1	263.8	258.3	252.8	243.5	235.8	230.3	228.6	230.3	235.8	243.5
150°	280.3	267.6	262.6	257.7	249.5	242.4	238.0	236.3	238.0	242.4	249.5
152.5°	282.5	271.5	267.1	262.7	255.0	249.0	244.6	244.0	244.6	249.0	255.0
155°	284.7	275.3	271.2	267.1	261.0	255.0	251.7	251.2	251.7	255.0	261.0
157.5°	286.3	278.1	274.5	270.9	266.0	260.5	257.7	257.2	257.7	260.5	266.0
160°	287.4	280.8	277.8	274.8	270.4	266.0	263.8	263.2	263.8	266.0	270.4
162.5°	288.0	282.5	280.3	278.1	274.2	270.9	268.7	269.3	268.7	270.9	274.2
165°	288.5	283.6	282.0	280.3	277.5	274.2	273.1	273.7	273.1	274.2	277.5
167.5°	288.5	284.7	283.6	282.5	280.3	278.1	277.0	277.5	277.0	278.1	280.3
170°	288.0	285.2	284.4	283.6	282.5	280.8	280.3	281.4	280.3	280.8	282.5
172.5°	287.4	285.8	285.2	284.7	284.1	282.5	283.0	283.6	283.0	282.5	284.1
175°	286.9	285.8	285.5	285.2	285.2	284.1	284.7	285.2	284.7	284.1	285.2
177.5°	286.3	285.8	285.8	285.8	285.8	284.7	285.2	286.3	285.2	284.7	285.8
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1900.6	1908.0	1906.5	1891.8	1875.5	1862.2	1837.1	1840.1	1831.2	1832.7	1841.6
5°	1853.4	1853.4	1847.5	1826.8	1800.2	1785.4	1757.4	1750.0	1732.3	1730.8	1729.3
7.5°	1803.2	1795.8	1788.4	1758.9	1726.4	1702.7	1664.3	1655.5	1637.8	1626.0	1620.0
10°	1744.1	1733.8	1719.0	1685.0	1645.2	1615.6	1575.7	1563.9	1530.0	1515.2	1506.3
12.5°	1679.1	1673.2	1649.6	1621.5	1556.5	1524.1	1466.5	1478.3	1444.3	1414.8	1410.3
15°	1614.1	1592.0	1578.7	1532.9	1454.6	1439.9	1394.1	1370.5	1339.5	1315.8	1315.8
17.5°	1550.6	1516.7	1487.1	1438.4	1380.8	1339.5	1305.5	1293.7	1255.3	1231.6	1227.2
20°	1466.5	1428.1	1420.7	1351.3	1311.4	1265.6	1233.1	1203.6	1175.5	1165.2	1157.8
22.5°	1386.7	1342.4	1330.6	1271.5	1231.6	1185.9	1153.4	1132.7	1112.0	1104.6	1091.4
25°	1301.1	1274.5	1256.8	1193.3	1148.9	1106.1	1084.0	1069.2	1050.0	1048.5	1039.7
27.5°	1218.4	1193.3	1175.5	1115.0	1082.5	1042.6	1024.9	1008.7	998.3	993.9	989.5
30°	1147.5	1119.4	1098.7	1054.4	1014.6	982.1	967.3	957.0	951.1	943.7	942.2
32.5°	1069.2	1053.0	1024.9	990.9	959.9	928.9	920.0	912.7	903.8	900.8	899.4
35°	1002.7	980.6	962.9	924.5	911.2	884.6	874.3	868.4	856.5	853.6	850.6
37.5°	937.8	917.1	897.9	874.3	849.2	834.4	828.5	819.6	813.7	815.2	812.2
40°	872.8	856.5	841.8	816.7	801.9	794.5	782.7	773.8	770.9	772.4	770.9
42.5°	809.3	794.5	785.7	766.5	751.7	744.3	736.9	728.1	732.5	732.5	736.9
45°	751.7	738.4	732.5	717.7	708.9	697.0	689.7	688.2	694.1	692.6	692.6
47.5°	692.6	688.2	680.8	667.5	655.7	648.3	646.8	646.8	652.7	655.7	654.2
50°	646.8	638.0	629.1	618.8	609.9	607.0	602.5	605.5	611.4	611.4	614.3
52.5°	589.2	583.3	580.4	571.5	565.6	565.6	565.6	567.1	571.5	576.0	574.5
55°	539.0	534.6	531.6	527.2	519.8	521.3	519.8	522.8	527.2	531.6	534.6
57.5°	485.9	484.4	481.4	474.1	474.1	472.6	477.0	478.5	485.9	488.8	493.3
60°	438.6	434.2	434.2	428.3	428.3	428.3	432.7	437.1	443.0	444.5	447.5
62.5°	388.4	388.4	386.9	382.5	382.5	386.9	388.4	394.3	397.3	397.3	401.7
65°	341.1	339.7	338.2	339.7	341.1	341.1	345.6	348.5	351.5	353.0	354.4
67.5°	293.9	292.4	295.4	293.9	296.8	302.7	301.3	305.7	310.1	310.1	311.6
70°	249.6	252.5	251.1	254.0	252.5	255.5	259.9	261.4	261.4	262.9	267.3
72.5°	208.2	208.2	208.2	206.8	208.2	211.2	214.1	215.6	218.6	220.0	224.5
75°	168.4	168.4	165.4	168.4	168.4	171.3	174.3	174.3	174.3	177.2	181.6
77.5°	127.0	128.5	127.0	130.0	130.0	131.4	134.4	132.9	135.9	137.3	138.8
80°	93.0	91.6	91.6	91.6	93.0	93.0	96.0	97.5	97.5	101.9	98.9
82.5°	59.1	60.5	59.1	60.5	60.5	62.0	60.5	62.0	63.5	66.5	65.0
85°	34.0	32.5	32.5	34.0	32.5	32.5	34.0	32.5	34.0	32.5	34.0
87.5°	13.3	11.8	11.8	11.8	11.8	10.3	10.3	8.9	8.9	8.9	7.4
90°	6.6	7.4	8.2	11.0	14.8	18.1	18.7	18.1	17.6	16.5	17.6
92.5°	23.1	26.1	29.1	44.0	64.8	83.5	84.6	70.9	55.5	47.3	41.2
95°	40.7	47.3	53.9	79.1	127.0	190.7	215.4	188.5	144.0	110.5	87.4
97.5°	55.0	62.4	69.8	102.2	168.7	271.5	351.2	353.9	294.6	235.2	179.7
100°	68.7	76.4	84.1	113.2	180.3	299.0	434.2	513.3	501.8	433.6	358.3
102.5°	81.3	89.0	96.7	123.1	180.8	288.5	436.9	572.7	637.5	635.3	585.3
105°	93.4	101.1	108.8	134.6	183.6	274.2	407.2	553.4	667.7	729.8	737.0
107.5°	105.5	113.2	120.9	146.2	189.6	266.5	379.8	512.8	635.3	727.6	781.5
110°	117.6	125.6	133.5	157.7	197.3	264.3	361.1	474.8	590.8	689.2	759.5

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	129.1	137.4	145.6	168.7	205.5	264.9	349.0	448.5	550.1	643.5	719.9
115°	141.8	149.2	156.6	180.3	213.8	267.1	340.7	427.6	518.2	602.9	674.9
117.5°	153.3	161.0	168.7	190.7	222.6	270.4	336.3	413.3	491.9	567.7	634.8
120°	164.9	172.6	180.3	201.7	231.4	273.7	332.5	402.3	473.2	541.3	599.6
122.5°	176.4	184.4	192.4	212.1	239.1	277.5	330.3	392.9	458.3	519.3	573.8
125°	187.4	195.1	202.8	222.6	247.3	281.4	327.5	384.2	444.1	500.7	549.0
127.5°	197.3	205.2	213.2	232.5	255.0	285.2	325.9	375.9	429.8	482.0	528.1
130°	206.6	214.3	222.0	241.3	262.1	289.6	324.8	367.7	416.0	463.3	506.7
132.5°	215.4	223.1	230.8	249.0	269.3	294.0	324.2	361.1	402.8	445.7	484.7
135°	223.1	230.8	238.5	256.1	275.3	297.3	323.7	355.0	390.7	427.0	463.3
137.5°	230.3	237.4	244.6	262.1	280.3	300.6	323.7	350.6	380.9	412.2	441.9
140°	236.3	243.4	250.6	267.1	284.1	302.8	323.1	346.8	371.5	397.9	423.2
142.5°	241.8	248.4	255.0	270.9	287.4	304.5	323.1	342.9	363.8	385.3	406.1
145°	247.9	253.9	259.9	274.8	290.2	305.6	322.0	339.6	356.7	374.8	391.8
147.5°	252.8	258.3	263.8	278.1	291.8	306.1	320.4	336.3	351.2	366.0	379.8
150°	257.7	262.6	267.6	280.3	292.9	305.6	318.8	331.9	345.1	357.2	368.8
152.5°	262.7	267.1	271.5	282.5	293.5	304.5	316.0	328.1	339.1	350.1	359.4
155°	267.1	271.2	275.3	284.7	294.0	303.4	312.7	323.1	333.6	342.4	350.6
157.5°	270.9	274.5	278.1	286.3	294.0	301.2	309.4	318.8	327.0	334.7	341.8
160°	274.8	277.8	280.8	287.4	294.0	299.5	306.1	313.8	321.0	327.0	333.0
162.5°	278.1	280.3	282.5	288.0	293.5	297.9	303.4	309.4	314.9	319.9	324.8
165°	280.3	282.0	283.6	288.5	292.4	295.7	299.5	304.5	308.9	312.7	316.6
167.5°	282.5	283.6	284.7	288.5	291.8	293.5	296.2	299.5	302.8	306.1	308.9
170°	283.6	284.4	285.2	288.0	290.7	291.8	293.5	295.7	298.4	300.1	302.3
172.5°	284.7	285.2	285.8	287.4	289.1	289.6	290.2	291.8	293.5	294.6	296.2
175°	285.2	285.5	285.8	286.9	288.0	287.4	288.0	288.5	290.2	290.7	291.3
177.5°	285.8	285.8	285.8	286.3	287.4	286.3	285.8	286.3	287.4	287.4	288.0
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1831.2	1835.7	1825.3	1822.4	1825.3	1815.0	1817.9	1820.9	1820.9	1825.3	1828.3
5°	1724.9	1719.0	1708.7	1705.7	1702.7	1707.2	1704.2	1708.7	1710.1	1720.5	1721.9
7.5°	1620.0	1611.2	1602.3	1593.5	1590.5	1583.1	1590.5	1590.5	1600.8	1597.9	1605.3
10°	1496.0	1494.5	1482.7	1478.3	1472.4	1460.6	1476.8	1472.4	1479.8	1493.0	1496.0
12.5°	1404.4	1388.2	1395.6	1374.9	1382.3	1370.5	1371.9	1371.9	1383.8	1385.2	1382.3
15°	1317.3	1304.0	1284.8	1276.0	1271.5	1265.6	1284.8	1286.3	1277.4	1298.1	1290.7
17.5°	1228.7	1228.7	1211.0	1206.5	1194.7	1200.6	1197.7	1199.2	1196.2	1211.0	1218.4
20°	1151.9	1144.5	1138.6	1140.1	1125.3	1122.4	1119.4	1122.4	1132.7	1143.0	1146.0
22.5°	1089.9	1085.4	1070.7	1073.6	1061.8	1066.2	1063.3	1070.7	1072.2	1072.2	1082.5
25°	1030.8	1024.9	1026.4	1020.5	1016.0	1016.0	1011.6	1016.0	1021.9	1024.9	1026.4
27.5°	986.5	982.1	974.7	970.3	973.2	965.8	971.7	976.2	976.2	973.2	976.2
30°	933.3	936.3	936.3	921.5	927.4	924.5	928.9	931.9	931.9	933.3	930.4
32.5°	897.9	889.0	887.6	886.1	886.1	880.2	880.2	884.6	886.1	887.6	892.0
35°	850.6	850.6	843.3	847.7	841.8	843.3	841.8	843.3	846.2	841.8	846.2
37.5°	807.8	809.3	806.3	809.3	810.8	807.8	804.9	810.8	807.8	807.8	804.9
40°	770.9	769.4	770.9	770.9	770.9	772.4	769.4	769.4	769.4	766.5	763.5
42.5°	739.9	731.0	734.0	735.4	731.0	731.0	732.5	731.0	735.4	726.6	726.6
45°	695.6	692.6	694.1	694.1	697.0	692.6	695.6	697.0	692.6	691.1	688.2
47.5°	655.7	658.7	655.7	658.7	658.7	661.6	655.7	657.2	658.7	652.7	648.3
50°	615.8	615.8	620.3	618.8	620.3	617.3	617.3	615.8	617.3	614.3	609.9
52.5°	578.9	574.5	581.9	580.4	578.9	577.4	576.0	577.4	574.5	571.5	571.5
55°	533.1	533.1	537.6	539.0	539.0	536.1	533.1	534.6	533.1	531.6	530.2
57.5°	496.2	490.3	493.3	494.7	494.7	490.3	493.3	490.3	490.3	491.8	487.3
60°	448.9	448.9	446.0	450.4	450.4	447.5	447.5	448.9	446.0	444.5	443.0
62.5°	398.7	400.2	404.6	406.1	407.6	404.6	401.7	403.2	403.2	398.7	400.2
65°	355.9	358.9	364.8	363.3	360.3	361.8	358.9	360.3	355.9	357.4	353.0
67.5°	314.6	313.1	314.6	314.6	317.5	316.0	313.1	313.1	311.6	316.0	311.6
70°	270.3	270.3	270.3	270.3	271.7	273.2	270.3	267.3	268.8	265.8	264.3
72.5°	224.5	225.9	224.5	227.4	223.0	225.9	225.9	224.5	223.0	223.0	223.0
75°	181.6	184.6	180.2	181.6	180.2	183.1	181.6	181.6	178.7	177.2	178.7
77.5°	138.8	140.3	137.3	138.8	137.3	138.8	138.8	137.3	137.3	137.3	137.3
80°	98.9	100.4	98.9	97.5	96.0	98.9	96.0	97.5	98.9	97.5	100.4
82.5°	63.5	63.5	62.0	63.5	60.5	60.5	62.0	62.0	60.5	63.5	60.5
85°	31.0	31.0	34.0	31.0	29.5	29.5	29.5	31.0	29.5	32.5	31.0
87.5°	7.4	5.9	7.4	7.4	5.9	5.9	7.4	5.9	7.4	8.9	5.9
90°	17.8	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	18.1	17.8
92.5°	39.0	36.8	36.3	34.1	34.6	33.5	34.6	34.1	36.3	36.8	39.0
95°	81.4	75.3	68.1	63.8	62.1	62.7	62.1	63.8	68.1	75.3	81.4
97.5°	163.2	146.7	125.3	114.3	108.3	105.0	108.3	114.3	125.3	146.7	163.2
100°	325.0	291.8	246.2	222.6	206.6	196.7	206.6	222.6	246.2	291.8	325.0
102.5°	549.6	513.9	463.3	418.8	397.9	383.6	397.9	418.8	463.3	513.9	549.6
105°	727.9	718.8	684.8	650.7	627.1	619.4	627.1	650.7	684.8	718.8	727.9
107.5°	792.5	803.5	802.9	798.0	790.8	778.2	790.8	798.0	802.9	803.5	792.5
110°	782.0	804.6	828.2	838.6	843.6	843.0	843.6	838.6	828.2	804.6	782.0

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	746.6	773.2	808.4	827.7	838.1	841.9	838.1	827.7	808.4	773.2	746.6
115°	703.2	731.5	770.5	795.8	810.1	815.0	810.1	795.8	770.5	731.5	703.2
117.5°	661.7	688.6	728.7	755.7	770.5	774.3	770.5	755.7	728.7	688.6	661.7
120°	624.6	649.6	688.1	713.9	729.8	735.3	729.8	713.9	688.1	649.6	624.6
122.5°	595.8	617.7	651.2	676.5	690.3	694.7	690.3	676.5	651.2	617.7	595.8
125°	569.6	590.2	622.1	643.0	656.7	661.1	656.7	643.0	622.1	590.2	569.6
127.5°	547.4	566.6	594.6	614.4	626.5	629.8	626.5	614.4	594.6	566.6	547.4
130°	524.8	543.0	569.9	588.6	599.6	604.0	599.6	588.6	569.9	543.0	524.8
132.5°	501.4	518.2	544.6	563.3	573.2	577.1	573.2	563.3	544.6	518.2	501.4
135°	478.7	494.1	517.7	535.8	545.7	547.9	545.7	535.8	517.7	494.1	478.7
137.5°	455.6	469.3	491.9	507.8	516.6	519.9	516.6	507.8	491.9	469.3	455.6
140°	435.3	447.4	464.9	479.2	487.5	490.8	487.5	479.2	464.9	447.4	435.3
142.5°	415.8	425.4	441.9	454.5	461.6	461.6	461.6	454.5	441.9	425.4	415.8
145°	399.8	407.8	421.0	430.3	435.8	437.5	435.8	430.3	421.0	407.8	399.8
147.5°	385.8	391.8	403.4	411.1	414.9	416.0	414.9	411.1	403.4	391.8	385.8
150°	373.8	378.7	386.9	393.5	396.8	397.3	396.8	393.5	386.9	378.7	373.8
152.5°	363.5	367.7	373.7	379.2	381.4	381.4	381.4	379.2	373.7	367.7	363.5
155°	353.6	356.7	362.7	366.6	368.8	367.7	368.8	366.6	362.7	356.7	353.6
157.5°	344.3	346.8	351.2	354.5	355.6	355.6	355.6	354.5	351.2	346.8	344.3
160°	335.0	336.9	340.7	343.5	344.0	344.0	344.0	343.5	340.7	336.9	335.0
162.5°	326.2	327.5	331.4	333.0	333.6	333.0	333.6	333.0	331.4	327.5	326.2
165°	317.7	318.8	321.0	323.1	323.1	322.6	323.1	323.1	321.0	318.8	317.7
167.5°	310.0	311.1	312.2	313.3	313.3	312.7	313.3	313.3	312.2	311.1	310.0
170°	302.8	303.4	303.9	305.6	305.0	303.9	305.0	305.6	303.9	303.4	302.8
172.5°	296.5	296.8	297.3	297.9	297.3	296.8	297.3	297.9	297.3	296.8	296.5
175°	291.6	291.8	291.8	292.4	291.8	290.7	291.8	292.4	291.8	291.8	291.6
177.5°	288.0	288.0	288.0	288.0	287.4	286.3	287.4	288.0	288.0	288.0	288.0
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3	1921.3
2.5°	1823.8	1835.7	1831.2	1815.0	1834.2	1834.2	1847.5	1847.5	1863.7	1869.6	1878.5
5°	1720.5	1729.3	1736.7	1729.3	1742.6	1763.3	1775.1	1785.4	1807.6	1816.5	1829.8
7.5°	1609.7	1626.0	1633.3	1633.3	1655.5	1679.1	1702.7	1717.5	1748.5	1760.3	1773.6
10°	1501.9	1521.1	1535.9	1534.4	1571.3	1586.1	1615.6	1649.6	1680.6	1698.3	1717.5
12.5°	1388.2	1398.5	1419.2	1448.7	1457.6	1484.2	1518.1	1561.0	1617.1	1633.3	1661.4
15°	1293.7	1321.7	1338.0	1351.3	1371.9	1397.0	1434.0	1475.3	1531.4	1566.9	1596.4
17.5°	1213.9	1250.8	1261.2	1258.2	1284.8	1323.2	1366.0	1397.0	1447.3	1490.1	1518.1
20°	1148.9	1163.7	1181.4	1188.8	1209.5	1250.8	1292.2	1327.6	1369.0	1403.0	1435.4
22.5°	1084.0	1095.8	1110.6	1123.8	1140.1	1163.7	1203.6	1247.9	1287.8	1320.3	1357.2
25°	1030.8	1038.2	1051.5	1061.8	1079.5	1095.8	1123.8	1172.6	1219.8	1239.0	1271.5
27.5°	979.1	985.0	993.9	1005.7	1014.6	1030.8	1055.9	1095.8	1144.5	1163.7	1208.0
30°	933.3	937.8	946.6	952.5	957.0	976.2	995.4	1026.4	1063.3	1089.9	1122.4
32.5°	890.5	894.9	903.8	905.3	911.2	921.5	939.2	967.3	999.8	1021.9	1050.0
35°	843.3	846.2	855.1	858.0	862.4	871.3	884.6	905.3	934.8	951.1	976.2
37.5°	806.3	804.9	810.8	815.2	821.1	825.5	830.0	850.6	872.8	887.6	906.8
40°	766.5	763.5	765.0	770.9	773.8	779.7	779.7	800.4	815.2	827.0	841.8
42.5°	726.6	725.1	722.2	725.1	728.1	729.5	731.0	745.8	760.6	770.9	787.1
45°	686.7	685.2	682.3	683.8	683.8	686.7	691.1	697.0	707.4	716.2	725.1
47.5°	649.8	646.8	642.4	640.9	643.9	643.9	643.9	649.8	660.1	663.1	671.9
50°	611.4	607.0	601.1	598.1	598.1	596.6	599.6	601.1	609.9	612.9	620.3
52.5°	570.0	567.1	561.2	555.3	556.8	553.8	555.3	556.8	559.7	564.1	568.6
55°	528.7	522.8	518.4	516.9	512.4	512.4	508.0	513.9	512.4	513.9	519.8
57.5°	488.8	482.9	475.5	472.6	468.1	466.7	463.7	462.2	463.7	468.1	472.6
60°	441.6	438.6	434.2	429.7	426.8	422.4	419.4	419.4	417.9	417.9	419.4
62.5°	395.8	394.3	388.4	386.9	384.0	381.0	376.6	373.6	373.6	376.6	378.1
65°	351.5	350.0	345.6	344.1	336.7	333.8	332.3	330.8	327.8	327.8	327.8
67.5°	310.1	305.7	305.7	298.3	292.4	289.5	286.5	285.0	285.0	285.0	286.5
70°	264.3	264.3	259.9	255.5	249.6	251.1	246.6	242.2	242.2	239.2	240.7
72.5°	220.0	218.6	214.1	212.7	208.2	203.8	200.8	203.8	199.4	197.9	199.4
75°	177.2	175.7	172.8	169.8	171.3	166.9	162.4	161.0	161.0	158.0	158.0
77.5°	135.9	138.8	132.9	131.4	128.5	125.5	124.1	122.6	122.6	122.6	125.5
80°	94.5	96.0	96.0	93.0	94.5	90.1	90.1	90.1	85.7	87.1	88.6
82.5°	60.5	60.5	59.1	60.5	59.1	59.1	57.6	57.6	56.1	56.1	57.6
85°	34.0	32.5	31.0	34.0	32.5	32.5	31.0	31.0	31.0	31.0	31.0
87.5°	7.4	8.9	8.9	8.9	8.9	10.3	10.3	10.3	11.8	11.8	11.8
90°	17.6	16.5	17.6	18.1	18.7	18.1	14.8	11.0	8.2	7.4	6.6
92.5°	41.2	47.3	55.5	70.9	84.6	83.5	64.8	44.0	29.1	26.1	23.1
95°	87.4	110.5	144.0	188.5	215.4	190.7	127.0	79.1	53.9	47.3	40.7
97.5°	179.7	235.2	294.6	353.9	351.2	271.5	168.7	102.2	69.8	62.4	55.0
100°	358.3	433.6	501.8	513.3	434.2	299.0	180.3	113.2	84.1	76.4	68.7
102.5°	585.3	635.3	637.5	572.7	436.9	288.5	180.8	123.1	96.7	89.0	81.3
105°	737.0	729.8	667.7	553.4	407.2	274.2	183.6	134.6	108.8	101.1	93.4
107.5°	781.5	727.6	635.3	512.8	379.8	266.5	189.6	146.2	120.9	113.2	105.5
110°	759.5	689.2	590.8	474.8	361.1	264.3	197.3	157.7	133.5	125.6	117.6

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	719.9	643.5	550.1	448.5	349.0	264.9	205.5	168.7	145.6	137.4	129.1
115°	674.9	602.9	518.2	427.6	340.7	267.1	213.8	180.3	156.6	149.2	141.8
117.5°	634.8	567.7	491.9	413.3	336.3	270.4	222.6	190.7	168.7	161.0	153.3
120°	599.6	541.3	473.2	402.3	332.5	273.7	231.4	201.7	180.3	172.6	164.9
122.5°	573.8	519.3	458.3	392.9	330.3	277.5	239.1	212.1	192.4	184.4	176.4
125°	549.0	500.7	444.1	384.2	327.5	281.4	247.3	222.6	202.8	195.1	187.4
127.5°	528.1	482.0	429.8	375.9	325.9	285.2	255.0	232.5	213.2	205.2	197.3
130°	506.7	463.3	416.0	367.7	324.8	289.6	262.1	241.3	222.0	214.3	206.6
132.5°	484.7	445.7	402.8	361.1	324.2	294.0	269.3	249.0	230.8	223.1	215.4
135°	463.3	427.0	390.7	355.0	323.7	297.3	275.3	256.1	238.5	230.8	223.1
137.5°	441.9	412.2	380.9	350.6	323.7	300.6	280.3	262.1	244.6	237.4	230.3
140°	423.2	397.9	371.5	346.8	323.1	302.8	284.1	267.1	250.6	243.4	236.3
142.5°	406.1	385.3	363.8	342.9	323.1	304.5	287.4	270.9	255.0	248.4	241.8
145°	391.8	374.8	356.7	339.6	322.0	305.6	290.2	274.8	259.9	253.9	247.9
147.5°	379.8	366.0	351.2	336.3	320.4	306.1	291.8	278.1	263.8	258.3	252.8
150°	368.8	357.2	345.1	331.9	318.8	305.6	292.9	280.3	267.6	262.6	257.7
152.5°	359.4	350.1	339.1	328.1	316.0	304.5	293.5	282.5	271.5	267.1	262.7
155°	350.6	342.4	333.6	323.1	312.7	303.4	294.0	284.7	275.3	271.2	267.1
157.5°	341.8	334.7	327.0	318.8	309.4	301.2	294.0	286.3	278.1	274.5	270.9
160°	333.0	327.0	321.0	313.8	306.1	299.5	294.0	287.4	280.8	277.8	274.8
162.5°	324.8	319.9	314.9	309.4	303.4	297.9	293.5	288.0	282.5	280.3	278.1
165°	316.6	312.7	308.9	304.5	299.5	295.7	292.4	288.5	283.6	282.0	280.3
167.5°	308.9	306.1	302.8	299.5	296.2	293.5	291.8	288.5	284.7	283.6	282.5
170°	302.3	300.1	298.4	295.7	293.5	291.8	290.7	288.0	285.2	284.4	283.6
172.5°	296.2	294.6	293.5	291.8	290.2	289.6	289.1	287.4	285.8	285.2	284.7
175°	291.3	290.7	290.2	288.5	288.0	287.4	288.0	286.9	285.8	285.5	285.2
177.5°	288.0	287.4	287.4	286.3	285.8	286.3	287.4	286.3	285.8	285.8	285.8
180°	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8	285.8

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1921.3	1921.3	1921.3	1921.3
2.5°	1885.9	1885.9	1908.0	1931.6
5°	1844.5	1854.9	1890.3	1922.8
7.5°	1804.6	1822.4	1866.7	1908.0
10°	1755.9	1779.5	1834.2	1882.9
12.5°	1708.7	1730.8	1794.3	1848.9
15°	1642.2	1670.3	1738.2	1806.1
17.5°	1575.7	1603.8	1686.5	1766.2
20°	1497.5	1534.4	1627.4	1733.8
22.5°	1425.1	1470.9	1574.3	1659.9
25°	1345.4	1416.2	1512.2	1623.0
27.5°	1274.5	1345.4	1442.8	1555.1
30°	1194.7	1267.1	1367.5	1470.9
32.5°	1117.9	1184.4	1281.9	1408.9
35°	1038.2	1101.7	1196.2	1324.7
37.5°	965.8	1027.9	1131.2	1249.4
40°	894.9	959.9	1048.5	1166.7
42.5°	828.5	886.1	965.8	1084.0
45°	767.9	809.3	883.1	993.9
47.5°	704.4	741.4	809.3	920.0
50°	645.4	676.4	735.4	838.8
52.5°	587.8	614.3	669.0	751.7
55°	536.1	561.2	601.1	682.3
57.5°	482.9	502.1	540.5	605.5
60°	431.2	448.9	480.0	533.1
62.5°	379.5	394.3	423.8	466.7
65°	333.8	345.6	367.7	404.6
67.5°	289.5	296.8	314.6	344.1
70°	246.6	252.5	267.3	290.9
72.5°	200.8	206.8	223.0	239.2
75°	162.4	163.9	175.7	189.0
77.5°	127.0	125.5	134.4	144.7
80°	87.1	91.6	98.9	103.4
82.5°	59.1	60.5	63.5	66.5
85°	32.5	34.0	34.0	38.4
87.5°	13.3	14.8	14.8	16.2
90°	5.5	4.4	2.2	0.5
92.5°	18.7	15.9	11.5	8.2
95°	31.9	26.9	21.4	19.2
97.5°	45.1	37.9	31.9	28.6
100°	57.7	48.9	44.0	42.3
102.5°	69.8	61.0	56.1	55.0
105°	81.3	73.1	69.2	67.0
107.5°	93.4	85.7	81.9	80.2
110°	106.1	98.9	95.6	93.4

TEST NUMBER: P1008669

CATALOG NUMBER: S122DIP-B1005D530UB50-4F0-XX-W2A-A4

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	118.2	111.6	107.7	105.5
115°	130.8	124.2	120.9	118.2
117.5°	142.9	136.8	133.5	131.3
120°	153.9	148.9	145.6	143.4
122.5°	165.4	159.9	156.6	155.0
125°	176.4	169.8	166.5	164.9
127.5°	186.9	179.7	175.3	173.1
130°	195.6	188.0	182.5	180.3
132.5°	203.9	195.6	189.6	186.9
135°	210.5	202.2	195.6	193.4
137.5°	217.6	208.8	202.2	199.5
140°	224.2	215.4	208.8	206.6
142.5°	230.3	221.5	215.4	213.8
145°	236.9	228.6	223.1	220.9
147.5°	243.5	235.8	230.3	228.6
150°	249.5	242.4	238.0	236.3
152.5°	255.0	249.0	244.6	244.0
155°	261.0	255.0	251.7	251.2
157.5°	266.0	260.5	257.7	257.2
160°	270.4	266.0	263.8	263.2
162.5°	274.2	270.9	268.7	269.3
165°	277.5	274.2	273.1	273.7
167.5°	280.3	278.1	277.0	277.5
170°	282.5	280.8	280.3	281.4
172.5°	284.1	282.5	283.0	283.6
175°	285.2	284.1	284.7	285.2
177.5°	285.8	284.7	285.2	286.3
180°	285.8	285.8	285.8	285.8

(END OF REPORT)