

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007985

Luminaire Tested: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007985
REPORT IS A COMBINATION OF REPORTS P983773 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7709.0 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007985

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007985

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53			47
1	96	91	86	82	87	83	79	76	69	67	64	56	54	53	45	43	42			36
2	86	78	72	66	79	72	66	61	60	56	52	49	46	43	38	36	34			29
3	79	68	61	54	72	63	56	51	52	47	43	43	39	36	34	31	29			24
4	72	60	52	46	65	55	48	42	46	41	36	38	34	30	30	27	24			20
5	66	53	45	39	60	49	42	36	41	35	31	34	29	26	27	23	21			17
6	60	48	39	33	55	44	37	31	37	31	27	30	26	22	24	21	18			15
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	19	16			13
8	52	39	31	26	47	36	29	24	30	25	21	25	21	17	20	17	14			12
9	48	35	28	23	44	33	26	21	28	22	18	23	19	16	19	15	13			11
10	45	32	25	20	41	30	23	19	26	20	16	21	17	14	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16776	16776	16776
5°	16852	16061	15970
10°	16739	15504	15278
15°	16503	14928	14568
20°	16206	14325	13895
25°	15911	13746	13284
30°	15499	13158	12680
35°	15081	12591	12236
40°	14643	12101	11794
45°	14224	11657	11410
50°	13774	11247	11030
55°	13302	10812	10643
60°	12723	10358	10237
65°	12122	9838	9768
70°	11442	9278	9266
75°	10567	8720	8791
80°	9197	8135	8300
85°	7811	7586	7873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14224 cd/sqm

TEST NUMBER: P1007985

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	100.5	1.3
10°-20°	288.2	3.7
20°-30°	436.6	5.7
30°-40°	531.7	6.9
40°-50°	572.0	7.4
50°-60°	555.5	7.2
60°-70°	485.2	6.3
70°-80°	373.4	4.8
80°-90°	252.3	3.3
90°-100°	213.7	2.8
100°-110°	279.6	3.6
110°-120°	490.5	6.4
120°-130°	721.9	9.4
130°-140°	737.0	9.6
140°-150°	670.2	8.7
150°-160°	536.2	7.0
160°-170°	345.5	4.5
170°-180°	118.9	1.5
0°-30°	825.2	10.7
0°-40°	1356.9	17.6
0°-60°	2484.5	32.2
0°-90°	3595.4	46.6
90°-120°	983.8	12.8
90°-150°	3113.0	40.4
90°-180°	4114.0	53.4
0°-180°	7709.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1060	1060	1060	1060	1060	
5°	1063	1058	1049	1058	1057	101
15°	1014	1017	1017	1031	1029	286
25°	922	932	946	965	969	424
35°	794	820	849	883	894	496
45°	651	693	746	794	810	503
55°	499	554	634	690	710	447
65°	341	416	507	570	590	339
75°	189	275	373	439	459	200
85°	55	150	249	313	335	58
90°	16	115	221	287	307	14
95°	71	113	212	275	292	79
105°	282	354	187	251	272	302
115°	526	558	650	277	229	517
125°	738	750	816	864	880	659
135°	911	925	949	990	1001	704
145°	1055	1054	1070	1085	1088	660
155°	1162	1154	1164	1170	1163	535
165°	1224	1219	1221	1228	1221	346
175°	1252	1246	1248	1254	1245	119
180°	1249	1249	1249	1249	1249	

TEST NUMBER: P1007985

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1059.8	1059.8	1059.8	1059.8	1059.8
2.5°	1067.5	1062.9	1052.2	1059.8	1056.8
5°	1062.9	1058.3	1049.1	1058.3	1056.8
7.5°	1055.2	1052.2	1044.5	1055.2	1053.7
10°	1046.0	1042.9	1038.3	1050.6	1049.1
12.5°	1030.7	1032.2	1029.1	1041.4	1039.9
15°	1013.8	1016.8	1016.8	1030.7	1029.1
17.5°	992.3	998.4	1003.0	1016.8	1016.8
20°	970.8	978.4	984.6	1001.5	1001.5
22.5°	947.7	956.9	966.1	983.0	986.1
25°	921.6	932.4	946.2	964.6	969.2
27.5°	890.9	907.8	923.1	946.2	949.3
30°	860.2	880.1	900.1	924.7	929.3
32.5°	826.4	849.4	874.0	903.2	912.4
35°	794.1	820.2	849.4	883.2	894.0
37.5°	758.8	788.0	824.8	861.7	872.5
40°	723.5	757.3	798.7	838.7	852.5
42.5°	689.7	723.5	772.6	817.2	831.0
45°	651.3	692.7	746.5	794.1	809.5
47.5°	614.4	658.9	720.4	769.5	786.4
50°	576.0	623.6	692.7	745.0	761.9
52.5°	539.1	589.8	663.6	717.3	735.7
55°	499.2	554.5	634.4	689.7	709.6
57.5°	460.8	522.2	602.1	662.0	682.0
60°	419.3	485.4	572.9	631.3	652.8
62.5°	382.5	451.6	539.1	602.1	622.1
65°	341.0	416.3	506.9	569.9	589.8
67.5°	304.1	382.5	474.6	537.6	559.1
70°	264.2	344.1	439.3	505.3	523.8
72.5°	227.3	310.3	407.0	471.6	494.6
75°	188.9	274.9	373.3	439.3	459.3
77.5°	152.1	241.2	341.0	407.0	428.5
80°	115.2	208.9	308.7	373.3	394.8
82.5°	84.5	176.6	278.0	342.5	362.5
85°	55.3	150.5	248.8	313.3	334.8
87.5°	33.8	126.0	224.3	287.2	307.2
90°	16.3	115.2	220.9	286.8	307.0
92.5°	36.4	114.2	210.6	272.3	291.7
95°	71.1	113.4	211.9	274.8	292.3
97.5°	116.6	108.4	212.0	271.5	290.9
100°	170.8	103.8	205.1	269.2	287.9
102.5°	228.9	277.8	196.1	261.4	281.0
105°	282.5	354.2	187.2	251.0	271.5
107.5°	346.7	406.1	178.3	240.5	261.0
110°	406.6	456.4	270.3	229.1	249.6

TEST NUMBER: P1007985

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	464.5	505.3	560.7	220.1	239.7
115°	525.9	558.2	650.0	277.4	229.2
117.5°	577.8	608.1	688.0	604.8	383.3
120°	637.4	657.2	734.9	788.7	683.6
122.5°	688.1	704.0	779.0	825.8	840.6
125°	738.1	749.8	816.1	864.0	880.5
127.5°	785.1	796.2	851.2	898.7	913.4
130°	829.4	842.3	884.5	931.4	942.7
132.5°	874.6	884.8	917.8	961.2	972.6
135°	911.0	925.4	949.0	990.3	1000.7
137.5°	950.8	961.6	978.3	1016.6	1024.7
140°	989.6	995.4	1008.4	1041.0	1045.8
142.5°	1022.2	1027.0	1038.8	1064.4	1067.6
145°	1055.0	1054.1	1069.5	1085.0	1088.2
147.5°	1084.9	1082.2	1097.5	1103.5	1104.5
150°	1113.8	1107.5	1121.9	1127.4	1122.8
152.5°	1138.2	1131.0	1144.5	1150.0	1143.6
155°	1161.7	1153.6	1164.4	1169.8	1162.6
157.5°	1180.7	1173.5	1181.6	1187.9	1180.7
160°	1197.0	1191.5	1197.0	1202.4	1196.1
162.5°	1211.4	1206.0	1210.5	1216.9	1208.7
165°	1224.1	1218.7	1221.4	1227.7	1221.4
167.5°	1234.0	1228.6	1231.3	1237.6	1229.5
170°	1242.2	1236.7	1238.6	1244.9	1236.7
172.5°	1247.6	1242.2	1244.0	1250.3	1242.2
175°	1252.1	1245.8	1247.6	1253.9	1244.9
177.5°	1253.9	1247.6	1248.5	1254.8	1246.7
180°	1249.4	1249.4	1249.4	1249.4	1249.4

(END OF REPORT)