

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007987

Luminaire Tested: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007987
REPORT IS A COMBINATION OF REPORTS P983775 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_4000K
Description: Define 2 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7666.0 lumens
Efficiency: N/A
Efficacy: 85.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007987

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007987

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	96	91	86	82	87	83	79	76	69	67	64	56	54	53	45	43	42
2	86	78	72	66	79	72	66	61	60	56	52	49	46	43	38	36	34
3	79	68	61	54	72	63	56	51	52	47	43	43	39	36	34	31	29
4	72	60	52	46	65	55	48	42	46	41	36	38	34	30	30	27	24
5	66	53	45	39	60	49	42	36	41	35	31	34	29	26	27	23	21
6	60	48	39	33	55	44	37	31	37	31	27	30	26	22	24	21	18
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	22	19	16
8	52	39	31	26	47	36	29	24	30	25	21	25	21	17	20	17	14
9	48	35	28	23	44	33	26	21	28	22	18	23	19	16	19	15	13
10	45	32	25	20	41	30	23	19	26	20	16	21	17	14	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16681	16681	16681
5°	16757	15969	15880
10°	16645	15416	15191
15°	16409	14845	14486
20°	16112	14243	13816
25°	15821	13668	13209
30°	15411	13083	12607
35°	14996	12520	12166
40°	14558	12033	11726
45°	14144	11591	11345
50°	13695	11183	10966
55°	13227	10751	10583
60°	12651	10300	10179
65°	12055	9782	9714
70°	11377	9225	9213
75°	10511	8668	8741
80°	9141	8090	8252
85°	7769	7544	7828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14144 cd/sqm

TEST NUMBER: P1007987

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.9	1.3
10°-20°	286.5	3.7
20°-30°	434.1	5.7
30°-40°	528.7	6.9
40°-50°	568.8	7.4
50°-60°	552.4	7.2
60°-70°	482.4	6.3
70°-80°	371.3	4.8
80°-90°	250.9	3.3
90°-100°	212.6	2.8
100°-110°	278.0	3.6
110°-120°	487.8	6.4
120°-130°	718.0	9.4
130°-140°	733.0	9.6
140°-150°	666.6	8.7
150°-160°	533.3	7.0
160°-170°	343.6	4.5
170°-180°	118.3	1.5
0°-30°	820.6	10.7
0°-40°	1349.2	17.6
0°-60°	2470.4	32.2
0°-90°	3574.9	46.6
90°-120°	978.4	12.8
90°-150°	3095.9	40.4
90°-180°	4091.0	53.4
0°-180°	7666.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1054	1054	1054	1054	1054	
5°	1057	1052	1043	1052	1051	100
15°	1008	1011	1011	1025	1023	284
25°	916	927	941	959	964	421
35°	790	816	845	878	889	494
45°	648	689	742	790	805	500
55°	496	551	631	686	706	444
65°	339	414	504	567	586	337
75°	188	273	371	437	457	199
85°	55	150	247	312	333	58
90°	16	115	220	285	305	14
95°	71	113	211	273	291	79
105°	281	352	186	250	270	301
115°	523	555	646	276	228	514
125°	734	746	812	859	876	655
135°	906	920	944	985	995	700
145°	1049	1048	1064	1079	1082	657
155°	1155	1147	1158	1164	1156	532
165°	1217	1212	1215	1221	1215	344
175°	1245	1239	1241	1247	1238	119
180°	1243	1243	1243	1243	1243	

TEST NUMBER: P1007987

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1053.8	1053.8	1053.8	1053.8	1053.8
2.5°	1061.5	1056.9	1046.2	1053.8	1050.8
5°	1056.9	1052.3	1043.1	1052.3	1050.8
7.5°	1049.2	1046.2	1038.5	1049.2	1047.7
10°	1040.1	1037.0	1032.4	1044.7	1043.1
12.5°	1024.8	1026.3	1023.3	1035.5	1034.0
15°	1008.0	1011.1	1011.1	1024.8	1023.3
17.5°	986.6	992.7	997.3	1011.1	1011.1
20°	965.2	972.9	979.0	995.8	995.8
22.5°	942.3	951.5	960.7	977.5	980.5
25°	916.4	927.1	940.8	959.1	963.7
27.5°	885.8	902.6	917.9	940.8	943.9
30°	855.3	875.1	895.0	919.4	924.0
32.5°	821.7	844.6	869.0	898.0	907.2
35°	789.6	815.6	844.6	878.2	888.9
37.5°	754.5	783.5	820.1	856.8	867.5
40°	719.3	752.9	794.2	833.9	847.6
42.5°	685.7	719.3	768.2	812.5	826.3
45°	647.6	688.8	742.3	789.6	804.9
47.5°	610.9	655.2	716.3	765.2	782.0
50°	572.7	620.1	688.8	740.7	757.5
52.5°	536.1	586.5	659.8	713.2	731.6
55°	496.4	551.3	630.8	685.7	705.6
57.5°	458.2	519.3	598.7	658.3	678.1
60°	416.9	482.6	569.7	627.7	649.1
62.5°	380.3	449.0	536.1	598.7	618.5
65°	339.1	413.9	504.0	566.6	586.5
67.5°	302.4	380.3	471.9	534.5	555.9
70°	262.7	342.1	436.8	502.5	520.8
72.5°	226.0	308.5	404.7	468.9	491.8
75°	187.9	273.4	371.1	436.8	456.7
77.5°	151.2	239.8	339.1	404.7	426.1
80°	114.5	207.7	307.0	371.1	392.5
82.5°	84.0	175.6	276.4	340.6	360.4
85°	55.0	149.7	247.4	311.6	332.9
87.5°	33.6	125.2	223.0	285.6	305.5
90°	16.2	114.7	219.6	285.2	305.3
92.5°	36.2	113.6	209.5	270.8	290.0
95°	70.6	112.8	210.7	273.3	290.7
97.5°	115.9	107.9	210.8	270.1	289.3
100°	169.8	103.2	203.9	267.6	286.2
102.5°	227.7	276.3	195.0	259.9	279.4
105°	280.9	352.2	186.1	249.5	269.9
107.5°	344.8	403.9	177.3	239.1	259.5
110°	404.4	453.9	268.8	227.8	248.2

TEST NUMBER: P1007987

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	462.0	502.5	557.6	218.9	238.4
115°	523.1	555.2	646.4	276.0	228.0
117.5°	574.6	604.8	684.2	601.5	381.2
120°	634.0	653.6	730.9	784.3	679.8
122.5°	684.3	700.2	774.7	821.4	836.0
125°	734.1	745.8	811.7	859.2	875.6
127.5°	780.8	791.8	846.6	893.7	908.4
130°	824.9	837.7	879.7	926.3	937.6
132.5°	869.9	879.9	912.7	956.0	967.3
135°	906.0	920.4	943.8	984.9	995.3
137.5°	945.6	956.4	973.1	1011.0	1019.0
140°	984.2	989.9	1002.9	1035.4	1040.1
142.5°	1016.6	1021.4	1033.1	1058.6	1061.8
145°	1049.3	1048.4	1063.7	1079.2	1082.3
147.5°	1078.9	1076.2	1091.5	1097.5	1098.5
150°	1107.7	1101.4	1115.8	1121.2	1116.7
152.5°	1132.0	1124.8	1138.3	1143.7	1137.4
155°	1155.4	1147.3	1158.1	1163.5	1156.3
157.5°	1174.2	1167.1	1175.1	1181.4	1174.2
160°	1190.4	1185.0	1190.4	1195.8	1189.5
162.5°	1204.8	1199.4	1203.9	1210.2	1202.1
165°	1217.4	1212.0	1214.7	1221.0	1214.7
167.5°	1227.3	1221.9	1224.6	1230.9	1222.8
170°	1235.4	1230.0	1231.8	1238.1	1230.0
172.5°	1240.8	1235.4	1237.2	1243.5	1235.4
175°	1245.3	1239.0	1240.8	1247.1	1238.1
177.5°	1247.1	1240.8	1241.7	1248.0	1239.9
180°	1242.6	1242.6	1242.6	1242.6	1242.6

(END OF REPORT)