

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007993

Luminaire Tested: S122DIP-B1005D925UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007993
REPORT IS A COMBINATION OF REPORTS P983781 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB2750-4F0-XX-W2A-F_5000K
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7432.0 lumens
Efficiency: N/A
Efficacy: 82.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007993

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007993

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	49	49	49	49
2	90	82	76	71	83	76	71	66	65	61	58	55	52	49	46	43	42	42	42	42
3	82	72	65	59	75	67	61	55	57	53	49	49	45	42	40	38	35	35	35	35
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31	31	31	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	27	27	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23	23	23	23
7	59	46	38	33	54	43	36	31	37	32	27	32	28	24	27	24	21	21	21	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	22	25	21	19	19	19	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	19	17	17	17	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	15	15	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1007993

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	1.9
10°-20°	406.8	5.5
20°-30°	597.8	8.0
30°-40°	694.3	9.3
40°-50°	693.4	9.3
50°-60°	604.6	8.1
60°-70°	446.9	6.0
70°-80°	252.9	3.4
80°-90°	68.9	0.9
90°-100°	39.6	0.5
100°-110°	147.7	2.0
110°-120°	391.6	5.3
120°-130°	649.6	8.7
130°-140°	690.0	9.3
140°-150°	641.3	8.6
150°-160°	515.6	6.9
160°-170°	332.2	4.5
170°-180°	114.3	1.5
0°-30°	1149.1	15.5
0°-40°	1843.4	24.8
0°-60°	3141.4	42.3
0°-90°	3910.1	52.6
90°-120°	578.9	7.8
90°-150°	2559.8	34.4
90°-180°	3522.0	47.4
0°-180°	7432.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	1	10	17	22	24	7
95°	56	28	34	38	37	67
105°	264	290	53	63	66	282
115°	500	515	536	134	71	492
125°	707	718	734	741	743	630
135°	874	888	896	905	903	676
145°	1014	1014	1028	1034	1030	634
155°	1117	1109	1120	1125	1118	515
165°	1177	1172	1174	1180	1174	333
175°	1204	1198	1200	1206	1197	115
180°	1201	1201	1201	1201	1201	

TEST NUMBER: P1007993

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	0.9	10.4	17.4	21.7	23.5
92.5°	21.7	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.2	37.4
97.5°	101.7	30.4	44.3	46.9	47.8
100°	153.9	34.8	49.5	56.5	58.2
102.5°	211.2	209.5	51.3	60.8	63.5
105°	264.3	290.3	53.0	62.6	66.1
107.5°	326.0	347.7	54.8	64.3	67.8
110°	385.1	403.3	152.1	65.2	68.7

TEST NUMBER: P1007993

CATALOG NUMBER: S122DIP-B1005D925UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	440.7	456.4	441.6	66.9	69.5
115°	499.8	514.6	536.3	133.9	71.3
117.5°	551.1	568.5	583.3	459.0	231.2
120°	608.5	621.5	637.2	647.6	530.3
122.5°	657.2	671.1	688.5	693.7	694.5
125°	706.7	718.0	734.5	740.6	743.2
127.5°	751.9	764.1	777.1	785.8	786.7
130°	794.5	808.4	818.0	827.5	826.7
132.5°	838.0	849.3	858.8	866.7	865.8
135°	874.5	888.4	896.2	904.9	903.2
137.5°	912.7	923.2	931.9	940.6	937.9
140°	950.1	957.1	966.6	974.5	970.1
142.5°	981.4	987.5	998.8	1005.7	1001.4
145°	1014.4	1013.6	1028.3	1034.4	1030.1
147.5°	1043.1	1040.5	1055.3	1059.6	1056.2
150°	1070.9	1064.9	1078.8	1084.0	1079.6
152.5°	1094.4	1087.5	1100.5	1105.7	1099.6
155°	1117.0	1109.2	1119.6	1124.8	1117.9
157.5°	1135.3	1128.3	1136.1	1142.2	1135.3
160°	1150.9	1145.7	1150.9	1156.1	1150.0
162.5°	1164.8	1159.6	1164.0	1170.0	1162.2
165°	1177.0	1171.8	1174.4	1180.5	1174.4
167.5°	1186.6	1181.3	1183.9	1190.0	1182.2
170°	1194.4	1189.2	1190.9	1197.0	1189.2
172.5°	1199.6	1194.4	1196.1	1202.2	1194.4
175°	1203.9	1197.9	1199.6	1205.7	1197.0
177.5°	1205.7	1199.6	1200.5	1206.5	1198.7
180°	1201.3	1201.3	1201.3	1201.3	1201.3

(END OF REPORT)