

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008719

Luminaire Tested: S122DIP-B1005D725UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008719
REPORT IS A COMBINATION OF REPORTS P983756 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D725UB50-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6342.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008719

CATALOG NUMBER: S122DIP-B1005D725UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008719

CATALOG NUMBER: S122DIP-B1005D725UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	100	96	92	88	94	90	87	83	79	76	74	69	67	65	59	58	56
2	91	84	78	72	85	79	73	69	69	65	61	60	57	54	52	50	48
3	83	74	66	60	78	69	63	57	61	56	52	53	49	46	46	43	41
4	76	65	57	51	71	61	54	49	54	49	44	48	43	39	41	38	35
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24315	24315	24315
5°	24355	23176	23013
10°	24156	22120	21681
15°	23803	21057	20282
20°	23324	19899	18956
25°	22848	18690	17633
30°	22249	17554	16243
35°	21683	16355	14879
40°	20984	15172	13589
45°	20289	13999	12325
50°	19533	12805	11011
55°	18732	11530	9770
60°	17837	10148	8477
65°	16854	8743	7118
70°	15608	7206	5748
75°	13879	5555	4439
80°	11792	3776	2857
85°	8560	1756	1216

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20289 cd/sqm

TEST NUMBER: P1008719

CATALOG NUMBER: S122DIP-B1005D725UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	144.6	2.3
10°-20°	406.8	6.4
20°-30°	597.8	9.4
30°-40°	694.3	10.9
40°-50°	693.4	10.9
50°-60°	604.6	9.5
60°-70°	446.9	7.0
70°-80°	252.9	4.0
80°-90°	69.2	1.1
90°-100°	53.8	0.8
100°-110°	171.0	2.7
110°-120°	292.7	4.6
120°-130°	384.9	6.1
130°-140°	432.0	6.8
140°-150°	423.7	6.7
150°-160°	355.4	5.6
160°-170°	235.7	3.7
170°-180°	82.4	1.3
0°-30°	1149.1	18.1
0°-40°	1843.4	29.1
0°-60°	3141.4	49.5
0°-90°	3910.5	61.7
90°-120°	517.5	8.2
90°-150°	1758.1	27.7
90°-180°	2432.0	38.3
0°-180°	6342.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1536	1536	1536	1536	1536	
5°	1536	1530	1514	1526	1523	146
15°	1462	1453	1434	1440	1433	412
25°	1323	1312	1286	1289	1286	609
35°	1142	1127	1103	1094	1087	713
45°	929	919	896	880	874	717
55°	703	694	676	659	651	629
65°	474	465	450	437	430	469
75°	248	245	238	229	232	265
85°	61	59	58	53	52	67
90°	1	10	26	24	25	6
95°	38	46	47	47	46	43
105°	158	160	162	163	163	167
115°	294	298	296	296	294	290
125°	427	434	432	429	429	382
135°	553	561	562	562	559	427
145°	671	676	680	681	678	419
155°	767	769	771	775	773	353
165°	834	834	834	839	835	235
175°	868	866	865	870	865	82
180°	870	870	870	870	870	

TEST NUMBER: P1008719

CATALOG NUMBER: S122DIP-B1005D725UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1536.1	1536.1	1536.1	1536.1	1536.1
2.5°	1544.9	1537.5	1521.3	1536.1	1533.1
5°	1536.1	1530.2	1513.9	1525.7	1522.8
7.5°	1525.7	1516.9	1500.6	1512.4	1509.5
10°	1509.5	1499.1	1481.4	1493.2	1488.8
12.5°	1487.3	1478.5	1460.7	1468.1	1465.2
15°	1462.2	1453.4	1434.2	1440.1	1432.7
17.5°	1431.2	1422.3	1403.1	1410.5	1403.1
20°	1397.2	1388.4	1367.7	1372.1	1366.2
22.5°	1363.3	1350.0	1330.8	1330.8	1327.8
25°	1323.4	1311.6	1286.5	1289.4	1286.5
27.5°	1279.1	1268.7	1249.5	1245.1	1237.7
30°	1234.8	1222.9	1200.8	1196.4	1190.5
32.5°	1187.5	1178.6	1155.0	1146.1	1140.2
35°	1141.7	1126.9	1103.3	1094.4	1087.1
37.5°	1090.0	1076.7	1053.1	1042.8	1035.4
40°	1036.8	1025.0	1001.4	988.1	982.2
42.5°	985.2	973.3	949.7	934.9	926.1
45°	929.0	918.7	896.5	880.3	874.4
47.5°	874.4	864.0	840.4	824.2	815.3
50°	816.8	809.4	788.7	768.0	760.6
52.5°	760.6	750.3	731.1	714.9	704.5
55°	703.0	694.2	676.5	658.7	651.4
57.5°	645.4	638.1	618.9	601.1	595.2
60°	587.8	581.9	561.3	545.0	540.6
62.5°	531.7	521.4	506.6	491.8	485.9
65°	474.1	465.3	450.5	437.2	429.8
67.5°	415.0	407.6	394.4	384.0	378.1
70°	360.4	354.5	341.2	330.8	324.9
72.5°	304.3	298.4	291.0	280.6	276.2
75°	248.1	245.2	237.8	228.9	231.9
77.5°	197.9	192.0	189.1	184.6	180.2
80°	147.7	146.2	143.3	138.8	135.9
82.5°	100.4	100.4	99.0	93.1	93.1
85°	60.6	59.1	57.6	53.2	51.7
87.5°	26.6	23.6	20.7	16.2	14.8
90°	0.7	9.5	25.7	24.2	25.0
92.5°	16.1	22.0	22.8	23.5	23.5
95°	38.2	45.5	47.0	47.0	45.5
97.5°	63.9	70.5	73.4	73.4	73.4
100°	93.2	99.1	101.3	101.3	100.5
102.5°	124.0	128.4	131.4	132.1	131.4
105°	157.8	160.0	161.5	162.9	162.9
107.5°	191.6	194.5	194.5	195.2	191.6
110°	223.8	228.3	228.3	228.3	226.0

TEST NUMBER: P1008719

CATALOG NUMBER: S122DIP-B1005D725UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	259.1	263.5	262.7	260.5	259.1
115°	293.6	298.0	296.5	295.8	293.6
117.5°	328.1	333.9	330.3	328.1	325.9
120°	362.6	368.4	362.6	362.6	360.4
122.5°	394.1	401.5	397.8	395.6	394.1
125°	427.1	433.8	431.5	429.3	428.6
127.5°	459.4	467.5	464.6	461.6	459.4
130°	489.5	499.1	497.6	496.1	493.2
132.5°	523.3	530.6	531.4	527.7	525.5
135°	552.6	560.7	562.2	561.5	559.3
137.5°	584.9	591.5	593.0	592.3	589.3
140°	613.6	620.2	623.8	623.8	620.9
142.5°	642.9	649.5	651.7	652.5	649.5
145°	670.8	675.9	680.4	681.1	678.1
147.5°	695.8	702.4	705.3	706.8	703.8
150°	721.4	725.9	728.8	731.0	728.8
152.5°	744.2	748.6	752.3	755.2	752.3
155°	767.0	769.2	771.4	775.0	772.8
157.5°	786.8	788.2	789.7	794.8	791.2
160°	804.4	805.9	806.6	811.0	808.1
162.5°	820.5	820.5	821.3	826.4	822.7
165°	834.5	833.7	833.7	838.9	835.2
167.5°	847.0	844.7	844.7	849.9	846.2
170°	856.5	854.3	853.6	858.7	854.3
172.5°	863.1	860.9	860.2	865.3	860.9
175°	868.2	866.0	864.6	869.7	865.3
177.5°	871.2	869.0	867.5	871.9	867.5
180°	869.7	869.7	869.7	869.7	869.7

(END OF REPORT)