

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008728

Luminaire Tested: S122DIP-B1005D925UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008728
REPORT IS A COMBINATION OF REPORTS P983765 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB27-4F0-XX-W2A-F1
Description: Define 2 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7277.0 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008728

CATALOG NUMBER: S122DIP-B1005D925UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1008728

CATALOG NUMBER: S122DIP-B1005D925UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37
4	75	64	56	50	70	60	53	48	52	47	42	45	40	37	38	35	32
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25067	25067	25067
5°	25108	23894	23724
10°	24904	22805	22353
15°	24540	21709	20909
20°	24047	20514	19542
25°	23556	19269	18178
30°	22937	18098	16746
35°	22355	16861	15339
40°	21634	15642	14009
45°	20918	14433	12705
50°	20138	13201	11353
55°	19313	11886	10071
60°	18389	10461	8739
65°	17377	9013	7339
70°	16089	7428	5926
75°	14310	5728	4576
80°	12159	3892	2945
85°	8814	1811	1253

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20918 cd/sqm

TEST NUMBER: P1008728

CATALOG NUMBER: S122DIP-B1005D925UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.0
10°-20°	419.4	5.8
20°-30°	616.3	8.5
30°-40°	715.8	9.8
40°-50°	714.9	9.8
50°-60°	623.3	8.6
60°-70°	460.8	6.3
70°-80°	260.7	3.6
80°-90°	72.1	1.0
90°-100°	71.8	1.0
100°-110°	228.2	3.1
110°-120°	390.5	5.4
120°-130°	513.6	7.1
130°-140°	576.5	7.9
140°-150°	565.4	7.8
150°-160°	474.2	6.5
160°-170°	314.5	4.3
170°-180°	109.9	1.5
0°-30°	1184.7	16.3
0°-40°	1900.5	26.1
0°-60°	3238.7	44.5
0°-90°	4032.3	55.4
90°-120°	690.5	9.5
90°-150°	2346.0	32.2
90°-180°	3245.0	44.6
0°-180°	7277.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1584	1584	1584	1584	1584	
5°	1584	1578	1561	1573	1570	150
15°	1508	1498	1479	1485	1477	425
25°	1364	1352	1326	1329	1326	628
35°	1177	1162	1138	1128	1121	735
45°	958	947	924	908	901	739
55°	725	716	697	679	672	648
65°	489	480	464	451	443	483
75°	256	253	245	236	239	273
85°	62	61	59	55	53	70
90°	1	13	34	32	33	7
95°	51	61	63	63	61	57
105°	211	214	216	217	217	222
115°	392	398	396	395	392	388
125°	570	579	576	573	572	509
135°	738	748	750	749	746	570
145°	895	902	908	909	905	559
155°	1023	1026	1029	1034	1031	471
165°	1114	1113	1113	1119	1114	314
175°	1159	1156	1154	1161	1155	110
180°	1161	1161	1161	1161	1161	

TEST NUMBER: P1008728

CATALOG NUMBER: S122DIP-B1005D925UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1583.6	1583.6	1583.6	1583.6	1583.6
2.5°	1592.8	1585.1	1568.4	1583.6	1580.6
5°	1583.6	1577.5	1560.8	1573.0	1569.9
7.5°	1573.0	1563.8	1547.1	1559.3	1556.2
10°	1556.2	1545.6	1527.3	1539.5	1534.9
12.5°	1533.4	1524.2	1506.0	1513.6	1510.5
15°	1507.5	1498.4	1478.6	1484.7	1477.0
17.5°	1475.5	1466.4	1446.6	1454.2	1446.6
20°	1440.5	1431.4	1410.0	1414.6	1408.5
22.5°	1405.5	1391.8	1372.0	1372.0	1368.9
25°	1364.4	1352.2	1326.3	1329.3	1326.3
27.5°	1318.7	1308.0	1288.2	1283.7	1276.0
30°	1273.0	1260.8	1238.0	1233.4	1227.3
32.5°	1224.3	1215.1	1190.8	1181.6	1175.5
35°	1177.1	1161.8	1137.5	1128.3	1120.7
37.5°	1123.8	1110.1	1085.7	1075.0	1067.4
40°	1068.9	1056.8	1032.4	1018.7	1012.6
42.5°	1015.7	1003.5	979.1	963.9	954.7
45°	957.8	947.1	924.3	907.5	901.4
47.5°	901.4	890.8	866.4	849.7	840.5
50°	842.1	834.4	813.1	791.8	784.2
52.5°	784.2	773.5	753.7	737.0	726.3
55°	724.8	715.7	697.4	679.1	671.5
57.5°	665.4	657.8	638.0	619.7	613.7
60°	606.0	600.0	578.6	561.9	557.3
62.5°	548.2	537.5	522.3	507.1	501.0
65°	488.8	479.7	464.4	450.7	443.1
67.5°	427.9	420.3	406.6	395.9	389.8
70°	371.5	365.5	351.7	341.1	335.0
72.5°	313.7	307.6	300.0	289.3	284.7
75°	255.8	252.8	245.2	236.0	239.1
77.5°	204.0	198.0	194.9	190.3	185.8
80°	152.3	150.7	147.7	143.1	140.1
82.5°	103.5	103.5	102.0	95.9	95.9
85°	62.4	60.9	59.4	54.8	53.3
87.5°	27.4	24.4	21.3	16.7	15.2
90°	1.0	12.7	34.3	32.3	33.3
92.5°	21.5	29.4	30.4	31.3	31.3
95°	50.9	60.7	62.7	62.7	60.7
97.5°	85.2	94.0	97.9	97.9	97.9
100°	124.4	132.2	135.2	135.2	134.2
102.5°	165.5	171.4	175.3	176.3	175.3
105°	210.6	213.5	215.5	217.4	217.4
107.5°	255.6	259.5	259.5	260.5	255.6
110°	298.7	304.6	304.6	304.6	301.6

TEST NUMBER: P1008728

CATALOG NUMBER: S122DIP-B1005D925UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	345.7	351.6	350.6	347.7	345.7
115°	391.7	397.6	395.7	394.7	391.7
117.5°	437.8	445.6	440.7	437.8	434.8
120°	483.8	491.6	483.8	483.8	480.9
122.5°	525.9	535.7	530.8	527.9	525.9
125°	570.0	578.8	575.9	572.9	572.0
127.5°	613.1	623.9	619.9	616.0	613.1
130°	653.2	666.0	664.0	662.1	658.1
132.5°	698.3	708.1	709.1	704.2	701.2
135°	737.5	748.2	750.2	749.2	746.3
137.5°	780.6	789.4	791.3	790.4	786.4
140°	818.8	827.6	832.5	832.5	828.5
142.5°	857.9	866.7	869.7	870.7	866.7
145°	895.1	902.0	907.9	908.9	904.9
147.5°	928.4	937.3	941.2	943.1	939.2
150°	962.7	968.6	972.5	975.5	972.5
152.5°	993.1	999.0	1003.9	1007.8	1003.9
155°	1023.4	1026.4	1029.3	1034.2	1031.3
157.5°	1049.9	1051.8	1053.8	1060.7	1055.8
160°	1073.4	1075.4	1076.3	1082.2	1078.3
162.5°	1094.9	1094.9	1095.9	1102.8	1097.9
165°	1113.5	1112.6	1112.6	1119.4	1114.5
167.5°	1130.2	1127.3	1127.3	1134.1	1129.2
170°	1142.9	1140.0	1139.0	1145.9	1140.0
172.5°	1151.7	1148.8	1147.8	1154.7	1148.8
175°	1158.6	1155.7	1153.7	1160.6	1154.7
177.5°	1162.5	1159.6	1157.6	1163.5	1157.6
180°	1160.6	1160.6	1160.6	1160.6	1160.6

(END OF REPORT)