

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008020

Luminaire Tested: S122DIP-B290D330UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008020
REPORT IS A COMBINATION OF REPORTS P983898 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D330UB2750-4F0-XX-W2A-F_3000K
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2489.0 lumens
Efficiency: N/A
Efficacy: 111.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008020

CATALOG NUMBER: S122DIP-B290D330UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1008020

CATALOG NUMBER: S122DIP-B290D330UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	34	32
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	21	19
8	53	41	34	28	49	38	31	27	33	27	23	27	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	23	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7280	7280	7280
5°	7292	6938	6890
10°	7232	6622	6491
15°	7127	6304	6072
20°	6983	5958	5675
25°	6840	5595	5278
30°	6661	5255	4863
35°	6491	4896	4455
40°	6282	4542	4069
45°	6074	4191	3690
50°	5847	3833	3296
55°	5609	3451	2925
60°	5341	3037	2537
65°	5044	2618	2132
70°	4673	2156	1721
75°	4156	1663	1328
80°	3529	1131	856
85°	2557	524	364

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6074 cd/sqm

TEST NUMBER: P1008020

CATALOG NUMBER: S122DIP-B290D330UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.3	1.7
10°-20°	121.8	4.9
20°-30°	179.0	7.2
30°-40°	207.9	8.4
40°-50°	207.6	8.3
50°-60°	181.0	7.3
60°-70°	133.8	5.4
70°-80°	75.7	3.0
80°-90°	20.8	0.8
90°-100°	14.8	0.6
100°-110°	55.3	2.2
110°-120°	146.6	5.9
120°-130°	243.1	9.8
130°-140°	258.3	10.4
140°-150°	240.0	9.6
150°-160°	193.0	7.8
160°-170°	124.3	5.0
170°-180°	42.8	1.7
0°-30°	344.0	13.8
0°-40°	551.9	22.2
0°-60°	940.5	37.8
0°-90°	1170.8	47.0
90°-120°	216.7	8.7
90°-150°	958.1	38.5
90°-180°	1318.0	53.0
0°-180°	2489.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	460	460	460	460	460	
5°	460	458	453	457	456	44
15°	438	435	429	431	429	123
25°	396	393	385	386	385	182
35°	342	337	330	328	326	213
45°	278	275	268	264	262	215
55°	210	208	202	197	195	188
65°	142	139	135	131	129	140
75°	74	73	71	68	69	79
85°	18	18	17	16	16	20
90°	0	4	6	8	9	2
95°	21	10	13	14	14	25
105°	99	109	20	23	25	106
115°	187	193	201	50	27	184
125°	264	269	275	277	278	236
135°	327	332	335	339	338	253
145°	380	379	385	387	386	237
155°	418	415	419	421	418	193
165°	440	439	440	442	440	124
175°	451	448	449	451	448	43
180°	450	450	450	450	450	

TEST NUMBER: P1008020

CATALOG NUMBER: S122DIP-B290D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	459.9	459.9	459.9	459.9	459.9
2.5°	462.5	460.3	455.5	459.9	459.0
5°	459.9	458.1	453.2	456.8	455.9
7.5°	456.8	454.1	449.3	452.8	451.9
10°	451.9	448.8	443.5	447.1	445.7
12.5°	445.3	442.6	437.3	439.5	438.7
15°	437.8	435.1	429.4	431.1	428.9
17.5°	428.5	425.8	420.1	422.3	420.1
20°	418.3	415.7	409.5	410.8	409.0
22.5°	408.1	404.2	398.4	398.4	397.5
25°	396.2	392.7	385.1	386.0	385.1
27.5°	382.9	379.8	374.1	372.8	370.6
30°	369.7	366.1	359.5	358.2	356.4
32.5°	355.5	352.9	345.8	343.1	341.4
35°	341.8	337.4	330.3	327.7	325.5
37.5°	326.3	322.4	315.3	312.2	310.0
40°	310.4	306.9	299.8	295.8	294.1
42.5°	294.9	291.4	284.3	279.9	277.3
45°	278.1	275.0	268.4	263.5	261.8
47.5°	261.8	258.7	251.6	246.7	244.1
50°	244.5	242.3	236.1	229.9	227.7
52.5°	227.7	224.6	218.9	214.0	210.9
55°	210.5	207.8	202.5	197.2	195.0
57.5°	193.2	191.0	185.3	180.0	178.2
60°	176.0	174.2	168.0	163.2	161.8
62.5°	159.2	156.1	151.7	147.2	145.5
65°	141.9	139.3	134.9	130.9	128.7
67.5°	124.3	122.0	118.1	115.0	113.2
70°	107.9	106.1	102.1	99.1	97.3
72.5°	91.1	89.3	87.1	84.0	82.7
75°	74.3	73.4	71.2	68.5	69.4
77.5°	59.3	57.5	56.6	55.3	53.9
80°	44.2	43.8	42.9	41.6	40.7
82.5°	30.1	30.1	29.6	27.9	27.9
85°	18.1	17.7	17.2	15.9	15.5
87.5°	8.0	7.1	6.2	4.9	4.4
90°	0.3	3.9	6.5	8.1	8.8
92.5°	8.1	6.8	7.8	8.5	8.8
95°	21.1	10.4	12.7	14.3	14.0
97.5°	38.1	11.4	16.6	17.6	17.9
100°	57.6	13.0	18.5	21.1	21.8
102.5°	79.1	78.4	19.2	22.8	23.8
105°	98.9	108.7	19.8	23.4	24.7
107.5°	122.0	130.1	20.5	24.1	25.4
110°	144.1	151.0	56.9	24.4	25.7



TEST NUMBER: P1008020

CATALOG NUMBER: S122DIP-B290D330UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.0	170.8	165.3	25.1	26.0
115°	187.1	192.6	200.7	50.1	26.7
117.5°	206.3	212.8	218.3	171.8	86.5
120°	227.8	232.6	238.5	242.4	198.5
122.5°	246.0	251.2	257.7	259.6	260.0
125°	264.5	268.7	274.9	277.2	278.2
127.5°	281.4	286.0	290.9	294.1	294.5
130°	297.4	302.6	306.2	309.7	309.4
132.5°	313.6	317.9	321.5	324.4	324.1
135°	327.3	332.5	335.4	338.7	338.0
137.5°	341.6	345.5	348.8	352.0	351.1
140°	355.6	358.2	361.8	364.7	363.1
142.5°	367.3	369.6	373.8	376.4	374.8
145°	379.7	379.4	384.9	387.2	385.6
147.5°	390.4	389.5	395.0	396.6	395.3
150°	400.8	398.6	403.8	405.7	404.1
152.5°	409.6	407.0	411.9	413.9	411.6
155°	418.1	415.2	419.1	421.0	418.4
157.5°	424.9	422.3	425.2	427.5	424.9
160°	430.8	428.8	430.8	432.7	430.5
162.5°	436.0	434.0	435.7	437.9	435.0
165°	440.5	438.6	439.6	441.8	439.6
167.5°	444.1	442.2	443.1	445.4	442.5
170°	447.0	445.1	445.7	448.0	445.1
172.5°	449.0	447.0	447.7	450.0	447.0
175°	450.6	448.3	449.0	451.3	448.0
177.5°	451.3	449.0	449.3	451.6	448.7
180°	449.6	449.6	449.6	449.6	449.6

(END OF REPORT)