

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008031

Luminaire Tested: S122DIP-B290D530UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008031
REPORT IS A COMBINATION OF REPORTS P983954 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B290D530UB2750-4F0-XX-W2A-D_3500K
Description: Define 2 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3298.0 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.31 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 28.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008031

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1008031

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39
1	93	88	84	80	83	79	76	73	63	60	58	47	46	44	33	32	31
2	84	76	70	65	75	69	63	59	54	50	47	41	38	36	29	27	25
3	76	67	59	53	68	60	54	49	47	43	39	36	33	30	25	23	21
4	70	59	51	45	62	53	46	41	42	37	33	32	28	25	22	20	18
5	64	52	44	38	57	47	40	35	37	32	28	28	25	22	20	17	16
6	59	46	38	33	52	42	35	30	33	28	24	25	22	19	18	15	14
7	54	42	34	28	48	38	31	26	30	25	21	23	19	17	16	14	12
8	50	38	30	25	45	34	27	23	27	22	19	21	17	15	15	12	11
9	46	34	27	22	42	31	25	20	25	20	17	19	16	13	14	11	9
10	43	31	24	19	39	28	22	18	23	18	15	18	14	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4850	4850	4850
5°	4872	4643	4617
10°	4839	4483	4417
15°	4770	4315	4212
20°	4684	4141	4017
25°	4599	3973	3840
30°	4479	3804	3665
35°	4360	3639	3537
40°	4232	3498	3409
45°	4112	3370	3298
50°	3982	3252	3188
55°	3845	3126	3076
60°	3678	2994	2959
65°	3505	2843	2824
70°	3309	2682	2678
75°	3054	2520	2542
80°	2659	2351	2399
85°	2260	2192	2276

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4112 cd/sqm

TEST NUMBER: P1008031

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.0	0.9
10°-20°	83.3	2.5
20°-30°	126.2	3.8
30°-40°	153.7	4.7
40°-50°	165.4	5.0
50°-60°	160.6	4.9
60°-70°	140.2	4.3
70°-80°	108.0	3.3
80°-90°	73.6	2.2
90°-100°	73.8	2.2
100°-110°	125.6	3.8
110°-120°	260.7	7.9
120°-130°	405.8	12.3
130°-140°	422.5	12.8
140°-150°	388.4	11.8
150°-160°	311.5	9.4
160°-170°	200.7	6.1
170°-180°	69.1	2.1
0°-30°	238.5	7.2
0°-40°	392.2	11.9
0°-60°	718.2	21.8
0°-90°	1040.0	31.5
90°-120°	460.1	14.0
90°-150°	1676.8	50.8
90°-180°	2258.0	68.5
0°-180°	3298.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	306	306	306	306	306	
5°	307	306	303	306	306	29
15°	293	294	294	298	298	83
25°	266	270	274	279	280	123
35°	230	237	246	255	258	143
45°	188	200	216	230	234	145
55°	144	160	183	199	205	129
65°	99	120	146	165	170	98
75°	55	80	108	127	133	58
85°	16	44	72	91	97	17
90°	5	36	69	90	96	5
95°	38	41	72	91	96	43
105°	162	190	70	92	98	173
115°	304	318	351	121	88	299
125°	428	435	459	474	480	382
135°	529	537	546	561	563	409
145°	613	612	621	628	627	383
155°	675	670	676	680	675	311
165°	711	708	710	713	710	201
175°	727	724	725	728	723	69
180°	726	726	726	726	726	

TEST NUMBER: P1008031

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	306.4	306.4	306.4	306.4	306.4
2.5°	308.6	307.3	304.1	306.4	305.5
5°	307.3	305.9	303.3	305.9	305.5
7.5°	305.0	304.1	301.9	305.0	304.6
10°	302.4	301.5	300.2	303.7	303.3
12.5°	297.9	298.4	297.5	301.0	300.6
15°	293.0	293.9	293.9	297.9	297.5
17.5°	286.8	288.6	289.9	293.9	293.9
20°	280.6	282.8	284.6	289.5	289.5
22.5°	274.0	276.6	279.3	284.2	285.1
25°	266.4	269.5	273.5	278.8	280.2
27.5°	257.5	262.4	266.9	273.5	274.4
30°	248.6	254.4	260.2	267.3	268.6
32.5°	238.9	245.5	252.6	261.1	263.7
35°	229.6	237.1	245.5	255.3	258.4
37.5°	219.3	227.8	238.4	249.1	252.2
40°	209.1	218.9	230.9	242.4	246.4
42.5°	199.4	209.1	223.3	236.2	240.2
45°	188.3	200.3	215.8	229.6	234.0
47.5°	177.6	190.5	208.2	222.5	227.3
50°	166.5	180.3	200.3	215.3	220.2
52.5°	155.8	170.5	191.8	207.4	212.7
55°	144.3	160.3	183.4	199.4	205.1
57.5°	133.2	151.0	174.1	191.4	197.1
60°	121.2	140.3	165.6	182.5	188.7
62.5°	110.6	130.5	155.8	174.1	179.8
65°	98.6	120.3	146.5	164.7	170.5
67.5°	87.9	110.6	137.2	155.4	161.6
70°	76.4	99.5	127.0	146.1	151.4
72.5°	65.7	89.7	117.7	136.3	143.0
75°	54.6	79.5	107.9	127.0	132.8
77.5°	44.0	69.7	98.6	117.7	123.9
80°	33.3	60.4	89.2	107.9	114.1
82.5°	24.4	51.1	80.4	99.0	104.8
85°	16.0	43.5	71.9	90.6	96.8
87.5°	9.8	36.4	64.8	83.0	88.8
90°	4.9	36.5	69.1	89.5	95.9
92.5°	17.1	38.5	67.2	85.6	91.5
95°	37.7	41.2	71.6	91.0	95.9
97.5°	64.5	40.6	74.8	92.8	98.6
100°	96.1	40.5	74.3	94.9	100.9
102.5°	130.3	143.9	72.3	94.1	100.5
105°	161.8	190.5	70.2	91.5	98.5
107.5°	199.1	223.0	68.2	89.1	96.1
110°	234.4	254.4	124.3	86.0	93.0

TEST NUMBER: P1008031

CATALOG NUMBER: S122DIP-B290D530UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	268.1	284.6	296.1	83.9	90.4
115°	303.8	317.6	350.6	120.9	87.9
117.5°	334.3	348.4	375.9	314.2	181.0
120°	368.9	378.6	405.8	424.5	358.6
122.5°	398.3	407.2	434.1	449.3	453.8
125°	427.9	434.7	458.9	474.5	480.1
127.5°	455.2	462.0	481.9	498.2	502.8
130°	480.9	488.8	504.0	520.4	523.4
132.5°	507.2	513.5	526.0	540.9	544.0
135°	528.7	537.1	546.3	560.9	563.4
137.5°	551.8	558.1	565.7	579.3	580.9
140°	574.4	578.2	584.9	596.7	596.8
142.5°	593.3	596.6	603.4	612.9	612.5
145°	612.9	612.3	621.3	627.6	627.2
147.5°	630.2	628.6	637.5	640.6	639.9
150°	647.0	643.3	651.7	654.9	652.3
152.5°	661.2	657.0	664.9	668.0	664.3
155°	674.8	670.1	676.4	679.6	675.4
157.5°	685.9	681.7	686.4	690.1	685.9
160°	695.3	692.2	695.3	698.5	694.8
162.5°	703.7	700.6	703.2	706.9	702.1
165°	711.1	707.9	709.5	713.2	709.5
167.5°	716.8	713.7	715.3	718.9	714.2
170°	721.6	718.4	719.5	723.2	718.4
172.5°	724.7	721.6	722.6	726.3	721.6
175°	727.4	723.7	724.7	728.4	723.2
177.5°	728.4	724.7	725.3	728.9	724.2
180°	725.8	725.8	725.8	725.8	725.8

(END OF REPORT)