

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1008738

Luminaire Tested: S122DIP-B1005D925UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1008738
REPORT IS A COMBINATION OF REPORTS P983790 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S122DIP-B1005D925UB30-4F0-XX-W2A-F4
Description: Define 2 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7649.2 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 89.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1008738

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1008738

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	56	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	53	47	51	46	42	44	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	30	27
6	63	51	43	37	58	48	41	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	25	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25286	25286	25286
5°	25327	24101	23931
10°	25120	23004	22546
15°	24753	21896	21092
20°	24255	20693	19713
25°	23759	19436	18336
30°	23137	18254	16892
35°	22549	17008	15473
40°	21822	15778	14131
45°	21100	14558	12816
50°	20312	13317	11451
55°	19481	11990	10160
60°	18550	10553	8816
65°	17526	9093	7403
70°	16232	7493	5978
75°	14433	5777	4615
80°	12263	3926	2971
85°	8899	1826	1265

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 21100 cd/sqm

TEST NUMBER: P1008738

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.3	2.0
10°-20°	423.0	5.5
20°-30°	621.6	8.1
30°-40°	722.0	9.4
40°-50°	721.1	9.4
50°-60°	628.8	8.2
60°-70°	464.8	6.1
70°-80°	263.0	3.4
80°-90°	72.7	1.0
90°-100°	208.3	2.7
100°-110°	704.1	9.2
110°-120°	740.1	9.7
120°-130°	608.6	8.0
130°-140°	489.0	6.4
140°-150°	369.4	4.8
150°-160°	259.7	3.4
160°-170°	152.9	2.0
170°-180°	49.7	0.7
0°-30°	1195.0	15.6
0°-40°	1917.0	25.1
0°-60°	3266.8	42.7
0°-90°	4067.3	53.2
90°-120°	1652.4	21.6
90°-150°	3119.5	40.8
90°-180°	3582.0	46.8
0°-180°	7649.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1597	1597	1597	1597	1597	
5°	1597	1591	1574	1587	1584	152
15°	1521	1511	1491	1498	1490	428
25°	1376	1364	1338	1341	1338	633
35°	1187	1172	1147	1138	1130	741
45°	966	955	932	915	909	746
55°	731	722	704	685	677	654
65°	493	484	468	455	447	487
75°	258	255	247	238	241	275
85°	63	61	60	55	54	70
90°	1	13	34	32	33	6
95°	35	85	387	146	113	36
105°	120	182	732	1309	1113	128
115°	212	268	612	1264	1465	211
125°	296	351	589	1024	1188	263
135°	348	415	582	861	985	269
145°	397	456	579	719	786	249
155°	452	488	562	636	661	208
165°	492	507	538	571	580	139
175°	513	513	518	524	523	49
180°	514	514	514	514	514	

TEST NUMBER: P1008738

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1597.4	1597.4	1597.4	1597.4	1597.4
2.5°	1606.6	1598.9	1582.0	1597.4	1594.3
5°	1597.4	1591.2	1574.3	1586.6	1583.6
7.5°	1586.6	1577.4	1560.5	1572.8	1569.7
10°	1569.7	1559.0	1540.6	1552.8	1548.2
12.5°	1546.7	1537.5	1519.1	1526.7	1523.7
15°	1520.6	1511.4	1491.4	1497.5	1489.9
17.5°	1488.3	1479.1	1459.1	1466.8	1459.1
20°	1453.0	1443.8	1422.3	1426.9	1420.8
22.5°	1417.7	1403.9	1383.9	1383.9	1380.8
25°	1376.2	1363.9	1337.8	1340.9	1337.8
27.5°	1330.1	1319.4	1299.4	1294.8	1287.1
30°	1284.1	1271.8	1248.7	1244.1	1238.0
32.5°	1234.9	1225.7	1201.1	1191.9	1185.8
35°	1187.3	1171.9	1147.4	1138.1	1130.5
37.5°	1133.5	1119.7	1095.1	1084.4	1076.7
40°	1078.2	1065.9	1041.4	1027.5	1021.4
42.5°	1024.5	1012.2	987.6	972.3	963.0
45°	966.1	955.4	932.3	915.4	909.3
47.5°	909.3	898.5	874.0	857.1	847.8
50°	849.4	841.7	820.2	798.7	791.0
52.5°	791.0	780.3	760.3	743.4	732.6
55°	731.1	721.9	703.5	685.0	677.4
57.5°	671.2	663.5	643.6	625.1	619.0
60°	611.3	605.2	583.7	566.8	562.2
62.5°	552.9	542.2	526.8	511.5	505.3
65°	493.0	483.8	468.5	454.6	447.0
67.5°	431.6	423.9	410.1	399.3	393.2
70°	374.8	368.6	354.8	344.1	337.9
72.5°	316.4	310.3	302.6	291.8	287.2
75°	258.0	255.0	247.3	238.1	241.1
77.5°	205.8	199.7	196.6	192.0	187.4
80°	153.6	152.1	149.0	144.4	141.3
82.5°	104.4	104.4	102.9	96.8	96.8
85°	63.0	61.4	59.9	55.3	53.8
87.5°	27.6	24.6	21.5	16.9	15.4
90°	1.0	13.4	33.6	32.1	32.6
92.5°	14.8	47.0	152.1	70.2	60.3
95°	34.6	84.9	387.3	146.2	112.6
97.5°	51.4	112.2	631.3	293.5	188.7
100°	76.1	137.4	780.5	584.4	353.7
102.5°	98.8	160.0	785.4	988.0	689.6
105°	120.5	181.8	732.1	1308.6	1113.4
107.5°	144.2	203.6	682.7	1424.6	1399.0
110°	168.0	225.8	649.1	1405.9	1515.5

TEST NUMBER: P1008738

CATALOG NUMBER: S122DIP-B1005D925UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	189.7	247.0	627.4	1342.2	1513.6
115°	212.4	268.2	612.5	1264.1	1465.1
117.5°	236.1	289.5	604.6	1189.5	1392.0
120°	257.9	310.2	597.7	1122.8	1321.9
122.5°	278.6	331.5	593.8	1071.0	1248.8
125°	296.4	350.8	588.8	1024.0	1188.5
127.5°	311.2	369.0	585.9	984.0	1132.2
130°	324.1	385.3	583.9	943.5	1085.8
132.5°	335.9	401.1	582.9	901.5	1037.4
135°	347.8	415.0	581.9	860.6	985.0
137.5°	358.6	426.8	581.9	819.0	934.6
140°	371.5	437.6	580.9	782.4	882.2
142.5°	384.3	446.6	580.9	747.4	829.9
145°	397.2	456.4	578.9	718.8	786.4
147.5°	411.0	464.4	576.0	693.6	747.9
150°	424.8	472.2	573.0	671.8	714.3
152.5°	438.7	480.2	568.1	653.5	685.6
155°	451.5	487.6	562.2	635.8	660.9
157.5°	462.4	493.5	556.2	619.0	639.2
160°	473.2	499.4	550.3	602.2	618.5
162.5°	484.1	503.8	545.4	586.3	598.7
165°	492.0	506.8	538.4	571.0	579.9
167.5°	498.9	509.8	532.5	557.2	562.2
170°	505.8	511.3	527.6	544.4	546.3
172.5°	509.8	512.8	521.6	533.0	533.5
175°	512.8	513.2	517.7	524.1	522.6
177.5°	514.7	513.7	513.7	517.7	514.7
180°	513.7	513.7	513.7	513.7	513.7

(END OF REPORT)